






# Contemporary and configurable

## Magneos Mini, a compact, contemporary accent lighting

Magneos Mini is the new family of projectors represents an outstanding lighting tool for shops, packing advanced Philips technology into a compact, contemporary design.



Measurements in mm

### Products benefits

- The Magneos projector family offers a choice of lamps, optics, accessories and colour finishes, enabling retailers to configure their own accent lighting solution
- All HID versions include Philips' PrimaVision gear to optimize lamp life and lower energy consumption

### Applications

- Accent lighting for retail and museums

### Product specifications




Type	Lamp	Gear	Optic	Colour	Materials	Accessories
MRS502 Mini (3C)	MASTERColour CDM-Tm Mini 20W and 35W, MASTERColour CDM-TC lamps	PrimaVision Mini electronic gear	Narrow beam (12°) Medium beam (24°) Wide beam (36°)	White RAL 9010 (WH) Grey (GR) or RAL colours on request	Aluminium housing	Filters and barndoors
MCS502 Mini (Baseplate)	MASTERColour CDM-Tm Mini 20W and 35W, MASTERColour CDM-TC lamps	PrimaVision Mini electronic gear	Narrow beam (12°) Medium beam (24°) Wide beam (36°)	White RAL 9010 (WH) Grey (GR) or RAL colours on request	Aluminium housing	Filters and barndoors

# PHILIPS

sense and simplicity

# Small lights, big ambience

## Fugato Micro, compact and appealing downlight



Measurements in mm

The Fugato downlight range including the Fugato Micro consists of fixed, adjustable and cardanic luminaires. The innovative features of this range create appealing effects and ambiances in retail spaces.



### Product benefits

- Ultra compact downlight designed around Philips' new MASTERColour CDM-Tm Mini lamp
- Low glare levels ensure visual comfort for both retail staff and shoppers
- Wide choice of optics offers optimum accent lighting
- The compact dimension and reduced heat emission allows the luminaire to be mounted close to the merchandise
- Low power consumption offers retailers the prospect of reduced operating costs

### Applications

- Accent lighting for retail and museums

### Product specifications

Type	Lamp	Gear	Optic	Colour	Materials
MBS244	1 x MASTERColour CDM-Tm Mini 20W or 35W	PrimaVision electronic gear	Narrow beam (12°) Medium beam (24°) Wide beam (36°)	White RAL 9010 (WH) Grey (GR) or RAL colours on request	Die-cast aluminium housing



© 2007 Koninklijke Philips Electronics N.V.  
All rights reserved.

Data subject to change  
3222 635 96691  
04/07

For more information please visit:

[www.philips.com/fugato](http://www.philips.com/fugato)

[www.philips.com/magneos](http://www.philips.com/magneos)