




Add sparkle to your shop

Fiorenza Micro, ultra compact design

The Fiorenza Projector range is designed to create a more dynamic in-store ambience by casting the products on display in the most attractive light imaginable. The latest addition is the Fiorenza Micro, an ultra-compact spotlight designed around our new MASTERColour CDM-Tm Mini.



Measurements in mm

Products benefits

- Fiorenza Micro offers a choice of beam angles, product colours and mounting versions
- Improved temperature comfort for both shoppers and staff
- The dedicated electronic gear improves product performance in terms of efficiency and heat management

Applications



- Accent lighting for retail and museums

Product specifications

Type	Lamp	Gear	Optic	Colour	Materials	Accessories
MRS705 (3-circuit track version)	MASTERColour CDM-Tm Mini 20W	PrimaVision Mini electronic gear	Narrow beam (12°) Medium beam (24°) Wide beam (36°)	White RAL 9010 (WH) Grey (GR) or RAL on request	Aluminium housing	Filters upon request
MCS705 (Base plate version)	MASTERColour CDM-Tm Mini 20W	PrimaVision Mini electronic gear	Narrow beam (12°) Medium beam (24°) Wide beam (36°)	White RAL 9010 (WH) Grey (GR) or RAL on request	Aluminium housing	Filters upon request

Balancing lighting and design

UnicOne, small but powerful accent lighting



Adjustment: Horizontal: 360°, Vertical: 77°

With the new UnicOne collection you can truly blend your luminaires into your interior architecture. Projectors, pendants and uplights all share the same simple, geometrical design, with refined facets and details, ensuring maximum visual harmony. Play with the different versions and sizes to create your very own design for general, accent and effect lighting.



Product benefits

- Powerful lighting accents in a small, appealing package
- The projector, pendant and uplight all feature the typical design characteristics of UnicOne
- The projector adds a sophisticated adjustment rod and hinge

Applications

- Accent and decorative lighting in retail, museums and hospitality environment

Product specifications

Type	Lamp	Gear	Optic	Colour	Materials	Accessories
MRS541 (3C)	MASTERCLOUR CDM-Tm Mini 20W and 35W	PrimaVision Mini electronic gear	Narrow beam (12°) Medium beam (24°) Wide beam (36°)	White RAL 9010 (WH) Grey (GR) or RAL on request	Aluminium housing	Filters
MCSS541 (BA)	MASTERCLOUR CDM-Tm Mini 20W and 35W	PrimaVision Mini electronic gear	Narrow beam (12°) Medium beam (24°) Wide beam (36°)	White RAL 9010 (WH) Grey (GR) or RAL on request	Aluminium housing	Filters
MPK541	Pendant	PrimaVision Mini electronic gear	Narrow beam (12°) Medium beam (24°) Wide beam (36°)	White RAL 9010 (WH) Grey (GR) or RAL on request	Aluminium housing	Filters
MWG541	Uplight	PrimaVision Mini electronic gear	Narrow beam (12°) Medium beam (24°) Wide beam (36°)	White RAL 9010 (WH) Grey (GR) or RAL on request	Aluminium housing	Filters



© 2007 Koninklijke Philips Electronics N.V.
All rights reserved.

Data subject to change
3222 635 9683 I
04/07

For more information please visit:

www.philips.com/unicone
www.philips.com/fiorenza