

## Recommended Dimmer List

| NO | Brand        | Man./Country | ID           | Type | Load     |
|----|--------------|--------------|--------------|------|----------|
| 1  | Bticino      | Italy        | ART5364      | R    | 60W-500W |
| 2  | Eljo         | Sweden       | SD300        | R    | 60W-300W |
| 3  | Relco        | Sweden       | RT65R0A      | R    | 60W-500W |
| 4  | Everflourish | Sweden       | EF0700DA     | R    | 50W-300W |
| 5  | Everflourish |              | EMD200       | R    | 40W-300W |
| 6  | Bush Jaeger  | Germany      | 2247U        | RL   | 20W-500W |
| 7  | Bush Jaeger  | Germany      | 2250U        | R    | 60W-600W |
| 8  | Bush Jaeger  | Germany      | 2200         | R    | 60W-400W |
| 9  | Jung         | Germany      | 266GDE       | R    | 60W-600W |
| 10 | Gira / Insta | Germany      | 030200 100   | R    | 60W-600W |
| 11 | Viko         | Bulgaria/H   | Viko         | RL   | 600W     |
| 12 | METESAN      | Bulgaria/H   | Merlin Gerin | R    | 600W     |
| 13 | Conrad       | Germany      | 614545       | R    | 300W     |
| 14 | Jung         | Insta        | 225 NV DE    | RL   | 20W-500W |
| 15 | N&L          |              | 433/4        | R    | 60W-400W |
| 16 | N&L          |              | 435 HAN      | RL   | 60W-600W |
| 17 | BERKER       | Insta        | 283010       | R    | 60W-400W |
| 18 | BERKER       | Insta        | 286610       | RL   | 20W-500W |
| 19 | Opus         |              | 852.39       | R    | 60W-400W |
| 20 | Opus         |              | 852.392      | RL   | 20W-500W |
| 21 | Drespa       |              |              | R    | 60W-400W |
| 22 | NIKO         |              | 09-013       | R    | 35W-320W |
| 23 | aa           | Albany       | ASA500       | R    | ~500W    |
| 24 | CLIPSAL      | Australia    | E32V500      | R    | ~500W    |
| 25 | PEHA         | Germany      | 463          | R    | 30W-315W |
| 26 | PEHA         | Germany      | 435HAN       | RL   | 60W-600W |
| 27 | Panasonic    | China        | WMS549       | R    | ~400W    |
| 28 | ELECTREX     | New Zealand  | DM500        | R    | ~500W    |
| 29 | SK           | Korea        | SKD-500      | R    | ~500W    |
| 30 | AHAM         | Korea        | ASW3502      | R    | ~500W    |
| 31 | HPM          | Australia    | Cat400L      | RL   | 10W~400W |
| 32 | TCL          | China        | LM2          | R    | ~630W    |
| 33 | Relco        | Italy        | RTM34SMA     | RLC  | 40W~500W |