





Installation instructions

Instructions de montage
Montageanleitung
Montage instructie
Istruzioni di montaggio

Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet
Montaj yönergeleri
Οδηγίες συναρμολόγησης
Instrukcja montażu

Szerelési utasítások
Návod k montáži
ИНСТРУКЦИЯ ПО МОНТАЖУ
Návod k montáži



		Pmax. (W)	Length(M)	
BCC200 LED-LP/RD		8.6	1.52	0.79
BCC200 LED-LP/GN		5.1	0.91	0.48
BCC200 LED-LP/BL		5.1	0.91	0.48
BCC200 LED-LP/AM		8.6	1.52	0.79
BCC200 LED-LP/CW		5.1	0.91	0.48
BCC200 LED-LP/RD		17	3.04	1.58
BCC200 LED-LP/GN		10	1.82	0.95
BCC200 LED-LP/BL		10	1.82	0.95
BCC200 LED-LP/AM		17	3.04	1.58
BCC200 LED-LP/CW		10	1.82	0.95
BCC200 LED-LP/RD		61	10.64	5.53
BCC200 LED-LP/GN		57	10.01	5.23
BCC200 LED-LP/BL		57	10.01	5.23
BCC200 LED-LP/AM		61	10.64	5.53
BCC200 LED-LP/CW		57	10.01	5.23
BCC200 LED-LP/RD		113	19.76	10.28
BCC200 LED-LP/GN		113	20.02	10.46
BCC200 LED-LP/BL		113	20.02	10.46
BCC200 LED-LP/AM		113	19.76	10.28
BCC200 LED-LP/CW		113	20.02	10.46
BCC200 LED-LP/RD		282	50.16	26.10
BCC200 LED-LP/GN		282	50.05	26.05
BCC200 LED-LP/BL		282	50.05	26.05
BCC200 LED-LP/AM		282	50.16	26.10
BCC200 LED-LP/CW		282	50.05	26.05
ECC200 PSU 220-240V 4A			1.5	
ECC200 PSU 220-240V 1.6A			1.5	
ZCC200 CMC L50 ALU				
ZCC200 CMC L1000 ALU				
ZCC200 CMC L2000 ALU				
ZCC200 CI000-M-F			1-0	

79x
LPLED's/mtr.

