

KEY	
	Dimmable, with lamps on one dimmer up to a max of 10% of the max dimmer load (8 max tested)
	Lamps are dimmable for up to x number of lamps only
	Lamps are dimmable across full dimming range, but exhibit flickering at a single distinct position in the range (usually 80% light level point)
	The majority of configurations show undesirable dimming behavior
	Configuration not tested
	Lamp is not designed for use with this dimmer type
	Name New added since previous version

Brand	Type #	Type	Load	Bulbs				Novature		230V Reflector				MR16	
				A55 6W	Glow Designer	806lm		Candle	Lustre	GU10 PF	GU10 7W & DimTone	PAR20	PAR30S	PAR38	MR16 7W
Schneider	ALT400901	RL	600VA												
Schneider	MTN572599	RL	20-500W						2-21						
Schneider	MTN572299	R	60-600W												
Schneider	STD400RC/RL	RLC	40-400W												
Schneider	CCTDD200001	RLC	40-400W												
Schneider	CCTDD200002	RLC	40-400W												
Schneider	MTN577099	R.L.C	25-420W												
Schneider	MTN577199	R.C	20-315W												
Schneider	E3030HD		40W-600W												
Schneider	SBD-SPL	RL	100W												
Schneider System M	MTN5140-0000	RL	100W												
Schneider Odace	S-5x0518	RL	100W												
Schneider Exxact	1900910(SE)	RL	100W												
Schneider Exxact	2622161(FI)	RL	100W												
Schneider Exxact	1470207(NO)	RL	100W												
Schneider	SND2200523	RL	500W	2-7 pcs	2-7 pcs				2-12 pcs						
Schneider	CCT011263	RL	315W												
Schneider Trend	ATTD1000RL	RL	315W												
Schneider Trend	1370814	RL	315W												
Schneider Artic	3512423	RL	315W												
Schneider Artic	1471021	RL	315W												
Schneider Exxact	1900913(SE)	RL	315W												
Schneider Exxact	2622008(FI)	RL	315W												
Schneider Exxact	1470216(NO)	RL	315W												
Schneider Unica	MGU3.512.xx	RL	315W												
Schneider Unica	MGU5.512.xx	RL	315W												
Schneider	MTN5135-0000	RL	315W												
Schneider	CCT011723	RLC	600W												
Schneider	LTD600RCL	RLC	600W												
Schneider Trend	1370833	RLC	600W												
Schneider Artic	3512448	RLC	600W												
Schneider Artic	1471011	RLC	600W												
Schneider	CCT011533	RC	315W												
Schneider	MGU3.515.18	RLC	350W												
Schneider	CCT0115C3	RC	1000W												
Scholki/NOVUM	ETD U1	RLC	35-500W												
Siemens	5TC8284	RC	20-600W												
VADSBO	LD 220	RLC	1-200W												
Varilight	IOI401M	?	?												
Varilight	IQT401M	RC	400W												
Varilight	J401	?	400/250W												
Varilight	V-Pro Z1J400M	RC	400W	1-11	6-10				1-16		1-11				
VEILENDING	MDC-10-MH		10-420W												
VIKO	KARRE	RL	600W												
VIKO	CARMEN BEYAZ	RL	600W	4 max	4 max						4 max				
Vimar	EIKON 20160	RL	500W/300VA	2 max	2 max						2 max				

(1) This dimmer has complex installation but works well under certain configurations