



## ArcTone – choose your own style

ArcTone is a range of projectors that create powerful lighting accents – ideal for retail applications such as fashion stores. They have a refined, compact form with curved edges. The combination of black and white or grey makes the fixture look even smaller and offers maximum variety in fixture appearance.

Thanks to ArcTone's 'mix & match' feature (you can combine the various options in finishing, colours, lamp types, optics and accessories), the projectors can be customized to the specific application.

With its choice of powerful LED sources and CDM lamps and gear, ArcTone enables you to create amazing light effects, while its compact, duo-colour form ensures a perfect match with a host of interior styles.

ArcTone projectors come in three sizes.



### ArcTone Projector Micro

Main light sources LED: 3 x LUXEON® K2 / 10, 25°  
 HID: 1 X MASTERCoulour CDM-Tm Mini / PGJ5/ 20,35W  
 Halogen: 1 X MASTERCapsule / GY6.35 / 45 W

Optic LED: Narrow (10°) or medium beam (25°)  
 HID/Halogen: Narrow (12°) or medium beam (24°, 36°)

Lamp included Yes :  
 LED: Warm white (3150 K) or Cool white (6000K)  
 HID: lamp color 830 or 930

Ballast Electronic , 220 - 240 V / 50 - 60 Hz


Installation On 3-circuit track (3C)  
 Direct on ceiling: baseplate with connection point (BA)

Material Aluminium

Colour White-Black, Grey-Black, Black.

Glossy white-black, Glossy black-black, Brushed aluminium-black, Chrome-black, RAL colours available on request

Accessories Protection glass, sculptural lens, dichroic color filters, glare control glass, honey comb and barndoors



Product shown: MRS/LRS/BRS531  
 All dimensions in mm



### ArcTone Projector Mini

HID: 1 X MASTERCoulour CDM-TC / G8.5 / 35, 70 W

Narrow (12°) or medium beam (24°, 36°)

Yes (lamp color 830, Elite 930 or 942)

Electronic , 220 - 240 V / 50 - 60 Hz


Installation On 3-circuit track (3C)  
 Direct on ceiling: baseplate with connection point (BA)

Aluminium

White-Black, Grey-Black, Black.

Glossy white-black, Glossy black-black, Brushed aluminium-black, Chrome-black, RAL colours available on request

Accessories Protection glass, sculptural lens, dichroic color filters, glare control glass, honey comb and barndoors



Product shown: MRS532  
 All dimensions in mm



### ArcTone Projector Mini - R111

HID: 1 X MASTERCoulour CDM-R111/ GX8.5 / 20, 35, 70W  
 Halogen: 1 X MASTERLine 111 / G53 / 45, 60 W

HID: MASTERCoulour 10°, 24°, 40°  
 Halogen: MASTERLine 24°, 45°

Yes (K or lamp color 830 or 942)

Electronic , 220 - 240 V / 50 - 60 Hz


Installation On 3-circuit track (3C)  
 Direct on ceiling: baseplate with connection point (BA)

Aluminium

White-Black, Grey-Black, Black.

Glossy white-black, Glossy black-black, Brushed aluminium-black, Chrome-black, RAL colours available on request

Accessories Protection glass, sculptural lens, dichroic color filters, glare control glass, honey comb and barndoors



Product shown: MCS/LCS533  
 All dimensions in mm