



Philips Energy Advantage
T8 25W Extra Long
Life Lamps featuring
ALTO II™ Technology

*Ideal for applications
where energy savings and
longer relamp cycles would
be beneficial*

Energy Advantage



**ALTO II™ means 50%
less mercury than the
original ALTO T8 lamps†**

† Original 2', 3' and 4' T8 lamps featuring ALTO® Lamp Technology had 3.5mg of mercury. New 2', 3' and 4' T8 lamps featuring ALTO II™ Technology have 1.7mg of mercury.

* Fluorescent lamps that are TCLP compliant reduce the amount of pollutants released into the environment.

Energy savings, extra long life, extra low mercury

Philips Energy Advantage T8 25W Extra Long Life lamps are an industry first. These lamps offer high energy savings, are environmentally responsible and have extra long life.

Outstanding energy savings

- Save 7 watts per lamp instantly when compared to a 32W T8 lamp
- Save \$28 in energy costs over the rated average life of the lamp**
- Operates on any Instant Start and Programmed Start Ballast‡

Extra long life

- Significantly reduce maintenance and recycling costs by extending the relamping cycle
- Up to 67% longer life than an industry standard T8 lamp^o
- Warranty period: 48 months

Better for the environment

- Only 1.7mg of mercury with ALTO II™ Technology
- Reduced impact on the environment without sacrificing performance

(**, ‡, ^o See back of page for footnotes)

PHILIPS
sense and simplicity

Philips Energy Advantage T8 25W Extra Long Life Lamps featuring ALTO II™ Technology


Ordering, Electrical and Technical Data (Subject to change without notice)

Product Number	Ordering Code	Watts	Pack. Qty.	Color Temp. (Kelvin)	Nom. Length (In.)	Rated Average Life (Hrs) ¹		Approx. Initial Lumens ²	Design Lumens ³	CRI	Lumen Maint.
						12-hr on Ins. Start	12-hr on Prog. Start				
15206-6	F32T8/ADV830/XLL/ALTO	25	25	3000	48	40,000	46,000	2400	2330	85	97%
15207-4	F32T8/ADV835/XLL/ALTO	25	25	3500	48	40,000	46,000	2400	2330	85	97%
15208-2	F32T8/ADV841/XLL/ALTO	25	25	4100	48	40,000	46,000	2400	2330	85	97%
15209-0	F32T8/ADV850/XLL/ALTO	25	25	5000	48	40,000	46,000	2350	2280	85	97%

- 1) Average life under engineering data with lamps turned off and restarted once every 12 operating hours.
 - 2) Approximate initial lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life, when the output is measured during operation on a reference ballast under standard laboratory conditions. For expected lamp lumen output, commercial ballast manufacturers can advise the appropriate ballast factor for each of their ballasts when they are informed of the designated lamp. The ballast factor is a multiplier applied to the designated lamp lumen output.
 - 3) Design lumens are the approximate lamp lumen output at 40% of the lamp's rated average life. This output is based upon measurements obtained during lamp operation on a reference ballast under standard laboratory conditions.
- Ⓢ Lamp meets US Federal Minimum Efficiency Standards.
 - This lamp is better for the environment because of its reduced mercury content. All Philips ALTO II™ lamps give you end-of-life options which can simplify and reduce your lamp disposal costs depending on your state and local regulations.


97% Lumen Maintenance

Philips Energy Advantage T8 25W XLL Lamps



Rated Average Life

Philips Energy Advantage T8 25W XLL Lamps



- 4) Average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Lamp life is appreciably longer if lamps are started less frequently.

Footnotes from front page:

- ** Based on wattage savings (7W) × rated average life (40,000 hours) × kWh rate (\$.10).
- ‡ Starting voltage should be equal to or greater than 550V. These lamps are not recommended for use where the temperature in fixture is below 70°F. Striations may occur where air movement is present in fixture. For best operation, use ballast with anti-striation circuitry.
- ◊ When compared to an industry standard 4' T8 32W lamp with 24,000 hours rated average life (12 hours per start on an instant start ballast), with 2800 lumens and 75 CRI.



© 2009 Philips Lighting Company. All rights reserved.
 Printed in USA 8/09
 P-5793-C
www.philips.com

Philips Lighting Company
 200 Franklin Square Drive
 Somerset, NJ 08873
 1-800-555-0050
 A Division of Philips Electronics North America Corporation

Philips Lighting
 281 Hillmount Road
 Markham, Ontario
 Canada L6C 2S3
 1-800-555-0050
 A Division of Philips Electronics Ltd.