



10-15% more efficient!

MASTER PL-C 2 Pin

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Benefits

- Optimal light performance for short or long operation per switch-on
- Multiple light color choice
- Good color rendering (CRI >80)

Features

- 2-pin base with a housing incorporating the special instant starter
- Fluorescent tri-phosphor technology
- Low light depreciation over lamp life

Application

- Designed for general or supplementary lighting in professional or home environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-C 2 Pin

Versions



10W, G24d-1, 2P



13W, G24d-1, 2P




18 W G24d-2



26W, G24d-3, 2P

MASTER PL-C 2 Pin

Dimensional drawing



| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|---|---------|----------|----------|----------|----------|
| MASTER PL-C 10W/827/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 75.5 mm | 95.0 mm | 117.4 mm |
| MASTER PL-C 26W/865/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |
| MASTER PL-C 10W/827/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 75.5 mm | 95.0 mm | 117.4 mm |
| MASTER PL-C 10W/830/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 75.5 mm | 95.0 mm | 117.4 mm |
| MASTER PL-C 10W/840/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 75.5 mm | 95.0 mm | 117.4 mm |
| MASTER PL-C 10W/840/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 75.5 mm | 95.0 mm | 117.4 mm |
| MASTER PL-C 10W/865/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 75.5 mm | 95.0 mm | 117.4 mm |
| MASTER PL-C 13W/827/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 139.4 mm |
| MASTER PL-C 13W/827/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 139.4 mm |
| MASTER PL-C 13W/830/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 139.4 mm |
| MASTER PL-C 13W/830/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 139.4 mm |
| MASTER PL-C 13W/840/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 139.4 mm |
| MASTER PL-C 13W/840/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 139.4 mm |
| MASTER PL-C 13W/865/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 139.4 mm |
| MASTER PL-C 13W/865/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 97.5 mm | 117.0 mm | 139.4 mm |
| MASTER PL-C 13W/827 GX23-2/2P 1CT/5X10CC | 27.1 mm | 27.1 mm | 80.7 mm | 99.0 mm | 121.6 mm |
| MASTER PL-C 18W/827/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 150.4 mm |
| MASTER PL-C 18W/827/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 150.4 mm |
| MASTER PL-C 18W/830/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 150.4 mm |
| MASTER PL-C 18W/ 830 /2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 150.4 mm |
| MASTER PL-C 18W/840/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 150.4 mm |
| MASTER PL-C 18W/840/2P 1CT/5X10CC | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 150.4 mm |
| MASTER PL-C 18W/840/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 150.4 mm |
| MASTER PL-C 18W/865/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 150.4 mm |
| MASTER PL-C 18W/865/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 109.5 mm | 128.0 mm | 150.4 mm |

MASTER PL-C 2 Pin

Dimensional drawing

| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|--|---------|----------|----------|----------|----------|
| MASTER PL-C 26W/827/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |
| MASTER PL-C 26W/827/2P 1CT/5X10CC | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |
| MASTER PL-C 26W/827/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |
| MASTER PL-C 26W/ 830/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |
| MASTER PL-C 26W/ 830/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |
| MASTER PL-C 26W/ 840/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |
| PL-C 26W/840/2P 1CT/ 5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |
| MASTER PL-C 26W/ 840/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |
| MASTER PL-C 26W/865/2P 1CT/5X10BOX | 27.1 mm | 27.1 mm | 130.5 mm | 149.0 mm | 171.4 mm |

| Approval and application | |
|----------------------------|---------|
| Mercury (Hg) Content (Nom) | 1.4 mg |
| Controls and dimming | |
| Dimmable | No |
| General information | |
| Life To 10% Failures (Nom) | 6500 h |
| Life To 50% Failures (Nom) | 10000 h |
| LSF 2000 h Rated | 99 % |
| LSF 4000 h Rated | 98 % |
| LSF 6000 h Rated | 92 % |
| LSF 8000 h Rated | 78 % |
| Temperature | |
| Design Temperature (Nom) | 28 °C |

Approval and application

| Order Code | Full Product Name | Energy Consumption kWh/ 1000 h | Mercury (Hg) Content (Max) |
|--------------|-------------------------------------|-----------------------------------|-------------------------------|
| 927903882701 | MASTER PL-C 10W/827/2P 1CT/5X10BOX | 13 kWh | - |
| 927903882740 | MASTER PL-C 10W/827/2P 1CT/5X10BOX | 11 kWh | 1.4 mg |
| 927903883040 | MASTER PL-C 10W/830/2P 1CT/5X10BOX | 11 kWh | 1.4 mg |
| 927903884002 | MASTER PL-C 10W/840/2P 1CT/5X10BOX | 13 kWh | - |
| 927903884040 | MASTER PL-C 10W/840/2P 1CT/5X10BOX | 11 kWh | 1.4 mg |
| 927903886502 | MASTER PL-C 10W/865/2P 1CT/5X10BOX | 13 kWh | - |
| 927904882701 | MASTER PL-C 13W/827/2P 1CT/5X10BOX | 17 kWh | - |
| 927904882740 | MASTER PL-C 13W/827/2P 1CT/5X10BOX | 14 kWh | 1.4 mg |
| 927904883001 | MASTER PL-C 13W/830/2P 1CT/5X10BOX | 17 kWh | - |
| 927904883040 | MASTER PL-C 13W/830/2P 1CT/5X10BOX | 14 kWh | 1.4 mg |
| 927904884002 | MASTER PL-C 13W/840/2P 1CT/5X10BOX | 17 kWh | - |
| 927904884040 | MASTER PL-C 13W/840/2P 1CT/5X10BOX | 14 kWh | 1.4 mg |
| 927904886502 | MASTER PL-C 13W/865/2P 1CT/5X10BOX | 17 kWh | - |
| 927904886540 | MASTER PL-C 13W/865/2P 1CT/5X10BOX | 14 kWh | 1.4 mg |
| 927904982762 | PL-C 13W/827/2P 1CT/5X10BOX | - | - |
| 927905782701 | MASTER PL-C 18W/827/2P 1CT/5X10BOX | 22 kWh | - |
| 927905782740 | MASTER PL-C 18W/827/2P 1CT/5X10BOX | 19 kWh | 1.4 mg |
| 927905783001 | MASTER PL-C 18W/830/2P 1CT/5X10BOX | 22 kWh | - |
| 927905783040 | MASTER PL-C 18W/830 /2P 1CT/5X10BOX | 19 kWh | 1.4 mg |
| 927905784001 | MASTER PL-C 18W/840/2P 1CT/5X10BOX | 22 kWh | - |
| 927905784003 | PL-C 18W/840/2P 1CT/5X10BOX | 22 kWh | - |
| 927905784040 | MASTER PL-C 18W/840/2P 1CT/5X10BOX | 19 kWh | 1.4 mg |
| 927905786502 | MASTER PL-C 18W/865/2P 1CT/5X10BOX | 22 kWh | - |
| 927905786540 | MASTER PL-C 18W/865/2P 1CT/5X10BOX | 19 kWh | 1.4 mg |
| 927906182701 | MASTER PL-C 26W/827/2P 1CT/5X10BOX | 32 kWh | - |
| 927906182703 | PL-C 26W/827/2P 1CT/5X10BOX | 32 kWh | - |

MASTER PL-C 2 Pin

| Order Code | Full Product Name | Energy Consumption kWh/ | Mercury (Hg) |
|--------------|------------------------------------|-------------------------|---------------|
| | | 1000 h | Content (Max) |
| 927906182740 | MASTER PL-C 26W/827/2P 1CT/5X10BOX | 27 kWh | 1.4 mg |
| 927906183001 | MASTER PL-C 26W/830/2P 1CT/5X10BOX | 32 kWh | - |
| 927906183040 | MASTER PL-C 26W/830/2P 1CT/5X10BOX | 27 kWh | 1.4 mg |
| 927906184001 | MASTER PL-C 26W/840/2P 1CT/5X10BOX | 32 kWh | - |
| 927906184003 | PL-C 26W/840/2P 1CT/5X10BOX | 32 kWh | - |
| 927906184040 | MASTER PL-C 26W/840/2P 1CT/5X10BOX | 27 kWh | 1.4 mg |
| 927906186540 | MASTER PL-C 26W/865/2P 1CT/5X10BOX | 27 kWh | 1.4 mg |
| 927906186565 | MASTER PL-C 26W/865/2P 1CT/5X10BOX | 32 kWh | - |

Operating and electrical

| Order Code | Full Product Name | Lamp Current | | Order Code | Full Product Name | Lamp Current | |
|--------------|--|--------------|-------------|--------------|---|--------------|-------------|
| | | (Nom) | Power (Nom) | | | (Nom) | Power (Nom) |
| 927903882701 | MASTER PL-C 10W/827/2P 1CT/ 5X10BOX | 0.190 A | 10.0 W | 927905783001 | MASTER PL-C 18W/830/2P 1CT/ 5X10BOX | 0.230 A | 17.9 W |
| 927903882740 | MASTER PL-C 10W/827/2P 1CT/ 5X10BOX | 0.190 A | 10.4 W | 927905783040 | MASTER PL-C 18W/830 /2P 1CT/ 5X10BOX | 0.230 A | 18.3 W |
| 927903883040 | MASTER PL-C 10W/830/2P 1CT/ 5X10BOX | 0.190 A | 10.4 W | 927905784001 | MASTER PL-C 18W/840/2P 1CT/ 5X10BOX | 0.230 A | 17.9 W |
| 927903884002 | MASTER PL-C 10W/840/2P 1CT/ 5X10BOX | 0.190 A | 10.0 W | 927905784003 | PL-C 18W/840/2P 1CT/5X10BOX | 0.230 A | 17.9 W |
| 927903884040 | MASTER PL-C 10W/840/2P 1CT/ 5X10BOX | 0.190 A | 10.4 W | 927905784040 | MASTER PL-C 18W/840/2P 1CT/ 5X10BOX | 0.230 A | 18.3 W |
| 927903886502 | MASTER PL-C 10W/865/2P 1CT/ 5X10BOX | 0.190 A | 10.0 W | 927905786502 | MASTER PL-C 18W/865/2P 1CT/ 5X10BOX | 0.230 A | 17.9 W |
| 927904882701 | MASTER PL-C 13W/827/2P 1CT/ 5X10BOX | 0.170 A | 13.4 W | 927905786540 | MASTER PL-C 18W/865/2P 1CT/ 5X10BOX | 0.230 A | 18.3 W |
| 927904882740 | MASTER PL-C 13W/827/2P 1CT/ 5X10BOX | 0.170 A | 13.8 W | 927906182701 | MASTER PL-C 26W/827/2P 1CT/ 5X10BOX | 0.335 A | 26.5 W |
| 927904883001 | MASTER PL-C 13W/830/2P 1CT/ 5X10BOX | 0.170 A | 13.4 W | 927906182703 | PL-C 26W/827/2P 1CT/5X10BOX | 0.335 A | 26.5 W |
| 927904883040 | MASTER PL-C 13W/830/2P 1CT/ 5X10BOX | 0.170 A | 13.8 W | 927906182740 | MASTER PL-C 26W/827/2P 1CT/ 5X10BOX | 0.335 A | 26.5 W |
| 927904884002 | MASTER PL-C 13W/840/2P 1CT/ 5X10BOX | 0.170 A | 13.4 W | 927906183001 | MASTER PL-C 26W/830/2P 1CT/ 5X10BOX | 0.335 A | 26.5 W |
| 927904884040 | MASTER PL-C 13W/840/2P 1CT/ 5X10BOX | 0.170 A | 13.8 W | 927906183040 | MASTER PL-C 26W/830/2P 1CT/ 5X10BOX | 0.335 A | 26.5 W |
| 927904886502 | MASTER PL-C 13W/865/2P 1CT/ 5X10BOX | 0.170 A | 13.4 W | 927906184001 | MASTER PL-C 26W/840/2P 1CT/ 5X10BOX | 0.335 A | 26.5 W |
| 927904886540 | MASTER PL-C 13W/865/2P 1CT/ 5X10BOX | 0.170 A | 13.8 W | 927906184003 | PL-C 26W/840/2P 1CT/5X10BOX | 0.335 A | 26.5 W |
| 927904982762 | PL-C 13W/827/2P 1CT/5X10BOX | 0.285 A | 12.7 W | 927906184040 | MASTER PL-C 26W/840/2P 1CT/ 5X10BOX | 0.335 A | 26.5 W |
| 927905782701 | MASTER PL-C 18W/827/2P 1CT/ 5X10BOX | 0.230 A | 17.9 W | 927906186540 | MASTER PL-C 26W/865/2P 1CT/ 5X10BOX | 0.335 A | 26.5 W |
| 927905782740 | MASTER PL-C 18W/827/2P 1CT/ 5X10BOX | 0.230 A | 18.3 W | 927906186565 | MASTER PL-C 26W/865/2P 1CT/ 5X10BOX | 0.335 A | 26.5 W |

General information

MASTER PL-C 2 Pin

| Order Code | Full Product Name | Cap-Base |
|--------------|------------------------------------|----------|
| 927903882701 | MASTER PL-C 10W/827/2P 1CT/5X10BOX | G24D-1 |
| 927903882740 | MASTER PL-C 10W/827/2P 1CT/5X10BOX | G24D-1 |
| 927903883040 | MASTER PL-C 10W/830/2P 1CT/5X10BOX | G24D-1 |
| 927903884002 | MASTER PL-C 10W/840/2P 1CT/5X10BOX | G24D-1 |
| 927903884040 | MASTER PL-C 10W/840/2P 1CT/5X10BOX | G24D-1 |
| 927903886502 | MASTER PL-C 10W/865/2P 1CT/5X10BOX | G24D-1 |
| 927904882701 | MASTER PL-C 13W/827/2P 1CT/5X10BOX | G24D-1 |
| 927904882740 | MASTER PL-C 13W/827/2P 1CT/5X10BOX | G24D-1 |
| 927904883001 | MASTER PL-C 13W/830/2P 1CT/5X10BOX | G24D-1 |
| 927904883040 | MASTER PL-C 13W/830/2P 1CT/5X10BOX | G24D-1 |
| 927904884002 | MASTER PL-C 13W/840/2P 1CT/5X10BOX | G24D-1 |
| 927904884040 | MASTER PL-C 13W/840/2P 1CT/5X10BOX | G24D-1 |
| 927904886502 | MASTER PL-C 13W/865/2P 1CT/5X10BOX | G24D-1 |
| 927904886540 | MASTER PL-C 13W/865/2P 1CT/5X10BOX | G24D-1 |
| 927904982762 | PL-C 13W/827/2P 1CT/5X10BOX | GX23-2 |
| 927905782701 | MASTER PL-C 18W/827/2P 1CT/5X10BOX | G24D-2 |
| 927905782740 | MASTER PL-C 18W/827/2P 1CT/5X10BOX | G24D-2 |

| Order Code | Full Product Name | Cap-Base |
|--------------|-------------------------------------|----------|
| 927905783001 | MASTER PL-C 18W/830/2P 1CT/5X10BOX | G24D-2 |
| 927905783040 | MASTER PL-C 18W/830 /2P 1CT/5X10BOX | G24D-2 |
| 927905784001 | MASTER PL-C 18W/840/2P 1CT/5X10BOX | G24D-2 |
| 927905784003 | PL-C 18W/840/2P 1CT/5X10BOX | G24D-2 |
| 927905784040 | MASTER PL-C 18W/840/2P 1CT/5X10BOX | G24D-2 |
| 927905786502 | MASTER PL-C 18W/865/2P 1CT/5X10BOX | G24D-2 |
| 927905786540 | MASTER PL-C 18W/865/2P 1CT/5X10BOX | G24D-2 |
| 927906182701 | MASTER PL-C 26W/827/2P 1CT/5X10BOX | G24D-3 |
| 927906182703 | PL-C 26W/827/2P 1CT/5X10BOX | G24D-3 |
| 927906182740 | MASTER PL-C 26W/827/2P 1CT/5X10BOX | G24D-3 |
| 927906183001 | MASTER PL-C 26W/830/2P 1CT/5X10BOX | G24D-3 |
| 927906183040 | MASTER PL-C 26W/830/2P 1CT/5X10BOX | G24D-3 |
| 927906184001 | MASTER PL-C 26W/840/2P 1CT/5X10BOX | G24D-3 |
| 927906184003 | PL-C 26W/840/2P 1CT/5X10BOX | G24D-3 |
| 927906184040 | MASTER PL-C 26W/840/2P 1CT/5X10BOX | G24D-3 |
| 927906186540 | MASTER PL-C 26W/865/2P 1CT/5X10BOX | G24D-3 |
| 927906186565 | MASTER PL-C 26W/865/2P 1CT/5X10BOX | G24D-3 |

Light technical (1/2)

| Order Code | Full Product Name | Chromaticity | | Color | |
|--------------|------------------------------------|--------------------|--------------------|-------|--------------------|
| | | Coordinate X (Nom) | Coordinate Y (Nom) | Code | Designation |
| 927903882701 | MASTER PL-C 10W/827/2P 1CT/5X10BOX | - | - | 827 | Incandescent White |
| 927903882740 | MASTER PL-C 10W/827/2P 1CT/5X10BOX | 0.463 | 0.42 | 827 | Incandescent White |
| 927903883040 | MASTER PL-C 10W/830/2P 1CT/5X10BOX | 0.44 | 0.403 | 830 | Warm White (WW) |
| 927903884002 | MASTER PL-C 10W/840/2P 1CT/5X10BOX | - | - | 840 | Cool White (CW) |
| 927903884040 | MASTER PL-C 10W/840/2P 1CT/5X10BOX | 0.38 | 0.38 | 840 | Cool White (CW) |
| 927903886502 | MASTER PL-C 10W/865/2P 1CT/5X10BOX | - | - | 865 | Cool Daylight |
| 927904882701 | MASTER PL-C 13W/827/2P 1CT/5X10BOX | - | - | 827 | Incandescent White |
| 927904882740 | MASTER PL-C 13W/827/2P 1CT/5X10BOX | 0.463 | 0.42 | 827 | Incandescent White |
| 927904883001 | MASTER PL-C 13W/830/2P 1CT/5X10BOX | - | - | 830 | Warm White (WW) |

| Order Code | Full Product Name | Chromaticity | | Color | |
|--------------|------------------------------------|--------------------|--------------------|-------|--------------------|
| | | Coordinate X (Nom) | Coordinate Y (Nom) | Code | Designation |
| 927904883040 | MASTER PL-C 13W/830/2P 1CT/5X10BOX | 0.44 | 0.403 | 830 | Warm White (WW) |
| 927904884002 | MASTER PL-C 13W/840/2P 1CT/5X10BOX | - | - | 840 | Cool White (CW) |
| 927904884040 | MASTER PL-C 13W/840/2P 1CT/5X10BOX | 0.38 | 0.38 | 840 | Cool White (CW) |
| 927904886502 | MASTER PL-C 13W/865/2P 1CT/5X10BOX | - | - | 865 | Cool Daylight |
| 927904886540 | MASTER PL-C 13W/865/2P 1CT/5X10BOX | 0.313 | 0.337 | 865 | Cool Daylight |
| 927904982762 | PL-C 13W/827/2P 1CT/5X10BOX | - | - | 827 | Incandescent White |
| 927905782701 | MASTER PL-C 18W/827/2P 1CT/5X10BOX | - | - | 827 | Incandescent White |
| 927905782740 | MASTER PL-C 18W/827/2P 1CT/5X10BOX | 0.463 | 0.42 | 827 | Incandescent White |
| 927905783001 | MASTER PL-C 18W/830/2P 1CT/5X10BOX | - | - | 830 | Warm White (WW) |

MASTER PL-C 2 Pin

| Order Code | Full Product Name | Chromaticity | | Color Code | Color Designation | Order Code | Full Product Name | Chromaticity | | Color Code | Color Designation |
|--------------|-------------------------------------|--------------------|--------------------|------------|--------------------|--------------|------------------------------------|--------------------|--------------------|------------|--------------------|
| | | Coordinate X (Nom) | Coordinate Y (Nom) | | | | | Coordinate X (Nom) | Coordinate Y (Nom) | | |
| 927905783040 | MASTER PL-C 18W/830 /2P 1CT/5X10BOX | 0.44 | 0.403 | 830 | Warm White (WW) | 927906182740 | MASTER PL-C 26W/827/2P 1CT/5X10BOX | 0.463 | 0.42 | 827 | Incandescent White |
| 927905784001 | MASTER PL-C 18W/840/2P 1CT/5X10BOX | - | - | 840 | Cool White (CW) | 927906183001 | MASTER PL-C 26W/830/2P 1CT/5X10BOX | - | - | 830 | Warm White (WW) |
| 927905784003 | PL-C 18W/840/2P 1CT/5X10BOX | - | - | 840 | Cool White (CW) | 927906183040 | MASTER PL-C 26W/830/2P 1CT/5X10BOX | 0.44 | 0.403 | 830 | Warm White (WW) |
| 927905784040 | MASTER PL-C 18W/840/2P 1CT/5X10BOX | 0.38 | 0.38 | 840 | Cool White (CW) | 927906184001 | MASTER PL-C 26W/840/2P 1CT/5X10BOX | - | - | 840 | Cool White (CW) |
| 927905786502 | MASTER PL-C 18W/865/2P 1CT/5X10BOX | - | - | 865 | Cool Daylight | 927906184003 | PL-C 26W/840/2P 1CT/5X10BOX | - | - | 840 | Cool White (CW) |
| 927905786540 | MASTER PL-C 18W/865/2P 1CT/5X10BOX | 0.313 | 0.337 | 865 | Cool Daylight | 927906184040 | MASTER PL-C 26W/840/2P 1CT/5X10BOX | 0.38 | 0.38 | 840 | Cool White (CW) |
| 927906182701 | MASTER PL-C 26W/827/2P 1CT/5X10BOX | - | - | 827 | Incandescent White | 927906186540 | MASTER PL-C 26W/865/2P 1CT/5X10BOX | 0.313 | 0.337 | 865 | Cool Daylight |
| 927906182703 | PL-C 26W/827/2P 1CT/5X10BOX | - | - | 827 | Incandescent White | 927906186565 | MASTER PL-C 26W/865/2P 1CT/5X10BOX | - | - | 865 | Cool Daylight |

Light technical (2/2)

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color Rendering Index (Nom) | LLMF 2000 h Rated | LLMF 4000 h Rated | LLMF 6000 h Rated | LLMF 8000 h Rated | Luminous | | |
|--------------|------------------------------------|------------------------------------|-----------------------------|-------------------|-------------------|-------------------|-------------------|------------------------|---------------------|-----------------------------|
| | | | | | | | | Efficacy (rated) (Nom) | Luminous Flux (Nom) | Luminous Flux (Rated) (Nom) |
| 927903882701 | MASTER PL-C 10W/827/2P 1CT/5X10BOX | 2700 K | >80 | 92 % | 87 % | 83 % | 81 % | 60 lm/W | 600 lm | 600 lm |
| 927903882740 | MASTER PL-C 10W/827/2P 1CT/5X10BOX | 2700 K | 82 | 92 % | 87 % | 83 % | 81 % | 60 lm/W | 600 lm | 600 lm |
| 927903883040 | MASTER PL-C 10W/830/2P 1CT/5X10BOX | 3000 K | 82 | 92 % | 87 % | 83 % | 81 % | 60 lm/W | 600 lm | 600 lm |
| 927903884002 | MASTER PL-C 10W/840/2P 1CT/5X10BOX | 4000 K | 82 | 92 % | 87 % | 83 % | 81 % | 60 lm/W | 600 lm | 600 lm |
| 927903884040 | MASTER PL-C 10W/840/2P 1CT/5X10BOX | 4000 K | 80 | 92 % | 87 % | 83 % | 81 % | 60 lm/W | 600 lm | 600 lm |
| 927903886502 | MASTER PL-C 10W/865/2P 1CT/5X10BOX | 6500 K | 82 | 90 % | 85 % | 81 % | 77 % | 56 lm/W | 600 lm | 600 lm |
| 927904882701 | MASTER PL-C 13W/827/2P 1CT/5X10BOX | 2700 K | 83 | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |
| 927904882740 | MASTER PL-C 13W/827/2P 1CT/5X10BOX | 2700 K | 82 | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |
| 927904883001 | MASTER PL-C 13W/830/2P 1CT/5X10BOX | 3000 K | 82 | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |
| 927904883040 | MASTER PL-C 13W/830/2P 1CT/5X10BOX | 3000 K | 82 | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |

MASTER PL-C 2 Pin

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color Rendering Index (Nom) | LLMF 2000 h Rated | LLMF 4000 h Rated | LLMF 6000 h Rated | LLMF 8000 h Rated | Luminous Efficacy (rated) (Nom) | Luminous Flux (Nom) | Luminous Flux (Rated) (Nom) |
|--------------|---|------------------------------------|-----------------------------|-------------------|-------------------|-------------------|-------------------|---------------------------------|---------------------|-----------------------------|
| 927904884002 | MASTER PL-C 13W/ 840/2P 1CT/5X10BOX | 4000 K | 82 | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |
| 927904884040 | MASTER PL-C 13W/ 840/2P 1CT/5X10BOX | 4000 K | 80 | 92 % | 87 % | 83 % | 81 % | 69 lm/W | 925 lm | 925 lm |
| 927904886502 | MASTER PL-C 13W/ 865/2P 1CT/5X10BOX | 6500 K | 80 | 90 % | 85 % | 81 % | 77 % | 63 lm/W | 845 lm | 845 lm |
| 927904886540 | MASTER PL-C 13W/ 865/2P 1CT/5X10BOX | 6500 K | 80 | 90 % | 85 % | 81 % | 77 % | 63 lm/W | 860 lm | 845 lm |
| 927904982762 | PL-C 13W/827/2P 1CT/ 5X10BOX | 2700 K | 82 | 92 % | 87 % | 84 % | 81 % | 62 lm/W | 800 lm | 800 lm |
| 927905782701 | MASTER PL-C 18W/ 827/2P 1CT/5X10BOX | 2700 K | 82 | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927905782740 | MASTER PL-C 18W/ 827/2P 1CT/5X10BOX | 2700 K | 82 | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927905783001 | MASTER PL-C 18W/ 830/2P 1CT/5X10BOX | 3000 K | 82 | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927905783040 | MASTER PL-C 18W/ 830 /2P 1CT/5X10BOX | 3000 K | 82 | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927905784001 | MASTER PL-C 18W/ 840/2P 1CT/5X10BOX | 4000 K | 82 | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927905784003 | PL-C 18W/840/2P 1CT/ 5X10BOX | 4000 K | 82 | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927905784040 | MASTER PL-C 18W/ 840/2P 1CT/5X10BOX | 4000 K | 80 | 92 % | 87 % | 83 % | 81 % | 67 lm/W | 1200 lm | 1200 lm |
| 927905786502 | MASTER PL-C 18W/ 865/2P 1CT/5X10BOX | 6500 K | 82 | 90 % | 85 % | 81 % | 77 % | 67 lm/W | 1200 lm | 1120 lm |
| 927905786540 | MASTER PL-C 18W/ 865/2P 1CT/5X10BOX | 6500 K | 80 | 90 % | 85 % | 81 % | 77 % | 67 lm/W | 1150 lm | 1120 lm |
| 927906182701 | MASTER PL-C 26W/ 827/2P 1CT/5X10BOX | 2700 K | 82 | 92 % | 87 % | 83 % | 81 % | 68 lm/W | 1800 lm | 1800 lm |
| 927906182703 | PL-C 26W/827/2P 1CT/ 5X10BOX | 2700 K | 82 | 92 % | 87 % | 83 % | 81 % | 68 lm/W | 1800 lm | 1800 lm |
| 927906182740 | MASTER PL-C 26W/ 827/2P 1CT/5X10BOX | 2700 K | 81 | 92 % | 87 % | 83 % | 81 % | 68 lm/W | 1800 lm | 1800 lm |
| 927906183001 | MASTER PL-C 26W/ 830/2P 1CT/5X10BOX | 3000 K | 82 | 92 % | 87 % | 83 % | 81 % | 68 lm/W | 1800 lm | 1800 lm |
| 927906183040 | MASTER PL-C 26W/ 830/2P 1CT/5X10BOX | 3000 K | 81 | 92 % | 87 % | 83 % | 81 % | 68 lm/W | 1800 lm | 1800 lm |
| 927906184001 | MASTER PL-C 26W/ 840/2P 1CT/5X10BOX | 4000 K | 82 | 92 % | 87 % | 83 % | 81 % | 68 lm/W | 1800 lm | 1800 lm |
| 927906184003 | PL-C 26W/840/2P 1CT/ 5X10BOX | 4100 K | 82 | 92 % | 87 % | 83 % | 81 % | 68 lm/W | 1800 lm | 1800 lm |
| 927906184040 | MASTER PL-C 26W/ 840/2P 1CT/5X10BOX | 4000 K | 80 | 92 % | 87 % | 83 % | 81 % | 68 lm/W | 1800 lm | 1800 lm |
| 927906186540 | MASTER PL-C 26W/ 865/2P 1CT/5X10BOX | 6500 K | 80 | 90 % | 85 % | 81 % | 77 % | 66 lm/W | 1740 lm | 1740 lm |
| 927906186565 | MASTER PL-C 26W/ 865/2P 1CT/5X10BOX | 6500 K | 80 | 90 % | 85 % | 81 % | 77 % | 66 lm/W | 1740 lm | 1740 lm |

MASTER PL-C 2 Pin

