



PrimaVision Twin (35W & 70W) for CDM - The cost-effective solution

PrimaVision Twin for CDM

Dual CDM lamp operation, single HID electronic gear – improves cost effectiveness and increases luminaire design flexibility

Benefits

- Cost-effective, plus design flexibility
- Optimal lamp performance thanks to minimal lamp power tolerance
- Lamp life increased by up to 30% for CDM lamps

Features

- Single gear for two lamps
- Loop Through feature (in independent version)
- Minimal lamp power spread
- Low gear energy losses
- Lamp end-of-life detection
- High Tambient and Tcase temperatures
- Long lifetime of 40,000 hours

Application

- 35 and 70 W: accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only


PrimaVision Twin for CDM

Versions



HID-PV C 2x35 /S CDM 220-240V 50/60Hz

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 | B2 |
|------------------|--------|------|-------|-------|------|------|
| HID-PV C 2x35 /S | 4.5 mm | 32.0 | 135.0 | 123.5 | 75.0 | 63.5 |
| CDM 220-240V | | mm | mm | mm | mm | mm |
| 50/60Hz | | | | | | |

