



# ET-Standard Transformer

## ET-S transformer

High-frequency electronic transformer (60, 105 and 150 W versions available), operation with 12 V halogen lamps

### Benefits

- High efficiency compared with magnetic transformer
- Easy luminaire design-in with EMI compliance
- Dimmable with Philips-approved leading- and trailing-edge dimmers

### Features

- 30,000 hours lifetime
- EMI-compliant
- Screw connector
- CE, SELV approval
- Safe operation with overload, short circuit and overheating protection

### Application


- Indoor residential: living rooms, decorative and accent lighting
- Professional applications: reception areas, offices, retail spaces and exhibition rooms

# ET-S transformer

## Versions



## Dimensional drawing



Product	D1	C1	B2	A1	A2	B1
ET-S 15 LED 220-240V	3.4 mm	29.0 mm	23.4 in	115.0 mm	105.0 mm	45.0 mm

