



Spot of bright white light

Brilliantline Alu

Superior-quality low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Aluminum coating prevents heat in the backlight.

Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement costs due to longer burning hours

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Low-pressure technology with UV-block glass allows use in luminaires without front glass
- Universal burning position
- Lifetime: 4000 hours
- Instant start

Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops

Warnings and Safety

- Due to the heat that radiates from the bulb, a minimum distance of 0,5 m is required between bulb and combustible materials or objects susceptible to drying or fading.


Brilliantline Alu

Versions



GU5.3, MR16

Dimensional drawing




Product	D (max)	C (max)
Brilliantline Alu 35W GU5.3 12V MR16 36D 1CT/10X5F	51 mm	46 mm




Brilliantline Alu

Accent Diagrams



LDAC_HALUMR_35W_36D-Accent diagram

Beam Diagrams



LDBE_HALUMR_35W_36D-Beam diagram

