



# The new halogen mains-voltage capsule. Compact shape, crisp white light

## Halogen Clickline G9

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

### Benefits

- Bright, sparkling halogen light to create the right atmosphere
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement cost due to longer burning hours

### Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Compact size, easy to fit in the luminaire
- Universal burning position
- Instant start

### Application

- General lighting in shops, restaurants, hotels, galleries, exhibitions and museums. Ideal for use in small, decorative luminaires


# Halogen Clickline G9

## Versions



G9, Clear

## Dimensional drawing



Product	D (max)	L	C (max)
Halogen MV Click 28W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen Capsule 28W G9 240V 1BC/15 SRP	12.75 mm	21.7 mm	44.6 mm
Halogen MV Click 42W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen Capsule 42W G9 240V 1BC/15 SRP	12.75 mm	21.7 mm	44.6 mm
Halogen MV Click 18W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Caps 28W G9 230V CL 1BC/10	13 mm	21.7 mm	45 mm
Halogen MV Caps 42W G9 230V CL 1BC/10	13 mm	21.7 mm	45 mm

# Halogen Clickline G9

## Approval and Application

Energy Efficiency Label (EEL) D

## Controls and Dimming

Dimmable Yes

## Operating and Electrical

Warm Up Time To 60% Light (Nom) instant full light

## General Information

Cap-Base G9

Operating Position UNIVERSAL

Rated Lifetime (Hours) 2000 h

Switching Cycle 8000X

## Luminaire Design Requirements

Bulb Temperature (Max) 950 °C

## Light Technical

Correlated Color Temperature (Nom) 2800 K

Color Rendering Index (Nom) 100

Llmf At End Of Nominal Lifetime (Min) 80 %

## Mechanical and Housing

Bulb Finish Clear

Bulb Shape T13

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	28 kWh
925640644205	Halogen MV Click 28W G9 230V CL 1CT	28 kWh
925640645506	Halogen Capsule 28W G9 240V 1BC/15 SRP	-
925640844202	Halogen MV Caps 42W G9 230V CL 1BC/10	42 kWh
925640844205	Halogen MV Click 42W G9 230V CL 1CT	42 kWh
925640845503	Halogen Capsule 42W G9 240V 1BC/15 SRP	-
925697744201	Halogen MV Click 18W G9 230V CL 1CT	18 kWh

## Operating and Electrical (1/2)

Order Code	Full Product Name	Lamp		Power (Rated) (Nom)	Starting Time (Max)
		Current (Nom)	Voltage (Nom)		
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	0.12 A	230 V	28.0 W	-
925640644205	Halogen MV Click 28W G9 230V CL 1CT	0.12 A	230 V	28.0 W	-
925640645506	Halogen Capsule 28W G9 240V 1BC/15 SRP	0.12 A	240 V	28 W	0.01 s
925640844202	Halogen MV Caps 42W G9 230V CL 1BC/10	0.18 A	230 V	42.0 W	-

Order Code	Full Product Name	Lamp		Power (Rated) (Nom)	Starting Time (Max)
		Current (Nom)	Voltage (Nom)		
925640844205	Halogen MV Click 42W G9 230V CL 1CT	0.18 A	230 V	42.0 W	-
925640845503	Halogen Capsule 42W G9 240V 1BC/15 SRP	0.18 A	240 V	42 W	0.01 s
925697744201	Halogen MV Click 18W G9 230V CL 1CT	0.08 A	230 V	18 W	-

## Operating and Electrical (2/2)

Order Code	Full Product Name	Starting Time (Nom)
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	0.0 s
925640644205	Halogen MV Click 28W G9 230V CL 1CT	0.0 s
925640645506	Halogen Capsule 28W G9 240V 1BC/15 SRP	-
925640844202	Halogen MV Caps 42W G9 230V CL 1BC/10	0.0 s

Order Code	Full Product Name	Starting Time (Nom)
925640844205	Halogen MV Click 42W G9 230V CL 1CT	0.0 s
925640845503	Halogen Capsule 42W G9 240V 1BC/15 SRP	-
925697744201	Halogen MV Click 18W G9 230V CL 1CT	0.0 s

## General Information

## Halogen Clickline G9

Order Code	Full Product Name	Nominal Lifetime (Nom)
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	2000 h
925640644205	Halogen MV Click 28W G9 230V CL 1CT	2000 h
925640645506	Halogen Capsule 28W G9 240V 1BC/15 SRP	-
925640844202	Halogen MV Caps 42W G9 230V CL 1BC/10	2000 h

Order Code	Full Product Name	Nominal Lifetime (Nom)
925640844205	Halogen MV Click 42W G9 230V CL 1CT	2000 h
925640845503	Halogen Capsule 42W G9 240V 1BC/15 SRP	-
925697744201	Halogen MV Click 18W G9 230V CL 1CT	2000 h

### Light Technical

Order Code	Full Product Name	Luminous	
		Efficacy (rated) (Nom)	Luminous Flux (Rated) (Nom)
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	12.1 lm/W	370 lm
925640644205	Halogen MV Click 28W G9 230V CL 1CT	12.1 lm/W	370 lm
925640645506	Halogen Capsule 28W G9 240V 1BC/15 SRP	12.1 lm/W	370 lm
925640844202	Halogen MV Caps 42W G9 230V CL 1BC/10	15 lm/W	630 lm

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Nom)	Luminous Flux (Rated) (Nom)	Luminous Flux (Rated) (Nom)
925640844205	Halogen MV Click 42W G9 230V CL 1CT	15 lm/W	630 lm	630 lm
925640845503	Halogen Capsule 42W G9 240V 1BC/15 SRP	15 lm/W	630 lm	630 lm
925697744201	Halogen MV Click 18W G9 230V CL 1CT	11.1 lm/W	204 lm	204 lm

