



The new halogen mains-voltage capsule. Compact shape, crisp white light

Halogen Clickline G9

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

Benefits

- Bright, sparkling halogen light to create the right atmosphere
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement cost due to longer burning hours

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Compact size, easy to fit in the luminaire
- Universal burning position
- Instant start

Application

- General lighting in shops, restaurants, hotels, galleries, exhibitions and museums. Ideal for use in small, decorative luminaires


Halogen Clickline G9

Versions



G9 T 13 mm Clear

Dimensional drawing



Product	D (max)	L	C (max)
Halogen MV Click 28W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Click 42W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Click 18W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Caps 28W G9 230V CL 1BC/10	13 mm	21.7 mm	45 mm
Halogen MV Caps 42W G9 230V CL 1BC/10	13 mm	21.7 mm	45 mm
Halogen MV Click 44.0W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Click 29.0W G9 230V CL 1CT	13 mm	21.7 mm	45 mm
Halogen MV Caps 44.0W G9 230V 1PF/10 SRT	13 mm	21.7 mm	45 mm
Halogen MV Click 19.0W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

Halogen Clickline G9

Controls and dimming

Dimmable	Yes
----------	-----

Operating and electrical

Voltage (Nom)	230 V
Starting Time (Nom)	0.0 s
Warm Up Time To 60% Light (Nom)	instant full light

General information

Cap-Base	G9
Nominal Lifetime (Nom)	2000 h
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	2000 h
Rated Lifetime (Years)	2 a
Switching Cycle	8000X

Luminaire design requirements

Bulb Temperature (Max)	950 °C
------------------------	--------

Light technical

Correlated Color Temperature (Nom)	2800 K
Color Rendering Index (Nom)	100
Llmf At End Of Nominal Lifetime (Min)	80 %

Mechanical and housing

Bulb Finish	Clear
Bulb Shape	T13

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	28 kWh
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	28 kWh
925640644205	Halogen MV Click 28W G9 230V CL 1CT	29 kWh
925640844201	Halogen MV Click 44.0W G9 230V CL 1CT	42 kWh
925640844202	Halogen MV Caps 42W G9 230V CL 1BC/10	42 kWh
925640844205	Halogen MV Click 42W G9 230V CL 1CT	44 kWh
925640844214	Halogen MV Caps 44.0W G9 230V 1PF/10 SRT	42 kWh
925697744201	Halogen MV Click 18W G9 230V CL 1CT	19 kWh
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	18 kWh

Operating and electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Nom)
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	0.12 A	28.0 W
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	0.12 A	28.0 W
925640644205	Halogen MV Click 28W G9 230V CL 1CT	0.12 A	29 W
925640844201	Halogen MV Click 44.0W G9 230V CL 1CT	0.18 A	42.0 W
925640844202	Halogen MV Caps 42W G9 230V CL 1BC/10	0.18 A	42.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Nom)
925640844205	Halogen MV Click 42W G9 230V CL 1CT	0.18 A	44 W
925640844214	Halogen MV Caps 44.0W G9 230V 1PF/10 SRT	0.18 A	42.0 W
925697744201	Halogen MV Click 18W G9 230V CL 1CT	0.08 A	19 W
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	0.08 A	18 W

Light technical (1/2)

Order Code	Full Product Name	Chromaticity		Luminous Efficacy	
		Coordinate X (Nom)	Coordinate Y (Nom)	(rated) (Nom)	Luminous Flux (Nom)
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	-	-	12.1 lm/W	370 lm

Order Code	Full Product Name	Chromaticity		Luminous Efficacy	
		Coordinate X (Nom)	Coordinate Y (Nom)	(rated) (Nom)	Luminous Flux (Nom)
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	-	-	12.1 lm/W	370 lm

Halogen Clickline G9

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Luminous	
				Efficacy (rated) (Nom)	Luminous Flux (Nom)
925640644205	Halogen MV Click 28W G9 230V CL 1CT	0.452	0.409	12.1 lm/W	350 lm
925640844201	Halogen MV Click 44.0W G9 230V CL 1CT	-	-	15 lm/W	630 lm
925640844202	Halogen MV Caps 42W G9 230V CL 1BC/10	-	-	15 lm/W	630 lm
925640844205	Halogen MV Click 42W G9 230V CL 1CT	0.452	0.409	15 lm/W	590 lm

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Luminous	
				Efficacy (rated) (Nom)	Luminous Flux (Nom)
925640844214	Halogen MV Caps 44.0W G9 230V 1PF/10 SRT	-	-	15 lm/W	630 lm
925697744201	Halogen MV Click 18W G9 230V CL 1CT	0.452	0.409	11.1 lm/W	195 lm
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	-	-	11.1 lm/W	204 lm

Light technical (2/2)

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
925640644201	Halogen MV Click 29.0W G9 230V CL 1CT	370 lm
925640644202	Halogen MV Caps 28W G9 230V CL 1BC/10	370 lm
925640644205	Halogen MV Click 28W G9 230V CL 1CT	370 lm
925640844201	Halogen MV Click 44.0W G9 230V CL 1CT	630 lm
925640844202	Halogen MV Caps 42W G9 230V CL 1BC/10	630 lm

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
925640844205	Halogen MV Click 42W G9 230V CL 1CT	630 lm
925640844214	Halogen MV Caps 44.0W G9 230V 1PF/10 SRT	630 lm
925697744201	Halogen MV Click 18W G9 230V CL 1CT	204 lm
925697744209	Halogen MV Click 19.0W G9 230V CL 1CT	204 lm

