



Crisp white light

Plusline Large (double ended)

PlusLine Large flood delivers maximum light output to light up large areas like outdoor, buildings and shops.

Benefits

- Bright, sparkling halogen light to create the right atmosphere
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Lifetime: 2000 hours

Application

- General lighting in shops, restaurants, hotels, galleries, exhibitions and museums.
Decorative outdoor: billboards, exhibitions and parking areas

Versions



R7s, T11/T12

Plusline Large (double ended)

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline Large 1000W R7s 230V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm
Plusline Large 1000W R7s 240V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm
Plusline Large 1500W R7s 230V 1CT/10	11 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm

Controls and dimming	
Dimmable	Yes
Operating and electrical	
Starting Time (Nom)	0.0 s
Warm Up Time To 60% Light (Nom)	instant full light
General information	
Cap-Base	R7S
Nominal Lifetime (Nom)	2000 h
Operating Position	P4
Rated Lifetime (Hours)	2000 h
Switching Cycle	8000X
Luminaire design requirements	
Bulb Temperature (Max)	900 °C
Light technical	
Correlated Color Temperature (Nom)	2900 K
Color Rendering Index (Nom)	100
Llmf At End Of Nominal Lifetime (Min)	80 %
Mechanical and housing	
Bulb Finish	Clear
Bulb Shape	T11

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
923932143203	Plusline Large 1000W R7s 230V 1CT/10	1000 kWh
923932145703	Plusline Large 1000W R7s 240V 1CT/10	1000 kWh
923932243203	Plusline Large 1500W R7s 230V 1CT/10	1500 kWh

Operating and electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power (Nom)
923932143203	Plusline Large 1000W R7s 230V 1CT/10	4.35 A	230 V	1000 W
923932145703	Plusline Large 1000W R7s 240V 1CT/10	4.17 A	240 V	1000.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power (Nom)
923932243203	Plusline Large 1500W R7s 230V 1CT/10	6.52 A	230 V	1500.0 W

Light technical

Plusline Large (double ended)

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
923932143203	Plusline Large 1000W R7s 230V 1CT/10	21.5 lm/W	21500 lm	21500 lm
923932145703	Plusline Large 1000W R7s 240V 1CT/10	21.5 lm/W	21500 lm	21500 lm

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
923932243203	Plusline Large 1500W R7s 230V 1CT/10	22 lm/W	33000 lm	33000 lm

