



Zadora – free to create

Zadora, fixed

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Benefits

- Halogen accent lighting with the high power of MASTERLine 35 mm and 50 mm dichroic lamps
- Fixed downlights with beam widths of 8°, 24°, 36° or 60° to create exactly the right decorative or accent effects
- Also available in complete, ready-to-install kit versions

Features

- Available in fixed and adjustable versions
- MASTERLine 35 mm and 50 mm dichroic lamps and Twistline Alu lamps
- Wide choice of beam widths

Application

- Office
- Retail

Specifications

Type	QBS570
	QBW163

Light source	Halogen:
	- 1 x MASTERLine ES / GU5.3 / 45 W
	- 1 x Brilliantline Dichroic / GU4 / 35 W
	- 1 x Capsuleline / G4 / 20 W
	- 1 x Twistline Dichro / GZ10 / 50 W

Zadora, fixed

Lamp beam angle	MASTERLine 25°, 40°
Lamp included	No
Lamp position	Vertical
Transformer	Electronic (ET)
Suspension / mounting	Bracket (BR)
Color	Grey (GR) White (WH) Black (BK) Anthracite (ANT) Aluminum (ALU) Matt finishing (MAT) Chrome (CR) Pink (PK) Gold (GO)

Material	Die-cast aluminum and steel
Installation	Fixation by means of spring fasteners
Maintenance	Direct lamp access
Remarks	Bracket (BR) installed to ensure a safe distance between luminaire and ceiling Dedicated ready to install versions available (K), downlight, lamp and electronic transformer
Main applications	Office, retail

Versions



Zadora QBS570 fixed downlight
with halogen lamp



Zadora QBS570 fixed downlight
with halogen lamp



Zadora QBS570 fixed downlight
with halogen lamp

Zadora, fixed

Application conditions

Ambient temperature range	-10 to +35 °C
---------------------------	---------------

Approval and application

Mech. impact protection code	IK03
------------------------------	------

Ingress protection code	IP20
-------------------------	------

Operating and electrical

Input Voltage	12 V
---------------	------

General information

Cap-Base	GU5.3
----------	-------

Protection class IEC	Safety class II
----------------------	-----------------

Gear	-
------	---

Lamp power	45 W
------------	------

Number of light sources	1 pc
-------------------------	------

Mechanical and housing

Order Code	Full Product Name	Color
910502538018	QBS570 1xHAL-MR50-45W 12V BR WH	White
910502538318	QBS570 1xHAL-MR50-45W 12V BR ALU	Aluminum
910502538918	QBS570 1xHAL-MR50-45W 12V BR MAT	Matt finishing

