



Contempo RVP150/250/350

ConTempo 150-250-350

The Contempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. Contempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

Benefits

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminum housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodized reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

Features

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminum housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodized reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

ConTempo 150-250-350

Application

- Functional: bays, outdoor storage areas, surveillance, parking areas, construction sites
- Recreational/sports: training fields, game courts, swimming pools
- Decorative: facades, edifices, billboards, gardens, patios, fountains, bridges, landscapes

Versions



RVP350/RVP250

