



SGP340 Selenium

Selenium SGP340 C

Selenium represents a long line of sound, efficient and ergonomic road lighting luminaires that combine a high resistance aluminium housing with a T-POT Selenium reflector optical performance. Its simple design helps it to integrate into every type of outdoor environment. Selenium is also equipped with a CT-POT reflector, suitable for CPO-T 140/60W lamps. Moreover, Selenium is available for step dimming up to 250W.

Benefits

- High resistance aluminium housing with a T-POT Selenium reflector optical performance.
- Equipped with a CT-POT reflector, suitable for CPO-T 140/60W lamps. Available for step dimming up to 250W.

Features

- Everlasting design, round modern shape to reduce daytime visual impact
- High-strength, sealed construction, IP66 protected optic and gear compartment
- Easy maintenance from above, tool-free lamp replacement
- Well-known T-pot optic optimised for high-pressure sodium lamps, with five different lamp settings; CT-POT delivers outstanding performance with Cosmopolis lamp
- Energy saving with its step dimming system
- Three tilt angles for optimal installation on mast or bracket (0, 5, 15°)

Application

- Motorways
- Major and minor roads
- Rural roads
- Crossings and roundabouts
- Industrial estates