



SGX320 Tunnelite

Tunnelite SGX320

Tunnel luminaire SGX320 suitable for use with SON-T 150-400W high pressure sodium vapour lamps.

Benefits

- Suitable for use with SON-T 150-400W high pressure sodium vapour lamps

Features

- The housing consists of extruded aluminum body with die cast end plates
- Reflector options: T-pot, asymmetric or symmetric
- Detachable gear tray for easy repair and maintenance
- Tool-free lamp replacement
- 3 types of installation options

Application

- Tunnels
- Underpasses
- Basement parking areas

Versions



Tunnelite SGX320

General information

Lamp family code	SON-T
Number of light sources	1 pc

General information

Order Code	Full Product Name	Cap-Base	Gear	Lamp power	Optic type	Order Code	Full Product Name	Cap-Base	Gear	Lamp power	Optic type
910401960880	SGX320 1xSON-T150W 220V-50Hz A	E40	SGR	150 W	Asymmetrical	910401961880	SGX320 1xSON-T150W 220V-50Hz S	E40	SGR	150 W	Symmetrical
910401960980	SGX320 1xSON-T250W 220V-50Hz A	E40	SGR	250 W	Asymmetrical	910401961980	SGX320 1xSON-T250W 220V-50Hz S	E40	SGR	250 W	Symmetrical
910401961080	SGX320 1xSON-T400W 220V A	-	CONV	400 W	Asymmetrical	910401962080	SGX320 1xSON-T400W 220V-50Hz S	E40	SGR	400 W	Symmetrical

