



TBS068

TBS068

An economical recessed mounted luminaire for TL-D fluorescent lamps with gloss or matt optics for indoor general lighting applications. It offers an economical lighting solution for exposed T-bar ceilings.

Features

- Extremely flat housing design
- Ease of installation by means of specially designed flip-flat plates

Application

- Office open plans
- Entrance halls

Versions



TBS068 recessed luminaire

TBS068

Dimensional drawing

Product	A	B
TBS068 2xTL-D36W HF C2	1197 mm	297 mm
TBS068 3xTL-D36W HF M2	1197 mm	297 mm
TBS068 2xTL-D36W HF M2	1197 mm	297 mm
TBS068 4xTL-D18W HF M2	597 mm	597 mm
TBS068 3xTL-D18W HF M2	597 mm	597 mm
TBS068 4XTLD-18W EBE M2	597 mm	597 mm
TBS068 2XTLD-36W EBE M2	1197 mm	297 mm

Approval and Application

Ingress protection code IP20

General Information

Lamp family code TL-D

General Information

Order Code	Full Product Name	Compensation circuit	Gear	Lamp power	Number of light sources	Optic type
910403398701	TBS068 2xTL-D36W HF C2	-	HF	36 W	2 pcs	High-gloss mirror ribbed aluminum louver
910403398901	TBS068 3xTL-D36W HF M2	-	HF	36 W	3 pcs	Matt mirror ribbed lamellae louver
910403399001	TBS068 2xTL-D36W HF M2	-	HF	36 W	2 pcs	Matt mirror ribbed lamellae louver
910403399101	TBS068 4xTL-D18W HF M2	-	HF	18 W	4 pcs	Matt mirror ribbed lamellae louver
910403399201	TBS068 3xTL-D18W HF M2	-	HF	18 W	3 pcs	Matt mirror ribbed lamellae louver
911400690880	TBS068 4XTLD-18W EBE M2	-	EBE	18 W	4 pcs	Film-coated matt mirror with ribbed louver
911400690980	TBS068 2XTLD-36W EBE M2	-	EBE	36 W	2 pcs	Film-coated matt mirror with ribbed louver

