



# TBS707 Wing-C

## TBS707

The Wing-C range of recessed luminaires revolutionize workspaces by offering a choice of direct/indirect light, which perform with excellent efficiency while creating elegance and sophistication that designers have been looking for. Apart from adding excitement to the workspace with its unconventional styling, it enhances peoples' comfort by providing glare free light. It blends the direct/indirect lighting experience with an even light distribution while offering the option of glare-free highlights or a softer, diffused, shadow-less light. Easy to install and seamlessly integrated into the ceiling, these luminaires add a touch of class to your office environment as well as to hotel lobbies, restaurants and retail outlets.

### Features

- Stylish and functional: ergonomically designed for the modern, high tech office environment. It is designed with wide, decorative and polycarbonate finish coupled with a robust construction. Such aesthetics offer elegance while easing cleaning and maintenance
- Ease of installation: special aluminium extrusions ensure reliable and error-free mounting of optics
- Elegant and comfortable solution: a choice to create a more comfortable environment with its high efficiency, low-glare and 3D OLC optics. An indirect lighting option is also available to create a soothing and shadow-less ambiance

### Application

- Open-plan offices
- Cell-offices
- Call centres
- Reception areas
- Corridors
- Retail outlets

# TBS707

## Versions




TBS707 recessed luminaire



TBS707 recessed luminaire

## Dimensional drawing



Product	H	L	W
TBS707 3xTL5-14W HFP IND FTB	140 mm	630 mm	620 mm
TBS707 2xTL5-28W/840 K HFP IND FTB CAU	140 mm	1230 mm	320 mm
TBS707 2xTL5-28W HFE IND	140 mm	1230 mm	320 mm
TBS707 3xTL5-28W HFE IND	140 mm	1230 mm	620 mm
TBS707 3xTL5-14W HFE IND	140 mm	630 mm	620 mm

### Approval and Application

Ingress protection code IP20

### General Information

Lamp family code TL5

Optic type -

## General Information

Order Code	Full Product Name	Gear	Kombipack	Lamp power	Number of light sources
911400614080	TBS707 3xTL5-14W HFP IND FTB	EBP	-	14 W	3 pcs
911400615580	TBS707 3xTL5-28W HFE IND	HFE	-	28 W	3 pcs
911400688180	TBS707 3xTL5-14W HFE IND	HFE	-	14 W	3 pcs

Order Code	Full Product Name	Gear	Kombipack	Lamp power	Number of light sources
911400614180	TBS707 2xTL5-28W/840 K HFP IND FTB CAU	EBP	Lamp(s) included	28 W	2 pcs
911400614680	TBS707 2xTL5-28W HFE IND	HFE	-	28 W	2 pcs

