



Sereno TBS869

Sereno TBS869/528

The new Philips range Sereno recessed luminaires are more energy efficient than ever before. The latest optical technology was used to create a highly effective optic, giving rise to new opportunities for saving energy. This family of advanced TL5 recessed luminaire with micro optic technology use up to 25% less energy than standard TL5 solutions. Even greater savings can be made by retrofitting TLD lighting installations with our new TL5 recessed luminaires. The quality of the lighting is maintained, thanks to the Omni directional Lighting Control optic which increases luminous efficacy while reducing glare in all directions and complying with relevant brightness limits. As a result, our luminaires enable sustainable and green lighting solutions to be created. Because daylight-linking and presence-detecting lighting control systems can be optionally packaged into your recessed luminaire lighting solution, your energy consumption can easily be halved in comparison to conventional office lighting solutions.

Features

- Energy efficiency: Sereno advanced TL5 recessed luminaire with micro optic technology use up to 25% less energy than standard TL5 solutions and with PHILIPS advance lighting control up to 75% energy saving.
- Architecturally appealing: comfort visual appearance and ultra flat light with only 47mm in height
- An easy choice offer installation, replacement and maintenance

Application

- General industries
- Representative offices
- Conference rooms
- Small offices
- General open plan offices
- Data processing offices
- Reception and public service areas

Sereno TBS869/528

Versions



Sereno TBS528 recessed

Approval and application

Ingress protection code IP20

General information

Lamp family code TL5

General information

Order Code	Full Product Name	Gear	Kombipack	Lamp power	Number of light sources	Optic type
910403390501	TBS528 2xTL5-14W/840 HFP M8 FU CAU	EBP	Lamp(s) included	14 W	2 pcs	Matt optic 3D micro-lamellae
910403390701	TBS528 2xTL5-28W HF M8 IPP	EBE	-	28 W	2 pcs	Matt optic 3D micro-lamellae
910403391101	TBS528 3xTL5-14W HF M8 IPP	EBE	-	14 W	3 pcs	Matt optic 3D micro-lamellae
910403391501	TBS528 4xTL5-14W HF M8 IPP	EBE	-	14 W	4 pcs	Matt optic 3D micro-lamellae
910403392001	TBS528 3xTL5-28W HF M2 IPP	EBE	-	28 W	3 pcs	Matt mirror ribbed lamellae louver
910403392101	TBS528 3xTL5-14W HF M2 IPP	EBE	-	14 W	3 pcs	Matt mirror ribbed lamellae louver
910403392301	TBS528 2xTL5-28W HF M2 IPP	EBE	-	28 W	2 pcs	Matt mirror ribbed lamellae louver
910403392401	TBS528 4xTL5-14W HF M2 IPP	EBE	-	14 W	4 pcs	Matt mirror ribbed lamellae louver
910403392901	TBS528 2xTL5-14W HF M8 IPP	EBE	-	14 W	2 pcs	Matt optic 3D micro-lamellae
910403393801	TBS528 2xTL5-28W HFA M2 IPP	HFA	-	28 W	2 pcs	Matt mirror ribbed lamellae louver
910403394701	TBS528 2xTL5-28W HFP M2 FU IPP	EBP	-	28 W	2 pcs	Matt mirror ribbed lamellae louver
910403396401	TBS528 2xTL5-28W HFP WV M2 FU IPC	EBP	-	28 W	2 pcs	Matt mirror ribbed lamellae louver

