



Basic fluorescent lighting

TL-D Standard Colours

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Benefits

- Create atmospheres from warm white to cool daylight

Features

- Standard colors with moderate color rendering
- Available in various color designations

Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where color rendering is not an important factor

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

TL-D Standard Colours


Versions



G13, T8

TL-D Standard Colours

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/54-765	28 mm	1199.4 mm	1206.5	1204.1 mm	1213.6
1SL/25			mm		mm
TLDRS32W-CO-25	28 mm	1199.4 mm	1206.5	1204.1 mm	1213.6
			mm		mm
TL-D 10W/33-640	28 mm	331.5 mm	338.6 mm	336.2 mm	345.7 mm
1SL/25					
TL-D 10W/54-765	28 mm	331.5 mm	338.6 mm	336.2 mm	345.7 mm
1SL/50					
TL-D 15W/33-640	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
1SL/9					
TL-D 15W/54-765	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
1SL/50					
TL-D 30W/33-640	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8
1SL/25					mm
TL-D 30W/54-765	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8
1SL/25					mm
TL-D 30W/54-765	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8
1SL/25					mm
TL-D 30W/54-765	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8
1SL/25					mm
TLD 30W STANDARD	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8
25PCS					mm
TL-D 18W/54-765	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					
TL-D 18W/33-640	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					
TL-D 18W/33-640	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					
TL-D 18W/33-640	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					
TL-D 18W/33-640	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					
TL-D 18W/33-640	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
UNP/25					
TL-D 18W/54-765	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					
TL-D 18W/54-765	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					
TL-D 18W/54-765	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					
TL-D 18W/54-765	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					
TL-D 36W/29-530	28 mm	1199.4 mm	1206.5	1204.1 mm	1213.6
1SL/25			mm		mm
TL-D 36W/33-640	28 mm	1199.4 mm	1206.5	1204.1 mm	1213.6
1SL/25			mm		mm
TL-D 36W/33-640	28 mm	1199.4 mm	1206.5	1204.1 mm	1213.6
1SL/25			mm		mm
TL-D 36W/33-640	28 mm	1199.4 mm	1206.5	1204.1 mm	1213.6
1SL/25			mm		mm

TL-D Standard Colours

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/33-640 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
TL-D 36W/33-640 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
TL-D 36W/33-640 UNP/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
TL-D 36W/54-765 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
TL-D 36W/54-765 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
TL-D 36W/54-765 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
TL-D 36W/54-765 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
TL-D 58W/33-640 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm
TL-D 58W/33-640 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm
TL-D 58W/54-765 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm
TL-D 58W/54-765 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm
TL-D 58W/54-765 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm
TL-D 58W/54-765 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm
TL-D 58W/54 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm
TL-D 58W/54-765 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm
TLDRS16W-CO-25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Controls and dimming

Dimmable	Yes
----------	-----

General information

Cap-Base	G13
----------	-----

Mechanical and housing

Bulb Shape	T8
------------	----

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
927869003301	TLDRS16W-CO-25	-	8.0 mg
927870003301	TLDRS32W-CO-25	-	8.0 mg
928024003331	TL-D 10W/33-640 1SL/25	-	8.0 mg
928024005436	TL-D 10W/54-765 1SL/50	-	8.0 mg
928024803347	TL-D 15W/33-640 1SL/9	-	8.0 mg

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
928024805436	TL-D 15W/54-765 1SL/50	20 kWh	8.0 mg
928025403351	TL-D 30W/33-640 1SL/25	36 kWh	5.0 mg
928025405451	TL-D 30W/54-765 1SL/25	36 kWh	5.0 mg
928025405453	TL-D 30W/54-765 1SL/25	36 kWh	5.0 mg
928025405482	TL-D 30W/54-765 1SL/25	36 kWh	5.0 mg

TL-D Standard Colours

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)
928025407548	TLD 30W STANDARD 25PCS	-	8.0 mg
928047305451	TL-D 18W/54-765 1SL/25	22 kWh	5.0 mg
928048003312	TL-D 18W/33-640 1SL/25	22 kWh	5.0 mg
928048003351	TL-D 18W/33-640 1SL/25	22 kWh	5.0 mg
928048003353	TL-D 18W/33-640 1SL/25	22 kWh	5.0 mg
928048003382	TL-D 18W/33-640 1SL/25	22 kWh	5.0 mg
928048003384	TL-D 18W/33-640 UNP/25	22 kWh	5.0 mg
928048005422	TL-D 18W/54-765 1SL/25	22 kWh	5.0 mg
928048005436	TL-D 18W/54-765 1SL/25	22 kWh	8.0 mg
928048005440	TL-D 18W/54-765 1SL/25	22 kWh	5.0 mg
928048005453	TL-D 18W/54-765 1SL/25	22 kWh	5.0 mg
928048502953	TL-D 36W/29-530 1SL/25	-	8.0 mg
928048503312	TL-D 36W/33-640 1SL/25	43 kWh	5.0 mg
928048503340	TL-D 36W/33-640 1SL/25	43 kWh	5.0 mg
928048503351	TL-D 36W/33-640 1SL/25	43 kWh	5.0 mg

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)
928048503353	TL-D 36W/33-640 1SL/25	43 kWh	5.0 mg
928048503382	TL-D 36W/33-640 1SL/25	43 kWh	5.0 mg
928048503384	TL-D 36W/33-640 UNP/25	43 kWh	5.0 mg
928048505422	TL-D 36W/54-765 1SL/25	43 kWh	5.0 mg
928048505436	TL-D 36W/54-765 1SL/25	43 kWh	8.0 mg
928048505440	TL-D 36W/54-765 1SL/25	43 kWh	5.0 mg
928048505451	TL-D 36W/54-765 1SL/25	43 kWh	5.0 mg
928048505453	TL-D 36W/54-765 1SL/25	43 kWh	5.0 mg
928049003312	TL-D 58W/33-640 1SL/25	68 kWh	5.0 mg
928049003351	TL-D 58W/33-640 1SL/25	68 kWh	5.0 mg
928049005422	TL-D 58W/54-765 1SL/25	68 kWh	5.0 mg
928049005451	TL-D 58W/54-765 1SL/25	68 kWh	5.0 mg
928049005453	TL-D 58W/54-765 1SL/25	68 kWh	5.0 mg
928049005481	TL-D 58W/54 1SL/25	68 kWh	5.0 mg
928049005482	TL-D 58W/54-765 1SL/25	68 kWh	5.0 mg

Operating and electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power (Nom)
927869003301	TLDRS16W-CO-25	0.265 A	70 V	16 W
927870003301	TLDRS32W-CO-25	0.265 A	139 V	32 W
928024003331	TL-D 10W/33-640 1SL/25	0.230 A	46 V	10 W
928024005436	TL-D 10W/54-765 1SL/50	0.230 A	46 V	10.0 W
928024803347	TL-D 15W/33-640 1SL/9	0.310 A	51 V	15.0 W
928024805436	TL-D 15W/54-765 1SL/50	0.310 A	51 V	15.0 W
928025403351	TL-D 30W/33-640 1SL/25	0.360 A	98 V	30 W
928025405451	TL-D 30W/54-765 1SL/25	0.360 A	98 V	30.0 W
928025405453	TL-D 30W/54-765 1SL/25	0.360 A	98 V	30.0 W
928025405482	TL-D 30W/54-765 1SL/25	0.360 A	98 V	30.0 W
928025407548	TLD 30W STANDARD 25PCS	0.360 A	98 V	30 W
928047305451	TL-D 18W/54-765 1SL/25	0.360 A	59 V	18.0 W
928048003312	TL-D 18W/33-640 1SL/25	0.360 A	59 V	18.0 W
928048003351	TL-D 18W/33-640 1SL/25	0.360 A	59 V	18.0 W
928048003353	TL-D 18W/33-640 1SL/25	0.360 A	59 V	18.0 W
928048003382	TL-D 18W/33-640 1SL/25	0.360 A	59 V	18.0 W
928048003384	TL-D 18W/33-640 UNP/25	0.360 A	59 V	18.0 W
928048005422	TL-D 18W/54-765 1SL/25	0.360 A	59 V	18.0 W
928048005436	TL-D 18W/54-765 1SL/25	0.360 A	59 V	18.0 W
928048005440	TL-D 18W/54-765 1SL/25	0.360 A	59 V	18.0 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power (Nom)
928048005453	TL-D 18W/54-765 1SL/25	0.360 A	59 V	18.0 W
928048502953	TL-D 36W/29-530 1SL/25	0.440 A	103 V	36.0 W
928048503312	TL-D 36W/33-640 1SL/25	0.440 A	103 V	36.0 W
928048503340	TL-D 36W/33-640 1SL/25	0.440 A	103 V	36.0 W
928048503351	TL-D 36W/33-640 1SL/25	0.440 A	103 V	36.0 W
928048503353	TL-D 36W/33-640 1SL/25	0.440 A	103 V	36.0 W
928048503382	TL-D 36W/33-640 1SL/25	0.440 A	103 V	36.0 W
928048503384	TL-D 36W/33-640 UNP/25	0.440 A	103 V	36.0 W
928048505422	TL-D 36W/54-765 1SL/25	0.440 A	103 V	36.0 W
928048505436	TL-D 36W/54-765 1SL/25	0.440 A	103 V	36.0 W
928048505440	TL-D 36W/54-765 1SL/25	0.440 A	103 V	36.0 W
928048505451	TL-D 36W/54-765 1SL/25	0.440 A	103 V	36.0 W
928048505453	TL-D 36W/54-765 1SL/25	0.440 A	103 V	36.0 W
928049003312	TL-D 58W/33-640 1SL/25	0.670 A	111 V	58.5 W
928049003351	TL-D 58W/33-640 1SL/25	0.670 A	111 V	58.5 W
928049005422	TL-D 58W/54-765 1SL/25	0.670 A	111 V	58.5 W
928049005451	TL-D 58W/54-765 1SL/25	0.670 A	111 V	58.5 W
928049005453	TL-D 58W/54-765 1SL/25	0.670 A	111 V	58.5 W
928049005481	TL-D 58W/54 1SL/25	0.670 A	111 V	58.5 W
928049005482	TL-D 58W/54-765 1SL/25	0.670 A	111 V	58.5 W

General information

TL-D Standard Colours

Order Code	Full Product Name	Life To 50%			Order Code	Full Product Name	Life To 50%		
		Failures Preheat (Nom)	Life To 10% Failures (Nom)	Life To 50% Failures (Nom)			Failures Preheat (Nom)	Life To 10% Failures (Nom)	Life To 50% Failures (Nom)
927869003301	TLDRS16W-CO-25	-	-	8000 h	928048005453	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
927870003301	TLDRS32W-CO-25	-	-	12000 h	928048502953	TL-D 36W/29-530 1SL/25	-	10000 h	13000 h
928024003331	TL-D 10W/33-640 1SL/25	-	-	5000 h	928048503312	TL-D 36W/33-640 1SL/25	-	10000 h	13000 h
928024005436	TL-D 10W/54-765 1SL/50	-	-	5000 h	928048503340	TL-D 36W/33-640 1SL/25	-	10000 h	13000 h
928024803347	TL-D 15W/33-640 1SL/9	20000 h	-	13000 h	928048503351	TL-D 36W/33-640 1SL/25	-	10000 h	13000 h
928024805436	TL-D 15W/54-765 1SL/50	20000 h	-	13000 h	928048503353	TL-D 36W/33-640 1SL/25	-	10000 h	13000 h
928025403351	TL-D 30W/33-640 1SL/25	-	10000 h	13000 h	928048503382	TL-D 36W/33-640 1SL/25	-	10000 h	13000 h
928025405451	TL-D 30W/54-765 1SL/25	-	10000 h	13000 h	928048503384	TL-D 36W/33-640 UNP/25	-	10000 h	13000 h
928025405453	TL-D 30W/54-765 1SL/25	-	10000 h	13000 h	928048505422	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928025405482	TL-D 30W/54-765 1SL/25	-	10000 h	13000 h	928048005436	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928025407548	TLD 30W STANDARD 25PCS	-	10000 h	13000 h	928048005440	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928047305451	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h	928048005442	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928048003312	TL-D 18W/33-640 1SL/25	-	10000 h	13000 h	928048005436	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928048003351	TL-D 18W/33-640 1SL/25	-	10000 h	13000 h	928048005440	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928048003353	TL-D 18W/33-640 1SL/25	-	10000 h	13000 h	928048005442	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928048003382	TL-D 18W/33-640 1SL/25	-	10000 h	13000 h	928048005436	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928048003384	TL-D 18W/33-640 UNP/25	-	10000 h	13000 h	928048005440	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928048005422	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h	928048005442	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928048005436	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h	928048005436	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h
928048005440	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h	928048005440	TL-D 18W/54-765 1SL/25	-	10000 h	13000 h

Light technical (1/2)

Order Code	Full Product Name	Color		Correlated Color Temperature (Nom)	Color Rendering		Lumen Maintenance	
		Code	Color Designation		Index (Nom)	Maintenance 10000 h (Nom)	Maintenance 2000 h (Nom)	Maintenance 5000 h (Nom)
927869003301	TLDRS16W-CO-25	33-640	Cool White (CW)	4100 K	63	-	90 %	83 %
927870003301	TLDRS32W-CO-25	33-640	Cool White (CW)	4100 K	60	-	90 %	83 %
928024003331	TL-D 10W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	60	-	85 %	80 %
928024005436	TL-D 10W/54-765 1SL/50	54-765	Cool Daylight	6200 K	75	-	85 %	80 %
928024803347	TL-D 15W/33-640 1SL/9	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928024805436	TL-D 15W/54-765 1SL/50	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928025403351	TL-D 30W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928025405451	TL-D 30W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928025405453	TL-D 30W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928025405482	TL-D 30W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928025407548	TLD 30W STANDARD 25PCS	75	Daylight	5000 K	70	-	90 %	83 %
928047305451	TL-D 18W/54-765 1SL/25	54-765	Cool Daylight	6200 K	75	-	90 %	83 %
928048003312	TL-D 18W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048003351	TL-D 18W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048003353	TL-D 18W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048003382	TL-D 18W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048003384	TL-D 18W/33-640 UNP/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048005422	TL-D 18W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928048005436	TL-D 18W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928048005440	TL-D 18W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928048005453	TL-D 18W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %

TL-D Standard Colours

Order Code	Full Product Name	Color		Correlated Color Temperature (Nom)	Color Rendering		Lumen Maintenance	
		Code	Color Designation		Index (Nom)	10000 h (Nom)	2000 h (Nom)	5000 h (Nom)
928048502953	TL-D 36W/29-530 1SL/25	29-530	Warm White (WW)	2900 K	51	75 %	90 %	80 %
928048503312	TL-D 36W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048503340	TL-D 36W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048503351	TL-D 36W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048503353	TL-D 36W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048503382	TL-D 36W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048503384	TL-D 36W/33-640 UNP/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928048505422	TL-D 36W/54-765 1SL/25	54-765	Cool Daylight	6200 K	75	-	90 %	83 %
928048505436	TL-D 36W/54-765 1SL/25	54-765	Cool Daylight	6500 K	72	75 %	90 %	80 %
928048505440	TL-D 36W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928048505451	TL-D 36W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928048505453	TL-D 36W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928049003312	TL-D 58W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928049003351	TL-D 58W/33-640 1SL/25	33-640	Cool White (CW)	4100 K	63	75 %	90 %	80 %
928049005422	TL-D 58W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928049005451	TL-D 58W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928049005453	TL-D 58W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928049005481	TL-D 58W/54 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %
928049005482	TL-D 58W/54-765 1SL/25	54-765	Cool Daylight	6200 K	72	75 %	90 %	80 %

Light technical (2/2)

Order Code	Full Product Name	Luminous Flux (Nom)	Order Code	Full Product Name	Luminous Flux (Nom)
927869003301	TLDRS16W-CO-25	1070 lm	928048005453	TL-D 18W/54-765 1SL/25	1050 lm
927870003301	TLDRS32W-CO-25	2350 lm	928048502953	TL-D 36W/29-530 1SL/25	2975 lm
928024003331	TL-D 10W/33-640 1SL/25	440 lm	928048503312	TL-D 36W/33-640 1SL/25	2850 lm
928024005436	TL-D 10W/54-765 1SL/50	390 lm	928048503340	TL-D 36W/33-640 1SL/25	2850 lm
928024803347	TL-D 15W/33-640 1SL/9	830 lm	928048503351	TL-D 36W/33-640 1SL/25	2850 lm
928024805436	TL-D 15W/54-765 1SL/50	725 lm	928048503353	TL-D 36W/33-640 1SL/25	2850 lm
928025403351	TL-D 30W/33-640 1SL/25	2100 lm	928048503382	TL-D 36W/33-640 1SL/25	2850 lm
928025405451	TL-D 30W/54-765 1SL/25	1825 lm	928048503384	TL-D 36W/33-640 UNP/25	2850 lm
928025405453	TL-D 30W/54-765 1SL/25	1825 lm	928048505422	TL-D 36W/54-765 1SL/25	2500 lm
928025405482	TL-D 30W/54-765 1SL/25	1825 lm	928048505436	TL-D 36W/54-765 1SL/25	2500 lm
928025407548	TLD 30W STANDARD 25PCS	1310 lm	928048505440	TL-D 36W/54-765 1SL/25	2500 lm
928047305451	TL-D 18W/54-765 1SL/25	1025 lm	928048505451	TL-D 36W/54-765 1SL/25	2500 lm
928048003312	TL-D 18W/33-640 1SL/25	1200 lm	928048505453	TL-D 36W/54-765 1SL/25	2500 lm
928048003351	TL-D 18W/33-640 1SL/25	1200 lm	928049003312	TL-D 58W/33-640 1SL/25	4600 lm
928048003353	TL-D 18W/33-640 1SL/25	1200 lm	928049003351	TL-D 58W/33-640 1SL/25	4600 lm
928048003382	TL-D 18W/33-640 1SL/25	1200 lm	928049005422	TL-D 58W/54-765 1SL/25	4000 lm
928048003384	TL-D 18W/33-640 UNP/25	1200 lm	928049005451	TL-D 58W/54-765 1SL/25	4000 lm
928048005422	TL-D 18W/54-765 1SL/25	1050 lm	928049005453	TL-D 58W/54-765 1SL/25	4000 lm
928048005436	TL-D 18W/54-765 1SL/25	1050 lm	928049005481	TL-D 58W/54 1SL/25	4000 lm
928048005440	TL-D 18W/54-765 1SL/25	1050 lm	928049005482	TL-D 58W/54-765 1SL/25	4000 lm

TL-D Standard Colours

