



# CoreLine Wall-mounted – the clear choice for LED

## CoreLine Wall-mounted

CoreLine Wall-mounted is a circular-shaped surface-mounted luminaire that is easy to apply in circulation areas such as hallways and staircases. The modern unobtrusive design, in combination with its homogeneous light distribution it delivers, ensures that this luminaire blends into most building architectures. With the push-in connectors, installation is fast and straightforward.

### Benefits

- Universal solution covering various application requirements
- Slim and unobtrusive design
- Delivering the right visual comfort in common areas
- Direct replacement for traditional wall-mounted luminaires

### Features

- Homogeneous light effect to cater for visual comfort
- Three lumen packages to cater for diverse applications
- Water- and vandal-proof as standard
- Easy installation with push-in connectors and through wiring possibility
- Optional emergency lighting (incl. self-test)
- Optional motion detector, including daylight sensing, dimming and grouping function
- Optional DALI versions

# CoreLine Wall-mounted

## Application

- Corridors
- Staircases
- Entrance areas
- Restrooms
- Emergency exits
- Parking garages
- Outdoor safety lighting

## Specifications

<b>Type</b>	WL130V (slim version)
	WL131V (deeper version)
<b>Light source</b>	Non-replaceable LED module
<b>Power (+/-10%)</b>	12 W (LED12S version)
	22 W (LED20S version)
	36 W (LED34S version)
<b>Beam angle</b>	120°
<b>Luminous flux</b>	1200 lm (LED12S version)
	2000 lm (LED20S version)
	3400 lm (LED34S version)
<b>Correlated Color Temperature</b>	3000 or 4000 K
<b>Color Rendering Index</b>	≥ 80
<b>Median useful life</b>	50,000 hours
<b>L70B50</b>	
<b>Median useful life</b>	38,000 hours
<b>L80B50</b>	
<b>Median useful life</b>	18,000 hours
<b>L90B50</b>	
<b>Average ambient temperature</b>	+25 °C

<b>Operating temperature range</b>	-20 to +35 °C (wall-mounted position)
	-20 to +25 °C (ceiling-mounted position)
	0 to +25 °C (emergency lighting)
<b>Driver</b>	Built-in, replaceable
<b>Mains voltage</b>	220-240V / 50-60 Hz
<b>Dimming</b>	Non-dimmable (PSU versions)
	Dimmable (PSR and DALI versions)
<b>Options</b>	Emergency lighting (integrated): 3 hours (EL3)
	Movement detection unit (integrated): on/off switch with day light override including grouping functionality (MDU)
	DALI driver and movement detection unit (integrated)
<b>Material</b>	Housing: Polyamide
	Difuser: high grade polycarbonate, UV resistant
<b>Color</b>	White (RAL 9003)
<b>Optical cover</b>	Polycarbonate difuser
<b>Connection</b>	Push-in connector
<b>Maintenance</b>	LED module closed, no internal cleaning required
<b>Installation</b>	Screw mounting, directly onto surface
	4-point screw installation of housing to wall
	Twist lock connection difuser to housing
	Through-wiring possible

## Versions



CoreLine Wall-mounted




CoreLine Wall-Mounted Gen2

# CoreLine Wall-mounted

## Product details



CoreLine\_Wall-mounted-  
WL131V\_D35\_CTO\_PSD-DPP.TIF




CoreLine\_Wall-mounted-  
WL130V-2DPP.TIF



CoreLine\_Wall-mounted-  
WL131V\_D35\_CTO\_PSR\_MDU-  
DPP.TIF



CoreLine\_Wall-mounted-  
WL130V\_CTO-DPP.TIF



CoreLine\_Wall-mounted-  
WL130V-1DPP.TIF



CoreLine\_Wall-mounted-  
WL130V\_D35\_CTO\_MDU-DPP.TIF

# CoreLine Wall-mounted

## Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP65

## General Information

Beam angle of light source	120 °
CE mark	CE mark
Protection class IEC	Safety class II
Optical cover/lens type	Opal bowl with painted cover
Driver included	Yes
ENEC mark	ENEC mark
Light source replaceable	No
Number of gear units	1 unit
Optic type	Opal prismatic reflector

## Initial Performance (IEC Compliant)

Init. Color Rendering Index	80
Luminous flux tolerance	+/-10%

## Mechanical and Housing

Color	White
-------	-------

-

Order Code	Full Product Name	Driver failure rate at 5000 h
910500465390	WL131V LED12S/830 PSED EL3 WH	1%
910500465391	WL131V LED12S/840 PSED EL3 WH	1%
910500465392	WL131V LED20S/830 PSED EL3 WH	1%
910500465393	WL131V LED20S/840 PSED EL3 WH	1%
910500465394	WL131V LED34S/830 PSED WH	1%
910500465395	WL131V LED34S/840 PSED WH	1%
910500465396	WL131V LED34S/830 PSED EL3 WH	1%
910500465397	WL131V LED34S/840 PSED EL3 WH	1%
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	1%
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	1%
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	1%
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	1%
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	1%
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	1%
910500465894	WL131V LED12S/830 PSU EL3 WH	-
910500465895	WL131V LED12S/840 PSU EL3 WH	-
910500465896	WL131V LED20S/830 PSU EL3 WH	-
910500465897	WL131V LED20S/840 PSU EL3 WH	-
911401807080	WL131V LED12S/830 PSU WH	-
911401807180	WL131V LED12S/840 PSU WH	-
911401807280	WL131V LED20S/830 PSU WH	-
911401807380	WL131V LED20S/840 PSU WH	-
912401483188	WL131V LED34S/830 PSU WH	0.7%
912401483189	WL131V LED34S/840 PSU WH	0.7%
912401483190	WL131V LED12S/830 PSR MDU WH	0.7%
912401483191	WL131V LED12S/840 PSR MDU WH	0.7%
912401483192	WL131V LED20S/830 PSR MDU WH	0.7%
912401483193	WL131V LED20S/840 PSR MDU WH	0.7%
912401483194	WL131V LED34S/830 PSR MDU WH	0.7%
912401483195	WL131V LED34S/840 PSR MDU WH	0.7%
912401483196	WL131V LED12S/830 PSED WH	0.7%
912401483197	WL131V LED12S/840 PSED WH	0.7%
912401483198	WL131V LED20S/830 PSED WH	0.7%
912401483199	WL131V LED20S/840 PSED WH	0.7%
912401483182	WL130V LED12S/830 PSU WH	0.7%
912401483183	WL130V LED12S/840 PSU WH	0.7%
912401483184	WL130V LED20S/830 PSU WH	0.7%
912401483185	WL130V LED20S/840 PSU WH	0.7%
912401483186	WL130V LED20S/830 PSU MDU WH	0.7%
912401483187	WL130V LED20S/840 PSU MDU WH	0.7%

## Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500465390	WL131V LED12S/830 PSED EL3 WH	0 to +40 °C	10%	No
910500465391	WL131V LED12S/840 PSED EL3 WH	0 to +40 °C	10%	No

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500465392	WL131V LED20S/830 PSED EL3 WH	0 to +40 °C	10%	No

## CoreLine Wall-mounted

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
910500465393	WL131V LED20S/840 PSED EL3 WH	0 to +40 °C	10%	No
910500465394	WL131V LED34S/830 PSED WH	-20 to +40 °C	10%	No
910500465395	WL131V LED34S/840 PSED WH	-20 to +40 °C	10%	No
910500465396	WL131V LED34S/830 PSED EL3 WH	0 to +40 °C	10%	No
910500465397	WL131V LED34S/840 PSED EL3 WH	0 to +40 °C	10%	No
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
910500465894	WL131V LED12S/830 PSU EL3 WH	0 to +40 °C	Not applicable	Yes
910500465895	WL131V LED12S/840 PSU EL3 WH	0 to +40 °C	Not applicable	Yes
910500465896	WL131V LED20S/830 PSU EL3 WH	0 to +40 °C	Not applicable	Yes
910500465897	WL131V LED20S/840 PSU EL3 WH	0 to +40 °C	Not applicable	Yes
911401807080	WL131V LED12S/830 PSU WH	-20 to +40 °C	Not applicable	Not applicable
911401807180	WL131V LED12S/840 PSU WH	-20 to +40 °C	Not applicable	Not applicable
911401807280	WL131V LED20S/830 PSU WH	-20 to +40 °C	Not applicable	Not applicable
911401807380	WL131V LED20S/840 PSU WH	-20 to +40 °C	Not applicable	Not applicable

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
912401483188	WL131V LED34S/830 PSU WH	-20 to +40 °C	Not applicable	Yes
912401483189	WL131V LED34S/840 PSU WH	-20 to +40 °C	Not applicable	Yes
912401483190	WL131V LED12S/830 PSR MDU WH	-20 to +40 °C	10%	Yes
912401483191	WL131V LED12S/840 PSR MDU WH	-20 to +40 °C	10%	Yes
912401483192	WL131V LED20S/830 PSR MDU WH	-20 to +40 °C	10%	Yes
912401483193	WL131V LED20S/840 PSR MDU WH	-20 to +40 °C	10%	Yes
912401483194	WL131V LED34S/830 PSR MDU WH	-20 to +40 °C	10%	Yes
912401483195	WL131V LED34S/840 PSR MDU WH	-20 to +40 °C	10%	Yes
912401483196	WL131V LED12S/830 PSED WH	-20 to +40 °C	10%	Yes
912401483197	WL131V LED12S/840 PSED WH	-20 to +40 °C	10%	Yes
912401483198	WL131V LED20S/830 PSED WH	-20 to +40 °C	10%	Yes
912401483199	WL131V LED20S/840 PSED WH	-20 to +40 °C	10%	Yes
912401483182	WL130V LED12S/830 PSU WH	-20 to +40 °C	Not applicable	Yes
912401483183	WL130V LED12S/840 PSU WH	-20 to +40 °C	Not applicable	Yes
912401483184	WL130V LED20S/830 PSU WH	-20 to +40 °C	Not applicable	Yes
912401483185	WL130V LED20S/840 PSU WH	-20 to +40 °C	Not applicable	Yes
912401483186	WL130V LED20S/830 PSU MDU WH	-20 to +40 °C	Not applicable	Yes
912401483187	WL130V LED20S/840 PSU MDU WH	-20 to +40 °C	Not applicable	Yes

# CoreLine Wall-mounted

## Controls and Dimming

Order Code	Full Product Name	Dimmable
910500465390	WL131V LED12S/830 PSED EL3 WH	Yes
910500465391	WL131V LED12S/840 PSED EL3 WH	Yes
910500465392	WL131V LED20S/830 PSED EL3 WH	Yes
910500465393	WL131V LED20S/840 PSED EL3 WH	Yes
910500465394	WL131V LED34S/830 PSED WH	Yes
910500465395	WL131V LED34S/840 PSED WH	Yes
910500465396	WL131V LED34S/830 PSED EL3 WH	Yes
910500465397	WL131V LED34S/840 PSED EL3 WH	Yes
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	Yes
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	Yes
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	Yes
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	Yes
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	Yes
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	Yes
910500465894	WL131V LED12S/830 PSU EL3 WH	No
910500465895	WL131V LED12S/840 PSU EL3 WH	No
910500465896	WL131V LED20S/830 PSU EL3 WH	No
910500465897	WL131V LED20S/840 PSU EL3 WH	No
911401807080	WL131V LED12S/830 PSU WH	No
911401807180	WL131V LED12S/840 PSU WH	No

Order Code	Full Product Name	Dimmable
911401807280	WL131V LED20S/830 PSU WH	No
911401807380	WL131V LED20S/840 PSU WH	No
912401483188	WL131V LED34S/830 PSU WH	No
912401483189	WL131V LED34S/840 PSU WH	No
912401483190	WL131V LED12S/830 PSR MDU WH	Yes
912401483191	WL131V LED12S/840 PSR MDU WH	Yes
912401483192	WL131V LED20S/830 PSR MDU WH	Yes
912401483193	WL131V LED20S/840 PSR MDU WH	Yes
912401483194	WL131V LED34S/830 PSR MDU WH	Yes
912401483195	WL131V LED34S/840 PSR MDU WH	Yes
912401483196	WL131V LED12S/830 PSED WH	Yes
912401483197	WL131V LED12S/840 PSED WH	Yes
912401483198	WL131V LED20S/830 PSED WH	Yes
912401483199	WL131V LED20S/840 PSED WH	Yes
912401483182	WL130V LED12S/830 PSU WH	No
912401483183	WL130V LED12S/840 PSU WH	No
912401483184	WL130V LED20S/830 PSU WH	No
912401483185	WL130V LED20S/840 PSU WH	No
912401483186	WL130V LED20S/830 PSU MDU WH	No
912401483187	WL130V LED20S/840 PSU MDU WH	No

## Operating and Electrical

Order Code	Full Product Name	Input Voltage
910500465390	WL131V LED12S/830 PSED EL3 WH	220-240 V
910500465391	WL131V LED12S/840 PSED EL3 WH	220-240 V
910500465392	WL131V LED20S/830 PSED EL3 WH	220-240 V
910500465393	WL131V LED20S/840 PSED EL3 WH	220-240 V
910500465394	WL131V LED34S/830 PSED WH	220-240 V
910500465395	WL131V LED34S/840 PSED WH	220-240 V
910500465396	WL131V LED34S/830 PSED EL3 WH	220-240 V
910500465397	WL131V LED34S/840 PSED EL3 WH	220-240 V
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	220-240 V
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	220-240 V
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	220-240 V
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	220-240 V
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	220-240 V
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	220-240 V
910500465894	WL131V LED12S/830 PSU EL3 WH	220/240 V
910500465895	WL131V LED12S/840 PSU EL3 WH	220/240 V
910500465896	WL131V LED20S/830 PSU EL3 WH	220/240 V
910500465897	WL131V LED20S/840 PSU EL3 WH	220/240 V
911401807080	WL131V LED12S/830 PSU WH	220/240 V
911401807180	WL131V LED12S/840 PSU WH	220/240 V

Order Code	Full Product Name	Input Voltage
911401807280	WL131V LED20S/830 PSU WH	220/240 V
911401807380	WL131V LED20S/840 PSU WH	220/240 V
912401483188	WL131V LED34S/830 PSU WH	220-240 V
912401483189	WL131V LED34S/840 PSU WH	220-240 V
912401483190	WL131V LED12S/830 PSR MDU WH	220-240 V
912401483191	WL131V LED12S/840 PSR MDU WH	220-240 V
912401483192	WL131V LED20S/830 PSR MDU WH	220-240 V
912401483193	WL131V LED20S/840 PSR MDU WH	220-240 V
912401483194	WL131V LED34S/830 PSR MDU WH	220-240 V
912401483195	WL131V LED34S/840 PSR MDU WH	220-240 V
912401483196	WL131V LED12S/830 PSED WH	220-240 V
912401483197	WL131V LED12S/840 PSED WH	220-240 V
912401483198	WL131V LED20S/830 PSED WH	220-240 V
912401483199	WL131V LED20S/840 PSED WH	220-240 V
912401483182	WL130V LED12S/830 PSU WH	220-240 V
912401483183	WL130V LED12S/840 PSU WH	220-240 V
912401483184	WL130V LED20S/830 PSU WH	220-240 V
912401483185	WL130V LED20S/840 PSU WH	220-240 V
912401483186	WL130V LED20S/830 PSU MDU WH	220-240 V
912401483187	WL130V LED20S/840 PSU MDU WH	220-240 V

## General Information (1/2)

## CoreLine Wall-mounted

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
910500465390	WL131V LED12S/830 PSED EL3 WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465391	WL131V LED12S/840 PSED EL3 WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465392	WL131V LED20S/830 PSED EL3 WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465393	WL131V LED20S/840 PSED EL3 WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465394	WL131V LED34S/830 PSED WH	-	-	-	Temperature 850 °C, duration 30 s
910500465395	WL131V LED34S/840 PSED WH	-	-	-	Temperature 850 °C, duration 30 s
910500465396	WL131V LED34S/830 PSED EL3 WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465397	WL131V LED34S/840 PSED EL3 WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465894	WL131V LED12S/830 PSU EL3 WH	Emergency lighting 3 hours duration	For mounting on easily flammable surfaces	-	Temperature 850 °C, duration 30 s
910500465895	WL131V LED12S/840 PSU EL3 WH	Emergency lighting 3 hours duration	For mounting on easily flammable surfaces	-	Temperature 850 °C, duration 30 s
910500465896	WL131V LED20S/830 PSU EL3 WH	Emergency lighting 3 hours duration	For mounting on easily flammable surfaces	-	Temperature 850 °C, duration 30 s
910500465897	WL131V LED20S/840 PSU EL3 WH	Emergency lighting 3 hours duration	For mounting on easily flammable surfaces	-	Temperature 850 °C, duration 30 s
911401807080	WL131V LED12S/830 PSU WH	-	For mounting on easily flammable surfaces	-	Temperature 650 °C, duration 30 s
911401807180	WL131V LED12S/840 PSU WH	-	For mounting on easily flammable surfaces	-	Temperature 650 °C, duration 30 s
911401807280	WL131V LED20S/830 PSU WH	-	For mounting on easily flammable surfaces	-	Temperature 650 °C, duration 30 s
911401807380	WL131V LED20S/840 PSU WH	-	For mounting on easily flammable surfaces	-	Temperature 650 °C, duration 30 s
912401483188	WL131V LED34S/830 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483189	WL131V LED34S/840 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483190	WL131V LED12S/830 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483191	WL131V LED12S/840 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483192	WL131V LED20S/830 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s

## CoreLine Wall-mounted

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
912401483193	WL131V LED20S/840 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483194	WL131V LED34S/830 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483195	WL131V LED34S/840 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483196	WL131V LED12S/830 PSED WH	-	-	-	Temperature 650 °C, duration 30 s
912401483197	WL131V LED12S/840 PSED WH	-	-	-	Temperature 650 °C, duration 30 s
912401483198	WL131V LED20S/830 PSED WH	-	-	-	Temperature 650 °C, duration 30 s
912401483199	WL131V LED20S/840 PSED WH	-	-	-	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
912401483182	WL130V LED12S/830 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483183	WL130V LED12S/840 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483184	WL130V LED20S/830 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483185	WL130V LED20S/840 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483186	WL130V LED20S/830 PSU MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483187	WL130V LED20S/840 PSU MDU WH	-	-	-	Temperature 650 °C, duration 30 s

### General Information (2/2)

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code	Service tag
910500465390	WL131V LED12S/830 PSED EL3 WH	LED12	-	WL131V	-
910500465391	WL131V LED12S/840 PSED EL3 WH	LED12	-	WL131V	-
910500465392	WL131V LED20S/830 PSED EL3 WH	LED20	-	WL131V	-
910500465393	WL131V LED20S/840 PSED EL3 WH	LED20	-	WL131V	-
910500465394	WL131V LED34S/830 PSED WH	LED34S	-	WL131V	-
910500465395	WL131V LED34S/840 PSED WH	LED34S	-	WL131V	-
910500465396	WL131V LED34S/830 PSED EL3 WH	LED34S	-	WL131V	-
910500465397	WL131V LED34S/840 PSED EL3 WH	LED34S	-	WL131V	-
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	LED12	Movement detection unit	WL131V	-
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	LED12	Movement detection unit	WL131V	-
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	LED20	Movement detection unit	WL131V	-

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code	Service tag
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	LED20	Movement detection unit	WL131V	-
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	LED34S	Movement detection unit	WL131V	-
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	LED34S	Movement detection unit	WL131V	-
910500465894	WL131V LED12S/830 PSU EL3 WH	LED12	-	WL131V	-
910500465895	WL131V LED12S/840 PSU EL3 WH	LED12	-	WL131V	-
910500465896	WL131V LED20S/830 PSU EL3 WH	LED20	-	WL131V	-
910500465897	WL131V LED20S/840 PSU EL3 WH	LED20	-	WL131V	-
911401807080	WL131V LED12S/830 PSU WH	LED12	-	-	-
911401807180	WL131V LED12S/840 PSU WH	LED12	-	-	-
911401807280	WL131V LED20S/830 PSU WH	LED20	-	-	-



## CoreLine Wall-mounted

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code	Service tag
911401807380	WL131V LED20S/840 PSU WH	LED20	-	-	-
912401483188	WL131V LED34S/830 PSU WH	LED34S	-	-	Yes
912401483189	WL131V LED34S/840 PSU WH	LED34S	-	-	Yes
912401483190	WL131V LED12S/830 PSR MDU WH	LED12	Movement detection unit	-	Yes
912401483191	WL131V LED12S/840 PSR MDU WH	LED12	Movement detection unit	-	Yes
912401483192	WL131V LED20S/830 PSR MDU WH	LED20	Movement detection unit	-	Yes
912401483193	WL131V LED20S/840 PSR MDU WH	LED20	Movement detection unit	-	Yes
912401483194	WL131V LED34S/830 PSR MDU WH	LED34S	Movement detection unit	-	Yes
912401483195	WL131V LED34S/840 PSR MDU WH	LED34S	Movement detection unit	-	Yes
912401483196	WL131V LED12S/830 PSED WH	LED12	-	-	Yes
912401483197	WL131V LED12S/840 PSED WH	LED12	-	-	Yes

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code	Service tag
912401483198	WL131V LED20S/830 PSED WH	LED20	-	-	Yes
912401483199	WL131V LED20S/840 PSED WH	LED20	-	-	Yes
912401483182	WL130V LED12S/830 PSU WH	LED12	-	-	Yes
912401483183	WL130V LED12S/840 PSU WH	LED12	-	-	Yes
912401483184	WL130V LED20S/830 PSU WH	LED20	-	-	Yes
912401483185	WL130V LED20S/840 PSU WH	LED20	-	-	Yes
912401483186	WL130V LED20S/830 PSU MDU WH	LED20	Movement detection unit	-	Yes
912401483187	WL130V LED20S/840 PSU MDU WH	LED20	Movement detection unit	-	Yes

### Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910500465390	WL131V LED12S/830 PSED EL3 WH	(0.44, 0.41)	3000 K	100 lm/W	1200 lm
910500465391	WL131V LED12S/840 PSED EL3 WH	(0.39, 0.39)	4000 K	100 lm/W	1200 lm
910500465392	WL131V LED20S/830 PSED EL3 WH	(0.44, 0.41)	3000 K	91 lm/W	2000 lm
910500465393	WL131V LED20S/840 PSED EL3 WH	(0.39, 0.39)	4000 K	91 lm/W	2000 lm
910500465394	WL131V LED34S/830 PSED WH	(0.44, 0.41)	3000 K	94 lm/W	3400 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910500465395	WL131V LED34S/840 PSED WH	(0.39, 0.39)	4000 K	94 lm/W	3400 lm
910500465396	WL131V LED34S/830 PSED EL3 WH	(0.44, 0.41)	3000 K	94 lm/W	3400 lm
910500465397	WL131V LED34S/840 PSED EL3 WH	(0.39, 0.39)	4000 K	94 lm/W	3400 lm
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	(0.44, 0.41)	3000 K	100 lm/W	1200 lm
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	(0.39, 0.39)	4000 K	100 lm/W	1200 lm

## CoreLine Wall-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	(0.44, 0.41)	3000 K	91 lm/W	2000 lm
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	(0.39, 0.39)	4000 K	91 lm/W	2000 lm
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	(0.44, 0.41)	3000 K	94 lm/W	3400 lm
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	(0.39, 0.39)	4000 K	94 lm/W	3400 lm
910500465894	WL131V LED12S/830 PSU EL3 WH	(0.44, 0.41)	3000 K	80 lm/W	1200 lm
910500465895	WL131V LED12S/840 PSU EL3 WH	(0.39, 0.39)	4000 K	80 lm/W	1200 lm
910500465896	WL131V LED20S/830 PSU EL3 WH	(0.44, 0.41)	3000 K	80 lm/W	2000 lm
910500465897	WL131V LED20S/840 PSU EL3 WH	(0.39, 0.39)	4000 K	80 lm/W	2000 lm
911401807080	WL131V LED12S/830 PSU WH	(0.44, 0.41)	3000 K	100 lm/W	1200 lm
911401807180	WL131V LED12S/840 PSU WH	(0.39, 0.39)	4000 K	100 lm/W	1200 lm
911401807280	WL131V LED20S/830 PSU WH	(0.44, 0.41)	3000 K	90 lm/W	2000 lm
911401807380	WL131V LED20S/840 PSU WH	(0.39, 0.39)	4000 K	90 lm/W	2000 lm
912401483188	WL131V LED34S/830 PSU WH	(0.44, 0.41)	3000 K	95 lm/W	3400 lm
912401483189	WL131V LED34S/840 PSU WH	(0.39, 0.39)	4000 K	95 lm/W	3400 lm
912401483190	WL131V LED12S/830 PSR MDU WH	(0.44, 0.41)	3000 K	80 lm/W	1200 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
912401483191	WL131V LED12S/840 PSR MDU WH	(0.39, 0.39)	4000 K	80 lm/W	1200 lm
912401483192	WL131V LED20S/830 PSR MDU WH	(0.44, 0.41)	3000 K	80 lm/W	2000 lm
912401483193	WL131V LED20S/840 PSR MDU WH	(0.39, 0.39)	4000 K	80 lm/W	2000 lm
912401483194	WL131V LED34S/830 PSR MDU WH	(0.44, 0.41)	3000 K	90 lm/W	3400 lm
912401483195	WL131V LED34S/840 PSR MDU WH	(0.39, 0.39)	4000 K	90 lm/W	3400 lm
912401483196	WL131V LED12S/830 PSED WH	(0.44, 0.41)	3000 K	90 lm/W	1200 lm
912401483197	WL131V LED12S/840 PSED WH	(0.39, 0.39)	4000 K	90 lm/W	1200 lm
912401483198	WL131V LED20S/830 PSED WH	(0.44, 0.41)	3000 K	90 lm/W	2000 lm
912401483199	WL131V LED20S/840 PSED WH	(0.39, 0.39)	4000 K	90 lm/W	2000 lm
912401483182	WL130V LED12S/830 PSU WH	(0.44, 0.41)	3000 K	100 lm/W	1200 lm
912401483183	WL130V LED12S/840 PSU WH	(0.39, 0.39)	4000 K	100 lm/W	1200 lm
912401483184	WL130V LED20S/830 PSU WH	(0.44, 0.41)	3000 K	90 lm/W	2000 lm
912401483185	WL130V LED20S/840 PSU WH	(0.44, 0.41)	4000 K	90 lm/W	2000 lm
912401483186	WL130V LED20S/830 PSU MDU WH	(0.44, 0.41)	3000 K	80 lm/W	2000 lm
912401483187	WL130V LED20S/840 SDCM<3	(0.39, 0.39)	4000 K	80 lm/W	2000 lm

## CoreLine Wall-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU MDU				
	WH				

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
910500465390	WL131V LED12S/830 PSED EL3 WH	12 W
910500465391	WL131V LED12S/840 PSED EL3 WH	12 W
910500465392	WL131V LED20S/830 PSED EL3 WH	22 W
910500465393	WL131V LED20S/840 PSED EL3 WH	22 W
910500465394	WL131V LED34S/830 PSED WH	36 W
910500465395	WL131V LED34S/840 PSED WH	36 W
910500465396	WL131V LED34S/830 PSED EL3 WH	36 W
910500465397	WL131V LED34S/840 PSED EL3 WH	36 W
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	12 W
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	12 W
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	22 W
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	22 W
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	36 W
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	36 W
910500465894	WL131V LED12S/830 PSU EL3 WH	15 W
910500465895	WL131V LED12S/840 PSU EL3 WH	15 W
910500465896	WL131V LED20S/830 PSU EL3 WH	25 W
910500465897	WL131V LED20S/840 PSU EL3 WH	25 W
911401807080	WL131V LED12S/830 PSU WH	12 W
911401807180	WL131V LED12S/840 PSU WH	12 W

Order Code	Full Product Name	Initial input power
911401807280	WL131V LED20S/830 PSU WH	22 W
911401807380	WL131V LED20S/840 PSU WH	22 W
912401483188	WL131V LED34S/830 PSU WH	36 W
912401483189	WL131V LED34S/840 PSU WH	36 W
912401483190	WL131V LED12S/830 PSR MDU WH	15 W
912401483191	WL131V LED12S/840 PSR MDU WH	15 W
912401483192	WL131V LED20S/830 PSR MDU WH	25 W
912401483193	WL131V LED20S/840 PSR MDU WH	25 W
912401483194	WL131V LED34S/830 PSR MDU WH	38 W
912401483195	WL131V LED34S/840 PSR MDU WH	38 W
912401483196	WL131V LED12S/830 PSED WH	13 W
912401483197	WL131V LED12S/840 PSED WH	13 W
912401483198	WL131V LED20S/830 PSED WH	23 W
912401483199	WL131V LED20S/840 PSED WH	23 W
912401483182	WL130V LED12S/830 PSU WH	12 W
912401483183	WL130V LED12S/840 PSU WH	12 W
912401483184	WL130V LED20S/830 PSU WH	22 W
912401483185	WL130V LED20S/840 PSU WH	22 W
912401483186	WL130V LED20S/830 PSU MDU WH	23 W
912401483187	WL130V LED20S/840 PSU MDU WH	23 W

