



# MSD Platinum – The power to light your creativity

## MSD Platinum (Touring/Stage)

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

### Benefits

- High beam intensity
- Freedom to create smaller and lighter fixtures
- High perceived brightness
- A long and reliable performance

### Features

- Very short arc
- Compact system
- High correlated color temperature
- Philips Platinum technology

### Application

- Events
- Shows/Theater
- Touring/Stage

# MSD Platinum (Touring/Stage)

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions





MSD Platinum 21 R MSDGLIM2017072



MSD Silver 330W

## Dimensional drawing








Product	D (max)	O	C (max)
MSD Platinum 20 R 1CT/8	58.5 mm	1.2 mm	72 mm
MSD Platinum 20 R UNP/24	58.5 mm	1.2 mm	72 mm
MSD Platinum 20 RB 1CT/8	58.5 mm	1.2 mm	72 mm
MSD Platinum 20 RB UNP/24	58.5 mm	1.2 mm	72 mm
MSD Platinum 400S Flex 1CT/8	58.5 mm	1.2 mm	72 mm
MSD Platinum 400S Flex UNP/24	58.5 mm	1.2 mm	72 mm
MSD Platinum 500S Flex 1CT/8	54.5 mm	1.4 mm	72 mm
MSD Platinum 500S Flex UNP/24	54.5 mm	1.4 mm	72 mm
MSD Silver 420W LL/24	58.5 mm	1 mm	70 mm
MSD Silver 420W LL/8	58.5 mm	1 mm	70 mm
MSD Silver 460W UNP/24	58.5 mm	1.3 mm	72 mm
MSD Silver 480W LL 1CT/8	58.5 mm	1.2 mm	72 mm
MSD Silver 480W LL UNP/24	58.5 mm	1.2 mm	72 mm
MSD Silver 480W/2 LL 1CT/8	58.5 mm	1.2 mm	72 mm
MSD Silver 480W/2 LL UNP/24	58.5 mm	1.2 mm	72 mm

Product	D (max)	O	C (max)
MSD Platinum 21 R 1CT/8	54.5 mm	1.2 mm	60 mm
MSD Platinum 21 R UNP/24	54.5 mm	1.2 mm	60 mm
MSD Platinum 25 R 1CT/8	54.5 mm	1.4 mm	60 mm
MSD Platinum 25 R UNP/24	54.5 mm	1.4 mm	60 mm
MSD Platinum 400L Flex 1CT/8	54.5 mm	1.2 mm	60 mm
MSD Platinum 400L Flex UNP/24	54.5 mm	1.2 mm	60 mm
MSD Platinum 500L Flex 1CT/8	54.5 mm	1.4 mm	60 mm
MSD Platinum 500L Flex UNP/24	54.5 mm	1.4 mm	60 mm

# MSD Platinum (Touring/Stage)

## Dimensional drawing



Product	D (max)	O	C (max)	T
MSD Platinum 200 Flex 1CT/8	56.5 mm	0.8 mm	60 mm	7 mm
MSD Platinum 200 Flex UNP/24	56.5 mm	0.8 mm	60 mm	7 mm

Product	D (max)	T (max)	O	C (max)
MSD Platinum 12 R LL 1CT/8	51.5 mm	6.8 mm	0.95 mm	57.1 mm
MSD Platinum 12 R LL UNP/24	51.5 mm	6.8 mm	0.95 mm	57.1 mm
MSD Platinum 14 R 1CT/8	51.5 mm	6.8 mm	0.95 mm	57.1 mm
MSD Platinum 14 R UNP/24	51.5 mm	6.8 mm	0.95 mm	57.1 mm
MSD Platinum 5 R 1CT/8	51.4 mm	6.8 mm	1.0 mm	57.1 mm
MSD Platinum 5 R UNP/24	51.4 mm	6.8 mm	1.0 mm	57.1 mm

Product	D (max)	O	C (max)
MSD Platinum 15 R 1CT/8	58.5 mm	1.3 mm	66.4 mm
MSD Platinum 15 R UNP/24	58.5 mm	1.3 mm	66.4 mm
MSD Platinum 16 R 1CT/8	58.5 mm	1.3 mm	66.4 mm
MSD Platinum 16 R UNP/24	58.5 mm	1.3 mm	66.4 mm
MSD Platinum 300S Flex 1CT/8	58.5 mm	1.0 mm	66.4 mm
MSD Platinum 300S Flex UNP/24	58.5 mm	1.0 mm	66.4 mm
MSD Silver 330W UNP/24	56.5 mm	1.3 mm	62.6 mm
MSD Silver 350W 1CT/8	58.5 mm	1.3 mm	66.4 mm
MSD Silver 350W UNP/24	58.5 mm	1.3 mm	66.4 mm

Product	D (max)	T (max)	O	C (max)
MSD Platinum 11 R 1CT/8	51.5 mm	10 mm	0.95 mm	53 mm
MSD Platinum 17 RA 1CT/8	51.4 mm	10.0 mm	1.0 mm	63 mm
MSD Platinum 17 RA UNP/24	51.4 mm	10.0 mm	1.0 mm	63 mm

# MSD Platinum (Touring/Stage)

## General Information

Cap-Base

-

## Controls and Dimming

Dimmable

Yes

## General Information

Order Code	Full Product Name	Operating Position
928197805308	MSD Platinum 21 R UNP/24	UNIVERSAL
928197805314	MSD Platinum 21 R 1CT/8	UNIVERSAL
928495505308	MSD Silver 330W UNP/24	UNIVERSAL
928495605308	MSD Silver 350W UNP/24	UNIVERSAL
928495605314	MSD Silver 350W 1CT/8	UNIVERSAL
928495705308	MSD Platinum 200 Flex UNP/24	UNIVERSAL
928495705314	MSD Platinum 200 Flex 1CT/8	UNIVERSAL
928191605308	MSD Platinum 15 R UNP/24	UNIVERSAL
928191605314	MSD Platinum 15 R 1CT/8	UNIVERSAL
928195205308	MSD Platinum 16 R UNP/24	UNIVERSAL
928195205314	MSD Platinum 16 R 1CT/8	UNIVERSAL
928496305308	MSD Platinum 300S Flex UNP/24	UNIVERSAL
928496305314	MSD Platinum 300S Flex 1CT/8	UNIVERSAL
928190805308	MSD Platinum 5 R UNP/24	UNIVERSAL
928190805314	MSD Platinum 5 R 1CT/8	UNIVERSAL
928196105308	MSD Platinum 14 R UNP/24	UNIVERSAL
928196105314	MSD Platinum 14 R 1CT/8	UNIVERSAL
928496705308	MSD Platinum 12 R LL UNP/24	UNIVERSAL
928496705314	MSD Platinum 12 R LL 1CT/8	UNIVERSAL
928191705314	MSD Platinum 11 R 1CT/8	UNIVERSAL
928197305308	MSD Platinum 17 RA UNP/24	UNIVERSAL
928197305314	MSD Platinum 17 RA 1CT/8	UNIVERSAL

Order Code	Full Product Name	Operating Position
928197205308	MSD Platinum 20 R UNP/24	UNIVERSAL
928197205314	MSD Platinum 20 R 1CT/8	UNIVERSAL
928495205308	MSD Platinum 20 RB UNP/24	UNIVERSAL
928495205314	MSD Platinum 20 RB 1CT/8	UNIVERSAL
928496505308	MSD Platinum 400S Flex UNP/24	UNIVERSAL
928496505314	MSD Platinum 400S Flex 1CT/8	UNIVERSAL
928498205308	MSD Platinum 500S Flex UNP/24	-
928498205314	MSD Platinum 500S Flex 1CT/8	-
928496105308	MSD Silver 460W UNP/24	UNIVERSAL
928498305308	MSD Silver 480W LL UNP/24	UNIVERSAL
928498305314	MSD Silver 480W LL 1CT/8	UNIVERSAL
928498605308	MSD Silver 480W/2 LL UNP/24	UNIVERSAL
928498605314	MSD Silver 480W/2 LL 1CT/8	UNIVERSAL
928499005308	MSD Silver 420W LL/24	UNIVERSAL
928499005314	MSD Silver 420W LL/8	UNIVERSAL
928495905308	MSD Platinum 25 R UNP/24	UNIVERSAL
928495905314	MSD Platinum 25 R 1CT/8	UNIVERSAL
928496405308	MSD Platinum 400L Flex UNP/24	UNIVERSAL
928496405314	MSD Platinum 400L Flex 1CT/8	UNIVERSAL
928498105308	MSD Platinum 500L Flex UNP/24	-
928498105314	MSD Platinum 500L Flex 1CT/8	-

## Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux (Min)
928197805308	MSD Platinum 21 R UNP/24	8000 K	-
928197805314	MSD Platinum 21 R 1CT/8	8000 K	-
928495505308	MSD Silver 330W UNP/24	8000 K	-
928495605308	MSD Silver 350W UNP/24	8000 K	-
928495605314	MSD Silver 350W 1CT/8	8000 K	-
928495705308	MSD Platinum 200 Flex UNP/24	7800 K	-
928495705314	MSD Platinum 200 Flex 1CT/8	7800 K	-
928191605308	MSD Platinum 15 R UNP/24	8000 K	11,000 lumen
928191605314	MSD Platinum 15 R 1CT/8	8000 K	11,000 lumen
928195205308	MSD Platinum 16 R UNP/24	8000 K	14,300 lumen
928195205314	MSD Platinum 16 R 1CT/8	8000 K	14,300 lumen
928496305308	MSD Platinum 300S Flex UNP/24	8000 K	-
928496305314	MSD Platinum 300S Flex 1CT/8	8000 K	-
928190805308	MSD Platinum 5 R UNP/24	8000 K	7,100 lumen
928190805314	MSD Platinum 5 R 1CT/8	8000 K	7,100 lumen

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux (Min)
928196105308	MSD Platinum 14 R UNP/24	7800 K	-
928196105314	MSD Platinum 14 R 1CT/8	7800 K	-
928496705308	MSD Platinum 12 R LL UNP/24	7800 K	15,000 lumen
928496705314	MSD Platinum 12 R LL 1CT/8	7800 K	15,000 lumen
928191705314	MSD Platinum 11 R 1CT/8	7800 K	-
928197305308	MSD Platinum 17 RA UNP/24	7000 K	-
928197305314	MSD Platinum 17 RA 1CT/8	7000 K	-
928197205308	MSD Platinum 20 R UNP/24	8000 K	-
928197205314	MSD Platinum 20 R 1CT/8	8000 K	-
928495205308	MSD Platinum 20 RB UNP/24	8000 K	-
928495205314	MSD Platinum 20 RB 1CT/8	8000 K	-
928496505308	MSD Platinum 400S Flex UNP/24	8000 K	-
928496505314	MSD Platinum 400S Flex 1CT/8	8000 K	-
928498205308	MSD Platinum 500S Flex UNP/24	8000 K	-
928498205314	MSD Platinum 500S Flex 1CT/8	8000 K	-

## MSD Platinum (Touring/Stage)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux (Min)
928498205314	MSD Platinum 500S Flex 1CT/8	8000 K	-
928496105308	MSD Silver 460W UNP/24	7800 K	-
928498305308	MSD Silver 480W LL UNP/24	7800 K	-
928498305314	MSD Silver 480W LL 1CT/8	7800 K	-
928498605308	MSD Silver 480W/2 LL UNP/24	7800 K	-
928498605314	MSD Silver 480W/2 LL 1CT/8	7800 K	-
928499005308	MSD Silver 420W LL/24	8000 K	-
928499005314	MSD Silver 420W LL/8	8000 K	-

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux (Min)
928495905308	MSD Platinum 25 R UNP/24	8000 K	-
928495905314	MSD Platinum 25 R 1CT/8	8000 K	-
928496405308	MSD Platinum 400L Flex UNP/24	8000 K	-
928496405314	MSD Platinum 400L Flex 1CT/8	8000 K	-
928498105308	MSD Platinum 500L Flex UNP/24	8000 K	-
928498105314	MSD Platinum 500L Flex 1CT/8	8000 K	-

