



High efficiency, visual comfort and a stylish design

LuxSpace, recessed

Today, every business is looking to optimize all its resources, and that means not only running costs like energy, but also user costs where they see a much bigger impact on return. LuxSpace is the ideal downlight solution. It's designed to provide the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (efficacy, color rendering CRI90 and light distribution). LuxSpace downlight offers a wide choice of options for creating desirable ambiances that support user comfort - no matter what the application. For office applications, LuxSpace also supports health and wellbeing with dedicated Tunable White products and lighting controls.

Benefits

- Best-in-class efficacy
- Gentle, uniform light with optimized distribution and glare control for visual comfort
- Supports lighting for wellbeing / human centric lighting with Tunable White and integrated lighting controls
- Perfect ceiling integration (narrow rim or rimless version for plaster ceilings)
- Excellent color rendering CRI90 (R9>50)

LuxSpace, recessed

Features

- Mini (DN560B) and compact (DN570B / DN571B) sizes for recessed
- Square recessed (DN572B) and surface-mounted (DN570C) round versions in compact size
- Choice of four optics: high-gloss, faceted, matt and white
- UGR19 and UGR22 versions with different product heights
- Selection of colors: High-gloss metalized, white (RAL9003), grey (RAL9006), black (RAL9004) as standard (or any other RAL color on request)
- Compliant for central emergency lighting with DC (upon request)
- Many extra options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), suspended deco glasses, through-wiring, Eca and B2ca cable and connector options
- Extended useful lifetime: 50,000 hours @L90

Application

- Offices
- Retail
- Hospitals and Care centers
- Hospitality
- Airports
- Museums
- Atriums

Specifications

Type	DN570B (low height recessed version) DN571B (deep recessed version)	Operating temperature range	+10 to +40 °C
Ceiling type	Plaster (board) ceiling	Driver	Separate
Light source	Non replaceable LED module	Mains voltage	230 or 240 V / 50-60 Hz
Power	11, 19, 23, 34 W (3000K) 11, 17.4, 21, 32 W (4000K)	Dimming	DALI dimming possible (PSD-E)
Light color:	830, 840, 927, 930 and 940	Options	Emergency lighting 3 hours (EL3) Protection glass (PG or PGO, IP54 front face) Through-wiring Rimless version for plaster ceiling (not for LED40S) Suspended glasses: opal (SG-O), frosted circle (SG-FRC) and frosted halo ring (SG-HR-FR)
Luminous flux (for 830 and 840 versions)	DN570B, high-gloss mirror or faceted reflector: 1350, 2200, 2600, 4000 lm DN570B, matt reflector: 1150, 1850, 2200, 4000 lm DN570B, white reflector: 1300, 2100, 2500, 4000 lm DN571B, high-gloss mirror or faceted reflector: 1300, 2100, 2500, 4000 lm DN571B, matt reflector: 1000, 1650, 1950, 4000 lm DN571B, white reflector: 1250, 2000, 2400, 4000 lm		Different cable and connector options available to support fast installation
Color Rendering Index	> 80 and > 90	Material	Housing and rim: aluminum Reflector: plastic, aluminum coated (for high-gloss and faceted optics)
Lumen maintenance at median useful life* 50000 h	L90	Color	Rim: white (RAL 9003), grey (RAL 9006), black (RAL 9004)
Control gear failure rate at median useful life 50000 h	5%	Optic	High-gloss mirror (C) Matt mirror (M) Faceted reflector (F) White reflector (WR)
Performance Ambient Temperature Tq	+25 °C	Connection	Push-in connector or with pull relief
		Installation	Fixation by means of spring fasteners
		Remarks	External driver included

LuxSpace, recessed

Versions



LuxSpace DN570B recessed
downlight with high-gloss optic



LuxSpace DN571B recessed
downlight with high-gloss optic



LuxSpace DN570B recessed
downlight with faceted optic



LuxSpace DN570B recessed
downlight with matt optic



LuxSpace DN570B recessed
downlight with white optic

Accessories



Protection glass

Ordercode 910503586401



Protection glass, opal

Ordercode 910503586402

Application conditions

Ambient temperature range	+10 to +25 °C
Suitable for random switching	Yes

Approval and application

Mech. impact protection code	IK02
------------------------------	------

Operating and electrical

Input Voltage	220 to 240 V
---------------	--------------

General information

CE mark	CE mark
Protection class IEC	Safety class II
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Number of gear units	1 unit

Initial performance (IEC compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Mechanical and housing

Color	White RAL 9003
-------	----------------

Application conditions

Order Code	Full Product Name	Maximum dim level
910505100834	DN570B LED12S/830 PSU-E C EW WH	-
910505100835	DN570B LED12S/840 PSU-E C WH	-
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	1%
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	1%
910505100842	DN570B LED20S/830 PSU-E C WH	-
910505100843	DN570B LED20S/840 PSU-E C WH	-
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	-
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	-
910505100850	DN570B LED20S/830 PSU-E C PG WH	-
910505100851	DN570B LED20S/840 PSU-E C PG WH	-
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	1%
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	1%
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	1%
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	1%
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	1%
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	1%
910505100868	DN570B LED24S/830 PSU-E C WH	Not applicable
910505100869	DN570B LED24S/840 PSU-E C WH	-
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	1%
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	1%
910505100884	DN570B LED40S/830 PSU-E C WH	Not applicable
910505100885	DN570B LED40S/840 PSU-E C WH	Not applicable
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	1%
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	1%
910505100903	DN570B LED60S/830 PSU-E C WH	-
910505100904	DN570B LED60S/840 PSU-E C WH	-
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	1%
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	1%
910505101204	DN570B LED12S/830 PSU-E C WH	-
910505102295	DN570B LED24S/830 WIA-E C WH	10%
910505102296	DN570B LED24S/840 WIA-E C WH	10%
910505102299	DN570B LED40S/830 WIA-E C WH	10%
910505102301	DN570B LED40S/840 WIA-E C WH	10%
910505102304	DN570B LED24S/930H PSU-E C WH	Not applicable
910505102305	DN570B LED24S/940H PSU-E C WH	Not applicable
910505100836	DN571B LED12S/830 PSU-E C WH	-
910505100837	DN571B LED12S/840 PSU-E C WH	-
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	1%
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	1%
910505100846	DN571B LED20S/830 PSU-E C WH	-
910505100847	DN571B LED20S/840 PSU-E C WH	-
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	-
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	-
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	1%
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	1%
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	1%
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	1%
910505100870	DN571B LED24S/830 PSU-E C WH	Not applicable
910505100871	DN571B LED24S/840 PSU-E C WH	-
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	1%
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	1%

Order Code	Full Product Name	Maximum dim level
910505100886	DN571B LED40S/830 PSU-E C WH	-
910505100887	DN571B LED40S/840 PSU-E C WH	-
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	1%
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	1%
910505102297	DN571B LED24S/830 WIA-E C WH	10%
910505102298	DN571B LED24S/840 WIA-E C WH	10%
910505102302	DN571B LED40S/830 WIA-E C WH	10%
910505102303	DN571B LED40S/840 WIA-E C WH	10%
910505102306	DN571B LED24S/930H PSU-E C WH	Not applicable
910505102307	DN571B LED24S/940H PSU-E C WH	Not applicable
910505100852	DN570B LED20S/830 PSU-E F WH	-
910505100853	DN570B LED20S/840 PSU-E F WH	-
910505100854	DN570B LED20S/830 PSU-E M WH	-
910505100855	DN570B LED20S/840 PSU-E M WH	-
910505100856	DN570B LED20S/830 PSU-E WR WH	-
910505100857	DN570B LED20S/840 PSU-E WR WH	-

Approval and application

Order Code	Full Product Name	Ingress protection code	Order Code	Full Product Name	Ingress protection code
910505100834	DN570B LED12S/830 PSU-E C EW WH	IP20	910505102301	DN570B LED40S/840 WIA-E C WH	IP20
910505100835	DN570B LED12S/840 PSU-E C WH	IP20	910505102304	DN570B LED24S/930H PSU-E C WH	IP20
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	IP20	910505102305	DN570B LED24S/940H PSU-E C WH	IP20
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	IP20	910505100836	DN571B LED12S/830 PSU-E C WH	IP20
910505100842	DN570B LED20S/830 PSU-E C WH	IP20	910505100837	DN571B LED12S/840 PSU-E C WH	IP20
910505100843	DN570B LED20S/840 PSU-E C WH	IP20	910505100840	DN571B LED12S/830 DIA-VLC-E C WH	IP20
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	IP20	910505100841	DN571B LED12S/840 DIA-VLC-E C WH	IP20
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	IP20	910505100846	DN571B LED20S/830 PSU-E C WH	IP20
910505100850	DN570B LED20S/830 PSU-E C PG WH	IP54/20	910505100847	DN571B LED20S/840 PSU-E C WH	IP20
910505100851	DN570B LED20S/840 PSU-E C PG WH	IP54/20	910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	IP20
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	IP20	910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	IP20
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	IP20	910505100864	DN571B LED20S/830 DIA-VLC-E C WH	IP20
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	IP20	910505100865	DN571B LED20S/840 DIA-VLC-E C WH	IP20
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	IP20	910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	IP20
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	IP54/20	910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	IP20
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	IP54/20	910505100870	DN571B LED24S/830 PSU-E C WH	IP20
910505100868	DN570B LED24S/830 PSU-E C WH	IP20	910505100871	DN571B LED24S/840 PSU-E C WH	IP20
910505100869	DN570B LED24S/840 PSU-E C WH	IP20	910505100874	DN571B LED24S/830 DIA-VLC-E C WH	IP20
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	IP20	910505100875	DN571B LED24S/840 DIA-VLC-E C WH	IP20
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	IP20	910505100886	DN571B LED40S/830 PSU-E C WH	IP20
910505100884	DN570B LED40S/830 PSU-E C WH	IP20	910505100887	DN571B LED40S/840 PSU-E C WH	IP20
910505100885	DN570B LED40S/840 PSU-E C WH	IP20	910505100890	DN571B LED40S/830 DIA-VLC-E C WH	IP20
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	IP20	910505100891	DN571B LED40S/840 DIA-VLC-E C WH	IP20
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	IP20	910505102297	DN571B LED24S/830 WIA-E C WH	IP20
910505100903	DN570B LED60S/830 PSU-E C WH	IP20	910505102298	DN571B LED24S/840 WIA-E C WH	IP20
910505100904	DN570B LED60S/840 PSU-E C WH	IP20	910505102302	DN571B LED40S/830 WIA-E C WH	IP20
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	IP20	910505102303	DN571B LED40S/840 WIA-E C WH	IP20
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	IP20	910505102306	DN571B LED24S/930H PSU-E C WH	IP20
910505101204	DN570B LED12S/830 PSU-E C WH	IP20	910505102307	DN571B LED24S/940H PSU-E C WH	IP20
910505102295	DN570B LED24S/830 WIA-E C WH	IP20	910505100852	DN570B LED20S/830 PSU-E F WH	IP20
910505102296	DN570B LED24S/840 WIA-E C WH	IP20	910505100853	DN570B LED20S/840 PSU-E F WH	IP20
910505102299	DN570B LED40S/830 WIA-E C WH	IP20	910505100854	DN570B LED20S/830 PSU-E M WH	IP20

Order Code	Full Product Name	Ingress protection code
910505100855	DN570B LED20S/840 PSU-E M WH	IP20
910505100856	DN570B LED20S/830 PSU-E WR WH	IP20

Order Code	Full Product Name	Ingress protection code
910505100857	DN570B LED20S/840 PSU-E WR WH	IP20

Controls and dimming

Order Code	Full Product Name	Dimmable
910505100834	DN570B LED12S/830 PSU-E C EW WH	No
910505100835	DN570B LED12S/840 PSU-E C WH	No
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	Yes
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	Yes
910505100842	DN570B LED20S/830 PSU-E C WH	No
910505100843	DN570B LED20S/840 PSU-E C WH	No
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	No
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	No
910505100850	DN570B LED20S/830 PSU-E C PG WH	No
910505100851	DN570B LED20S/840 PSU-E C PG WH	No
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	Yes
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	Yes
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	Yes
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	Yes
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	Yes
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	Yes
910505100868	DN570B LED24S/830 PSU-E C WH	No
910505100869	DN570B LED24S/840 PSU-E C WH	No
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	Yes
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	Yes
910505100884	DN570B LED40S/830 PSU-E C WH	No
910505100885	DN570B LED40S/840 PSU-E C WH	No
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	Yes
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	Yes
910505100903	DN570B LED60S/830 PSU-E C WH	No
910505100904	DN570B LED60S/840 PSU-E C WH	No
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	Yes
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	Yes
910505101204	DN570B LED12S/830 PSU-E C WH	No
910505102295	DN570B LED24S/830 WIA-E C WH	Wireless Dim
910505102296	DN570B LED24S/840 WIA-E C WH	Wireless Dim
910505102299	DN570B LED40S/830 WIA-E C WH	Wireless Dim
910505102301	DN570B LED40S/840 WIA-E C WH	Wireless Dim
910505102304	DN570B LED24S/930H PSU-E C WH	No

Order Code	Full Product Name	Dimmable
910505102305	DN570B LED24S/940H PSU-E C WH	No
910505100836	DN571B LED12S/830 PSU-E C WH	No
910505100837	DN571B LED12S/840 PSU-E C WH	No
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	Yes
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	Yes
910505100846	DN571B LED20S/830 PSU-E C WH	No
910505100847	DN571B LED20S/840 PSU-E C WH	No
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	No
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	No
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	Yes
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	Yes
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	Yes
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	Yes
910505100870	DN571B LED24S/830 PSU-E C WH	No
910505100871	DN571B LED24S/840 PSU-E C WH	No
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	Yes
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	Yes
910505100886	DN571B LED40S/830 PSU-E C WH	No
910505100887	DN571B LED40S/840 PSU-E C WH	No
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	Yes
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	Yes
910505102297	DN571B LED24S/830 WIA-E C WH	Wireless Dim
910505102298	DN571B LED24S/840 WIA-E C WH	Wireless Dim
910505102302	DN571B LED40S/830 WIA-E C WH	Wireless Dim
910505102303	DN571B LED40S/840 WIA-E C WH	Wireless Dim
910505102306	DN571B LED24S/930H PSU-E C WH	No
910505102307	DN571B LED24S/940H PSU-E C WH	No
910505100852	DN570B LED20S/830 PSU-E F WH	No
910505100853	DN570B LED20S/840 PSU-E F WH	No
910505100854	DN570B LED20S/830 PSU-E M WH	No
910505100855	DN570B LED20S/840 PSU-E M WH	No
910505100856	DN570B LED20S/830 PSU-E WR WH	No
910505100857	DN570B LED20S/840 PSU-E WR WH	No

General information

Order Code	Full Product			Product	
	Name	Glow-wire test	Optic type	Family Code	Service tag
910505100834	DN570B LED12S/830 PSU-E C EW WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes

Order Code	Full Product			Product	
	Name	Glow-wire test	Optic type	Family Code	Service tag
910505100835	DN570B LED12S/840 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100838	DN570B LED12S/830	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes

Order Code	Full Product			Product	
	Name	Glow-wire test	Optic type	Family Code	Service tag
	DIA-VLC-E C WH				
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100842	DN570B LED20S/830 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100843	DN570B LED20S/840 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100850	DN570B LED20S/830 PSU-E C PG WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100851	DN570B LED20S/840 PSU-E C PG WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100863	DN570B LED20S/840	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes

Order Code	Full Product			Product	
	Name	Glow-wire test	Optic type	Family Code	Service tag
	DIA-VLC-E C PG WH				
910505100868	DN570B LED24S/830 PSU-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN570B	Yes
910505100869	DN570B LED24S/840 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100884	DN570B LED40S/830 PSU-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN570B	Yes
910505100885	DN570B LED40S/840 PSU-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN570B	Yes
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100903	DN570B LED60S/830 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100904	DN570B LED60S/840 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505101204	DN570B LED12S/830 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	-
910505102295	DN570B LED24S/830 WIA-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN570B	-

Order Code	Full Product			Product	
	Name	Glow-wire test	Optic type	Family Code	Service tag
910505102296	DN570B LED24S/840 WIA-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN570B	-
910505102299	DN570B LED40S/830 WIA-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN570B	-
910505102301	DN570B LED40S/840 WIA-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN570B	-
910505102304	DN570B LED24S/930H PSU-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN570B	-
910505102305	DN570B LED24S/940H PSU-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN570B	-
910505100836	DN571B LED12S/830 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100837	DN571B LED12S/840 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100846	DN571B LED20S/830 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100847	DN571B LED20S/840 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100865	DN571B LED20S/840	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes

Order Code	Full Product			Product	
	Name	Glow-wire test	Optic type	Family Code	Service tag
	DIA-VLC-E C WH				
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100870	DN571B LED24S/830 PSU-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN571B	Yes
910505100871	DN571B LED24S/840 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100886	DN571B LED40S/830 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100887	DN571B LED40S/840 PSU-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN571B	Yes
910505102297	DN571B LED24S/830 WIA-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN571B	-
910505102298	DN571B LED24S/840 WIA-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN571B	-
910505102302	DN571B LED40S/830 WIA-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN571B	-
910505102303	DN571B LED40S/840 WIA-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN571B	-

Order Code	Full Product			Product	
	Name	Glow-wire test	Optic type	Family Code	Service tag
910505102306	DN571B LED24S/930H PSU-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN571B	-
910505102307	DN571B LED24S/940H PSU-E C WH	Temperature 650 °C, duration 30 s	High-gloss mirror	DN571B	-
910505100852	DN570B LED20S/830 PSU-E F WH	Temperature 850 °C, duration 5 s	Facetted reflector	DN570B	Yes
910505100853	DN570B LED20S/840 PSU-E F WH	Temperature 850 °C, duration 5 s	Facetted reflector	DN570B	Yes

Order Code	Full Product			Product	
	Name	Glow-wire test	Optic type	Family Code	Service tag
910505100854	DN570B LED20S/830 PSU-E M WH	Temperature 850 °C, duration 5 s	Matt optic decorative	DN570B	Yes
910505100855	DN570B LED20S/840 PSU-E M WH	Temperature 850 °C, duration 5 s	Matt optic decorative	DN570B	Yes
910505100856	DN570B LED20S/830 PSU-E WR WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes
910505100857	DN570B LED20S/840 PSU-E WR WH	Temperature 850 °C, duration 5 s	High-gloss mirror	DN570B	Yes

Initial performance (IEC compliant) (1/2)

Order Code	Full Product		Init. Corr.	Init. Color	Initial LED
	Name	Initial chromaticity	Color Temperature	Rendering Index	luminaire efficacy
910505100834	DN570B LED12S/830 PSU-E C EW WH	(0.43, 0.40) SDCM <2	3000 K	>80	131 lm/W
910505100835	DN570B LED12S/840 PSU-E C WH	(0.38, 0.38) SDCM <2	4000 K	>80	141 lm/W
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM <2	3000 K	>80	131 lm/W
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2	4000 K	>80	141 lm/W
910505100842	DN570B LED20S/830 PSU-E C WH	(0.43, 0.40) SDCM <2	3000 K	>80	134 lm/W
910505100843	DN570B LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM <2	4000 K	>80	149 lm/W
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40) SDCM <2	3000 K	>80	113 lm/W
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38) SDCM <2	4000 K	>80	124 lm/W
910505100850	DN570B LED20S/830	(0.43, 0.40) SDCM <2	3000 K	>80	134 lm/W

Order Code	Full Product		Init. Corr.	Init. Color	Initial LED
	Name	Initial chromaticity	Color Temperature	Rendering Index	luminaire efficacy
910505100851	DN570B LED20S/840 PSU-E C PG WH	(0.38, 0.38) SDCM <2	4000 K	>80	149 lm/W
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM <2	3000 K	>80	134 lm/W
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2	4000 K	>80	149 lm/W
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40) SDCM <2	3000 K	>80	113 lm/W
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38) SDCM <2	4000 K	>80	124 lm/W
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	(0.43, 0.40) SDCM <2	3000 K	>80	134 lm/W
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	(0.38, 0.38) SDCM <2	4000 K	>80	149 lm/W

LuxSpace, recessed

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910505100868	DN570B LED24S/830 PSU-E C WH	(0.43, 0.40)	3000 K	>80	130 lm/W
910505100869	DN570B LED24S/840 PSU-E C WH	(0.38, 0.38)	4000 K	>80	141 lm/W
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	>80	130 lm/W
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	>80	141 lm/W
910505100884	DN570B LED40S/830 PSU-E C WH	(0.43, 0.40)	3000 K	>80	133 lm/W
910505100885	DN570B LED40S/840 PSU-E C WH	(0.38, 0.38)	4000 K	>80	147 lm/W
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	>80	133 lm/W
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	>80	147 lm/W
910505100903	DN570B LED60S/830 PSU-E C WH	(0.43, 0.40)	3000 K	>80	129 lm/W
910505100904	DN570B LED60S/840 PSU-E C WH	(0.38, 0.38)	4000 K	>80	141 lm/W
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	>80	129 lm/W
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	>80	141 lm/W
910505101204	DN570B LED12S/830 PSU-E C WH	(0.43, 0.40)	3000 K	>80	131 lm/W
910505102295	DN570B LED24S/830 WIA-E C WH	(0.43, 0.40)	3000 K	>80	130 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910505102296	DN570B LED24S/840 WIA-E C WH	(0.38, 0.38)	4000 K	>80	130 lm/W
910505102299	DN570B LED40S/830 WIA-E C WH	(0.43, 0.40)	3000 K	>80	133 lm/W
910505102301	DN570B LED40S/840 WIA-E C WH	(0.38, 0.38)	4000 K	>80	147 lm/W
910505102304	DN570B LED24S/ 930H PSU-E C WH	(0.43, 0.40)	3000 K	>90	130 lm/W
910505102305	DN570B LED24S/ 940H PSU-E C WH	(0.38, 0.38)	4000 K	>90	133 lm/W
910505100836	DN571B LED12S/830 PSU-E C WH	(0.43, 0.40)	3000 K	>80	131 lm/W
910505100837	DN571B LED12S/840 PSU-E C WH	(0.38, 0.38)	4000 K	>80	141 lm/W
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	>80	131 lm/W
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	>80	141 lm/W
910505100846	DN571B LED20S/830 PSU-E C WH	(0.43, 0.40)	3000 K	>80	134 lm/W
910505100847	DN571B LED20S/840 PSU-E C WH	(0.38, 0.38)	4000 K	>80	149 lm/W
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40)	3000 K	>80	113 lm/W
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38)	4000 K	>80	124 lm/W
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	>80	134 lm/W

LuxSpace, recessed

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	>80	149 lm/W
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40)	3000 K	>80	113 lm/W
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38)	4000 K	>80	124 lm/W
910505100870	DN571B LED24S/830 PSU-E C WH	(0.43, 0.40)	3000 K	>80	130 lm/W
910505100871	DN571B LED24S/840 PSU-E C WH	(0.38, 0.38)	4000 K	>80	141 lm/W
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	>80	130 lm/W
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	>80	141 lm/W
910505100886	DN571B LED40S/830 PSU-E C WH	(0.43, 0.40)	3000 K	>80	133 lm/W
910505100887	DN571B LED40S/840 PSU-E C WH	(0.38, 0.38)	4000 K	>80	147 lm/W
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40)	3000 K	>80	133 lm/W
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38)	4000 K	>80	147 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910505102297	DN571B LED24S/830 WIA-E C WH	(0.43, 0.40)	3000 K	>80	130 lm/W
910505102298	DN571B LED24S/840 WIA-E C WH	(0.38, 0.38)	4000 K	>80	130 lm/W
910505102302	DN571B LED40S/830 WIA-E C WH	(0.43, 0.40)	3000 K	>80	133 lm/W
910505102303	DN571B LED40S/840 WIA-E C WH	(0.38, 0.38)	4000 K	>80	147 lm/W
910505102306	DN571B LED24S/930H PSU-E C WH	(0.43, 0.40)	3000 K	>90	130 lm/W
910505102307	DN571B LED24S/940H PSU-E C WH	(0.38, 0.38)	4000 K	>90	133 lm/W
910505100852	DN570B LED20S/830 PSU-E F WH	(0.43, 0.40)	3000 K	>80	134 lm/W
910505100853	DN570B LED20S/840 PSU-E F WH	(0.38, 0.38)	4000 K	>80	149 lm/W
910505100854	DN570B LED20S/830 PSU-E M WH	(0.43, 0.40)	3000 K	>80	113 lm/W
910505100855	DN570B LED20S/840 PSU-E M WH	(0.38, 0.38)	4000 K	>80	127 lm/W
910505100856	DN570B LED20S/830 PSU-E WR WH	(0.43, 0.40)	3000 K	>80	134 lm/W
910505100857	DN570B LED20S/840 PSU-E WR WH	(0.38, 0.38)	4000 K	>80	149 lm/W

Initial performance (IEC compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Initial input power
910505100834	DN570B LED12S/830 PSU-E C EW WH	1300 lm	9.9 W
910505100835	DN570B LED12S/840 PSU-E C WH	1300 lm	9.2 W
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	1300 lm	9.9 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	1300 lm	9.2 W
910505100842	DN570B LED20S/830 PSU-E C WH	2200 lm	16.4 W
910505100843	DN570B LED20S/840 PSU-E C WH	2200 lm	14.8 W

LuxSpace, recessed

Order Code	Full Product Name	Initial luminous flux	Initial input power
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	2200 lm	19.4 W
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	2200 lm	17.8 W
910505100850	DN570B LED20S/830 PSU-E C PG WH	2200 lm	16.4 W
910505100851	DN570B LED20S/840 PSU-E C PG WH	2200 lm	14.8 W
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	2200 lm	16.4 W
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	2200 lm	14.8 W
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	2200 lm	19.4 W
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	2200 lm	17.8 W
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	2200 lm	16.4 W
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	2200 lm	14.8 W
910505100868	DN570B LED24S/830 PSU-E C WH	2600 lm	20 W
910505100869	DN570B LED24S/840 PSU-E C WH	2600 lm	18.4 W
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	2600 lm	20 W
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	2600 lm	18.4 W
910505100884	DN570B LED40S/830 PSU-E C WH	4400 lm	33 W
910505100885	DN570B LED40S/840 PSU-E C WH	4400 lm	30 W
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	4400 lm	33 W
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	4400 lm	30 W
910505100903	DN570B LED60S/830 PSU-E C WH	6200 lm	48 W
910505100904	DN570B LED60S/840 PSU-E C WH	6200 lm	44 W
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	6200 lm	48 W
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	6200 lm	44 W
910505101204	DN570B LED12S/830 PSU-E C WH	1300 lm	9.9 W
910505102295	DN570B LED24S/830 WIA-E C WH	2600 lm	20 W
910505102296	DN570B LED24S/840 WIA-E C WH	2600 lm	20 W
910505102299	DN570B LED40S/830 WIA-E C WH	4400 lm	33 W
910505102301	DN570B LED40S/840 WIA-E C WH	4400 lm	30 W
910505102304	DN570B LED24S/930H PSU-E C WH	2600 lm	20 W
910505102305	DN570B LED24S/940H PSU-E C WH	2600 lm	20 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910505100836	DN571B LED12S/830 PSU-E C WH	1300 lm	9.9 W
910505100837	DN571B LED12S/840 PSU-E C WH	1300 lm	9.2 W
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	1300 lm	9.9 W
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	1300 lm	9.2 W
910505100846	DN571B LED20S/830 PSU-E C WH	2200 lm	16.4 W
910505100847	DN571B LED20S/840 PSU-E C WH	2200 lm	14.8 W
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	2200 lm	19.4 W
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	2200 lm	17.8 W
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	2200 lm	16.4 W
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	2200 lm	14.8 W
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	2200 lm	19.4 W
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	2200 lm	17.8 W
910505100870	DN571B LED24S/830 PSU-E C WH	2600 lm	20 W
910505100871	DN571B LED24S/840 PSU-E C WH	2600 lm	18.4 W
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	2600 lm	20 W
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	2600 lm	18.4 W
910505100886	DN571B LED40S/830 PSU-E C WH	4400 lm	33 W
910505100887	DN571B LED40S/840 PSU-E C WH	4400 lm	30 W
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	4400 lm	33 W
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	4400 lm	30 W
910505102297	DN571B LED24S/830 WIA-E C WH	2600 lm	20 W
910505102298	DN571B LED24S/840 WIA-E C WH	2600 lm	20 W
910505102302	DN571B LED40S/830 WIA-E C WH	4400 lm	33 W
910505102303	DN571B LED40S/840 WIA-E C WH	4400 lm	30 W
910505102306	DN571B LED24S/930H PSU-E C WH	2600 lm	20 W
910505102307	DN571B LED24S/940H PSU-E C WH	2600 lm	20 W
910505100852	DN570B LED20S/830 PSU-E F WH	2200 lm	16.4 W
910505100853	DN570B LED20S/840 PSU-E F WH	2200 lm	14.8 W
910505100854	DN570B LED20S/830 PSU-E M WH	1860 lm	16.4 W
910505100855	DN570B LED20S/840 PSU-E M WH	1860 lm	14.8 W
910505100856	DN570B LED20S/830 PSU-E WR WH	2200 lm	16.4 W
910505100857	DN570B LED20S/840 PSU-E WR WH	2200 lm	14.8 W

Light technical

Order Code	Full Product Name	Stroboscopic effect
910505100834	DN570B LED12S/830 PSU-E C EW WH	-
910505100835	DN570B LED12S/840 PSU-E C WH	-

Order Code	Full Product Name	Stroboscopic effect
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	-
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	-

LuxSpace, recessed

Order Code	Full Product Name	Stroboscopic effect
910505100842	DN570B LED20S/830 PSU-E C WH	-
910505100843	DN570B LED20S/840 PSU-E C WH	-
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	-
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	-
910505100850	DN570B LED20S/830 PSU-E C PG WH	-
910505100851	DN570B LED20S/840 PSU-E C PG WH	-
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	-
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	-
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	-
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	-
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	-
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	-
910505100868	DN570B LED24S/830 PSU-E C WH	0.4
910505100869	DN570B LED24S/840 PSU-E C WH	-
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	-
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	-
910505100884	DN570B LED40S/830 PSU-E C WH	0.4
910505100885	DN570B LED40S/840 PSU-E C WH	0.4
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	-
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	-
910505100903	DN570B LED60S/830 PSU-E C WH	-
910505100904	DN570B LED60S/840 PSU-E C WH	-
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	-
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	-
910505101204	DN570B LED12S/830 PSU-E C WH	-
910505102295	DN570B LED24S/830 WIA-E C WH	0.5
910505102296	DN570B LED24S/840 WIA-E C WH	0.5
910505102299	DN570B LED40S/830 WIA-E C WH	0.5
910505102301	DN570B LED40S/840 WIA-E C WH	0.5
910505102304	DN570B LED24S/930H PSU-E C WH	0.4
910505102305	DN570B LED24S/940H PSU-E C WH	0.4
910505100836	DN571B LED12S/830 PSU-E C WH	-

Order Code	Full Product Name	Stroboscopic effect
910505100837	DN571B LED12S/840 PSU-E C WH	-
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	-
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	-
910505100846	DN571B LED20S/830 PSU-E C WH	-
910505100847	DN571B LED20S/840 PSU-E C WH	-
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	-
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	-
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	-
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	-
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	-
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	-
910505100870	DN571B LED24S/830 PSU-E C WH	0.4
910505100871	DN571B LED24S/840 PSU-E C WH	-
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	-
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	-
910505100886	DN571B LED40S/830 PSU-E C WH	-
910505100887	DN571B LED40S/840 PSU-E C WH	-
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	-
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	-
910505102297	DN571B LED24S/830 WIA-E C WH	0.5
910505102298	DN571B LED24S/840 WIA-E C WH	0.5
910505102302	DN571B LED40S/830 WIA-E C WH	0.5
910505102303	DN571B LED40S/840 WIA-E C WH	0.5
910505102306	DN571B LED24S/930H PSU-E C WH	0.4
910505102307	DN571B LED24S/940H PSU-E C WH	0.4
910505100852	DN570B LED20S/830 PSU-E F WH	-
910505100853	DN570B LED20S/840 PSU-E F WH	-
910505100854	DN570B LED20S/830 PSU-E M WH	-
910505100855	DN570B LED20S/840 PSU-E M WH	-
910505100856	DN570B LED20S/830 PSU-E WR WH	-
910505100857	DN570B LED20S/840 PSU-E WR WH	-

