



PL-C is an efficient medium-wattage compact fluorescent lamp

PL-C consumer products

The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base. Not suitable for dimming.

Benefits

- Reliable and hassle free
- Good color rendering (CRI >80)

Features

- 2-pin base with a housing incorporating the special instant starter
- Low light depreciation over lamp life
- Long life performance

Application

- Suitable for luminaire specially designed for PL-S 2 pin lamps which can include downlighters, wall units, table and desk lamps, pendant lamps and outdoor lighting.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


PL-C consumer products

Versions



26W, G24d-3, 2P

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 26W/840/2P 1BC/6	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

