



TrueLine, recessed - True line of light: elegant, energy- efficient and compliant with office lighting norms

TrueLine, recessed

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. TrueLine, recessed is able to meet both sets of requirements. TrueLine is also available in suspended and surface-mounted versions.

Benefits

- The most uniform exit window
- Extremely high efficacy for a line luminaire
- Luminaire housing dimensions that are most popular with architects

TrueLine, recessed

Features

- Luminous efficacy > 100 lm/W
- Complies with office lighting norms
- Stand-alone and continuous lines
- Suspended version also available
- Direct and indirect light
- Homogeneous exit window
- Future-proof: PoE

Application

- General lighting for mid- and high-end office buildings

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If The above advice is not taken and The luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Versions



TrueLine recessed-RC532B L1130





TrueLine Recessed-U3











TrueLine Recessed-U0

Dimensional drawing




Dimensional drawing



TrueLine, recessed

Dimensional drawing



Product details

TrueLine_recessed-
RC530B_PCV_L1130-DP.tif



TrueLine-
RC530_RC531_RC534B_VPC-
DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-1DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-2DPP.tif



TrueLine-
RC530_RC531_RC534B_VPC_PI5-
DPP.tif



TrueLine-
RC534B_SM534C_SP534P-DPP.tif



TrueLine, recessed

Product details

TrueLine_Recessed-U3



TrueLine_Recessed-U0



General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit

Light Technical

Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	0.4

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application

CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Mech. impact protection code	IK02
Ingress protection code	IP20

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Application Conditions

Maximum dim level	1%
Suitable for random switching	No

General Information

Order Code	Full Product Name	Product family code
910505103101	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	RC530B
910505103102	RC532B LED25S/940 PSD W8L113 VPC PI5	RC532B
910505103103	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	RC531B
910505103104	RC530B LED15S/940 PSD W8L113 PCV PI5	RC530B
910505103105	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	RC530B
910505103106	RC532B LED19S/940 PSD W8L141 PCV PI5	RC532B
910505103107	RC530B LED31S/940 PSD W8L141 PCV PI5	RC530B
910505103109	RC533B LED15S/940 PSD W8L113 PCV PI5	RC533B
910505103110	RC530B LED43S/940 PSD W8L141 PCV PI5	RC530B
910505103111	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	RC531B
910505103112	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	RC531B
910505103113	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	RC530B
910505103114	RC530B LED19S/940 PSD W8L141 PCV PI5	RC530B
910505103115	RC530B LED34S/940 PSD W8L113 PCV PI5	RC530B
910505103116	RC531B LED15S/930 PSD W8L113 PCV PI5	RC531B
910505103117	RC531B LED15S/940 PSD W8L113 PCV PI5	RC531B
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	RC532B
910505103119	RC532B LED25S/940 PSD W8L113 PCV PI5	RC532B
910505103121	RC531B LED31S/940 PSD W8L141 PCV PI5	RC531B
910505103126	RC533B LED31S/940 PSD W8L141 PCV PI5	RC533B
910505103127	RC530B LED50S/940 PSD W8L141 PCV PI5	RC530B
910505103129	RC531B LED19S/940 PSD W8L141 PCV PI5	RC531B
910505103131	RC533B LED19S/940 PSD W8L141 PCV PI5	RC533B
910505103149	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	RC530B
910505103150	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	RC530B
910505103284	RC530B LED34S/TW9 DIA W8L113 PCV PI5	RC530B
910505103286	RC530B LED40S/TW9 DIA W8L113 PCV PI5	RC530B
910505103287	RC530B LED50S/TW9 DIA W8L145 PCV PI5	RC530B
910505103292	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	RC530B
910505103293	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	RC530B
910505103122	RC532B LED31S/940 PSD W8L141 PCV PI5	RC532B
910505103124	RC532B LED43S/940 PSD W8L141 PCV PI5	RC532B
910505103138	RC531B LED31S/940 W8L150 VPC ELP3 PI6	RC531B
910505103140	RC531B LED19S/940 W8L150 VPC ELP3 PI6	RC531B
910505103141	RC530B LED50S/940 W8L150 VPC ELP3 PI6	RC530B
910505103144	RC530B LED43S/940 W8L150 VPC ELP3 PI6	RC530B
910505103154	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	RC530B

Order Code	Full Product Name	Product family code
910505103135	RC530B LED43S/940 W8L145 PCV ELP3 PI6	RC530B
910505103136	RC530B LED50S/940 W8L145 PCV ELP3 PI6	RC530B
910505103139	RC531B LED19S/940 W8L145 PCV ELP3 PI6	RC531B
910505103145	RC531B LED31S/940 W8L145 PCV ELP3 PI6	RC531B
910505103153	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	RC531B
910505103120	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	RC534B
910505103123	RC534B LED50S/940 PSD W8L141 PCV PI5	RC534B
910505103128	RC534B LED43S/940 PSD W8L141 PCV PI5	RC534B
910505103125	RC535B LED50S/940 PSD W8L141 PCV PI5	RC535B
910505103130	RC535B LED43S/940 PSD W8L141 PCV PI5	RC535B
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	RC530B
910505103155	RC532B LED43S/940 SRD W8L145 PCV U4 W	RC532B
910505103156	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	RC530B
910505103157	RC530B LED34S/930 SRD W8L120 VPC U4 W	RC530B
910505103158	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	RC530B
910505103159	RC530B LED25S/930 SRD W8L120 VPC U4 W	RC530B
910505103160	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	RC530B
910505103285	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	RC530B
910505103288	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	RC530B
910505103289	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	RC530B
910505103290	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	RC534B
910505103291	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	RC530B
910505103147	RC530B LED40S/940 POE W8L120 VPC U0	RC530B

Light Technical

Order Code	Full Product Name	Beam angle of	
		light source	Optic type
910505103101	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	- degree(s)	Wide beam
910505103102	RC532B LED25S/940 PSD W8L113 VPC PI5	- degree(s)	Wide beam
910505103103	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	- degree(s)	Wide beam
910505103104	RC530B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	Wide beam
910505103105	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	- degree(s)	Wide beam
910505103106	RC532B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103107	RC530B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103109	RC533B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	Wide beam
910505103110	RC530B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103111	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	- degree(s)	Wide beam
910505103112	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	- degree(s)	Wide beam
910505103113	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	- degree(s)	Wide beam

Order Code	Full Product Name	Beam angle of	
		light source	Optic type
910505103114	RC530B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103115	RC530B LED34S/940 PSD W8L113 PCV PI5	- degree(s)	Wide beam
910505103116	RC531B LED15S/930 PSD W8L113 PCV PI5	- degree(s)	Wide beam
910505103117	RC531B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	Wide beam
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	Wide beam
910505103119	RC532B LED25S/940 PSD W8L113 PCV PI5	- degree(s)	Wide beam
910505103121	RC531B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103126	RC533B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103127	RC530B LED50S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103129	RC531B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103131	RC533B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103149	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	- degree(s)	Wide beam

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Optic type
910505103150	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	- degree(s)	Wide beam
910505103284	RC530B LED34S/TW9 DIA W8L113 PCV PI5	120 degree(s)	Wide beam
910505103286	RC530B LED40S/TW9 DIA W8L113 PCV PI5	120 degree(s)	Wide beam
910505103287	RC530B LED50S/TW9 DIA W8L145 PCV PI5	120 degree(s)	Wide beam
910505103292	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	120 degree(s)	Wide beam
910505103293	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	120 degree(s)	Wide beam
910505103122	RC532B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103124	RC532B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	Wide beam
910505103138	RC531B LED31S/940 W8L150 VPC ELP3 PI6	- degree(s)	Wide beam
910505103140	RC531B LED19S/940 W8L150 VPC ELP3 PI6	- degree(s)	Wide beam
910505103141	RC530B LED50S/940 W8L150 VPC ELP3 PI6	- degree(s)	Wide beam
910505103144	RC530B LED43S/940 W8L150 VPC ELP3 PI6	- degree(s)	Wide beam
910505103154	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	- degree(s)	Wide beam
910505103135	RC530B LED43S/940 W8L145 PCV ELP3 PI6	- degree(s)	Wide beam
910505103136	RC530B LED50S/940 W8L145 PCV ELP3 PI6	- degree(s)	Wide beam
910505103139	RC531B LED19S/940 W8L145 PCV ELP3 PI6	- degree(s)	Wide beam
910505103145	RC531B LED31S/940 W8L145 PCV ELP3 PI6	- degree(s)	Wide beam
910505103153	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	- degree(s)	Wide beam

Order Code	Full Product Name	Beam angle of light source	Optic type
910505103120	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	- degree(s)	Asymmetrical mirror
910505103123	RC534B LED50S/940 PSD W8L141 PCV PI5	- degree(s)	Asymmetrical mirror
910505103128	RC534B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	Asymmetrical mirror
910505103125	RC535B LED50S/940 PSD W8L141 PCV PI5	- degree(s)	Asymmetrical mirror
910505103130	RC535B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	Asymmetrical mirror
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	- degree(s)	Wide beam
910505103155	RC532B LED43S/940 SRD W8L145 PCV U4 W	- degree(s)	Wide beam
910505103156	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	- degree(s)	Wide beam
910505103157	RC530B LED34S/930 SRD W8L120 VPC U4 W	- degree(s)	Wide beam
910505103158	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	- degree(s)	Wide beam
910505103159	RC530B LED25S/930 SRD W8L120 VPC U4 W	- degree(s)	Wide beam
910505103160	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	- degree(s)	Wide beam
910505103285	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	120 degree(s)	Wide beam
910505103288	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	120 degree(s)	Wide beam
910505103289	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	120 degree(s)	Wide beam
910505103290	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	120 degree(s)	Wide beam
910505103291	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	120 degree(s)	Wide beam
910505103147	RC530B LED40S/940 POE W8L120 VPC U0	- degree(s)	Wide beam

Operating and Electrical

Order Code	Full Product Name	Input Voltage
910505103101	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	220 to 240 V
910505103102	RC532B LED25S/940 PSD W8L113 VPC PI5	220 to 240 V
910505103103	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	220 to 240 V
910505103104	RC530B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V
910505103105	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	220 to 240 V
910505103106	RC532B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103107	RC530B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103109	RC533B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V
910505103110	RC530B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103111	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	220 to 240 V
910505103112	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	220 to 240 V

Order Code	Full Product Name	Input Voltage
910505103113	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	220 to 240 V
910505103114	RC530B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103115	RC530B LED34S/940 PSD W8L113 PCV PI5	220 to 240 V
910505103116	RC531B LED15S/930 PSD W8L113 PCV PI5	220 to 240 V
910505103117	RC531B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V
910505103119	RC532B LED25S/940 PSD W8L113 PCV PI5	220 to 240 V
910505103121	RC531B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103126	RC533B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103127	RC530B LED50S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103129	RC531B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V

Order Code	Full Product Name	Input Voltage
910505103131	RC533B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103149	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	220 to 240 V
910505103150	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	220 to 240 V
910505103284	RC530B LED34S/TW9 DIA W8L113 PCV PI5	220 to 240 V
910505103286	RC530B LED40S/TW9 DIA W8L113 PCV PI5	220 to 240 V
910505103287	RC530B LED50S/TW9 DIA W8L145 PCV PI5	220 to 240 V
910505103292	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	220 to 240 V
910505103293	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	220 to 240 V
910505103122	RC532B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103124	RC532B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103138	RC531B LED31S/940 W8L150 VPC ELP3 PI6	220 to 240 V
910505103140	RC531B LED19S/940 W8L150 VPC ELP3 PI6	220 to 240 V
910505103141	RC530B LED50S/940 W8L150 VPC ELP3 PI6	220 to 240 V
910505103144	RC530B LED43S/940 W8L150 VPC ELP3 PI6	220 to 240 V
910505103154	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	220 to 240 V
910505103135	RC530B LED43S/940 W8L145 PCV ELP3 PI6	220 to 240 V
910505103136	RC530B LED50S/940 W8L145 PCV ELP3 PI6	220 to 240 V
910505103139	RC531B LED19S/940 W8L145 PCV ELP3 PI6	220 to 240 V
910505103145	RC531B LED31S/940 W8L145 PCV ELP3 PI6	220 to 240 V

Order Code	Full Product Name	Input Voltage
910505103153	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	220 to 240 V
910505103120	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	220 to 240 V
910505103123	RC534B LED50S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103128	RC534B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103125	RC535B LED50S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103130	RC535B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	51 to 54 V
910505103155	RC532B LED43S/940 SRD W8L145 PCV U4 W	220 to 240 V
910505103156	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	220 to 240 V
910505103157	RC530B LED34S/930 SRD W8L120 VPC U4 W	220 to 240 V
910505103158	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	220 to 240 V
910505103159	RC530B LED25S/930 SRD W8L120 VPC U4 W	220 to 240 V
910505103160	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	220 to 240 V
910505103285	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	220 to 240 V
910505103288	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	220 to 240 V
910505103289	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	220 to 240 V
910505103290	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	220 to 240 V
910505103291	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	220 to 240 V
910505103147	RC530B LED40S/940 POE W8L120 VPC U0	51 to 54 V

Approval and Application

Order Code	Full Product Name	Protection class IEC
910505103101	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	Safety class I
910505103102	RC532B LED25S/940 PSD W8L113 VPC PI5	Safety class I
910505103103	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	Safety class I
910505103104	RC530B LED15S/940 PSD W8L113 PCV PI5	Safety class I
910505103105	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	Safety class I
910505103106	RC532B LED19S/940 PSD W8L141 PCV PI5	Safety class I
910505103107	RC530B LED31S/940 PSD W8L141 PCV PI5	Safety class I
910505103109	RC533B LED15S/940 PSD W8L113 PCV PI5	Safety class I
910505103110	RC530B LED43S/940 PSD W8L141 PCV PI5	Safety class I
910505103111	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	Safety class I
910505103112	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	Safety class I
910505103113	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	Safety class I
910505103114	RC530B LED19S/940 PSD W8L141 PCV PI5	Safety class I
910505103115	RC530B LED34S/940 PSD W8L113 PCV PI5	Safety class I
910505103116	RC531B LED15S/930 PSD W8L113 PCV PI5	Safety class I
910505103117	RC531B LED15S/940 PSD W8L113 PCV PI5	Safety class I
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	Safety class I
910505103119	RC532B LED25S/940 PSD W8L113 PCV PI5	Safety class I
910505103121	RC531B LED31S/940 PSD W8L141 PCV PI5	Safety class I
910505103126	RC533B LED31S/940 PSD W8L141 PCV PI5	Safety class I
910505103127	RC530B LED50S/940 PSD W8L141 PCV PI5	Safety class I
910505103129	RC531B LED19S/940 PSD W8L141 PCV PI5	Safety class I
910505103131	RC533B LED19S/940 PSD W8L141 PCV PI5	Safety class I
910505103149	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	Safety class I
910505103150	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	Safety class I
910505103284	RC530B LED34S/TW9 DIA W8L113 PCV PI5	Safety class I
910505103286	RC530B LED40S/TW9 DIA W8L113 PCV PI5	Safety class I
910505103287	RC530B LED50S/TW9 DIA W8L145 PCV PI5	Safety class I
910505103292	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	Safety class I

Order Code	Full Product Name	Protection class IEC
910505103293	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	Safety class I
910505103122	RC532B LED31S/940 PSD W8L141 PCV PI5	Safety class I
910505103124	RC532B LED43S/940 PSD W8L141 PCV PI5	Safety class I
910505103138	RC531B LED31S/940 W8L150 VPC ELP3 PI6	Safety class I
910505103140	RC531B LED19S/940 W8L150 VPC ELP3 PI6	Safety class I
910505103141	RC530B LED50S/940 W8L150 VPC ELP3 PI6	Safety class I
910505103144	RC530B LED43S/940 W8L150 VPC ELP3 PI6	Safety class I
910505103154	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	Safety class I
910505103135	RC530B LED43S/940 W8L145 PCV ELP3 PI6	Safety class I
910505103136	RC530B LED50S/940 W8L145 PCV ELP3 PI6	Safety class I
910505103139	RC531B LED19S/940 W8L145 PCV ELP3 PI6	Safety class I
910505103145	RC531B LED31S/940 W8L145 PCV ELP3 PI6	Safety class I
910505103153	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	Safety class I
910505103120	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	Safety class I
910505103123	RC534B LED50S/940 PSD W8L141 PCV PI5	Safety class I
910505103128	RC534B LED43S/940 PSD W8L141 PCV PI5	Safety class I
910505103125	RC535B LED50S/940 PSD W8L141 PCV PI5	Safety class I
910505103130	RC535B LED43S/940 PSD W8L141 PCV PI5	Safety class I
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	Safety class III
910505103155	RC532B LED43S/940 SRD W8L145 PCV U4 W	Safety class I
910505103156	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	Safety class I
910505103157	RC530B LED34S/930 SRD W8L120 VPC U4 W	Safety class I
910505103158	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	Safety class I
910505103159	RC530B LED25S/930 SRD W8L120 VPC U4 W	Safety class I
910505103160	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	Safety class I
910505103285	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	Safety class I
910505103288	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	Safety class I
910505103289	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	Safety class I
910505103290	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	Safety class I

TrueLine, recessed

Order Code	Full Product Name	Protection class IEC	Order Code	Full Product Name	Protection class IEC
910505103291	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	Safety class I	910505103147	RC530B LED40S/940 POE W8L120 VPC U0	Safety class III

