



TrueLine, suspended - True line of light: elegant, energy- efficient and compliant with office lighting norms

TrueLine, suspended

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. TrueLine, suspended is able to meet both sets of requirements. TrueLine is also available in recessed and surface-mounted versions.

Benefits

- The most uniform exit window
- Extremely high efficacy for a line luminaire
- Luminaire housing dimensions most favored by architects

TrueLine, suspended

Features

- Luminous efficacy > 100 lm/W
- Complies with office lighting norms
- Stand-alone and continuous lines
- Recessed version also available
- Direct and indirect light
- Homogeneous exit window
- Future-proof: PoE

Application

- General lighting for mid- and high-end office buildings

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If The above advice is not taken and The luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Versions



TrueLine-SP534P



TrueLine-SP530 L570 WH




TrueLine-SP530 L2810 BK




TrueLine-SP530 L570 Alu

Dimensional drawing




TrueLine, suspended





Dimensional drawing



1104













1344



TrueLine, suspended

Dimensional drawing



Product details



TrueLine_Suspended-line-side-view



TrueLine_Suspended-line-top-view

TrueLine, suspended

Product details



TrueLine Suspended black housing



TrueLine_Suspended-top-view



TrueLine_Suspended-U3



TrueLine_Suspended-U0



TrueLine Suspended-SP530P-LF-
power-cable-03



TrueLine-SP-line-U3



TrueLine Suspended black housing



TrueLine_SM_SP-line-connection-
side-view-2

TrueLine, suspended

General Information

Driver included	Yes
Light source replaceable	No

Light Technical

Beam angle of light source	120 degree(s)
Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	0.4

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application

CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Mech. impact protection code	IK02
Ingress protection code	IP20

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Application Conditions

Maximum dim level	1%
Suitable for random switching	No

General Information

Order Code	Full Product Name	Number of gear units	Product family code
910505103203	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	1 unit	SP532P
910505103206	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	1 unit	SP534P
910505103210	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	1 unit	SP532P
910505103213	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	1 unit	SP534P
910505103246	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	1 unit	SP530P
910505103248	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	1 unit	SP532P
910505103161	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP533P
910505103162	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	1 unit	SP532P
910505103163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP530P
910505103164	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103165	SP530P LED25S/940 POE SW2 L1130 ALU	1 unit	SP530P
910505103166	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP531P
910505103167	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP530P
910505103168	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103169	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103170	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103171	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP530P
910505103172	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	1 unit	SP533P
910505103173	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103174	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103175	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	1 unit	SP532P
910505103176	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	1 unit	SP533P
910505103177	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP534P
910505103180	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP533P
910505103181	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103182	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP533P
910505103183	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103185	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
910505103186	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP533P
910505103187	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
910505103188	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	1 unit	SP532P
910505103189	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	1 unit	SP532P
910505103191	SP530P LED31S/940 POE U3 SW2 L1450 ALU	1 unit	SP530P
910505103192	SP530P LED40S/940 POE U3 SW2 L1170 ALU	1 unit	SP530P
910505103193	SP530P LED40S/940 POE U0 SW2 L1170 ALU	1 unit	SP530P
910505103194	SP530P LED43S/940 POE U0 SW2 L1450 ALU	1 unit	SP530P
910505103196	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP530P
910505103184	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP534P
910505103245	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	1 unit	SP531P
910505103249	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	1 unit	SP533P
910505103256	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	1 unit	SP530P
910505103282	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	2 units	SP530P
910505103283	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	2 units	SP532P
910505103257	SP531P LED30S/930 SRD U4LFPI3 L2290 ALU	1 unit	SP531P
910505103260	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	1 unit	SP532P
910505103261	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	1 unit	SP533P
910505103263	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	1 unit	SP533P
910505103269	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	1 unit	SP530P
910505103273	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	1 unit	SP532P
910505103274	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	1 unit	SP533P
910505103258	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	1 unit	SP530P

Order Code	Full Product Name	Number of gear units	Product family code
910505103262	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	1 unit	SP532P
910505103270	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	1 unit	SP530P
910505103281	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	2 units	SP532P
910505103244	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	1 unit	SP530P
910505103247	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	1 unit	SP532P
910505103259	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	1 unit	SP530P
910505103271	SP531P LED62S/930 PSD PI5 SM2L2810 WH	1 unit	SP531P
910505103272	SP532P LED94S/940 PSD PI5 SM2L2810 WH	1 unit	SP532P
910505103197	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	1 unit	SP532P
910505103198	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	1 unit	SP531P
910505103199	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	1 unit	SP530P
910505103201	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	1 unit	SP532P
910505103202	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	1 unit	SP532P
910505103207	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	1 unit	SP532P
910505103204	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	1 unit	SP532P
910505103205	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	1 unit	SP532P
910505103208	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	1 unit	SP532P
910505103209	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	1 unit	SP534P
910505103211	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	1 unit	SP532P
910505103212	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	1 unit	SP532P
910505103279	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	1 unit	SP532P
910505103280	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	2 units	SP533P
910505103214	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	1 unit	SP532P
910505103215	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	1 unit	SP530P
910505103216	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	1 unit	SP532P

Light Technical

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
910505103203	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	Wide beam	910505103180	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	Wide beam
910505103206	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	Asymmetrical mirror	910505103181	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	Wide beam
910505103210	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	Wide beam	910505103182	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	Wide beam
910505103213	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	Asymmetrical mirror	910505103183	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	Wide beam
910505103246	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	Wide beam	910505103185	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	Wide beam
910505103248	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	Wide beam	910505103186	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	Wide beam
910505103161	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	Wide beam	910505103187	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	Wide beam
910505103162	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	Wide beam	910505103188	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	Wide beam
910505103163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	Wide beam	910505103189	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	Wide beam
910505103164	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	Wide beam	910505103191	SP530P LED31S/940 POE U3 SW2 L1450 ALU	Wide beam
910505103165	SP530P LED25S/940 POE SW2 L1130 ALU	Wide beam	910505103192	SP530P LED40S/940 POE U3 SW2 L1170 ALU	Wide beam
910505103166	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	Wide beam	910505103193	SP530P LED40S/940 POE U0 SW2 L1170 ALU	Wide beam
910505103167	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	Wide beam	910505103194	SP530P LED43S/940 POE U0 SW2 L1450 ALU	Wide beam
910505103168	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	Wide beam	910505103196	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	Wide beam
910505103169	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	Wide beam	910505103184	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	Asymmetrical mirror
910505103170	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	Wide beam	910505103245	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	Wide beam
910505103171	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	Wide beam	910505103249	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	Wide beam
910505103172	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	Wide beam	910505103256	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	Wide beam
910505103173	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	Wide beam	910505103282	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	Wide beam
910505103174	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	Wide beam	910505103283	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	Wide beam
910505103175	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	Wide beam	910505103257	SP531P LED30S/930 SRD U4LFIPI3 L2290 ALU	Wide beam
910505103176	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	Wide beam	910505103260	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	Wide beam
910505103177	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	Asymmetrical mirror	910505103261	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	Wide beam

Order Code	Full Product Name	Optic type
910505103263	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	Wide beam
910505103269	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	Wide beam
910505103273	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	Wide beam
910505103274	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	Wide beam
910505103258	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	Wide beam
910505103262	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	Wide beam
910505103270	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	Wide beam
910505103281	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	Wide beam
910505103244	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	Wide beam
910505103247	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	Wide beam
910505103259	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	Wide beam
910505103271	SP531P LED62S/930 PSD PI5 SM2L2810 WH	Wide beam
910505103272	SP532P LED94S/940 PSD PI5 SM2L2810 WH	Wide beam
910505103197	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	Wide beam
910505103198	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	Wide beam

Order Code	Full Product Name	Optic type
910505103199	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	Wide beam
910505103201	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	Wide beam
910505103202	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	Wide beam
910505103207	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	Wide beam
910505103204	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	Wide beam
910505103205	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	Wide beam
910505103208	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	Wide beam
910505103209	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	Asymmetrical mirror
910505103211	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	Wide beam
910505103212	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	Wide beam
910505103279	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	Wide beam
910505103280	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	Wide beam
910505103214	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	Wide beam
910505103215	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	Wide beam
910505103216	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	Wide beam

Operating and Electrical

Order Code	Full Product Name	Input Voltage
910505103203	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	220 to 240 V
910505103206	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	220 to 240 V
910505103210	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	220 to 240 V
910505103213	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	220 to 240 V
910505103246	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	220 to 240 V
910505103248	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	220 to 240 V
910505103161	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103162	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	220 to 240 V
910505103163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103164	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103165	SP530P LED25S/940 POE SW2 L1130 ALU	51 to 54 V
910505103166	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103167	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103168	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103169	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103170	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103171	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103172	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103173	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103174	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103175	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	220 to 240 V
910505103176	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	220 to 240 V
910505103177	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103180	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103181	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103182	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103183	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103185	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103186	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103187	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103188	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	220 to 240 V
910505103189	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	220 to 240 V
910505103191	SP530P LED31S/940 POE U3 SW2 L1450 ALU	51 to 54 V

Order Code	Full Product Name	Input Voltage
910505103192	SP530P LED40S/940 POE U3 SW2 L1170 ALU	51 to 54 V
910505103193	SP530P LED40S/940 POE U0 SW2 L1170 ALU	51 to 54 V
910505103194	SP530P LED43S/940 POE U0 SW2 L1450 ALU	51 to 54 V
910505103196	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V
910505103184	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505103245	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	220 to 240 V
910505103249	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	220 to 240 V
910505103256	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	220 to 240 V
910505103282	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	220 to 240 V
910505103283	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	220 to 240 V
910505103257	SP531P LED30S/930 SRD U4LFPI3 L2290 ALU	220 to 240 V
910505103260	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	220 to 240 V
910505103261	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	220 to 240 V
910505103263	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	220 to 240 V
910505103269	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	220 to 240 V
910505103273	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	220 to 240 V
910505103274	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	220 to 240 V
910505103258	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	220 to 240 V
910505103262	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	220 to 240 V
910505103270	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	220 to 240 V
910505103281	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	220 to 240 V
910505103244	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	220 to 240 V
910505103247	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	220 to 240 V
910505103259	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	220 to 240 V
910505103271	SP531P LED62S/930 PSD PI5 SM2L2810 WH	220 to 240 V
910505103272	SP532P LED94S/940 PSD PI5 SM2L2810 WH	220 to 240 V
910505103197	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	220 to 240 V
910505103198	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	220 to 240 V
910505103199	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	220 to 240 V
910505103201	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	220 to 240 V
910505103202	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	220 to 240 V
910505103207	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	220 to 240 V
910505103204	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	220 to 240 V

Order Code	Full Product Name	Input Voltage
910505103205	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	220 to 240 V
910505103208	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	220 to 240 V
910505103209	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	220 to 240 V
910505103211	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	220 to 240 V
910505103212	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	220 to 240 V

Order Code	Full Product Name	Input Voltage
910505103279	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	220 to 240 V
910505103280	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	220 to 240 V
910505103214	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	220 to 240 V
910505103215	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	220 to 240 V
910505103216	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	220 to 240 V

Approval and Application

Order Code	Full Product Name	Protection class IEC
910505103203	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	Safety class I
910505103206	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	Safety class I
910505103210	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	Safety class I
910505103213	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	Safety class I
910505103246	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	Safety class I
910505103248	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	Safety class I
910505103161	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103162	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	Safety class I
910505103163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103164	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103165	SP530P LED25S/940 POE SW2 L1130 ALU	Safety class III
910505103166	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103167	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103168	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103169	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103170	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103171	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103172	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	Safety class I
910505103173	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	Safety class I
910505103174	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	Safety class I
910505103175	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	Safety class I
910505103176	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	Safety class I
910505103177	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103180	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103181	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103182	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103183	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103185	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103186	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	Safety class I
910505103187	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103188	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	Safety class I
910505103189	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	Safety class I
910505103191	SP530P LED31S/940 POE U3 SW2 L1450 ALU	Safety class III
910505103192	SP530P LED40S/940 POE U3 SW2 L1170 ALU	Safety class III
910505103193	SP530P LED40S/940 POE U0 SW2 L1170 ALU	Safety class III
910505103194	SP530P LED43S/940 POE U0 SW2 L1450 ALU	Safety class III
910505103196	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	Safety class I
910505103184	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	Safety class I

Order Code	Full Product Name	Protection class IEC
910505103245	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	Safety class I
910505103249	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	Safety class I
910505103256	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	Safety class I
910505103282	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	Safety class I
910505103283	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	Safety class I
910505103257	SP531P LED30S/930 SRD U4LFIPI3 L2290 ALU	Safety class I
910505103260	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	Safety class I
910505103261	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	Safety class I
910505103263	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	Safety class I
910505103269	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	Safety class I
910505103273	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	Safety class I
910505103274	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	Safety class I
910505103258	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	Safety class I
910505103262	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	Safety class I
910505103270	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	Safety class I
910505103281	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	Safety class I
910505103244	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	Safety class I
910505103247	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	Safety class I
910505103259	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	Safety class I
910505103271	SP531P LED62S/930 PSD PI5 SM2L2810 WH	Safety class I
910505103272	SP532P LED94S/940 PSD PI5 SM2L2810 WH	Safety class I
910505103197	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	Safety class I
910505103198	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	Safety class I
910505103199	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	Safety class I
910505103201	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	Safety class I
910505103202	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	Safety class I
910505103207	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	Safety class I
910505103204	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	Safety class I
910505103205	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	Safety class I
910505103208	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	Safety class I
910505103209	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	Safety class I
910505103211	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	Safety class I
910505103212	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	Safety class I
910505103279	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	Safety class I
910505103280	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	Safety class I
910505103214	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	Safety class I
910505103215	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	Safety class I
910505103216	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	Safety class I

TrueLine, suspended



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2023, May 22 - data subject to change