



StreetSaver - save costs, enjoy quality

StreetSaver gen2

In order to comply with EU regulations passed in 2015, municipalities need to replace all mercury-based lamps with lamps that are mercury-free. However, municipalities often have limited budget to handle these huge replacement operations, especially in this period of economic austerity. At the same time, municipal authorities are facing tremendous pressure to save energy and to reduce light pollution of the night sky (many mercury installations have a transparent bowl, sending light everywhere). StreetSaver is an affordable, high-quality solution that enables municipalities to address all these issues by changing their mercury-based luminaires to LED systems – and importantly, it requires only limited investment.

Benefits

- Affordable LED post-top solution with good lighting performance
- High product quality and robust design
- Good lifespan thanks to mid-power LED and 4KV surge protection

Features

- Dedicated LED design
- Aluminum housing and polycarbonate flat glass
- Connection directly at the bottom of the pole thanks to its 6 m cable

Application

- Parks and plazas, pedestrian areas
- Commercial plazas, parking areas
- Residential areas

Specifications

Type	BPP008
Light source	Integral LED-module

Power	27 W
Beam angle	Not applicable

StreetSaver gen2

Luminous flux	2500 lm (4000 K)
	2300 lm 3000 K)
Luminaire efficacy	93 lm/W (4000 K)
	85 lm/W (3000 K)
Correlated Color	3000 or 4000 K
Temperature	
Color Rendering Index	> 70, 4000 K
	> 80, 3000 K
Useful life - L70B50	50,000 hours at 35 °C
Operating temperature range	-40 °C < T
Driver	Built-in (self ballasted LED-module)
Mains voltage	220-240 V / 50-60 Hz
Inrush current	2.56 A
Dimming	No
Optic	Symmetrical

Optical element	Wide-street optic
Optical cover	Polycarbonate bowl/ cover opal
Material	Housing: high-pressure, die-cast aluminum
	Optical cover: polycarbonate, opal
Color	Canopy: ultra-dark grey, approx RAL 7043 (GR)
Connection	6 m cable
Maintenance	No maintenance necessary
Installation	Top pole Ø 60 mm
	Pre-wired with 6 m cable enables connexion directly at the bottom of the pole
	Recommended mounting height: 3 - 6 m Projected area: 0.115 m²
Remarks	Luminaire is delivered 'ready-to-install', thanks to the 6 m cable that enable connexion directly at the junction box at the bottom of the pole

Versions



LED Module 2500 lm

Product details

StreetSaver_G2-DPP.tif



StreetSaver gen2

Approval and Application

Mech. impact protection code	IK08
Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV differential mode and 4 kV common mode

Controls and Dimming

Dimmable	No
----------	----

General Information

Luminaire light beam spread	-
CE mark	CE mark
Light source color	Neutral white
Optical cover/lens type	Acrylate micro-lens optic
Driver included	Yes
Flammability mark	-
Light source replaceable	No
Number of gear units	1 unit
Optic type	Symmetrical

Light Technical

Standard tilt angle side entry	0°
Standard tilt angle posttop	-
Upward light output ratio	0

Mechanical and Housing

Color	Aluminum and gray
-------	-------------------

General Information

Order Code	Full Product Name	Lamp family code
911401663403	BPP008 LED-MP 740 PSU I GR 60P	LED25
911401663503	BPP008 LED-MP 830 PSU I GR 60P	LED23

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Color		
		Init. Corr. Color Temperature	Rendering Index	Initial luminous flux
911401663403	BPP008 LED-MP 740 PSU I GR 60P	4000 K	70	2500 lm

Order Code	Full Product Name	Init. Color		
		Init. Corr. Color Temperature	Rendering Index	Initial luminous flux
911401663503	BPP008 LED-MP 830 PSU I GR 60P	3000 K	80	2300 lm

