



# A flexible and affordable retail toolbox

## GreenSpace Accent Pendant

Thanks to the GreenSpace Accent family, retailers and building operators can now easily make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Pendant can be installed on a regular 3C adaptor or onto a ceiling mount with track interface for quick and easy installation. The cable can be cut to length to perfectly match the installation height of the luminaire. For fashion and food retailers, GreenSpace Accent Pendant is available with special light flavors and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to discover more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

### Benefits

- Clean and robust design
- Full retail application coverage
- Lighting flexibility beyond CDM

### Features

- Driver integrated in a compact housing
- High quality of light enabled by the Philips PerfectAccent reflectors
- Light flavors for fashion and LED recipes for food included
- Cable can be cut to length, and can be installed on track or ceiling

### Application

- Food retail
- Fashion retail
- Hospitality

# GreenSpace Accent Pendant

## Specifications

Aiming possibilities from the horizontal	to °
Aiming possibilities from the vertical	to °
Ambient Temperature	+10 to +25 °C
Beam angle lightsource	120 °
Beam spread luminaire	24°, 60°
Main color of the Luminaire	Black RAL 9004, silver RAL 9006, white RAL 9003
Connection	Flying leads/wires (Flying leads/wires)
Dimming	No, yes
Driver	Power supply unit (Power supply unit) Power supply unit with DALI interface (Power supply unit with DALI interface)
Initial correlated color temperature	2200 K, 2700 K, 3000 K, 4000 K
Initial input power	14.4 W, 16.4 W, 20.5 W, 22 W, 23.5 W, 25 W, 26 W, 28 W, 29 W, 31.5 W, 36 W, 41 W
Initial LED luminaire efficacy	86, 92, 100, 103, 106, 108, 114, 115, 118, 120, 123, 142 lm/W

Initial luminous flux	1700 lm, 1900 lm, 2700 lm, 3900 lm, 4000 lm
Input frequency	50 to 60 Hz
Input voltage	220 to 240 V
Inrush current (A)	7.7, 10.2, 11, 12.6, 20.4 A
Light source color	827 warm white, 830 warm white, 840 neutral white, fresh meat, premium color with CRI ≥90, premium white with CRI ≥90, rosé
Light source replaceable	No
Material	Bracket:
Material	Gear box:
Material	Housing: aluminum die cast
Material	Reflector: polycarbonate aluminum coated
Optic	Medium beam, very wide beam, wide beam
Optical cover	Polycarbonate
Tilt angle housing	Standard tilt angle posttop: Standard tilt angle side entry:
Type	PT320T
Warranty period	5 years

## Versions



GSA Pendant Track Mounted



GSA Pendant Track Mounted



GSA Pendant Ceiling Mounted

## Product details



GreenSpace Accent Pendant  
PT320T C-1



GreenSpace Accent Pendant  
PT320T C-2

# GreenSpace Accent Pendant

## Product details



GreenSpace Accent Pendant  
PT320T BBS



GreenSpace Accent Pendant  
PT320T



GreenSpace Accent Pendant  
PT320T RPS



GreenSpace Accent Pendant  
PT320T BCS



GreenSpace Accent Pendant  
PT320T SOS



GreenSpace Accent Pendant  
PT320C

# GreenSpace Accent Pendant

## Application Conditions

Ambient temperature range	+10 to +25 °C
Suitable for random switching	Yes

## Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

## Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

## General Information

Beam angle of light source	120 °
CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Product Family Code	PT320T

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

## Application Conditions

Order Code	Full Product Name	Maximum dim level
910505101516	PT320T 17S/830 PSU MB CP BK	Not applicable
910505101518	PT320T 19S/FMT DIA-VLC VWB CP BK	1%
910505101520	PT320T 27S/827 DIA-VLC MB CP BK	1%
910505101522	PT320T 27S/840 DIA-VLC MB CP BK	1%
910505101524	PT320T 27S/PW930 PSU VWB CP BK	Not applicable
910505101528	PT320T 39S/840 PSU MB CP BK	Not applicable
910505101530	PT320T 39S/PW930 PSU MB CP BK	Not applicable
910505101517	PT320T 17S/PW930 PSU WB CP WH	Not applicable
910505101519	PT320T 19S/ROSE DIA-VLC VWB CP WH	1%
910505101521	PT320T 27S/830 DIA-VLC MB CP WH	1%
910505101523	PT320T 27S/PC930 PSU MB CP WH	Not applicable
910505101526	PT320T 27S/ROSE DIA-VLC VWB CP WH	1%
910505101527	PT320T 39S/830 PSU VWB CP WH	Not applicable
910505101529	PT320T 39S/PC930 PSU MB CP WH	Not applicable
910505101525	PT320T 27S/PW930 PSU VWB CP SI	Not applicable

## Controls and Dimming

Order Code	Full Product Name	Dimmable
910505101516	PT320T 17S/830 PSU MB CP BK	No
910505101518	PT320T 19S/FMT DIA-VLC VWB CP BK	Yes
910505101520	PT320T 27S/827 DIA-VLC MB CP BK	Yes
910505101522	PT320T 27S/840 DIA-VLC MB CP BK	Yes
910505101524	PT320T 27S/PW930 PSU VWB CP BK	No
910505101528	PT320T 39S/840 PSU MB CP BK	No
910505101530	PT320T 39S/PW930 PSU MB CP BK	No
910505101517	PT320T 17S/PW930 PSU WB CP WH	No

Order Code	Full Product Name	Dimmable
910505101519	PT320T 19S/ROSE DIA-VLC VWB CP WH	Yes
910505101521	PT320T 27S/830 DIA-VLC MB CP WH	Yes
910505101523	PT320T 27S/PC930 PSU MB CP WH	No
910505101526	PT320T 27S/ROSE DIA-VLC VWB CP WH	Yes
910505101527	PT320T 39S/830 PSU VWB CP WH	No
910505101529	PT320T 39S/PC930 PSU MB CP WH	No
910505101525	PT320T 27S/PW930 PSU VWB CP SI	No

## General Information

Order Code	Full Product Name	Optic type
910505101516	PT320T 17S/830 PSU MB CP BK	Medium beam
910505101518	PT320T 19S/FMT DIA-VLC VWB CP BK	Very wide beam
910505101520	PT320T 27S/827 DIA-VLC MB CP BK	Medium beam
910505101522	PT320T 27S/840 DIA-VLC MB CP BK	Medium beam
910505101524	PT320T 27S/PW930 PSU VWB CP BK	Very wide beam
910505101528	PT320T 39S/840 PSU MB CP BK	Very wide beam
910505101530	PT320T 39S/PW930 PSU MB CP BK	Medium beam
910505101517	PT320T 17S/PW930 PSU WB CP WH	Wide beam

Order Code	Full Product Name	Optic type
910505101519	PT320T 19S/ROSE DIA-VLC VWB CP WH	Very wide beam
910505101521	PT320T 27S/830 DIA-VLC MB CP WH	Medium beam
910505101523	PT320T 27S/PC930 PSU MB CP WH	Medium beam
910505101526	PT320T 27S/ROSE DIA-VLC VWB CP WH	Very wide beam
910505101527	PT320T 39S/830 PSU VWB CP WH	Very wide beam
910505101529	PT320T 39S/PC930 PSU MB CP WH	Medium beam
910505101525	PT320T 27S/PW930 PSU VWB CP SI	Very wide beam

# GreenSpace Accent Pendant

## Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910505101516	PT320T 17S/830 PSU MB CP BK	(0.434, 0.403)	3000 K	≥80	118 lm/W
910505101518	PT320T 19S/FMT DIA-VLC VWB CP BK	(0.406, 0.350)	3000 K	>90	86 lm/W
910505101520	PT320T 27S/827 DIA-VLC MB CP BK	(0.458, 0.410)	2700 K	≥80	115 lm/W
910505101522	PT320T 27S/840 DIA-VLC MB CP BK	(0.382, 0.380)	4000 K	≥80	120 lm/W
910505101524	PT320T 27S/PW930 PSU VWB CP BK	(0.422, 0.386)	3000 K	≥90	103 lm/W
910505101528	PT320T 39S/840 PSU MB CP BK	(0.382, 0.380)	2200 K	≥80	142 lm/W
910505101530	PT320T 39S/PW930 PSU MB CP BK	(0.422, 0.386)	3000 K	≥90	108 lm/W
910505101517	PT320T 17S/PW930 PSU WB CP WH	(0.422, 0.386)	3000 K	≥90	114 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910505101519	PT320T 19S/ROSE DIA-VLC VWB CP WH	(0.49, 0.38)	2200 K	≥80	92 lm/W
910505101521	PT320T 27S/830 DIA-VLC MB CP WH	(0.434, 0.403)	3000 K	≥80	115 lm/W
910505101523	PT320T 27S/PC930 PSU MB CP WH	(0.422, 0.386)	3000 K	≥90	106 lm/W
910505101526	PT320T 27S/ROSE DIA-VLC VWB CP WH	(0.49, 0.38)	4000 K	≥80	92 lm/W
910505101527	PT320T 39S/830 PSU VWB CP WH	(0.434, 0.403)	3000 K	≥80	123 lm/W
910505101529	PT320T 39S/PC930 PSU MB CP WH	(0.422, 0.386)	3000 K	≥90	100 lm/W
910505101525	PT320T 27S/PW930 PSU VWB CP SI	(0.422, 0.386)	3000 K	≥90	103 lm/W

## Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Initial input power
910505101516	PT320T 17S/830 PSU MB CP BK	1700 lm	14.4 W
910505101518	PT320T 19S/FMT DIA-VLC VWB CP BK	1900 lm	22 W
910505101520	PT320T 27S/827 DIA-VLC MB CP BK	2700 lm	23.5 W
910505101522	PT320T 27S/840 DIA-VLC MB CP BK	2700 lm	23.5 W
910505101524	PT320T 27S/PW930 PSU VWB CP BK	2700 lm	26 W
910505101528	PT320T 39S/840 PSU MB CP BK	4000 lm	28 W
910505101530	PT320T 39S/PW930 PSU MB CP BK	3900 lm	36 W
910505101517	PT320T 17S/PW930 PSU WB CP WH	1700 lm	16.4 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910505101519	PT320T 19S/ROSE DIA-VLC VWB CP WH	1900 lm	20.5 W
910505101521	PT320T 27S/830 DIA-VLC MB CP WH	2700 lm	23.5 W
910505101523	PT320T 27S/PC930 PSU MB CP WH	2700 lm	25 W
910505101526	PT320T 27S/ROSE DIA-VLC VWB CP WH	2700 lm	29 W
910505101527	PT320T 39S/830 PSU VWB CP WH	3900 lm	31.5 W
910505101529	PT320T 39S/PC930 PSU MB CP WH	3900 lm	41 W
910505101525	PT320T 27S/PW930 PSU VWB CP SI	2700 lm	26 W

## Mechanical and Housing

Order Code	Full Product Name	Color
910505101516	PT320T 17S/830 PSU MB CP BK	Black RAL 9004
910505101518	PT320T 19S/FMT DIA-VLC VWB CP BK	Black RAL 9004

Order Code	Full Product Name	Color
910505101520	PT320T 27S/827 DIA-VLC MB CP BK	Black RAL 9004
910505101522	PT320T 27S/840 DIA-VLC MB CP BK	Black RAL 9004

## GreenSpace Accent Pendant

Order Code	Full Product Name	Color
910505101524	PT320T 27S/PW930 PSU VWB CP BK	Black RAL 9004
910505101528	PT320T 39S/840 PSU MB CP BK	Black RAL 9004
910505101530	PT320T 39S/PW930 PSU MB CP BK	Black RAL 9004
910505101517	PT320T 17S/PW930 PSU WB CP WH	White RAL 9003
910505101519	PT320T 19S/ROSE DIA-VLC VWB CP WH	White RAL 9003
910505101521	PT320T 27S/830 DIA-VLC MB CP WH	White RAL 9003

Order Code	Full Product Name	Color
910505101523	PT320T 27S/PC930 PSU MB CP WH	White RAL 9003
910505101526	PT320T 27S/ROSE DIA-VLC VWB CP WH	White RAL 9003
910505101527	PT320T 39S/830 PSU VWB CP WH	White RAL 9003
910505101529	PT320T 39S/PC930 PSU MB CP WH	White RAL 9003
910505101525	PT320T 27S/PW930 PSU VWB CP SI	Silver RAL 9006

