



Lighting your way to success

SportsStar-BVP621/BVP622/EVP622

Philips SportsStar LED Floodlight sets the standard in high quality optical distribution with high performance and low light pollution (or effective light control). From Sports to Area Lighting, our system, including the high masts needed, projects the light exactly where it should be going. Choose the right illumination levels for any given setting with Philips SportsStar LED Floodlight.

Benefits

- Fit for both high mast area and sports application
- Multiple lens covers as much as of customer needs
- Compatible with systems, including Philips Arenavision system
- Robust quality and reliability
- Comply with HDTV broadcasting requirement

Features


- Both integrated version and remote version
- Wide range of optics
- DALI, 1-10V and DMX control interface
- Salty Spray 1,000hrs
- Typical lifetime up to 50K hours (L70B50)
- Flicker free (<1%) performance

SportsStar-BVP621/BVP622/EVP622

Application

- Airport Apron
- Port & Container Yard
- Large industrial areas
- Large Car Park Areas
- Building facades
- Transportation Terminals & Tollways
- Golf Driving Range
- General flood lighting
- Professional Sports Stadium
- Recreational Sports Stadium

Versions



BVP621 GM GC



BVP622 GM GC



BVP621 GM GC



BVP622 GM GC



EVP622 GM

Accessories



EVP622 GM GC

Ordercode 911401594851,
911401594951, 911401597051,
911401597151, 911401597251

Approval and Application

Mech. impact protection code IK08

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401593251	BVP621 LED1028/730 900W SP PSD GC O	10%
911401593351	BVP621 LED1028/730 900W AIRP PSD GC O	10%
911401593451	BVP621 LED1110/740 900W SP PSD GC O	10%
911401593551	BVP621 LED1110/740 900W AIRP PSD GC O	10%
911401593651	BVP621 LED1110/757 900W SP PSD GC O	10%
911401593751	BVP621 LED1110/757 900W AIRP PSD GC O	10%
911401595051	BVP621 LED1028/730 900W NB PSD GM O	10%
911401595151	BVP621 LED1028/730 900W AWB PSD GM O	10%
911401595251	BVP621 LED1110/740 900W NB PSD GM O	10%
911401595351	BVP621 LED1110/740 900W AWB PSD GM O	10%
911401595451	BVP621 LED1110/757 900W NB PSD GM O	10%
911401595551	BVP621 LED1110/757 900W AWB PSD GM O	10%
911401595651	BVP621 LED1110/757 900W SWB PSC GM O	10%
911401595751	BVP621 LED1110/757 900W AWB PSC GM O	10%
911401595851	BVP621 LED922/857 900W SWB PSC GM O	10%
911401595951	BVP621 LED922/857 900W AWB PSC GM O	10%
911401593851	BVP622 LED922/857 900W SP 9007 GC 5C O	-
911401593951	BVP622 LED922/857 900W S3 9007 GC 5C O	-
911401594051	BVP622 LED922/857 900W S5 9007 GC 5C O	-
911401594151	BVP622 LED922/857 900W S6 9007 GC 5C O	-
911401594251	BVP622 LED922/857 900W S7 9007 GC 5C O	-
911401594351	BVP622 LED850/957 900W SP 9007 DMX GC O	-
911401594451	BVP622 LED850/957 900W S3 9007 DMX GC O	-
911401594551	BVP622 LED850/957 900W S5 9007 DMX GC O	-
911401594651	BVP622 LED850/957 900W S6 9007 DMX GC O	-
911401594751	BVP622 LED850/957 900W S7 9007 DMX GC O	-
911401596051	BVP622 LED922/857 900W NB GM 5C O	-
911401596151	BVP622 LED922/857 900W S3 GM 5C O	-

Order Code	Full Product Name	Maximum dim level
911401596251	BVP622 LED922/857 900W S5 GM 5C O	-
911401596351	BVP622 LED922/857 900W S6 GM 5C O	-
911401596451	BVP622 LED922/857 900W S7 GM 5C O	-
911401596551	BVP622 LED850/957 900W NB DMX GM O	-
911401596651	BVP622 LED850/957 900W S3 DMX GM O	-
911401596751	BVP622 LED850/957 900W S5 DMX GM O	-
911401596851	BVP622 LED850/957 900W S6 DMX GM O	-
911401596951	BVP622 LED850/957 900W S7 DMX GM O	-
911401636303	BVP621 LED860/WW 960W 220-240V AIRP	-
911401824298	BVP621 LED456/WW 480W 220-240V AWB GM	Not applicable
911401824398	BVP621 LED760/WW 800W 220-240V NB GM	Not applicable
911401824498	BVP621 LED456/WW 480W 220-240V NB GM	Not applicable
911401824598	BVP621 LED456/WW 480W 220-240V SWB GM	Not applicable
911401824698	BVP621 LED912/WW 960W 220-240V AWB GM	Not applicable
911401824798	BVP621 LED760/WW 800W 220-240V AWB GM	Not applicable
911401824898	BVP621 LED608/WW 640W 220-240V AWB GM	Not applicable
911401824998	BVP621 LED456/WW 480W 220-240V SMB GM	Not applicable
911401825198	BVP621 LED912/WW 960W 220-240V SMB GM	Not applicable
911401828098	BVP621 LED912/WW 960W 220-240V NB GM	Not applicable
911401649204	EVP622 IP66 960W 220-240V GM 5C O	-
911401650204	EVP622 IP66 960W 220-240V FIX 5C O	-
911401850198	BVP622 LED739/957 960W NB DMX GM	Not applicable
911401850298	BVP622 LED739/957 960W S5 DMX GM	Not applicable
911401850398	BVP622 LED739/957 960W S6 DMX GM	Not applicable
911401850498	BVP622 LED739/957 960W S7 DMX GM	Not applicable
911401849098	EVP622 IP66 960W 220-240V GM	Not applicable
911401849998	EVP622 IP66 960W 220-240V DMX GM	1%

Approval and Application

Order Code	Full Product Name	Surge Protection (Common/ Differential)
911401593251	BVP621 LED1028/730 900W SP PSD GC O	-
911401593351	BVP621 LED1028/730 900W AIRP PSD GC O	-
911401593451	BVP621 LED1110/740 900W SP PSD GC O	-
911401593551	BVP621 LED1110/740 900W AIRP PSD GC O	-
911401593651	BVP621 LED1110/757 900W SP PSD GC O	-
911401593751	BVP621 LED1110/757 900W AIRP PSD GC O	-

Order Code	Full Product Name	Surge Protection (Common/ Differential)
911401595051	BVP621 LED1028/730 900W NB PSD GM O	-
911401595151	BVP621 LED1028/730 900W AWB PSD GM O	-
911401595251	BVP621 LED1110/740 900W NB PSD GM O	-
911401595351	BVP621 LED1110/740 900W AWB PSD GM O	-
911401595451	BVP621 LED1110/757 900W NB PSD GM O	-
911401595551	BVP621 LED1110/757 900W AWB PSD GM O	-

SportsStar-BVP621/BVP622/EVP622

Order Code	Full Product Name	Surge Protection (Common/ Differential)
911401595651	BVP621 LED1110/757 900W SWB PSC GM O	-
911401595751	BVP621 LED1110/757 900W AWB PSC GM O	-
911401595851	BVP621 LED922/857 900W SWB PSC GM O	-
911401595951	BVP621 LED922/857 900W AWB PSC GM O	-
911401593851	BVP622 LED922/857 900W SP 9007 GC 5C O	-
911401593951	BVP622 LED922/857 900W S3 9007 GC 5C O	-
911401594051	BVP622 LED922/857 900W S5 9007 GC 5C O	-
911401594151	BVP622 LED922/857 900W S6 9007 GC 5C O	-
911401594251	BVP622 LED922/857 900W S7 9007 GC 5C O	-
911401594351	BVP622 LED850/957 900W SP 9007 DMX GC O	-
911401594451	BVP622 LED850/957 900W S3 9007 DMX GC O	-
911401594551	BVP622 LED850/957 900W S5 9007 DMX GC O	-
911401594651	BVP622 LED850/957 900W S6 9007 DMX GC O	-
911401594751	BVP622 LED850/957 900W S7 9007 DMX GC O	-
911401596051	BVP622 LED922/857 900W NB GM 5C O	-
911401596151	BVP622 LED922/857 900W S3 GM 5C O	-
911401596251	BVP622 LED922/857 900W S5 GM 5C O	-
911401596351	BVP622 LED922/857 900W S6 GM 5C O	-
911401596451	BVP622 LED922/857 900W S7 GM 5C O	-
911401596551	BVP622 LED850/957 900W NB DMX GM O	-
911401596651	BVP622 LED850/957 900W S3 DMX GM O	-
911401596751	BVP622 LED850/957 900W S5 DMX GM O	-
911401596851	BVP622 LED850/957 900W S6 DMX GM O	-
911401596951	BVP622 LED850/957 900W S7 DMX GM O	-
911401636303	BVP621 LED860/WW 960W 220-240V AIRP	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode

Order Code	Full Product Name	Surge Protection (Common/ Differential)
911401824298	BVP621 LED456/WW 480W 220-240V AWB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401824398	BVP621 LED760/WW 800W 220-240V NB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401824498	BVP621 LED456/WW 480W 220-240V NB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401824598	BVP621 LED456/WW 480W 220-240V SWB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401824698	BVP621 LED912/WW 960W 220-240V AWB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401824798	BVP621 LED760/WW 800W 220-240V AWB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401824898	BVP621 LED608/WW 640W 220-240V AWB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401824998	BVP621 LED456/WW 480W 220-240V SMB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401825198	BVP621 LED912/WW 960W 220-240V SMB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401828098	BVP621 LED912/WW 960W 220-240V NB GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401649204	EVP622 IP66 960W 220-240V GM 5C O	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401650204	EVP622 IP66 960W 220-240V FIX 5C O	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
911401850198	BVP622 LED739/957 960W NB DMX GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401850298	BVP622 LED739/957 960W S5 DMX GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401850398	BVP622 LED739/957 960W S6 DMX GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401850498	BVP622 LED739/957 960W S7 DMX GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
911401849098	EVP622 IP66 960W 220-240V GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode

SportsStar-BVP621/BVP622/EVP622

Order Code	Full Product Name	Surge Protection (Common/ Differential)
911401849998	EVP622 IP66 960W 220-240V DMX GM	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401593251	BVP621 LED1028/730 900W SP PSD GC O	Yes
911401593351	BVP621 LED1028/730 900W AIRP PSD GC O	Yes
911401593451	BVP621 LED1110/740 900W SP PSD GC O	Yes
911401593551	BVP621 LED1110/740 900W AIRP PSD GC O	Yes
911401593651	BVP621 LED1110/757 900W SP PSD GC O	Yes
911401593751	BVP621 LED1110/757 900W AIRP PSD GC O	Yes
911401595051	BVP621 LED1028/730 900W NB PSD GM O	Yes
911401595151	BVP621 LED1028/730 900W AWB PSD GM O	Yes
911401595251	BVP621 LED1110/740 900W NB PSD GM O	Yes
911401595351	BVP621 LED1110/740 900W AWB PSD GM O	Yes
911401595451	BVP621 LED1110/757 900W NB PSD GM O	Yes
911401595551	BVP621 LED1110/757 900W AWB PSD GM O	Yes
911401595651	BVP621 LED1110/757 900W SWB PSC GM O	Yes
911401595751	BVP621 LED1110/757 900W AWB PSC GM O	Yes
911401595851	BVP621 LED922/857 900W SWB PSC GM O	Yes
911401595951	BVP621 LED922/857 900W AWB PSC GM O	Yes
911401593851	BVP622 LED922/857 900W SP 9007 GC 5C O	No
911401593951	BVP622 LED922/857 900W S3 9007 GC 5C O	No
911401594051	BVP622 LED922/857 900W S5 9007 GC 5C O	No
911401594151	BVP622 LED922/857 900W S6 9007 GC 5C O	No
911401594251	BVP622 LED922/857 900W S7 9007 GC 5C O	No
911401594351	BVP622 LED850/957 900W SP 9007 DMX GC O	No
911401594451	BVP622 LED850/957 900W S3 9007 DMX GC O	No
911401594551	BVP622 LED850/957 900W S5 9007 DMX GC O	No
911401594651	BVP622 LED850/957 900W S6 9007 DMX GC O	No
911401594751	BVP622 LED850/957 900W S7 9007 DMX GC O	No
911401596051	BVP622 LED922/857 900W NB GM 5C O	No
911401596151	BVP622 LED922/857 900W S3 GM 5C O	No

Order Code	Full Product Name	Dimmable
911401596251	BVP622 LED922/857 900W S5 GM 5C O	No
911401596351	BVP622 LED922/857 900W S6 GM 5C O	No
911401596451	BVP622 LED922/857 900W S7 GM 5C O	No
911401596551	BVP622 LED850/957 900W NB DMX GM O	No
911401596651	BVP622 LED850/957 900W S3 DMX GM O	No
911401596751	BVP622 LED850/957 900W S5 DMX GM O	No
911401596851	BVP622 LED850/957 900W S6 DMX GM O	No
911401596951	BVP622 LED850/957 900W S7 DMX GM O	No
911401636303	BVP621 LED860/WW 960W 220-240V AIRP	No
911401824298	BVP621 LED456/WW 480W 220-240V AWB GM	No
911401824398	BVP621 LED760/WW 800W 220-240V NB GM	No
911401824498	BVP621 LED456/WW 480W 220-240V NB GM	No
911401824598	BVP621 LED456/WW 480W 220-240V SWB GM	No
911401824698	BVP621 LED912/WW 960W 220-240V AWB GM	No
911401824798	BVP621 LED760/WW 800W 220-240V AWB GM	No
911401824898	BVP621 LED608/WW 640W 220-240V AWB GM	No
911401824998	BVP621 LED456/WW 480W 220-240V SMB GM	No
911401825198	BVP621 LED912/WW 960W 220-240V SMB GM	No
911401828098	BVP621 LED912/WW 960W 220-240V NB GM	No
911401649204	EVP622 IP66 960W 220-240V GM 5C O	No
911401650204	EVP622 IP66 960W 220-240V FIX 5C O	No
911401850198	BVP622 LED739/957 960W NB DMX GM	No
911401850298	BVP622 LED739/957 960W S5 DMX GM	No
911401850398	BVP622 LED739/957 960W S6 DMX GM	No
911401850498	BVP622 LED739/957 960W S7 DMX GM	No
911401849098	EVP622 IP66 960W 220-240V GM	No
911401849998	EVP622 IP66 960W 220-240V DMX GM	Yes

General Information (1/2)

Order Code	Full Product Name	Luminaire light		Light source		Driver included	Flammability mark	Lamp family code
		beam spread	CE mark	color	Optical cover/lens type			
911401593251	BVP621 LED1028/730 900W SP PSD GC O	-	-	730 warm white	Polycarbonate micro lens optic	Yes	-	-
911401593351	BVP621 LED1028/730 900W AIRP PSD GC O	-	-	730 warm white	Polycarbonate micro lens optic	Yes	-	-
911401593451	BVP621 LED1110/740 900W SP PSD GC O	-	-	740 neutral white	Polycarbonate micro lens optic	Yes	-	-
911401593551	BVP621 LED1110/740 900W AIRP PSD GC O	-	-	740 neutral white	Polycarbonate micro lens optic	Yes	-	-

SportsStar-BVP621/BVP622/EVP622

Order Code	Full Product Name	Luminaire light		Light source		Driver included	Flammability mark	Lamp family code
		beam spread	CE mark	color	Optical cover/lens type			
911401593651	BVP621 LED1110/757 900W SP PSD GC O	-	-	757 cool white	Polycarbonate micro lens optic	Yes	-	-
911401593751	BVP621 LED1110/757 900W AIRP PSD GC O	-	-	757 cool white	Polycarbonate micro lens optic	Yes	-	-
911401595051	BVP621 LED1028/730 900W NB PSD GM O	-	CE mark	730 warm white	Polycarbonate micro lens optic	Yes	-	-
911401595151	BVP621 LED1028/730 900W AWB PSD GM O	-	CE mark	730 warm white	Polycarbonate micro lens optic	Yes	-	-
911401595251	BVP621 LED1110/740 900W NB PSD GM O	-	CE mark	740 neutral white	Polycarbonate micro lens optic	Yes	-	-
911401595351	BVP621 LED1110/740 900W AWB PSD GM O	-	CE mark	740 neutral white	Polycarbonate micro lens optic	Yes	-	-
911401595451	BVP621 LED1110/757 900W NB PSD GM O	-	CE mark	757 cool white	Polycarbonate micro lens optic	Yes	-	-
911401595551	BVP621 LED1110/757 900W AWB PSD GM O	-	CE mark	757 cool white	Polycarbonate micro lens optic	Yes	-	-
911401595651	BVP621 LED1110/757 900W SWB PSC GM O	-	CE mark	757 cool white	Polycarbonate micro lens optic	Yes	-	-
911401595751	BVP621 LED1110/757 900W AWB PSC GM O	-	CE mark	757 cool white	Polycarbonate micro lens optic	Yes	-	-
911401595851	BVP621 LED922/857 900W SWB PSC GM O	-	CE mark	857 daylight	Polycarbonate micro lens optic	Yes	-	-
911401595951	BVP621 LED922/857 900W AWB PSC GM O	-	CE mark	857 daylight	Polycarbonate micro lens optic	Yes	-	-
911401593851	BVP622 LED922/857 900W SP 9007 GC 5C O	-	-	857 daylight	Polycarbonate micro lens optic	No	-	-
911401593951	BVP622 LED922/857 900W S3 9007 GC 5C O	-	-	857 daylight	Polycarbonate micro lens optic	No	-	-
911401594051	BVP622 LED922/857 900W S5 9007 GC 5C O	-	-	857 daylight	Polycarbonate micro lens optic	No	-	-
911401594151	BVP622 LED922/857 900W S6 9007 GC 5C O	-	-	857 daylight	Polycarbonate micro lens optic	No	-	-
911401594251	BVP622 LED922/857 900W S7 9007 GC 5C O	-	-	857 daylight	Polycarbonate micro lens optic	No	-	-
911401594351	BVP622 LED850/957 900W SP 9007 DMX GC O	-	-	957 cool white	Polycarbonate micro lens optic	No	-	-
911401594451	BVP622 LED850/957 900W S3 9007 DMX GC O	-	-	957 cool white	Polycarbonate micro lens optic	No	-	-
911401594551	BVP622 LED850/957 900W S5 9007 DMX GC O	-	-	957 cool white	Polycarbonate micro lens optic	No	-	-
911401594651	BVP622 LED850/957 900W S6 9007 DMX GC O	-	-	957 cool white	Polycarbonate micro lens optic	No	-	-
911401594751	BVP622 LED850/957 900W S7 9007 DMX GC O	-	-	957 cool white	Polycarbonate micro lens optic	No	-	-
911401596051	BVP622 LED922/857 900W NB GM 5C O	-	CE mark	857 daylight	Polycarbonate micro lens optic	No	-	-
911401596151	BVP622 LED922/857 900W S3 GM 5C O	-	CE mark	857 daylight	Polycarbonate micro lens optic	No	-	-
911401596251	BVP622 LED922/857 900W S5 GM 5C O	-	CE mark	857 daylight	Polycarbonate micro lens optic	No	-	-

SportsStar-BVP621/BVP622/EVP622

Order Code	Full Product Name	Luminaire light		Light source		Driver included	Flammability mark	Lamp family code
		beam spread	CE mark	color	Optical cover/lens type			
911401596351	BVP622 LED922/857 900W S6 GM 5C O	-	CE mark	857 daylight	Polycarbonate micro lens optic	No	-	-
911401596451	BVP622 LED922/857 900W S7 GM 5C O	-	CE mark	857 daylight	Polycarbonate micro lens optic	No	-	-
911401596551	BVP622 LED850/957 900W NB DMX GM O	-	CE mark	957 cool white	Polycarbonate micro lens optic	No	-	-
911401596651	BVP622 LED850/957 900W S3 DMX GM O	-	CE mark	957 cool white	Polycarbonate micro lens optic	No	-	-
911401596751	BVP622 LED850/957 900W S5 DMX GM O	-	CE mark	957 cool white	Polycarbonate micro lens optic	No	-	-
911401596851	BVP622 LED850/957 900W S6 DMX GM O	-	CE mark	957 cool white	Polycarbonate micro lens optic	No	-	-
911401596951	BVP622 LED850/957 900W S7 DMX GM O	-	CE mark	957 cool white	Polycarbonate micro lens optic	No	-	-
911401636303	BVP621 LED860/WW 960W 220-240V AIRP	15° x 95°	-	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401824298	BVP621 LED456/WW 480W 220-240V AWB GM	15° x 95°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401824398	BVP621 LED760/WW 800W 220-240V NB GM	13°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401824498	BVP621 LED456/WW 480W 220-240V NB GM	13°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401824598	BVP621 LED456/WW 480W 220-240V SWB GM	30° x 80°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401824698	BVP621 LED912/WW 960W 220-240V AWB GM	15° x 95°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401824798	BVP621 LED760/WW 800W 220-240V AWB GM	15° x 95°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401824898	BVP621 LED608/WW 640W 220-240V AWB GM	15° x 95°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401824998	BVP621 LED456/WW 480W 220-240V SMB GM	50°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401825198	BVP621 LED912/WW 960W 220-240V SMB GM	50°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401828098	BVP621 LED912/WW 960W 220-240V NB GM	13°	CE mark	Warm white	Polycarbonate micro lens optic	Yes	-	-
911401649204	EVP622 IP66 960W 220-240V GM 5C O	-	CE mark	-	-	Yes	-	-
911401650204	EVP622 IP66 960W 220-240V FIX 5C O	-	-	-	-	Yes	-	-
911401850198	BVP622 LED739/957 960W NB DMX GM	13°	CE mark	Cool white	Polycarbonate micro lens optic	No	-	-
911401850298	BVP622 LED739/957 960W S5 DMX GM	17°	CE mark	Cool white	Polycarbonate micro lens optic	No	-	-
911401850398	BVP622 LED739/957 960W S6 DMX GM	21°	CE mark	Cool white	Polycarbonate micro lens optic	No	-	-
911401850498	BVP622 LED739/957 960W S7 DMX GM	29°	CE mark	Cool white	Polycarbonate micro lens optic	No	-	-
911401849098	EVP622 IP66 960W 220-240V GM	-	CE mark	-	-	Yes	-	-
911401849998	EVP622 IP66 960W 220-240V DMX GM	-	CE mark	-	-	Yes	-	-

General Information (2/2)

SportsStar-BVP621/BVP622/EVP622

Order Code	Full Product Name	Light source replaceable	Number of gear units	Optic type
911401593251	BVP621 LED1028/730 900W SP PSD GC O	No	-	-
911401593351	BVP621 LED1028/730 900W AIRP PSD GC O	No	-	-
911401593451	BVP621 LED1110/740 900W SP PSD GC O	No	-	-
911401593551	BVP621 LED1110/740 900W AIRP PSD GC O	No	-	-
911401593651	BVP621 LED1110/757 900W SP PSD GC O	No	-	-
911401593751	BVP621 LED1110/757 900W AIRP PSD GC O	No	-	-
911401595051	BVP621 LED1028/730 900W NB PSD GM O	No	-	-
911401595151	BVP621 LED1028/730 900W AWB PSD GM O	No	-	-
911401595251	BVP621 LED1110/740 900W NB PSD GM O	No	-	-
911401595351	BVP621 LED1110/740 900W AWB PSD GM O	No	-	-
911401595451	BVP621 LED1110/757 900W NB PSD GM O	No	-	-
911401595551	BVP621 LED1110/757 900W AWB PSD GM O	No	-	-
911401595651	BVP621 LED1110/757 900W SWB PSC GM O	No	-	-
911401595751	BVP621 LED1110/757 900W AWB PSC GM O	No	-	-
911401595851	BVP621 LED922/857 900W SWB PSC GM O	No	-	-
911401595951	BVP621 LED922/857 900W AWB PSC GM O	No	-	-
911401593851	BVP622 LED922/857 900W SP 9007 GC 5C O	No	-	-
911401593951	BVP622 LED922/857 900W S3 9007 GC 5C O	No	-	-
911401594051	BVP622 LED922/857 900W S5 9007 GC 5C O	No	-	-
911401594151	BVP622 LED922/857 900W S6 9007 GC 5C O	No	-	-
911401594251	BVP622 LED922/857 900W S7 9007 GC 5C O	No	-	-
911401594351	BVP622 LED850/957 900W SP 9007 DMX GC O	No	-	-
911401594451	BVP622 LED850/957 900W S3 9007 DMX GC O	No	-	-
911401594551	BVP622 LED850/957 900W S5 9007 DMX GC O	No	-	-
911401594651	BVP622 LED850/957 900W S6 9007 DMX GC O	No	-	-

Order Code	Full Product Name	Light source replaceable	Number of gear units	Optic type
911401594751	BVP622 LED850/957 900W S7 9007 DMX GC O	No	-	-
911401596051	BVP622 LED922/857 900W NB GM 5C O	No	-	-
911401596151	BVP622 LED922/857 900W S3 GM 5C O	No	-	-
911401596251	BVP622 LED922/857 900W S5 GM 5C O	No	-	-
911401596351	BVP622 LED922/857 900W S6 GM 5C O	No	-	-
911401596451	BVP622 LED922/857 900W S7 GM 5C O	No	-	-
911401596551	BVP622 LED850/957 900W NB DMX GM O	No	-	-
911401596651	BVP622 LED850/957 900W S3 DMX GM O	No	-	-
911401596751	BVP622 LED850/957 900W S5 DMX GM O	No	-	-
911401596851	BVP622 LED850/957 900W S6 DMX GM O	No	-	-
911401596951	BVP622 LED850/957 900W S7 DMX GM O	No	-	-
911401636303	BVP621 LED860/WW 960W 220-240V AIRP	Yes	2 units	Asymmetrical wide beam
911401824298	BVP621 LED456/WW 480W 220-240V AWB GM	Yes	1 unit	Asymmetrical wide beam
911401824398	BVP621 LED760/WW 800W 220-240V NB GM	Yes	1 unit	Narrow beam
911401824498	BVP621 LED456/WW 480W 220-240V NB GM	Yes	1 unit	Narrow beam
911401824598	BVP621 LED456/WW 480W 220-240V SWB GM	Yes	1 unit	Symmetrical wide beam
911401824698	BVP621 LED912/WW 960W 220-240V AWB GM	Yes	2 units	Asymmetrical wide beam
911401824798	BVP621 LED760/WW 800W 220-240V AWB GM	Yes	1 unit	Asymmetrical wide beam
911401824898	BVP621 LED608/WW 640W 220-240V AWB GM	Yes	1 unit	Asymmetrical wide beam
911401824998	BVP621 LED456/WW 480W 220-240V SMB GM	Yes	1 unit	Symmetrical medium beam
911401825198	BVP621 LED912/WW 960W 220-240V SMB GM	Yes	2 units	Symmetrical medium beam
911401828098	BVP621 LED912/WW 960W 220-240V NB GM	Yes	2 units	Narrow beam
911401649204	EVP622 IP66 960W 220-240V GM 5C O	No	1 unit	-
911401650204	EVP622 IP66 960W 220-240V FIX 5C O	No	1 unit	-
911401850198	BVP622 LED739/957 960W NB DMX GM	Yes	2 units	Narrow beam

SportsStar-BVP621/BVP622/EVP622

Order Code	Full Product Name	Light source replaceable	Number of gear units	Optic type
911401850298	BVP622 LED739/957 960W S5 DMX GM	Yes	2 units	Beam category S5
911401850398	BVP622 LED739/957 960W S6 DMX GM	Yes	2 units	Beam category S6
911401850498	BVP622 LED739/957 960W S7 DMX GM	Yes	2 units	Beam category S7

Order Code	Full Product Name	Light source replaceable	Number of gear units	Optic type
911401849098	EVP622 IP66 960W 220-240V GM	-	2 units	-
911401849998	EVP622 IP66 960W 220-240V DMX GM	-	2 units	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
911401593251	BVP621 LED1028/730 900W SP PSD GC O	3000 K	>70	102800 lm
911401593351	BVP621 LED1028/730 900W AIRP PSD GC O	3000 K	>70	102800 lm
911401593451	BVP621 LED1110/740 900W SP PSD GC O	4000 K	>70	111000 lm
911401593551	BVP621 LED1110/740 900W AIRP PSD GC O	4000 K	>70	111000 lm
911401593651	BVP621 LED1110/757 900W SP PSD GC O	5700 K	>70	111000 lm
911401593751	BVP621 LED1110/757 900W AIRP PSD GC O	5700 K	>70	111000 lm
911401595051	BVP621 LED1028/730 900W NB PSD GM O	3000 K	>70	102800 lm
911401595151	BVP621 LED1028/730 900W AWB PSD GM O	3000 K	>70	102800 lm
911401595251	BVP621 LED1110/740 900W NB PSD GM O	4000 K	>70	111000 lm
911401595351	BVP621 LED1110/740 900W AWB PSD GM O	4000 K	>70	111000 lm
911401595451	BVP621 LED1110/757 900W NB PSD GM O	5700 K	>70	111000 lm
911401595551	BVP621 LED1110/757 900W AWB PSD GM O	5700 K	>70	111000 lm
911401595651	BVP621 LED1110/757 900W SWB PSC GM O	5700 K	>70	111000 lm
911401595751	BVP621 LED1110/757 900W AWB PSC GM O	5700 K	>70	111000 lm
911401595851	BVP621 LED922/857 900W SWB PSC GM O	5700 K	>80	92200 lm
911401595951	BVP621 LED922/857 900W AWB PSC GM O	5700 K	>80	92200 lm
911401593851	BVP622 LED922/857 900W SP 9007 GC 5C O	5700 K	>80	92200 lm
911401593951	BVP622 LED922/857 900W S3 9007 GC 5C O	5700 K	>80	92200 lm
911401594051	BVP622 LED922/857 900W S5 9007 GC 5C O	5700 K	>80	92200 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
911401594151	BVP622 LED922/857 900W S6 9007 GC 5C O	5700 K	>80	92200 lm
911401594251	BVP622 LED922/857 900W S7 9007 GC 5C O	5700 K	>80	92200 lm
911401594351	BVP622 LED850/957 900W SP 9007 DMX GC O	5700 K	>90	85000 lm
911401594451	BVP622 LED850/957 900W S3 9007 DMX GC O	5700 K	>90	85000 lm
911401594551	BVP622 LED850/957 900W S5 9007 DMX GC O	5700 K	>90	85000 lm
911401594651	BVP622 LED850/957 900W S6 9007 DMX GC O	5700 K	>90	85000 lm
911401594751	BVP622 LED850/957 900W S7 9007 DMX GC O	5700 K	>90	85000 lm
911401596051	BVP622 LED922/857 900W NB GM 5C O	5700 K	>80	92200 lm
911401596151	BVP622 LED922/857 900W S3 GM 5C O	5700 K	>80	92200 lm
911401596251	BVP622 LED922/857 900W S5 GM 5C O	5700 K	>80	92200 lm
911401596351	BVP622 LED922/857 900W S6 GM 5C O	5700 K	>80	92200 lm
911401596451	BVP622 LED922/857 900W S7 GM 5C O	5700 K	>80	92200 lm
911401596551	BVP622 LED850/957 900W NB DMX GM O	5700 K	>90	85000 lm
911401596651	BVP622 LED850/957 900W S3 DMX GM O	5700 K	>90	85000 lm
911401596751	BVP622 LED850/957 900W S5 DMX GM O	5700 K	>90	85000 lm
911401596851	BVP622 LED850/957 900W S6 DMX GM O	5700 K	>90	85000 lm
911401596951	BVP622 LED850/957 900W S7 DMX GM O	5700 K	>90	85000 lm

SportsStar-BVP621/BVP622/EVP622

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
911401636303	BVP621 LED860/WW 960W 220-240V AIRP	3000 K	70	86400 lm
911401824298	BVP621 LED456/WW 480W 220-240V AWB GM	3000 K	70	45600 lm
911401824398	BVP621 LED760/WW 800W 220-240V NB GM	3000 K	70	76000 lm
911401824498	BVP621 LED456/WW 480W 220-240V NB GM	3000 K	70	45600 lm
911401824598	BVP621 LED456/WW 480W 220-240V SWB GM	3000 K	70	45600 lm
911401824698	BVP621 LED912/WW 960W 220-240V AWB GM	3000 K	70	91200 lm
911401824798	BVP621 LED760/WW 800W 220-240V AWB GM	3000 K	70	76000 lm
911401824898	BVP621 LED608/WW 640W 220-240V AWB GM	3000 K	70	60800 lm
911401824998	BVP621 LED456/WW 480W 220-240V SMB GM	3000 K	70	45600 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
911401825198	BVP621 LED912/WW 960W 220-240V SMB GM	3000 K	70	91200 lm
911401828098	BVP621 LED912/WW 960W 220-240V NB GM	3000 K	70	91200 lm
911401649204	EVP622 IP66 960W 220-240V GM 5C O	- K	-	-
911401650204	EVP622 IP66 960W 220-240V FIX 5C O	- K	-	-
911401850198	BVP622 LED739/957 960W NB DMX GM	5700 K	90	73900 lm
911401850298	BVP622 LED739/957 960W S5 DMX GM	5700 K	90	73900 lm
911401850398	BVP622 LED739/957 960W S6 DMX GM	5700 K	90	73900 lm
911401850498	BVP622 LED739/957 960W S7 DMX GM	5700 K	90	73900 lm
911401849098	EVP622 IP66 960W 220-240V GM	- K	-	-
911401849998	EVP622 IP66 960W 220-240V DMX GM	- K	-	-

Light Technical

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop
911401593251	BVP621 LED1028/730 900W SP PSD GC O	-	-
911401593351	BVP621 LED1028/730 900W AIRP PSD GC O	-	-
911401593451	BVP621 LED1110/740 900W SP PSD GC O	-	-
911401593551	BVP621 LED1110/740 900W AIRP PSD GC O	-	-
911401593651	BVP621 LED1110/757 900W SP PSD GC O	-	-
911401593751	BVP621 LED1110/757 900W AIRP PSD GC O	-	-
911401595051	BVP621 LED1028/730 900W NB PSD GM O	-	-
911401595151	BVP621 LED1028/730 900W AWB PSD GM O	-	-
911401595251	BVP621 LED1110/740 900W NB PSD GM O	-	-
911401595351	BVP621 LED1110/740 900W AWB PSD GM O	-	-
911401595451	BVP621 LED1110/757 900W NB PSD GM O	-	-
911401595551	BVP621 LED1110/757 900W AWB PSD GM O	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop
911401595651	BVP621 LED1110/757 900W SWB PSC GM O	-	-
911401595751	BVP621 LED1110/757 900W AWB PSC GM O	-	-
911401595851	BVP621 LED922/857 900W SWB PSC GM O	-	-
911401595951	BVP621 LED922/857 900W AWB PSC GM O	-	-
911401593851	BVP622 LED922/857 900W SP 9007 GC 5C O	-	-
911401593951	BVP622 LED922/857 900W S3 9007 GC 5C O	-	-
911401594051	BVP622 LED922/857 900W S5 9007 GC 5C O	-	-
911401594151	BVP622 LED922/857 900W S6 9007 GC 5C O	-	-
911401594251	BVP622 LED922/857 900W S7 9007 GC 5C O	-	-
911401594351	BVP622 LED850/957 900W SP 9007 DMX GC O	-	-
911401594451	BVP622 LED850/957 900W S3 9007 DMX GC O	-	-

SportsStar-BVP621/BVP622/EVP622

Order Code	Full Product Name	Standard tilt	Standard tilt
		angle side entry	angle posttop
911401594551	BVP622 LED850/957 900W S5 9007 DMX GC O	-	-
911401594651	BVP622 LED850/957 900W S6 9007 DMX GC O	-	-
911401594751	BVP622 LED850/957 900W S7 9007 DMX GC O	-	-
911401596051	BVP622 LED922/857 900W NB GM 5C O	-	-
911401596151	BVP622 LED922/857 900W S3 GM 5C O	-	-
911401596251	BVP622 LED922/857 900W S5 GM 5C O	-	-
911401596351	BVP622 LED922/857 900W S6 GM 5C O	-	-
911401596451	BVP622 LED922/857 900W S7 GM 5C O	-	-
911401596551	BVP622 LED850/957 900W NB DMX GM O	-	-
911401596651	BVP622 LED850/957 900W S3 DMX GM O	-	-
911401596751	BVP622 LED850/957 900W S5 DMX GM O	-	-
911401596851	BVP622 LED850/957 900W S6 DMX GM O	-	-
911401596951	BVP622 LED850/957 900W S7 DMX GM O	-	-
911401636303	BVP621 LED860/WW 960W 220-240V AIRP	-	-
911401824298	BVP621 LED456/WW 480W 220-240V AWB GM	-	-
911401824398	BVP621 LED760/WW 800W 220-240V NB GM	-	-

Order Code	Full Product Name	Standard tilt	Standard tilt
		angle side entry	angle posttop
911401824498	BVP621 LED456/WW 480W 220-240V NB GM	-	-
911401824598	BVP621 LED456/WW 480W 220-240V SWB GM	-	-
911401824698	BVP621 LED912/WW 960W 220-240V AWB GM	-	-
911401824798	BVP621 LED760/WW 800W 220-240V AWB GM	-	-
911401824898	BVP621 LED608/WW 640W 220-240V AWB GM	-	-
911401824998	BVP621 LED456/WW 480W 220-240V SMB GM	-	-
911401825198	BVP621 LED912/WW 960W 220-240V SMB GM	-	-
911401828098	BVP621 LED912/WW 960W 220-240V NB GM	-	-
911401649204	EVP622 IP66 960W 220-240V GM 5C O	-	-
911401650204	EVP622 IP66 960W 220-240V FIX 5C O	-	-
911401850198	BVP622 LED739/957 960W NB DMX GM	-	-
911401850298	BVP622 LED739/957 960W S5 DMX GM	-	-
911401850398	BVP622 LED739/957 960W S6 DMX GM	-	-
911401850498	BVP622 LED739/957 960W S7 DMX GM	-	-
911401849098	EVP622 IP66 960W 220-240V GM	-	-
911401849998	EVP622 IP66 960W 220-240V DMX GM	-	-

Mechanical and Housing

Order Code	Full Product Name	Color
911401593251	BVP621 LED1028/730 900W SP PSD GC O	White and gray
911401593351	BVP621 LED1028/730 900W AIRP PSD GC O	White and gray
911401593451	BVP621 LED1110/740 900W SP PSD GC O	White and gray
911401593551	BVP621 LED1110/740 900W AIRP PSD GC O	White and gray
911401593651	BVP621 LED1110/757 900W SP PSD GC O	White and gray
911401593751	BVP621 LED1110/757 900W AIRP PSD GC O	White and gray
911401595051	BVP621 LED1028/730 900W NB PSD GM O	White and gray
911401595151	BVP621 LED1028/730 900W AWB PSD GM O	White and gray
911401595251	BVP621 LED1110/740 900W NB PSD GM O	White and gray
911401595351	BVP621 LED1110/740 900W AWB PSD GM O	White and gray
911401595451	BVP621 LED1110/757 900W NB PSD GM O	White and gray
911401595551	BVP621 LED1110/757 900W AWB PSD GM O	White and gray
911401595651	BVP621 LED1110/757 900W SWB PSC GM O	White and gray
911401595751	BVP621 LED1110/757 900W AWB PSC GM O	White and gray
911401595851	BVP621 LED922/857 900W SWB PSC GM O	White and gray
911401595951	BVP621 LED922/857 900W AWB PSC GM O	White and gray
911401593851	BVP622 LED922/857 900W SP 9007 GC 5C O	Aluminum
911401593951	BVP622 LED922/857 900W S3 9007 GC 5C O	Aluminum
911401594051	BVP622 LED922/857 900W S5 9007 GC 5C O	Aluminum

Order Code	Full Product Name	Color
911401594151	BVP622 LED922/857 900W S6 9007 GC 5C O	Aluminum
911401594251	BVP622 LED922/857 900W S7 9007 GC 5C O	Aluminum
911401594351	BVP622 LED850/957 900W SP 9007 DMX GC O	Aluminum
911401594451	BVP622 LED850/957 900W S3 9007 DMX GC O	Aluminum
911401594551	BVP622 LED850/957 900W S5 9007 DMX GC O	Aluminum
911401594651	BVP622 LED850/957 900W S6 9007 DMX GC O	Aluminum
911401594751	BVP622 LED850/957 900W S7 9007 DMX GC O	Aluminum
911401596051	BVP622 LED922/857 900W NB GM 5C O	White
911401596151	BVP622 LED922/857 900W S3 GM 5C O	White
911401596251	BVP622 LED922/857 900W S5 GM 5C O	White
911401596351	BVP622 LED922/857 900W S6 GM 5C O	White
911401596451	BVP622 LED922/857 900W S7 GM 5C O	White
911401596551	BVP622 LED850/957 900W NB DMX GM O	White
911401596651	BVP622 LED850/957 900W S3 DMX GM O	White
911401596751	BVP622 LED850/957 900W S5 DMX GM O	White
911401596851	BVP622 LED850/957 900W S6 DMX GM O	White
911401596951	BVP622 LED850/957 900W S7 DMX GM O	White
911401636303	BVP621 LED860/WW 960W 220-240V AIRP	White
911401824298	BVP621 LED456/WW 480W 220-240V AWB GM	White and black

SportsStar-BVP621/BVP622/EVP622

Order Code	Full Product Name	Color
911401824398	BVP621 LED760/WW 800W 220-240V NB GM	White and black
911401824498	BVP621 LED456/WW 480W 220-240V NB GM	White and black
911401824598	BVP621 LED456/WW 480W 220-240V SWB GM	White and black
911401824698	BVP621 LED912/WW 960W 220-240V AWB GM	White and black
911401824798	BVP621 LED760/WW 800W 220-240V AWB GM	White and black
911401824898	BVP621 LED608/WW 640W 220-240V AWB GM	White and black
911401824998	BVP621 LED456/WW 480W 220-240V SMB GM	White and black
911401825198	BVP621 LED912/WW 960W 220-240V SMB GM	White and black
911401828098	BVP621 LED912/WW 960W 220-240V NB GM	White and black

Order Code	Full Product Name	Color
911401649204	EVP622 IP66 960W 220-240V GM 5C O	Black
911401650204	EVP622 IP66 960W 220-240V FIX 5C O	Black
911401850198	BVP622 LED739/957 960W NB DMX GM	White
911401850298	BVP622 LED739/957 960W S5 DMX GM	White
911401850398	BVP622 LED739/957 960W S6 DMX GM	White
911401850498	BVP622 LED739/957 960W S7 DMX GM	White
911401849098	EVP622 IP66 960W 220-240V GM	black
911401849998	EVP622 IP66 960W 220-240V DMX GM	black

