



The most competitive specification downlight for TCO attractiveness with diversity and system compatibility

GreenSpace G5

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

Benefits

- Energy efficient
- Design compactness
- Smart lighting









Features

- High optical efficiency
- Compact form factor
- DALI/DALI-VLC/POE compatible




Application

- Office
- shopping mall
- hotel
- retail etc.

Dimensional drawing



Dimensional drawing



General Information

Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit

Light Technical

Optical cover/lens type	Transparent bowl with white cover
Color rendering index (CRI)	>80
Optic type	High-gloss high reflectance

Mechanical and Housing

Housing Color	Black and white
---------------	-----------------

Approval and Application

Mech. impact protection code	IK02
------------------------------	------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Over Time Performance (IEC Compliant)

Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)

General Information

Order Code	Full Product Name	CE mark
911401571841	DN390B LED6/830 PSU D100 ALU GC	-
911401571941	DN390B LED6/840 PSU D100 ALU GC	-
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	-
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	-
911401575041	DN390B LED6/865 PSU D100 ALU WP GC	-
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	-
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	-
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	-
911401576541	DN391B LED11/830 PSU D100 ALU GC	-
911401576641	DN391B LED11/840 PSU D100 ALU GC	-
911401576741	DN391B LED11/830 PSD D100 ALU GC	-
911401576841	DN391B LED11/840 PSD D100 ALU GC	-
911401578041	DN390B LED6/830 PSU D100 ALU GM	CE mark
911401578141	DN390B LED6/840 PSU D100 ALU GM	CE mark
911401578241	DN390B LED6/865 PSU D100 ALU GM	CE mark
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	CE mark
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	CE mark
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	CE mark
911401571641	DN390B LED6/830 PSU D100 WH GC	-
911401571741	DN390B LED6/840 PSU D100 WH GC	-
911401577741	DN390B LED6/830 PSU D100 WH GM	CE mark
911401577841	DN390B LED6/840 PSU D100 WH GM	CE mark
911401577941	DN390B LED6/865 PSU D100 WH GM	CE mark
911401582841	DN390B LED6/830 PSU D100 WH CAU	CE mark
911401582941	DN390B LED6/840 PSU D100 WH CAU	CE mark
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	CE mark
911401583741	DN390B LED6/840 PSU D100 WH WP CAU	CE mark
911401572341	DN391B LED11/830 PSU D150 ALU GC	-
911401572441	DN391B LED11/840 PSU D150 ALU GC	-
911401572541	DN391B LED11/865 PSU D150 ALU GC	-
911401572841	DN391B LED11/830 PSD D150 ALU GC	-
911401572941	DN391B LED11/840 PSD D150 ALU GC	-
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	-
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	-
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	-
911401575941	DN392B LED16/830 POE D150 ALU GC	-
911401576041	DN392B LED16/840 POE D150 ALU GC	-
911401577141	DN392B LED16/830 PSU D150 ALU GC	-
911401577241	DN392B LED16/840 PSU D150 ALU GC	-
911401577541	DN392B LED16/830 PSD D150 ALU GC	-
911401577641	DN392B LED16/840 PSD D150 ALU GC	-
911401578641	DN391B LED11/830 PSU D150 ALU GM	CE mark
911401578741	DN391B LED11/840 PSU D150 ALU GM	CE mark
911401578841	DN391B LED11/865 PSU D150 ALU GM	CE mark
911401579241	DN392B LED16/830 PSU D150 ALU GM	CE mark
911401579341	DN392B LED16/840 PSU D150 ALU GM	CE mark
911401579441	DN392B LED16/865 PSU D150 ALU GM	CE mark
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	CE mark
911401581141	DN391B LED11/840 PSU D150 ALU WP GM	CE mark
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	CE mark
911401581841	DN391B LED11/830 PSD D150 ALU GM	CE mark

Order Code	Full Product Name	CE mark
911401581941	DN391B LED11/840 PSD D150 ALU GM	CE mark
911401584441	DN391B LED11/830 PSD D150 ALU CAU	CE mark
911401584541	DN391B LED11/840 PSD D150 ALU CAU	CE mark
911401585641	DN392B LED16/830 PSD D150 ALU GM	CE mark
911401585741	DN392B LED16/840 PSD D150 ALU GM	CE mark
911401585941	DN391B LED11/830 PSU D150 ALU R	-
911401586141	DN391B LED11/840 PSU D150 ALU R	-
911401572041	DN391B LED11/830 PSU D150 WH GC	-
911401572141	DN391B LED11/840 PSU D150 WH GC	-
911401572241	DN391B LED11/865 PSU D150 WH GC	-
911401572641	DN391B LED11/830 PSD D150 WH GC	-
911401572741	DN391B LED11/840 PSD D150 WH GC	-
911401575741	DN392B LED16/830 POE D150 WH GC	-
911401575841	DN392B LED16/840 POE D150 WH GC	-
911401576941	DN392B LED16/830 PSU D150 WH GC	-
911401577041	DN392B LED16/840 PSU D150 WH GC	-
911401577341	DN392B LED16/830 PSD D150 WH GC	-
911401577441	DN392B LED16/840 PSD D150 WH GC	-
911401578341	DN391B LED11/830 PSU D150 WH GM	CE mark
911401578441	DN391B LED11/840 PSU D150 WH GM	CE mark
911401578541	DN391B LED11/865 PSU D150 WH GM	CE mark
911401578941	DN392B LED16/830 PSU D150 WH GM	CE mark
911401579041	DN392B LED16/840 PSU D150 WH GM	CE mark
911401579141	DN392B LED16/865 PSU D150 WH GM	CE mark
911401581641	DN391B LED11/830 PSD D150 WH GM	CE mark
911401581741	DN391B LED11/840 PSD D150 WH GM	CE mark
911401583041	DN391B LED11/830 PSU D150 WH CAU	CE mark
911401583141	DN391B LED11/840 PSU D150 WH CAU	CE mark
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	CE mark
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	CE mark
911401584241	DN391B LED11/830 PSD D150 WH CAU	CE mark
911401584341	DN391B LED11/840 PSD D150 WH CAU	CE mark
911401585441	DN392B LED16/830 PSD D150 WH GM	CE mark
911401585541	DN392B LED16/840 PSD D150 WH GM	CE mark
911401585841	DN391B LED11/830 PSU D150 WH R	-
911401586041	DN391B LED11/840 PSU D150 WH R	-
911401573341	DN392B LED16/830 PSU D200 ALU GC	-
911401573441	DN392B LED16/840 PSU D200 ALU GC	-
911401573541	DN392B LED16/865 PSU D200 ALU GC	-
911401573841	DN392B LED16/830 PSD D200 ALU GC	-
911401573941	DN392B LED16/840 PSD D200 ALU GC	-
911401574241	DN393B LED22/830 PSU D200 ALU GC	-
911401574341	DN393B LED22/840 PSU D200 ALU GC	-
911401574641	DN393B LED22/830 PSD D200 ALU GC	-
911401574741	DN393B LED22/840 PSD D200 ALU GC	-
911401576341	DN393B LED22/830 POE D200 ALU GC	-
911401576441	DN393B LED22/840 POE D200 ALU GC	-
911401579841	DN392B LED16/830 PSU D200 ALU GM	CE mark
911401579941	DN392B LED16/840 PSU D200 ALU GM	CE mark
911401580041	DN392B LED16/865 PSU D200 ALU GM	CE mark
911401580441	DN393B LED22/830 PSU D200 ALU GM	CE mark
911401580541	DN393B LED22/840 PSU D200 ALU GM	CE mark

Order Code	Full Product Name	CE mark
911401580641	DN393B LED22/865 PSU D200 ALU GM	CE mark
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	CE mark
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	CE mark
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	CE mark
911401582241	DN392B LED16/830 PSD D200 ALU GM	CE mark
911401582341	DN392B LED16/840 PSD D200 ALU GM	CE mark
911401582641	DN393B LED22/830 PSD D200 ALU GM	CE mark
911401582741	DN393B LED22/840 PSD D200 ALU GM	CE mark
911401584841	DN392B LED16/830 PSD D200 ALU CAU	CE mark
911401584941	DN392B LED16/840 PSD D200 ALU CAU	CE mark
911401585241	DN393B LED22/830 PSD D200 ALU CAU	CE mark
911401585341	DN393B LED22/840 PSD D200 ALU CAU	CE mark
911401586341	DN393B LED22/830 PSU D200 ALU R	-
911401586541	DN393B LED22/840 PSU D200 ALU R	-
911401573041	DN392B LED16/830 PSU D200 WH GC	-
911401573141	DN392B LED16/840 PSU D200 WH GC	-
911401573241	DN392B LED16/865 PSU D200 WH GC	-
911401573641	DN392B LED16/830 PSD D200 WH GC	-
911401573741	DN392B LED16/840 PSD D200 WH GC	-
911401574041	DN393B LED22/830 PSU D200 WH GC	-
911401574141	DN393B LED22/840 PSU D200 WH GC	-
911401574441	DN393B LED22/830 PSD D200 WH GC	-
911401574541	DN393B LED22/840 PSD D200 WH GC	-
911401576141	DN393B LED22/830 POE D200 WH GC	-
911401576241	DN393B LED22/840 POE D200 WH GC	-
911401579541	DN392B LED16/830 PSU D200 WH GM	CE mark
911401579641	DN392B LED16/840 PSU D200 WH GM	CE mark
911401579741	DN392B LED16/865 PSU D200 WH GM	CE mark
911401580141	DN393B LED22/830 PSU D200 WH GM	CE mark
911401580241	DN393B LED22/840 PSU D200 WH GM	CE mark
911401580341	DN393B LED22/865 PSU D200 WH GM	CE mark
911401582041	DN392B LED16/830 PSD D200 WH GM	CE mark
911401582141	DN392B LED16/840 PSD D200 WH GM	CE mark
911401582441	DN393B LED22/830 PSD D200 WH GM	CE mark
911401582541	DN393B LED22/840 PSD D200 WH GM	CE mark
911401583241	DN392B LED16/830 PSU D200 WH CAU	CE mark
911401583341	DN392B LED16/840 PSU D200 WH CAU	CE mark
911401583441	DN393B LED22/830 PSU D200 WH CAU	CE mark
911401583541	DN393B LED22/840 PSU D200 WH CAU	CE mark
911401584041	DN393B LED22/830 PSU D200 WH WP CAU	CE mark
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	CE mark
911401584641	DN392B LED16/830 PSD D200 WH CAU	CE mark
911401584741	DN392B LED16/840 PSD D200 WH CAU	CE mark
911401585041	DN393B LED22/830 PSD D200 WH CAU	CE mark
911401585141	DN393B LED22/840 PSD D200 WH CAU	CE mark
911401586241	DN393B LED22/830 PSU D200 WH R	-
911401586441	DN393B LED22/840 PSU D200 WH R	-

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401571841	DN390B LED6/830 PSU D100 ALU GC	60 degree(s)	3000 K	104 lm/W	570 lumen
911401571941	DN390B LED6/840 PSU D100 ALU GC	60 degree(s)	4000 K	109 lm/W	600 lumen
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	60 degree(s)	3000 K	104 lm/W	570 lumen
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	60 degree(s)	4000 K	109 lm/W	600 lumen
911401575041	DN390B LED6/865 PSU D100 ALU WP GC	60 degree(s)	6500 K	109 lm/W	600 lumen
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	60 degree(s)	3000 K	111 lm/W	1,050 lumen
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	60 degree(s)	4000 K	116 lm/W	1,100 lumen
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	60 degree(s)	6500 K	116 lm/W	1,100 lumen
911401576541	DN391B LED11/830 PSU D100 ALU GC	60 degree(s)	3000 K	111 lm/W	1,050 lumen
911401576641	DN391B LED11/840 PSU D100 ALU GC	60 degree(s)	4000 K	116 lm/W	1,100 lumen
911401576741	DN391B LED11/830 PSD D100 ALU GC	60 degree(s)	3000 K	83 lm/W	950 lumen
911401576841	DN391B LED11/840 PSD D100 ALU GC	60 degree(s)	4000 K	82 lm/W	950 lumen
911401578041	DN390B LED6/830 PSU D100 ALU GM	60 degree(s)	3000 K	104 lm/W	570 lumen
911401578141	DN390B LED6/840 PSU D100 ALU GM	60 degree(s)	4000 K	109 lm/W	600 lumen

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401578241	DN390B LED6/865 PSU D100 ALU GM	60 degree(s)	6500 K	109 lm/W	600 lumen
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	60 degree(s)	3000 K	104 lm/W	570 lumen
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	60 degree(s)	4000 K	109 lm/W	600 lumen
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	60 degree(s)	6500 K	109 lm/W	600 lumen
911401571641	DN390B LED6/830 PSU D100 WH GC	72 degree(s)	3000 K	104 lm/W	570 lumen
911401571741	DN390B LED6/840 PSU D100 WH GC	72 degree(s)	4000 K	109 lm/W	600 lumen
911401577741	DN390B LED6/830 PSU D100 WH GM	72 degree(s)	3000 K	104 lm/W	570 lumen
911401577841	DN390B LED6/840 PSU D100 WH GM	72 degree(s)	4000 K	109 lm/W	600 lumen
911401577941	DN390B LED6/865 PSU D100 WH GM	72 degree(s)	6500 K	109 lm/W	600 lumen
911401582841	DN390B LED6/830 PSU D100 WH CAU	72 degree(s)	3000 K	104 lm/W	570 lumen
911401582941	DN390B LED6/840 PSU D100 WH CAU	72 degree(s)	4000 K	109 lm/W	600 lumen
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	72 degree(s)	3000 K	104 lm/W	570 lumen
911401583741	DN390B LED6/840 PSU D100 WH WP CAU	72 degree(s)	4000 K	109 lm/W	600 lumen
911401572341	DN391B LED11/830 PSU D150 ALU GC	60 degree(s)	3000 K	111 lm/W	1,050 lumen

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401572441	DN391B LED11/840 PSU D150 ALU GC	60 degree(s)	4000 K	116 lm/W	1,100 lumen
911401572541	DN391B LED11/865 PSU D150 ALU GC	60 degree(s)	6500 K	116 lm/W	1,100 lumen
911401572841	DN391B LED11/830 PSD D150 ALU GC	60 degree(s)	3000 K	91 lm/W	1,050 lumen
911401572941	DN391B LED11/840 PSD D150 ALU GC	60 degree(s)	4000 K	96 lm/W	1,100 lumen
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	60 degree(s)	3000 K	103 lm/W	1,500 lumen
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	60 degree(s)	6500 K	110 lm/W	1,600 lumen
911401575941	DN392B LED16/830 POE D150 ALU GC	60 degree(s)	3000 K	103 lm/W	1,500 lumen
911401576041	DN392B LED16/840 POE D150 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401577141	DN392B LED16/830 PSU D150 ALU GC	60 degree(s)	3000 K	103 lm/W	1,500 lumen
911401577241	DN392B LED16/840 PSU D150 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401577541	DN392B LED16/830 PSD D150 ALU GC	60 degree(s)	3000 K	97 lm/W	1,500 lumen
911401577641	DN392B LED16/840 PSD D150 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401578641	DN391B LED11/830 PSU D150 ALU GM	60 degree(s)	3000 K	111 lm/W	1,050 lumen
911401578741	DN391B LED11/840 PSU D150 ALU GM	60 degree(s)	4000 K	116 lm/W	1,100 lumen

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401578841	DN391B LED11/865 PSU D150 ALU GM	60 degree(s)	6500 K	116 lm/W	1,100 lumen
911401579241	DN392B LED16/830 PSU D150 ALU GM	60 degree(s)	3000 K	103 lm/W	1,500 lumen
911401579341	DN392B LED16/840 PSU D150 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401579441	DN392B LED16/865 PSU D150 ALU GM	60 degree(s)	6500 K	110 lm/W	1,600 lumen
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	60 degree(s)	3000 K	111 lm/W	1,050 lumen
911401581141	DN391B LED11/840 PSU D150 ALU WP GM	60 degree(s)	4000 K	116 lm/W	1,100 lumen
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	60 degree(s)	6500 K	116 lm/W	1,100 lumen
911401581841	DN391B LED11/830 PSD D150 ALU GM	60 degree(s)	3000 K	91 lm/W	1,050 lumen
911401581941	DN391B LED11/840 PSD D150 ALU GM	60 degree(s)	4000 K	96 lm/W	1,100 lumen
911401584441	DN391B LED11/830 PSD D150 ALU CAU	60 degree(s)	3000 K	91 lm/W	1,050 lumen
911401584541	DN391B LED11/840 PSD D150 ALU CAU	60 degree(s)	4000 K	96 lm/W	1,100 lumen
911401585641	DN392B LED16/830 PSD D150 ALU GM	60 degree(s)	3000 K	97 lm/W	1,500 lumen
911401585741	DN392B LED16/840 PSD D150 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401585941	DN391B LED11/830 PSU D150 ALU R	60 degree(s)	3000 K	111 lm/W	1,050 lumen
911401586141	DN391B LED11/840 PSU D150 ALU R	60 degree(s)	4000 K	116 lm/W	1,100 lumen

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401572041	DN391B LED11/830 PSU D150 WH GC	85 degree(s)	3000 K	111 lm/W	1,050 lumen
911401572141	DN391B LED11/840 PSU D150 WH GC	85 degree(s)	4000 K	116 lm/W	1,100 lumen
911401572241	DN391B LED11/865 PSU D150 WH GC	85 degree(s)	6500 K	116 lm/W	1,100 lumen
911401572641	DN391B LED11/830 PSD D150 WH GC	85 degree(s)	3000 K	91 lm/W	1,050 lumen
911401572741	DN391B LED11/840 PSD D150 WH GC	85 degree(s)	4000 K	96 lm/W	1,100 lumen
911401575741	DN392B LED16/830 POE D150 WH GC	85 degree(s)	3000 K	103 lm/W	1,500 lumen
911401575841	DN392B LED16/840 POE D150 WH GC	85 degree(s)	4000 K	110 lm/W	1,600 lumen
911401576941	DN392B LED16/830 PSU D150 WH GC	85 degree(s)	3000 K	103 lm/W	1,500 lumen
911401577041	DN392B LED16/840 PSU D150 WH GC	85 degree(s)	4000 K	110 lm/W	1,600 lumen
911401577341	DN392B LED16/830 PSD D150 WH GC	85 degree(s)	3000 K	97 lm/W	1,500 lumen
911401577441	DN392B LED16/840 PSD D150 WH GC	85 degree(s)	4000 K	110 lm/W	1,600 lumen
911401578341	DN391B LED11/830 PSU D150 WH GM	85 degree(s)	3000 K	111 lm/W	1,050 lumen
911401578441	DN391B LED11/840 PSU D150 WH GM	85 degree(s)	4000 K	116 lm/W	1,100 lumen
911401578541	DN391B LED11/865 PSU D150 WH GM	85 degree(s)	6500 K	116 lm/W	1,100 lumen
911401578941	DN392B LED16/830 PSU D150 WH GM	85 degree(s)	3000 K	103 lm/W	1,500 lumen
911401579041	DN392B LED16/840 PSU D150 WH GM	85 degree(s)	4000 K	110 lm/W	1,600 lumen

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401579141	DN392B LED16/865 PSU D150 WH GM	85 degree(s)	6500 K	110 lm/W	1,600 lumen
911401581641	DN391B LED11/830 PSD D150 WH GM	85 degree(s)	3000 K	91 lm/W	1,050 lumen
911401581741	DN391B LED11/840 PSD D150 WH GM	85 degree(s)	4000 K	96 lm/W	1,100 lumen
911401583041	DN391B LED11/830 PSU D150 WH CAU	85 degree(s)	3000 K	111 lm/W	1,050 lumen
911401583141	DN391B LED11/840 PSU D150 WH CAU	85 degree(s)	4000 K	116 lm/W	1,100 lumen
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	85 degree(s)	3000 K	111 lm/W	1,050 lumen
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	85 degree(s)	4000 K	116 lm/W	1,100 lumen
911401584241	DN391B LED11/830 PSD D150 WH CAU	85 degree(s)	3000 K	91 lm/W	1,050 lumen
911401584341	DN391B LED11/840 PSD D150 WH CAU	85 degree(s)	4000 K	96 lm/W	1,100 lumen
911401585441	DN392B LED16/830 PSD D150 WH GM	85 degree(s)	3000 K	97 lm/W	1,500 lumen
911401585541	DN392B LED16/840 PSD D150 WH GM	85 degree(s)	4000 K	110 lm/W	1,600 lumen
911401585841	DN391B LED11/830 PSU D150 WH R	85 degree(s)	3000 K	111 lm/W	1,050 lumen
911401586041	DN391B LED11/840 PSU D150 WH R	85 degree(s)	4000 K	116 lm/W	1,100 lumen
911401573341	DN392B LED16/830 PSU D200 ALU GC	60 degree(s)	3000 K	103 lm/W	1,500 lumen
911401573441	DN392B LED16/840 PSU D200 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lumen

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401573541	DN392B LED16/865 PSU D200 ALU GC	60 degree(s)	6500 K	110 lm/W	1,600 lumen
911401573841	DN392B LED16/830 PSD D200 ALU GC	60 degree(s)	3000 K	97 lm/W	1,500 lumen
911401573941	DN392B LED16/840 PSD D200 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401574241	DN393B LED22/830 PSU D200 ALU GC	60 degree(s)	3000 K	111 lm/W	2,100 lumen
911401574341	DN393B LED22/840 PSU D200 ALU GC	60 degree(s)	4000 K	116 lm/W	2,200 lumen
911401574641	DN393B LED22/830 PSD D200 ALU GC	60 degree(s)	3000 K	102 lm/W	2,100 lumen
911401574741	DN393B LED22/840 PSD D200 ALU GC	60 degree(s)	4000 K	107 lm/W	2,200 lumen
911401576341	DN393B LED22/830 POE D200 ALU GC	60 degree(s)	3000 K	102 lm/W	2,100 lumen
911401576441	DN393B LED22/840 POE D200 ALU GC	60 degree(s)	4000 K	107 lm/W	2,200 lumen
911401579841	DN392B LED16/830 PSU D200 ALU GM	60 degree(s)	3000 K	103 lm/W	1,500 lumen
911401579941	DN392B LED16/840 PSU D200 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401580041	DN392B LED16/865 PSU D200 ALU GM	60 degree(s)	6500 K	110 lm/W	1,600 lumen
911401580441	DN393B LED22/830 PSU D200 ALU GM	60 degree(s)	3000 K	111 lm/W	2,100 lumen
911401580541	DN393B LED22/840 PSU D200 ALU GM	60 degree(s)	4000 K	116 lm/W	2,200 lumen
911401580641	DN393B LED22/865 PSU D200 ALU GM	60 degree(s)	6500 K	116 lm/W	2,200 lumen
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	60 degree(s)	3000 K	111 lm/W	2,100 lumen

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	60 degree(s)	4000 K	116 lm/W	2,200 lumen
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	60 degree(s)	6500 K	116 lm/W	2,200 lumen
911401582241	DN392B LED16/830 PSD D200 ALU GM	60 degree(s)	3000 K	97 lm/W	1,500 lumen
911401582341	DN392B LED16/840 PSD D200 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401582641	DN393B LED22/830 PSD D200 ALU GM	60 degree(s)	3000 K	102 lm/W	2,100 lumen
911401582741	DN393B LED22/840 PSD D200 ALU GM	60 degree(s)	4000 K	107 lm/W	2,200 lumen
911401584841	DN392B LED16/830 PSD D200 ALU CAU	60 degree(s)	3000 K	97 lm/W	1,500 lumen
911401584941	DN392B LED16/840 PSD D200 ALU CAU	60 degree(s)	4000 K	110 lm/W	1,600 lumen
911401585241	DN393B LED22/830 PSD D200 ALU CAU	60 degree(s)	3000 K	102 lm/W	2,100 lumen
911401585341	DN393B LED22/840 PSD D200 ALU CAU	60 degree(s)	4000 K	107 lm/W	2,200 lumen
911401586341	DN393B LED22/830 PSU D200 ALU R	60 degree(s)	3000 K	111 lm/W	2,100 lumen
911401586541	DN393B LED22/840 PSU D200 ALU R	60 degree(s)	4000 K	116 lm/W	2,200 lumen
911401573041	DN392B LED16/830 PSU D200 WH GC	92 degree(s)	3000 K	103 lm/W	1,500 lumen
911401573141	DN392B LED16/840 PSU D200 WH GC	92 degree(s)	4000 K	110 lm/W	1,600 lumen
911401573241	DN392B LED16/865 PSU D200 WH GC	92 degree(s)	6500 K	110 lm/W	1,600 lumen

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401573641	DN392B LED16/830 PSD D200 WH GC	92 degree(s)	3000 K	97 lm/W	1,500 lumen
911401573741	DN392B LED16/840 PSD D200 WH GC	92 degree(s)	4000 K	110 lm/W	1,600 lumen
911401574041	DN393B LED22/830 PSU D200 WH GC	92 degree(s)	3000 K	111 lm/W	2,100 lumen
911401574141	DN393B LED22/840 PSU D200 WH GC	92 degree(s)	4000 K	116 lm/W	2,200 lumen
911401574441	DN393B LED22/830 PSD D200 WH GC	92 degree(s)	3000 K	102 lm/W	2,100 lumen
911401574541	DN393B LED22/840 PSD D200 WH GC	92 degree(s)	4000 K	107 lm/W	2,200 lumen
911401576141	DN393B LED22/830 POE D200 WH GC	92 degree(s)	3000 K	102 lm/W	2,100 lumen
911401576241	DN393B LED22/840 POE D200 WH GC	92 degree(s)	4000 K	107 lm/W	2,200 lumen
911401579541	DN392B LED16/830 PSU D200 WH GM	92 degree(s)	3000 K	103 lm/W	1,500 lumen
911401579641	DN392B LED16/840 PSU D200 WH GM	92 degree(s)	4000 K	110 lm/W	1,600 lumen
911401579741	DN392B LED16/865 PSU D200 WH GM	92 degree(s)	6500 K	110 lm/W	1,600 lumen
911401580141	DN393B LED22/830 PSU D200 WH GM	92 degree(s)	3000 K	111 lm/W	2,100 lumen
911401580241	DN393B LED22/840 PSU D200 WH GM	92 degree(s)	4000 K	116 lm/W	2,200 lumen
911401580341	DN393B LED22/865 PSU D200 WH GM	92 degree(s)	6500 K	116 lm/W	2,200 lumen
911401582041	DN392B LED16/830 PSD D200 WH GM	92 degree(s)	3000 K	97 lm/W	1,500 lumen
911401582141	DN392B LED16/840 PSD D200 WH GM	92 degree(s)	4000 K	110 lm/W	1,600 lumen

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401582441	DN393B LED22/830 PSD D200 WH GM	92 degree(s)	3000 K	102 lm/W	2,100 lumen
911401582541	DN393B LED22/840 PSD D200 WH GM	92 degree(s)	4000 K	107 lm/W	2,200 lumen
911401583241	DN392B LED16/830 PSU D200 WH CAU	92 degree(s)	3000 K	103 lm/W	1,500 lumen
911401583341	DN392B LED16/840 PSU D200 WH CAU	92 degree(s)	4000 K	110 lm/W	1,600 lumen
911401583441	DN393B LED22/830 PSU D200 WH CAU	92 degree(s)	3000 K	111 lm/W	2,100 lumen
911401583541	DN393B LED22/840 PSU D200 WH CAU	92 degree(s)	4000 K	116 lm/W	2,200 lumen
911401584041	DN393B LED22/830 PSU D200 WH WP CAU	92 degree(s)	3000 K	111 lm/W	2,100 lumen
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	92 degree(s)	4000 K	116 lm/W	2,200 lumen
911401584641	DN392B LED16/830 PSD D200 WH CAU	92 degree(s)	3000 K	97 lm/W	1,500 lumen
911401584741	DN392B LED16/840 PSD D200 WH CAU	92 degree(s)	4000 K	110 lm/W	1,600 lumen
911401585041	DN393B LED22/830 PSD D200 WH CAU	92 degree(s)	3000 K	102 lm/W	2,100 lumen
911401585141	DN393B LED22/840 PSD D200 WH CAU	92 degree(s)	4000 K	107 lm/W	2,200 lumen
911401586241	DN393B LED22/830 PSU D200 WH R	92 degree(s)	3000 K	111 lm/W	2,100 lumen
911401586441	DN393B LED22/840 PSU D200 WH R	92 degree(s)	4000 K	116 lm/W	2,200 lumen

Operating and Electrical

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401571841	DN390B LED6/830 PSU D100 ALU GC	220-240 V	50 or 60 Hz	5.5 W
911401571941	DN390B LED6/840 PSU D100 ALU GC	220-240 V	50 or 60 Hz	5.5 W
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	5.5 W
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	5.5 W
911401575041	DN390B LED6/865 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	5.5 W
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	9.5 W
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	9.5 W
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	9.5 W
911401575641	DN391B LED11/830 PSU D100 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401576641	DN391B LED11/840 PSU D100 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401576741	DN391B LED11/830 PSD D100 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401576841	DN391B LED11/840 PSD D100 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401578041	DN390B LED6/830 PSU D100 ALU GM	220-240 V	50 or 60 Hz	5.5 W
911401578141	DN390B LED6/840 PSU D100 ALU GM	220-240 V	50 or 60 Hz	5.5 W
911401578241	DN390B LED6/865 PSU D100 ALU GM	220-240 V	50 or 60 Hz	5.5 W
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	220-240 V	50 or 60 Hz	5.5 W
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	220-240 V	50 or 60 Hz	5.5 W
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	220-240 V	50 or 60 Hz	5.5 W
911401571641	DN390B LED6/830 PSU D100 WH GC	220-240 V	50 or 60 Hz	5.5 W
911401571741	DN390B LED6/840 PSU D100 WH GC	220-240 V	50 or 60 Hz	5.5 W
911401577741	DN390B LED6/830 PSU D100 WH GM	220-240 V	50 or 60 Hz	5.5 W
911401577841	DN390B LED6/840 PSU D100 WH GM	220-240 V	50 or 60 Hz	5.5 W
911401577941	DN390B LED6/865 PSU D100 WH GM	220-240 V	50 or 60 Hz	5.5 W
911401582841	DN390B LED6/830 PSU D100 WH CAU	220-240 V	50 or 60 Hz	5.5 W
911401582941	DN390B LED6/840 PSU D100 WH CAU	220-240 V	50 or 60 Hz	5.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	220-240 V	50 or 60 Hz	5.5 W
911401583741	DN390B LED6/840 PSU D100 WH WP CAU	220-240 V	50 or 60 Hz	5.5 W
911401572341	DN391B LED11/830 PSU D150 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401572441	DN391B LED11/840 PSU D150 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401572541	DN391B LED11/865 PSU D150 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401572841	DN391B LED11/830 PSD D150 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401572941	DN391B LED11/840 PSD D150 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	220-240 V	50 or 60 Hz	14.5 W
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	220-240 V	50 or 60 Hz	14.5 W
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	220-240 V	50 or 60 Hz	14.5 W
911401575941	DN392B LED16/830 POE D150 ALU GC	53 V	- Hz	14.5 W
911401576041	DN392B LED16/840 POE D150 ALU GC	53 V	- Hz	14.5 W
911401577141	DN392B LED16/830 PSU D150 ALU GC	220-240 V	50 or 60 Hz	14.5 W
911401577241	DN392B LED16/840 PSU D150 ALU GC	220-240 V	50 or 60 Hz	14.5 W
911401577541	DN392B LED16/830 PSD D150 ALU GC	220-240 V	50 or 60 Hz	15.5 W
911401577641	DN392B LED16/840 PSD D150 ALU GC	220-240 V	50 or 60 Hz	15.5 W
911401578641	DN391B LED11/830 PSU D150 ALU GM	220-240 V	50 or 60 Hz	9.5 W
911401578741	DN391B LED11/840 PSU D150 ALU GM	220-240 V	50 or 60 Hz	9.5 W
911401578841	DN391B LED11/865 PSU D150 ALU GM	220-240 V	50 or 60 Hz	9.5 W
911401579241	DN392B LED16/830 PSU D150 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401579341	DN392B LED16/840 PSU D150 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401579441	DN392B LED16/865 PSU D150 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	220-240 V	50 or 60 Hz	9.5 W
911401581141	DN391B LED11/840 PSU D150 ALU WP GM	220-240 V	50 or 60 Hz	9.5 W
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	220-240 V	50 or 60 Hz	9.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401581841	DN391B LED11/830 PSD D150 ALU GM	220-240 V	50 or 60 Hz	11.5 W
911401581941	DN391B LED11/840 PSD D150 ALU GM	220-240 V	50 or 60 Hz	11.5 W
911401584441	DN391B LED11/830 PSD D150 ALU CAU	220-240 V	50 or 60 Hz	11.5 W
911401584541	DN391B LED11/840 PSD D150 ALU CAU	220-240 V	50 or 60 Hz	11.5 W
911401585641	DN392B LED16/830 PSD D150 ALU GM	220-240 V	50 or 60 Hz	15.5 W
911401585741	DN392B LED16/840 PSD D150 ALU GM	220-240 V	50 or 60 Hz	15.5 W
911401585941	DN391B LED11/830 PSU D150 ALU R	220-240 V	50 or 60 Hz	9.5 W
911401586141	DN391B LED11/840 PSU D150 ALU R	220-240 V	50 or 60 Hz	9.5 W
911401572041	DN391B LED11/830 PSU D150 WH GC	220-240 V	50 or 60 Hz	9.5 W
911401572141	DN391B LED11/840 PSU D150 WH GC	220-240 V	50 or 60 Hz	9.5 W
911401572241	DN391B LED11/865 PSU D150 WH GC	220-240 V	50 or 60 Hz	9.5 W
911401572641	DN391B LED11/830 PSD D150 WH GC	220-240 V	50 or 60 Hz	11.5 W
911401572741	DN391B LED11/840 PSD D150 WH GC	220-240 V	50 or 60 Hz	11.5 W
911401575741	DN392B LED16/830 POE D150 WH GC	53 V	- Hz	14.5 W
911401575841	DN392B LED16/840 POE D150 WH GC	53 V	- Hz	14.5 W
911401576941	DN392B LED16/830 PSU D150 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401577041	DN392B LED16/840 PSU D150 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401577341	DN392B LED16/830 PSD D150 WH GC	220-240 V	50 or 60 Hz	15.5 W
911401577441	DN392B LED16/840 PSD D150 WH GC	220-240 V	50 or 60 Hz	15.5 W
911401578341	DN391B LED11/830 PSU D150 WH GM	220-240 V	50 or 60 Hz	9.5 W
911401578441	DN391B LED11/840 PSU D150 WH GM	220-240 V	50 or 60 Hz	9.5 W
911401578541	DN391B LED11/865 PSU D150 WH GM	220-240 V	50 or 60 Hz	9.5 W
911401578941	DN392B LED16/830 PSU D150 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401579041	DN392B LED16/840 PSU D150 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401579141	DN392B LED16/865 PSU D150 WH GM	220-240 V	50 or 60 Hz	14.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401581641	DN391B LED11/830 PSD D150 WH GM	220-240 V	50 or 60 Hz	11.5 W
911401581741	DN391B LED11/840 PSD D150 WH GM	220-240 V	50 or 60 Hz	11.5 W
911401583041	DN391B LED11/830 PSU D150 WH CAU	220-240 V	50 or 60 Hz	9.5 W
911401583141	DN391B LED11/840 PSU D150 WH CAU	220-240 V	50 or 60 Hz	9.5 W
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	220-240 V	50 or 60 Hz	9.5 W
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	220-240 V	50 or 60 Hz	9.5 W
911401584241	DN391B LED11/830 PSD D150 WH CAU	220-240 V	50 or 60 Hz	11.5 W
911401584341	DN391B LED11/840 PSD D150 WH CAU	220-240 V	50 or 60 Hz	11.5 W
911401585441	DN392B LED16/830 PSD D150 WH GM	220-240 V	50 or 60 Hz	15.5 W
911401585541	DN392B LED16/840 PSD D150 WH GM	220-240 V	50 or 60 Hz	15.5 W
911401585841	DN391B LED11/830 PSU D150 WH R	220-240 V	50 or 60 Hz	9.5 W
911401586041	DN391B LED11/840 PSU D150 WH R	220-240 V	50 or 60 Hz	9.5 W
911401573341	DN392B LED16/830 PSU D200 ALU GC	220-240 V	50 or 60 Hz	14.5 W
911401573441	DN392B LED16/840 PSU D200 ALU GC	220-240 V	50 or 60 Hz	14.5 W
911401573541	DN392B LED16/865 PSU D200 ALU GC	220-240 V	50 or 60 Hz	14.5 W
911401573841	DN392B LED16/830 PSD D200 ALU GC	220-240 V	50 or 60 Hz	15.5 W
911401573941	DN392B LED16/840 PSD D200 ALU GC	220-240 V	50 or 60 Hz	15.5 W
911401574241	DN393B LED22/830 PSU D200 ALU GC	220-240 V	50 or 60 Hz	19 W
911401574341	DN393B LED22/840 PSU D200 ALU GC	220-240 V	50 or 60 Hz	19 W
911401574641	DN393B LED22/830 PSD D200 ALU GC	220-240 V	50 or 60 Hz	20.5 W
911401574741	DN393B LED22/840 PSD D200 ALU GC	220-240 V	50 or 60 Hz	20.5 W
911401576341	DN393B LED22/830 POE D200 ALU GC	53 V	- Hz	20.5 W
911401576441	DN393B LED22/840 POE D200 ALU GC	53 V	- Hz	20.5 W
911401579841	DN392B LED16/830 PSU D200 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401579941	DN392B LED16/840 PSU D200 ALU GM	220-240 V	50 or 60 Hz	14.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
91140158004 1	DN392B LED16/865 PSU D200 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401580441	DN393B LED22/830 PSU D200 ALU GM	220-240 V	50 or 60 Hz	19 W
911401580541	DN393B LED22/840 PSU D200 ALU GM	220-240 V	50 or 60 Hz	19 W
911401580641	DN393B LED22/865 PSU D200 ALU GM	220-240 V	50 or 60 Hz	19 W
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	220-240 V	50 or 60 Hz	19 W
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	220-240 V	50 or 60 Hz	19 W
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	220-240 V	50 or 60 Hz	19 W
911401582241	DN392B LED16/830 PSD D200 ALU GM	220-240 V	50 or 60 Hz	15.5 W
911401582341	DN392B LED16/840 PSD D200 ALU GM	220-240 V	50 or 60 Hz	15.5 W
911401582641	DN393B LED22/830 PSD D200 ALU GM	220-240 V	50 or 60 Hz	20.5 W
911401582741	DN393B LED22/840 PSD D200 ALU GM	220-240 V	50 or 60 Hz	20.5 W
911401584841	DN392B LED16/830 PSD D200 ALU CAU	220-240 V	50 or 60 Hz	15.5 W
911401584941	DN392B LED16/840 PSD D200 ALU CAU	220-240 V	50 or 60 Hz	15.5 W
911401585241	DN393B LED22/830 PSD D200 ALU CAU	220-240 V	50 or 60 Hz	20.5 W
911401585341	DN393B LED22/840 PSD D200 ALU CAU	220-240 V	50 or 60 Hz	20.5 W
911401586341	DN393B LED22/830 PSU D200 ALU R	220-240 V	50 or 60 Hz	19 W
911401586541	DN393B LED22/840 PSU D200 ALU R	220-240 V	50 or 60 Hz	19 W
911401573041	DN392B LED16/830 PSU D200 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401573141	DN392B LED16/840 PSU D200 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401573241	DN392B LED16/865 PSU D200 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401573641	DN392B LED16/830 PSD D200 WH GC	220-240 V	50 or 60 Hz	15.5 W
911401573741	DN392B LED16/840 PSD D200 WH GC	220-240 V	50 or 60 Hz	15.5 W
911401574041	DN393B LED22/830 PSU D200 WH GC	220-240 V	50 or 60 Hz	19 W
911401574141	DN393B LED22/840 PSU D200 WH GC	220-240 V	50 or 60 Hz	19 W
911401574441	DN393B LED22/830 PSD D200 WH GC	220-240 V	50 or 60 Hz	20.5 W
911401574541	DN393B LED22/840 PSD D200 WH GC	220-240 V	50 or 60 Hz	20.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401576141	DN393B LED22/830 POE D200 WH GC	53 V	- Hz	20.5 W
911401576241	DN393B LED22/840 POE D200 WH GC	53 V	- Hz	20.5 W
911401579541	DN392B LED16/830 PSU D200 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401579641	DN392B LED16/840 PSU D200 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401579741	DN392B LED16/865 PSU D200 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401580141	DN393B LED22/830 PSU D200 WH GM	220-240 V	50 or 60 Hz	19 W
911401580241	DN393B LED22/840 PSU D200 WH GM	220-240 V	50 or 60 Hz	19 W
911401580341	DN393B LED22/865 PSU D200 WH GM	220-240 V	50 or 60 Hz	19 W
911401582041	DN392B LED16/830 PSD D200 WH GM	220-240 V	50 or 60 Hz	15.5 W
911401582141	DN392B LED16/840 PSD D200 WH GM	220-240 V	50 or 60 Hz	15.5 W
911401582441	DN393B LED22/830 PSD D200 WH GM	220-240 V	50 or 60 Hz	20.5 W
911401582541	DN393B LED22/840 PSD D200 WH GM	220-240 V	50 or 60 Hz	20.5 W
911401583241	DN392B LED16/830 PSU D200 WH CAU	220-240 V	50 or 60 Hz	14.5 W
911401583341	DN392B LED16/840 PSU D200 WH CAU	220-240 V	50 or 60 Hz	14.5 W
911401583441	DN393B LED22/830 PSU D200 WH CAU	220-240 V	50 or 60 Hz	19 W
911401583541	DN393B LED22/840 PSU D200 WH CAU	220-240 V	50 or 60 Hz	19 W
911401584041	DN393B LED22/830 PSU D200 WH WP CAU	220-240 V	50 or 60 Hz	19 W
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	220-240 V	50 or 60 Hz	19 W
911401584641	DN392B LED16/830 PSD D200 WH CAU	220-240 V	50 or 60 Hz	15.5 W
911401584741	DN392B LED16/840 PSD D200 WH CAU	220-240 V	50 or 60 Hz	15.5 W
911401585041	DN393B LED22/830 PSD D200 WH CAU	220-240 V	50 or 60 Hz	20.5 W
911401585141	DN393B LED22/840 PSD D200 WH CAU	220-240 V	50 or 60 Hz	20.5 W
911401586241	DN393B LED22/830 PSU D200 WH R	220-240 V	50 or 60 Hz	19 W
911401586441	DN393B LED22/840 PSU D200 WH R	220-240 V	50 or 60 Hz	19 W

Temperature

Order Code	Full Product Name	Ambient temperature range	Order Code	Full Product Name	Ambient temperature range
911401571841	DN390B LED6/830 PSU D100 ALU GC	-20 to +40 °C	911401581941	DN391B LED11/840 PSD D150 ALU GM	-20 to +40 °C
911401571941	DN390B LED6/840 PSU D100 ALU GC	-20 to +40 °C	911401584441	DN391B LED11/830 PSD D150 ALU CAU	-20 to +40 °C
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	-20 to +40 °C	911401584541	DN391B LED11/840 PSD D150 ALU CAU	-20 to +40 °C
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	-20 to +40 °C	911401585641	DN392B LED16/830 PSD D150 ALU GM	-20 to +40 °C
911401575041	DN390B LED6/865 PSU D100 ALU WP GC	-20 to +40 °C	911401585741	DN392B LED16/840 PSD D150 ALU GM	-20 to +40 °C
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	-20 to +40 °C	911401585941	DN391B LED11/830 PSU D150 ALU R	-20 to +40 °C
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	-20 to +40 °C	911401586141	DN391B LED11/840 PSU D150 ALU R	-20 to +40 °C
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	-20 to +40 °C	911401572041	DN391B LED11/830 PSU D150 WH GC	-20 to +40 °C
911401576541	DN391B LED11/830 PSU D100 ALU GC	-20 to +40 °C	911401572141	DN391B LED11/840 PSU D150 WH GC	-20 to +40 °C
911401576641	DN391B LED11/840 PSU D100 ALU GC	-20 to +40 °C	911401572241	DN391B LED11/865 PSU D150 WH GC	-20 to +40 °C
911401576741	DN391B LED11/830 PSD D100 ALU GC	-20 to +40 °C	911401572641	DN391B LED11/830 PSD D150 WH GC	-20 to +40 °C
911401576841	DN391B LED11/840 PSD D100 ALU GC	-20 to +40 °C	911401572741	DN391B LED11/840 PSD D150 WH GC	-20 to +40 °C
911401578041	DN390B LED6/830 PSU D100 ALU GM	-20 to +40 °C	911401575741	DN392B LED16/830 POE D150 WH GC	0 to +40 °C
911401578141	DN390B LED6/840 PSU D100 ALU GM	-20 to +40 °C	911401575841	DN392B LED16/840 POE D150 WH GC	0 to +40 °C
911401578241	DN390B LED6/865 PSU D100 ALU GM	-20 to +40 °C	911401576941	DN392B LED16/830 PSU D150 WH GC	-20 to +40 °C
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	-20 to +40 °C	911401577041	DN392B LED16/840 PSU D150 WH GC	-20 to +40 °C
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	-20 to +40 °C	911401577341	DN392B LED16/830 PSD D150 WH GC	-20 to +40 °C
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	-20 to +40 °C	911401577441	DN392B LED16/840 PSD D150 WH GC	-20 to +40 °C
911401571641	DN390B LED6/830 PSU D100 WH GC	-20 to +40 °C	911401578341	DN391B LED11/830 PSU D150 WH GM	-20 to +40 °C
911401571741	DN390B LED6/840 PSU D100 WH GC	-20 to +40 °C	911401578441	DN391B LED11/840 PSU D150 WH GM	-20 to +40 °C
911401577741	DN390B LED6/830 PSU D100 WH GM	-20 to +40 °C	911401578541	DN391B LED11/865 PSU D150 WH GM	-20 to +40 °C
911401577841	DN390B LED6/840 PSU D100 WH GM	-20 to +40 °C	911401578941	DN392B LED16/830 PSU D150 WH GM	-20 to +40 °C
911401577941	DN390B LED6/865 PSU D100 WH GM	-20 to +40 °C	911401579041	DN392B LED16/840 PSU D150 WH GM	-20 to +40 °C
911401582841	DN390B LED6/830 PSU D100 WH CAU	-20 to +40 °C	911401579141	DN392B LED16/865 PSU D150 WH GM	-20 to +40 °C
911401582941	DN390B LED6/840 PSU D100 WH CAU	-20 to +40 °C	911401581641	DN391B LED11/830 PSD D150 WH GM	-20 to +40 °C
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	-20 to +40 °C	911401581741	DN391B LED11/840 PSD D150 WH GM	-20 to +40 °C
911401583741	DN390B LED6/840 PSU D100 WH WP CAU	-20 to +40 °C	911401583041	DN391B LED11/830 PSU D150 WH CAU	-20 to +40 °C
911401572341	DN391B LED11/830 PSU D150 ALU GC	-20 to +40 °C	911401583141	DN391B LED11/840 PSU D150 WH CAU	-20 to +40 °C
911401572441	DN391B LED11/840 PSU D150 ALU GC	-20 to +40 °C	911401583841	DN391B LED11/830 PSU D150 WH WP CAU	-20 to +40 °C
911401572541	DN391B LED11/865 PSU D150 ALU GC	-20 to +40 °C	911401583941	DN391B LED11/840 PSU D150 WH WP CAU	-20 to +40 °C
911401572841	DN391B LED11/830 PSD D150 ALU GC	-20 to +40 °C	911401584241	DN391B LED11/830 PSD D150 WH CAU	-20 to +40 °C
911401572941	DN391B LED11/840 PSD D150 ALU GC	-20 to +40 °C	911401584341	DN391B LED11/840 PSD D150 WH CAU	-20 to +40 °C
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	-20 to +40 °C	911401585441	DN392B LED16/830 PSD D150 WH GM	-20 to +40 °C
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	-20 to +40 °C	911401585541	DN392B LED16/840 PSD D150 WH GM	-20 to +40 °C
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	-20 to +40 °C	911401585841	DN391B LED11/830 PSU D150 WH R	-20 to +40 °C
911401575941	DN392B LED16/830 POE D150 ALU GC	0 to +40 °C	911401586041	DN391B LED11/840 PSU D150 WH R	-20 to +40 °C
911401576041	DN392B LED16/840 POE D150 ALU GC	0 to +40 °C	911401573341	DN392B LED16/830 PSU D200 ALU GC	-20 to +40 °C
911401577141	DN392B LED16/830 PSU D150 ALU GC	-20 to +40 °C	911401573441	DN392B LED16/840 PSU D200 ALU GC	-20 to +40 °C
911401577241	DN392B LED16/840 PSU D150 ALU GC	-20 to +40 °C	911401573541	DN392B LED16/865 PSU D200 ALU GC	-20 to +40 °C
911401577541	DN392B LED16/830 PSD D150 ALU GC	0 to +40 °C	911401573841	DN392B LED16/830 PSD D200 ALU GC	-20 to +40 °C
911401577641	DN392B LED16/840 PSD D150 ALU GC	-20 to +40 °C	911401573941	DN392B LED16/840 PSD D200 ALU GC	-20 to +40 °C
911401578641	DN391B LED11/830 PSU D150 ALU GM	-20 to +40 °C	911401574241	DN393B LED22/830 PSU D200 ALU GC	-20 to +40 °C
911401578741	DN391B LED11/840 PSU D150 ALU GM	-20 to +40 °C	911401574341	DN393B LED22/840 PSU D200 ALU GC	-20 to +40 °C
911401578841	DN391B LED11/865 PSU D150 ALU GM	-20 to +40 °C	911401574641	DN393B LED22/830 PSD D200 ALU GC	-20 to +40 °C
911401579241	DN392B LED16/830 PSU D150 ALU GM	-20 to +40 °C	911401574741	DN393B LED22/840 PSD D200 ALU GC	-20 to +40 °C
911401579341	DN392B LED16/840 PSU D150 ALU GM	-20 to +40 °C	911401576341	DN393B LED22/830 POE D200 ALU GC	0 to +40 °C
911401579441	DN392B LED16/865 PSU D150 ALU GM	-20 to +40 °C	911401576441	DN393B LED22/840 POE D200 ALU GC	0 to +40 °C
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	-20 to +40 °C	911401579841	DN392B LED16/830 PSU D200 ALU GM	-20 to +40 °C
911401581141	DN391B LED11/840 PSU D150 ALU WP GM	-20 to +40 °C	911401579941	DN392B LED16/840 PSU D200 ALU GM	-20 to +40 °C
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	-20 to +40 °C	911401580041	DN392B LED16/865 PSU D200 ALU GM	-20 to +40 °C
911401581841	DN391B LED11/830 PSD D150 ALU GM	-20 to +40 °C			

Order Code	Full Product Name	Ambient temperature range
911401580441	DN393B LED22/830 PSU D200 ALU GM	-20 to +40 °C
911401580541	DN393B LED22/840 PSU D200 ALU GM	-20 to +40 °C
911401580641	DN393B LED22/865 PSU D200 ALU GM	-20 to +40 °C
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	-20 to +40 °C
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	-20 to +40 °C
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	-20 to +40 °C
911401582241	DN392B LED16/830 PSD D200 ALU GM	-20 to +40 °C
911401582341	DN392B LED16/840 PSD D200 ALU GM	-20 to +40 °C
911401582641	DN393B LED22/830 PSD D200 ALU GM	-20 to +40 °C
911401582741	DN393B LED22/840 PSD D200 ALU GM	-20 to +40 °C
911401584841	DN392B LED16/830 PSD D200 ALU CAU	-20 to +40 °C
911401584941	DN392B LED16/840 PSD D200 ALU CAU	-20 to +40 °C
911401585241	DN393B LED22/830 PSD D200 ALU CAU	-20 to +40 °C
911401585341	DN393B LED22/840 PSD D200 ALU CAU	-20 to +40 °C
911401586341	DN393B LED22/830 PSU D200 ALU R	-20 to +40 °C
911401586541	DN393B LED22/840 PSU D200 ALU R	-20 to +40 °C
911401573041	DN392B LED16/830 PSU D200 WH GC	-20 to +40 °C
911401573141	DN392B LED16/840 PSU D200 WH GC	-20 to +40 °C
911401573241	DN392B LED16/865 PSU D200 WH GC	-20 to +40 °C
911401573641	DN392B LED16/830 PSD D200 WH GC	-20 to +40 °C
911401573741	DN392B LED16/840 PSD D200 WH GC	-20 to +40 °C
911401574041	DN393B LED22/830 PSU D200 WH GC	-20 to +40 °C
911401574141	DN393B LED22/840 PSU D200 WH GC	-20 to +40 °C
911401574441	DN393B LED22/830 PSD D200 WH GC	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401574541	DN393B LED22/840 PSD D200 WH GC	-20 to +40 °C
911401576141	DN393B LED22/830 POE D200 WH GC	0 to +40 °C
911401576241	DN393B LED22/840 POE D200 WH GC	0 to +40 °C
911401579541	DN392B LED16/830 PSU D200 WH GM	-20 to +40 °C
911401579641	DN392B LED16/840 PSU D200 WH GM	-20 to +40 °C
911401579741	DN392B LED16/865 PSU D200 WH GM	-20 to +40 °C
911401580241	DN393B LED22/830 PSU D200 WH GM	-20 to +40 °C
911401580341	DN393B LED22/865 PSU D200 WH GM	-20 to +40 °C
911401582041	DN392B LED16/830 PSD D200 WH GM	-20 to +40 °C
911401582141	DN392B LED16/840 PSD D200 WH GM	-20 to +40 °C
911401582441	DN393B LED22/830 PSD D200 WH GM	-20 to +40 °C
911401582541	DN393B LED22/840 PSD D200 WH GM	-20 to +40 °C
911401583241	DN392B LED16/830 PSU D200 WH CAU	-20 to +40 °C
911401583341	DN392B LED16/840 PSU D200 WH CAU	-20 to +40 °C
911401583441	DN393B LED22/830 PSU D200 WH CAU	-20 to +40 °C
911401583541	DN393B LED22/840 PSU D200 WH CAU	-20 to +40 °C
911401584041	DN393B LED22/830 PSU D200 WH WP CAU	-20 to +40 °C
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	-20 to +40 °C
911401584641	DN392B LED16/830 PSD D200 WH CAU	-20 to +40 °C
911401584741	DN392B LED16/840 PSD D200 WH CAU	-20 to +40 °C
911401585041	DN393B LED22/830 PSD D200 WH CAU	-20 to +40 °C
911401585141	DN393B LED22/840 PSD D200 WH CAU	-20 to +40 °C
911401586241	DN393B LED22/830 PSU D200 WH R	-20 to +40 °C
911401586441	DN393B LED22/840 PSU D200 WH R	-20 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401571841	DN390B LED6/830 PSU D100 ALU GC	No
911401571941	DN390B LED6/840 PSU D100 ALU GC	No
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	No
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	No
911401575041	DN390B LED6/865 PSU D100 ALU WP GC	No
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	No
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	No
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	No
911401576541	DN391B LED11/830 PSU D100 ALU GC	No
911401576641	DN391B LED11/840 PSU D100 ALU GC	No
911401576741	DN391B LED11/830 PSD D100 ALU GC	Yes
911401576841	DN391B LED11/840 PSD D100 ALU GC	Yes
911401578041	DN390B LED6/830 PSU D100 ALU GM	No
911401578141	DN390B LED6/840 PSU D100 ALU GM	No
911401578241	DN390B LED6/865 PSU D100 ALU GM	No
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	No
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	No
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	No
911401571641	DN390B LED6/830 PSU D100 WH GC	No
911401571741	DN390B LED6/840 PSU D100 WH GC	No
911401577741	DN390B LED6/830 PSU D100 WH GM	No

Order Code	Full Product Name	Dimmable
911401577841	DN390B LED6/840 PSU D100 WH GM	No
911401577941	DN390B LED6/865 PSU D100 WH GM	No
911401582841	DN390B LED6/830 PSU D100 WH CAU	No
911401582941	DN390B LED6/840 PSU D100 WH CAU	No
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	No
911401583741	DN390B LED6/840 PSU D100 WH WP CAU	No
911401572341	DN391B LED11/830 PSU D150 ALU GC	No
911401572441	DN391B LED11/840 PSU D150 ALU GC	No
911401572541	DN391B LED11/865 PSU D150 ALU GC	No
911401572841	DN391B LED11/830 PSD D150 ALU GC	Yes
911401572941	DN391B LED11/840 PSD D150 ALU GC	Yes
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	No
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	No
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	No
911401575941	DN392B LED16/830 POE D150 ALU GC	Yes
911401576041	DN392B LED16/840 POE D150 ALU GC	Yes
911401577141	DN392B LED16/830 PSU D150 ALU GC	No
911401577241	DN392B LED16/840 PSU D150 ALU GC	No
911401577541	DN392B LED16/830 PSD D150 ALU GC	Yes
911401577641	DN392B LED16/840 PSD D150 ALU GC	Yes
911401578641	DN391B LED11/830 PSU D150 ALU GM	No

Order Code	Full Product Name	Dimmable
911401578741	DN391B LED11/840 PSU D150 ALU GM	No
911401578841	DN391B LED11/865 PSU D150 ALU GM	No
911401579241	DN392B LED16/830 PSU D150 ALU GM	No
911401579341	DN392B LED16/840 PSU D150 ALU GM	No
911401579441	DN392B LED16/865 PSU D150 ALU GM	No
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	No
911401581141	DN391B LED11/840 PSU D150 ALU WP GM	No
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	No
911401581841	DN391B LED11/830 PSD D150 ALU GM	Yes
911401581941	DN391B LED11/840 PSD D150 ALU GM	Yes
911401584441	DN391B LED11/830 PSD D150 ALU CAU	Yes
911401584541	DN391B LED11/840 PSD D150 ALU CAU	Yes
911401585641	DN392B LED16/830 PSD D150 ALU GM	Yes
911401585741	DN392B LED16/840 PSD D150 ALU GM	Yes
911401585941	DN391B LED11/830 PSU D150 ALU R	No
911401586141	DN391B LED11/840 PSU D150 ALU R	No
911401572041	DN391B LED11/830 PSU D150 WH GC	No
911401572141	DN391B LED11/840 PSU D150 WH GC	No
911401572241	DN391B LED11/865 PSU D150 WH GC	No
911401572641	DN391B LED11/830 PSD D150 WH GC	Yes
911401572741	DN391B LED11/840 PSD D150 WH GC	Yes
911401575741	DN392B LED16/830 POE D150 WH GC	Yes
911401575841	DN392B LED16/840 POE D150 WH GC	Yes
911401576941	DN392B LED16/830 PSU D150 WH GC	No
911401577041	DN392B LED16/840 PSU D150 WH GC	No
911401577341	DN392B LED16/830 PSD D150 WH GC	Yes
911401577441	DN392B LED16/840 PSD D150 WH GC	Yes
911401578341	DN391B LED11/830 PSU D150 WH GM	No
911401578441	DN391B LED11/840 PSU D150 WH GM	No
911401578541	DN391B LED11/865 PSU D150 WH GM	No
911401578941	DN392B LED16/830 PSU D150 WH GM	No
911401579041	DN392B LED16/840 PSU D150 WH GM	No
911401579141	DN392B LED16/865 PSU D150 WH GM	No
911401581641	DN391B LED11/830 PSD D150 WH GM	Yes
911401581741	DN391B LED11/840 PSD D150 WH GM	Yes
911401583041	DN391B LED11/830 PSU D150 WH CAU	No
911401583141	DN391B LED11/840 PSU D150 WH CAU	No
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	No
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	No
911401584241	DN391B LED11/830 PSD D150 WH CAU	Yes
911401584341	DN391B LED11/840 PSD D150 WH CAU	Yes
911401585441	DN392B LED16/830 PSD D150 WH GM	Yes
911401585541	DN392B LED16/840 PSD D150 WH GM	Yes
911401585841	DN391B LED11/830 PSU D150 WH R	No
911401586041	DN391B LED11/840 PSU D150 WH R	No
911401573341	DN392B LED16/830 PSU D200 ALU GC	No
911401573441	DN392B LED16/840 PSU D200 ALU GC	No
911401573541	DN392B LED16/865 PSU D200 ALU GC	No
911401573841	DN392B LED16/830 PSD D200 ALU GC	Yes
911401573941	DN392B LED16/840 PSD D200 ALU GC	Yes
911401574241	DN393B LED22/830 PSU D200 ALU GC	No
911401574341	DN393B LED22/840 PSU D200 ALU GC	No

Order Code	Full Product Name	Dimmable
911401574641	DN393B LED22/830 PSD D200 ALU GC	Yes
911401574741	DN393B LED22/840 PSD D200 ALU GC	Yes
911401576341	DN393B LED22/830 POE D200 ALU GC	Yes
911401576441	DN393B LED22/840 POE D200 ALU GC	Yes
911401579841	DN392B LED16/830 PSU D200 ALU GM	No
911401579941	DN392B LED16/840 PSU D200 ALU GM	No
911401580041	DN392B LED16/865 PSU D200 ALU GM	No
911401580441	DN393B LED22/830 PSU D200 ALU GM	No
911401580541	DN393B LED22/840 PSU D200 ALU GM	No
911401580641	DN393B LED22/865 PSU D200 ALU GM	No
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	No
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	No
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	No
911401582241	DN392B LED16/830 PSD D200 ALU GM	Yes
911401582341	DN392B LED16/840 PSD D200 ALU GM	Yes
911401582641	DN393B LED22/830 PSD D200 ALU GM	Yes
911401582741	DN393B LED22/840 PSD D200 ALU GM	Yes
911401584841	DN392B LED16/830 PSD D200 ALU CAU	Yes
911401584941	DN392B LED16/840 PSD D200 ALU CAU	Yes
911401585241	DN393B LED22/830 PSD D200 ALU CAU	Yes
911401585341	DN393B LED22/840 PSD D200 ALU CAU	Yes
911401586341	DN393B LED22/830 PSU D200 ALU R	No
911401586541	DN393B LED22/840 PSU D200 ALU R	No
911401573041	DN392B LED16/830 PSU D200 WH GC	No
911401573141	DN392B LED16/840 PSU D200 WH GC	No
911401573241	DN392B LED16/865 PSU D200 WH GC	No
911401573641	DN392B LED16/830 PSD D200 WH GC	Yes
911401573741	DN392B LED16/840 PSD D200 WH GC	Yes
911401574041	DN393B LED22/830 PSU D200 WH GC	No
911401574141	DN393B LED22/840 PSU D200 WH GC	No
911401574441	DN393B LED22/830 PSD D200 WH GC	Yes
911401574541	DN393B LED22/840 PSD D200 WH GC	Yes
911401576141	DN393B LED22/830 POE D200 WH GC	Yes
911401576241	DN393B LED22/840 POE D200 WH GC	Yes
911401579541	DN392B LED16/830 PSU D200 WH GM	No
911401579641	DN392B LED16/840 PSU D200 WH GM	No
911401579741	DN392B LED16/865 PSU D200 WH GM	No
911401580141	DN393B LED22/830 PSU D200 WH GM	No
911401580241	DN393B LED22/840 PSU D200 WH GM	No
911401580341	DN393B LED22/865 PSU D200 WH GM	No
911401582041	DN392B LED16/830 PSD D200 WH GM	Yes
911401582141	DN392B LED16/840 PSD D200 WH GM	Yes
911401582441	DN393B LED22/830 PSD D200 WH GM	Yes
911401582541	DN393B LED22/840 PSD D200 WH GM	Yes
911401583241	DN392B LED16/830 PSU D200 WH CAU	No
911401583341	DN392B LED16/840 PSU D200 WH CAU	No
911401583441	DN393B LED22/830 PSU D200 WH CAU	No
911401583541	DN393B LED22/840 PSU D200 WH CAU	No
911401584041	DN393B LED22/830 PSU D200 WH WP CAU	No
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	No
911401584641	DN392B LED16/830 PSD D200 WH CAU	Yes
911401584741	DN392B LED16/840 PSD D200 WH CAU	Yes

Order Code	Full Product Name	Dimmable
911401585041	DN393B LED22/830 PSD D200 WH CAU	Yes
911401585141	DN393B LED22/840 PSD D200 WH CAU	Yes

Order Code	Full Product Name	Dimmable
911401586241	DN393B LED22/830 PSU D200 WH R	No
911401586441	DN393B LED22/840 PSU D200 WH R	No

Approval and Application

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401571841	DN390B LED6/830 PSU D100 ALU GC	Safety class I	IP20
911401571941	DN390B LED6/840 PSU D100 ALU GC	Safety class I	IP20
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	Safety class I	IP20/54
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	Safety class I	IP20/54
911401575041	DN390B LED6/865 PSU D100 ALU WP GC	Safety class I	IP20/54
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	Safety class I	IP20/54
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	Safety class I	IP20/54
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	Safety class I	IP20/54
911401576541	DN391B LED11/830 PSU D100 ALU GC	Safety class I	IP20
911401576641	DN391B LED11/840 PSU D100 ALU GC	Safety class I	IP20
911401576741	DN391B LED11/830 PSD D100 ALU GC	Safety class I	IP20
911401576841	DN391B LED11/840 PSD D100 ALU GC	Safety class I	IP20
911401578041	DN390B LED6/830 PSU D100 ALU GM	Safety class I	IP20
911401578141	DN390B LED6/840 PSU D100 ALU GM	Safety class I	IP20
911401578241	DN390B LED6/865 PSU D100 ALU GM	Safety class I	IP20
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	Safety class I	IP20/54
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	Safety class I	IP20/54
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	Safety class I	IP20/54
911401571641	DN390B LED6/830 PSU D100 WH GC	Safety class I	IP20
911401571741	DN390B LED6/840 PSU D100 WH GC	Safety class I	IP20
911401577741	DN390B LED6/830 PSU D100 WH GM	Safety class I	IP20
911401577841	DN390B LED6/840 PSU D100 WH GM	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401577941	DN390B LED6/865 PSU D100 WH GM	Safety class I	IP20
911401582841	DN390B LED6/830 PSU D100 WH CAU	Safety class I	IP20
911401582941	DN390B LED6/840 PSU D100 WH CAU	Safety class I	IP20
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	Safety class I	IP20/54
911401583741	DN390B LED6/840 PSU D100 WH WP CAU	Safety class I	IP20/54
911401572341	DN391B LED11/830 PSU D150 ALU GC	Safety class I	IP20
911401572441	DN391B LED11/840 PSU D150 ALU GC	Safety class I	IP20
911401572541	DN391B LED11/865 PSU D150 ALU GC	Safety class I	IP20
911401572841	DN391B LED11/830 PSD D150 ALU GC	Safety class I	IP20
911401572941	DN391B LED11/840 PSD D150 ALU GC	Safety class I	IP20
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	Safety class I	IP20/54
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	Safety class I	IP20/54
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	Safety class I	IP20/54
911401575941	DN392B LED16/830 POE D150 ALU GC	Safety class III	IP20
911401576041	DN392B LED16/840 POE D150 ALU GC	Safety class III	IP20
911401577141	DN392B LED16/830 PSU D150 ALU GC	Safety class I	IP20
911401577241	DN392B LED16/840 PSU D150 ALU GC	Safety class I	IP20
911401577541	DN392B LED16/830 PSD D150 ALU GC	Safety class I	IP20
911401577641	DN392B LED16/840 PSD D150 ALU GC	Safety class I	IP20
911401578641	DN391B LED11/830 PSU D150 ALU GM	Safety class I	IP20
911401578741	DN391B LED11/840 PSU D150 ALU GM	Safety class I	IP20
911401578841	DN391B LED11/865 PSU D150 ALU GM	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401579241	DN392B LED16/830 PSU D150 ALU GM	Safety class I	IP20
911401579341	DN392B LED16/840 PSU D150 ALU GM	Safety class I	IP20
911401579441	DN392B LED16/865 PSU D150 ALU GM	Safety class I	IP20
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	Safety class I	IP20/54
911401581141	DN391B LED11/840 PSU D150 ALU WP GM	Safety class I	IP20/54
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	Safety class I	IP20/54
911401581841	DN391B LED11/830 PSD D150 ALU GM	Safety class I	IP20
911401581941	DN391B LED11/840 PSD D150 ALU GM	Safety class I	IP20
911401584441	DN391B LED11/830 PSD D150 ALU CAU	Safety class I	IP20
911401584541	DN391B LED11/840 PSD D150 ALU CAU	Safety class I	IP20
911401585641	DN392B LED16/830 PSD D150 ALU GM	Safety class I	IP20
911401585741	DN392B LED16/840 PSD D150 ALU GM	Safety class I	IP20
911401585941	DN391B LED11/830 PSU D150 ALU R	Safety class II	IP20
911401586141	DN391B LED11/840 PSU D150 ALU R	Safety class II	IP20
911401572041	DN391B LED11/830 PSU D150 WH GC	Safety class I	IP20
911401572141	DN391B LED11/840 PSU D150 WH GC	Safety class I	IP20
911401572241	DN391B LED11/865 PSU D150 WH GC	Safety class I	IP20
911401572641	DN391B LED11/830 PSD D150 WH GC	Safety class I	IP20
911401572741	DN391B LED11/840 PSD D150 WH GC	Safety class I	IP20
911401575741	DN392B LED16/830 POE D150 WH GC	Safety class III	IP20
911401575841	DN392B LED16/840 POE D150 WH GC	Safety class III	IP20
911401576941	DN392B LED16/830 PSU D150 WH GC	Safety class I	IP20
911401577041	DN392B LED16/840 PSU D150 WH GC	Safety class I	IP20
911401577341	DN392B LED16/830 PSD D150 WH GC	Safety class I	IP20
911401577441	DN392B LED16/840 PSD D150 WH GC	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401578341	DN391B LED11/830 PSU D150 WH GM	Safety class I	IP20
911401578441	DN391B LED11/840 PSU D150 WH GM	Safety class I	IP20
911401578541	DN391B LED11/865 PSU D150 WH GM	Safety class I	IP20
911401578941	DN392B LED16/830 PSU D150 WH GM	Safety class I	IP20
911401579041	DN392B LED16/840 PSU D150 WH GM	Safety class I	IP20
911401579141	DN392B LED16/865 PSU D150 WH GM	Safety class I	IP20
911401581641	DN391B LED11/830 PSD D150 WH GM	Safety class I	IP20
911401581741	DN391B LED11/840 PSD D150 WH GM	Safety class I	IP20
911401583041	DN391B LED11/830 PSU D150 WH CAU	Safety class I	IP20
911401583141	DN391B LED11/840 PSU D150 WH CAU	Safety class I	IP20
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	Safety class I	IP20/54
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	Safety class I	IP20/54
911401584241	DN391B LED11/830 PSD D150 WH CAU	Safety class I	IP20
911401584341	DN391B LED11/840 PSD D150 WH CAU	Safety class I	IP20
911401585441	DN392B LED16/830 PSD D150 WH GM	Safety class I	IP20
911401585541	DN392B LED16/840 PSD D150 WH GM	Safety class I	IP20
911401585841	DN391B LED11/830 PSU D150 WH R	Safety class II	IP20
911401586041	DN391B LED11/840 PSU D150 WH R	Safety class II	IP20
911401573341	DN392B LED16/830 PSU D200 ALU GC	Safety class I	IP20
911401573441	DN392B LED16/840 PSU D200 ALU GC	Safety class I	IP20
911401573541	DN392B LED16/865 PSU D200 ALU GC	Safety class I	IP20
911401573841	DN392B LED16/830 PSD D200 ALU GC	Safety class I	IP20
911401573941	DN392B LED16/840 PSD D200 ALU GC	Safety class I	IP20
911401574241	DN393B LED22/830 PSU D200 ALU GC	Safety class I	IP20
911401574341	DN393B LED22/840 PSU D200 ALU GC	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401574641	DN393B LED22/830 PSD D200 ALU GC	Safety class I	IP20
911401574741	DN393B LED22/840 PSD D200 ALU GC	Safety class I	IP20
911401576341	DN393B LED22/830 POE D200 ALU GC	Safety class III	IP20
911401576441	DN393B LED22/840 POE D200 ALU GC	Safety class III	IP20
911401579841	DN392B LED16/830 PSU D200 ALU GM	Safety class I	IP20
911401579941	DN392B LED16/840 PSU D200 ALU GM	Safety class I	IP20
911401580041	DN392B LED16/865 PSU D200 ALU GM	Safety class I	IP20
911401580441	DN393B LED22/830 PSU D200 ALU GM	Safety class I	IP20
911401580541	DN393B LED22/840 PSU D200 ALU GM	Safety class I	IP20
911401580641	DN393B LED22/865 PSU D200 ALU GM	Safety class I	IP20
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	Safety class I	IP20/54
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	Safety class I	IP20/54
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	Safety class I	IP20/54
911401582241	DN392B LED16/830 PSD D200 ALU GM	Safety class I	IP20
911401582341	DN392B LED16/840 PSD D200 ALU GM	Safety class I	IP20
911401582641	DN393B LED22/830 PSD D200 ALU GM	Safety class I	IP20
911401582741	DN393B LED22/840 PSD D200 ALU GM	Safety class I	IP20
911401584841	DN392B LED16/830 PSD D200 ALU CAU	Safety class I	IP20
911401584941	DN392B LED16/840 PSD D200 ALU CAU	Safety class I	IP20
911401585241	DN393B LED22/830 PSD D200 ALU CAU	Safety class I	IP20
911401585341	DN393B LED22/840 PSD D200 ALU CAU	Safety class I	IP20
911401586341	DN393B LED22/830 PSU D200 ALU R	Safety class II	IP20
911401586541	DN393B LED22/840 PSU D200 ALU R	Safety class II	IP20
911401573041	DN392B LED16/830 PSU D200 WH GC	Safety class I	IP20
911401573141	DN392B LED16/840 PSU D200 WH GC	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401573241	DN392B LED16/865 PSU D200 WH GC	Safety class I	IP20
911401573641	DN392B LED16/830 PSD D200 WH GC	Safety class I	IP20
911401573741	DN392B LED16/840 PSD D200 WH GC	Safety class I	IP20
911401574041	DN393B LED22/830 PSU D200 WH GC	Safety class I	IP20
911401574141	DN393B LED22/840 PSU D200 WH GC	Safety class I	IP20
911401574441	DN393B LED22/830 PSD D200 WH GC	Safety class I	IP20
911401574541	DN393B LED22/840 PSD D200 WH GC	Safety class I	IP20
911401576141	DN393B LED22/830 POE D200 WH GC	Safety class III	IP20
911401576241	DN393B LED22/840 POE D200 WH GC	Safety class III	IP20
911401579541	DN392B LED16/830 PSU D200 WH GM	Safety class I	IP20
911401579641	DN392B LED16/840 PSU D200 WH GM	Safety class I	IP20
911401579741	DN392B LED16/865 PSU D200 WH GM	Safety class I	IP20
911401580141	DN393B LED22/830 PSU D200 WH GM	Safety class I	IP20
911401580241	DN393B LED22/840 PSU D200 WH GM	Safety class I	IP20
911401580341	DN393B LED22/865 PSU D200 WH GM	Safety class I	IP20
911401582041	DN392B LED16/830 PSD D200 WH GM	Safety class I	IP20
911401582141	DN392B LED16/840 PSD D200 WH GM	Safety class I	IP20
911401582441	DN393B LED22/830 PSD D200 WH GM	Safety class I	IP20
911401582541	DN393B LED22/840 PSD D200 WH GM	Safety class I	IP20
911401583241	DN392B LED16/830 PSU D200 WH CAU	Safety class I	IP20
911401583341	DN392B LED16/840 PSU D200 WH CAU	Safety class I	IP20
911401583441	DN393B LED22/830 PSU D200 WH CAU	Safety class I	IP20
911401583541	DN393B LED22/840 PSU D200 WH CAU	Safety class I	IP20
911401584041	DN393B LED22/830 PSU D200 WH WP CAU	Safety class I	IP20/54
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	Safety class I	IP20/54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401584641	DN392B LED16/830 PSD D200 WH CAU	Safety class I	IP20
911401584741	DN392B LED16/840 PSD D200 WH CAU	Safety class I	IP20
911401585041	DN393B LED22/830 PSD D200 WH CAU	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401585141	DN393B LED22/840 PSD D200 WH CAU	Safety class I	IP20
911401586241	DN393B LED22/830 PSU D200 WH R	Safety class II	IP20
911401586441	DN393B LED22/840 PSU D200 WH R	Safety class II	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401571841	DN390B LED6/830 PSU D100 ALU GC	(0.44,0.403) SDCM<5
911401571941	DN390B LED6/840 PSU D100 ALU GC	(0.38,0.38) SDCM<5
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	(0.44,0.403) SDCM<5
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	(0.38,0.38) SDCM<5
911401575041	DN390B LED6/865 PSU D100 ALU WP GC	(0.31,0.32) SDCM<5
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	(0.44,0.403) SDCM<5
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	(0.38,0.38) SDCM<5
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	(0.31,0.32) SDCM<5
911401576541	DN391B LED11/830 PSU D100 ALU GC	(0.44,0.403) SDCM<5
911401576641	DN391B LED11/840 PSU D100 ALU GC	(0.38,0.38) SDCM<5
911401576741	DN391B LED11/830 PSD D100 ALU GC	(0.44,0.403) SDCM<5
911401576841	DN391B LED11/840 PSD D100 ALU GC	(0.38,0.38) SDCM<5
911401578041	DN390B LED6/830 PSU D100 ALU GM	(0.44,0.403) SDCM<5
911401578141	DN390B LED6/840 PSU D100 ALU GM	(0.38,0.38) SDCM<5
911401578241	DN390B LED6/865 PSU D100 ALU GM	(0.31,0.32) SDCM<5
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	(0.44,0.403) SDCM<5
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	(0.38,0.38) SDCM<5
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	(0.31,0.32) SDCM<5
911401571641	DN390B LED6/830 PSU D100 WH GC	(0.44,0.403) SDCM<5
911401571741	DN390B LED6/840 PSU D100 WH GC	(0.38,0.38) SDCM<5
911401577741	DN390B LED6/830 PSU D100 WH GM	(0.44,0.403) SDCM<5
911401577841	DN390B LED6/840 PSU D100 WH GM	(0.38,0.38) SDCM<5
911401577941	DN390B LED6/865 PSU D100 WH GM	(0.31,0.32) SDCM<5
911401582841	DN390B LED6/830 PSU D100 WH CAU	(0.44,0.403) SDCM<5
911401582941	DN390B LED6/840 PSU D100 WH CAU	(0.38,0.38) SDCM<5
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	(0.44,0.403) SDCM<5
911401583741	DN390B LED6/840 PSU D100 WH WP CAU	(0.38,0.38) SDCM<5
911401572341	DN391B LED11/830 PSU D150 ALU GC	(0.44,0.403) SDCM<5
911401572441	DN391B LED11/840 PSU D150 ALU GC	(0.38,0.38) SDCM<5
911401572541	DN391B LED11/865 PSU D150 ALU GC	(0.31,0.32) SDCM<5
911401572841	DN391B LED11/830 PSD D150 ALU GC	(0.44,0.403) SDCM<5
911401572941	DN391B LED11/840 PSD D150 ALU GC	(0.38,0.38) SDCM<5
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	(0.44,0.403) SDCM<5
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	(0.38,0.38) SDCM<5
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	(0.31,0.32) SDCM<5
911401575941	DN392B LED16/830 POE D150 ALU GC	(0.44,0.403) SDCM<5
911401576041	DN392B LED16/840 POE D150 ALU GC	(0.38,0.38) SDCM<5
911401577141	DN392B LED16/830 PSU D150 ALU GC	(0.44,0.403) SDCM<5
911401577241	DN392B LED16/840 PSU D150 ALU GC	(0.38,0.38) SDCM<5
911401577541	DN392B LED16/830 PSD D150 ALU GC	(0.44,0.403) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401577641	DN392B LED16/840 PSD D150 ALU GC	(0.38,0.38) SDCM<5
911401578641	DN391B LED11/830 PSU D150 ALU GM	(0.44,0.403) SDCM<5
911401578741	DN391B LED11/840 PSU D150 ALU GM	(0.38,0.38) SDCM<5
911401578841	DN391B LED11/865 PSU D150 ALU GM	(0.31,0.32) SDCM<5
911401579241	DN392B LED16/830 PSU D150 ALU GM	(0.44,0.403) SDCM<5
911401579341	DN392B LED16/840 PSU D150 ALU GM	(0.38,0.38) SDCM<5
911401579441	DN392B LED16/865 PSU D150 ALU GM	(0.31,0.32) SDCM<5
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	(0.44,0.403) SDCM<5
911401581141	DN391B LED11/840 PSU D150 ALU WP GM	(0.38,0.38) SDCM<5
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	(0.31,0.32) SDCM<5
911401581841	DN391B LED11/830 PSD D150 ALU GM	(0.44,0.403) SDCM<5
911401581941	DN391B LED11/840 PSD D150 ALU GM	(0.38,0.38) SDCM<5
911401584441	DN391B LED11/830 PSD D150 ALU CAU	(0.44,0.403) SDCM<5
911401584541	DN391B LED11/840 PSD D150 ALU CAU	(0.38,0.38) SDCM<5
911401585641	DN392B LED16/830 PSD D150 ALU GM	(0.44,0.403) SDCM<5
911401585741	DN392B LED16/840 PSD D150 ALU GM	(0.38,0.38) SDCM<5
911401585941	DN391B LED11/830 PSU D150 ALU R	(0.44,0.403) SDCM<5
911401586141	DN391B LED11/840 PSU D150 ALU R	(0.38,0.38) SDCM<5
911401572041	DN391B LED11/830 PSU D150 WH GC	(0.44,0.403) SDCM<5
911401572141	DN391B LED11/840 PSU D150 WH GC	(0.38,0.38) SDCM<5
911401572241	DN391B LED11/865 PSU D150 WH GC	(0.31,0.32) SDCM<5
911401572641	DN391B LED11/830 PSD D150 WH GC	(0.44,0.403) SDCM<5
911401572741	DN391B LED11/840 PSD D150 WH GC	(0.38,0.38) SDCM<5
911401575741	DN392B LED16/830 POE D150 WH GC	(0.44,0.403) SDCM<5
911401575841	DN392B LED16/840 POE D150 WH GC	(0.38,0.38) SDCM<5
911401576941	DN392B LED16/830 PSU D150 WH GC	(0.44,0.403) SDCM<5
911401577041	DN392B LED16/840 PSU D150 WH GC	(0.38,0.38) SDCM<5
911401577341	DN392B LED16/830 PSD D150 WH GC	(0.44,0.403) SDCM<5
911401577441	DN392B LED16/840 PSD D150 WH GC	(0.38,0.38) SDCM<5
911401578341	DN391B LED11/830 PSU D150 WH GM	(0.44,0.403) SDCM<5
911401578441	DN391B LED11/840 PSU D150 WH GM	(0.38,0.38) SDCM<5
911401578541	DN391B LED11/865 PSU D150 WH GM	(0.31,0.32) SDCM<5
911401578941	DN392B LED16/830 PSU D150 WH GM	(0.44,0.403) SDCM<5
911401579041	DN392B LED16/840 PSU D150 WH GM	(0.38,0.38) SDCM<5
911401579141	DN392B LED16/865 PSU D150 WH GM	(0.31,0.32) SDCM<5
911401581641	DN391B LED11/830 PSD D150 WH GM	(0.44,0.403) SDCM<5
911401581741	DN391B LED11/840 PSD D150 WH GM	(0.38,0.38) SDCM<5
911401583041	DN391B LED11/830 PSU D150 WH CAU	(0.44,0.403) SDCM<5
911401583141	DN391B LED11/840 PSU D150 WH CAU	(0.38,0.38) SDCM<5
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	(0.44,0.403) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	(0.38,0.38) SDCM<5
911401584241	DN391B LED11/830 PSD D150 WH CAU	(0.44,0.403) SDCM<5
911401584341	DN391B LED11/840 PSD D150 WH CAU	(0.38,0.38) SDCM<5
911401585441	DN392B LED16/830 PSD D150 WH GM	(0.44,0.403) SDCM<5
911401585541	DN392B LED16/840 PSD D150 WH GM	(0.38,0.38) SDCM<5
911401585841	DN391B LED11/830 PSU D150 WH R	(0.44,0.403) SDCM<5
911401586041	DN391B LED11/840 PSU D150 WH R	(0.38,0.38) SDCM<5
911401573341	DN392B LED16/830 PSU D200 ALU GC	(0.44,0.403) SDCM<5
911401573441	DN392B LED16/840 PSU D200 ALU GC	(0.38,0.38) SDCM<5
911401573541	DN392B LED16/865 PSU D200 ALU GC	(0.31,0.32) SDCM<5
911401573841	DN392B LED16/830 PSD D200 ALU GC	(0.44,0.403) SDCM<5
911401573941	DN392B LED16/840 PSD D200 ALU GC	(0.38,0.38) SDCM<5
911401574241	DN393B LED22/830 PSU D200 ALU GC	(0.44,0.403) SDCM<5
911401574341	DN393B LED22/840 PSU D200 ALU GC	(0.38,0.38) SDCM<5
911401574641	DN393B LED22/830 PSD D200 ALU GC	(0.44,0.403) SDCM<5
911401574741	DN393B LED22/840 PSD D200 ALU GC	(0.38,0.38) SDCM<5
911401576341	DN393B LED22/830 POE D200 ALU GC	(0.44,0.403) SDCM<5
911401576441	DN393B LED22/840 POE D200 ALU GC	(0.38,0.38) SDCM<5
911401579841	DN392B LED16/830 PSU D200 ALU GM	(0.44,0.403) SDCM<5
911401579941	DN392B LED16/840 PSU D200 ALU GM	(0.38,0.38) SDCM<5
911401580041	DN392B LED16/865 PSU D200 ALU GM	(0.31,0.32) SDCM<5
911401580441	DN393B LED22/830 PSU D200 ALU GM	(0.44,0.403) SDCM<5
911401580541	DN393B LED22/840 PSU D200 ALU GM	(0.38,0.38) SDCM<5
911401580641	DN393B LED22/865 PSU D200 ALU GM	(0.31,0.32) SDCM<5
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	(0.44,0.403) SDCM<5
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	(0.38,0.38) SDCM<5
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	(0.31,0.32) SDCM<5
911401582241	DN392B LED16/830 PSD D200 ALU GM	(0.44,0.403) SDCM<5
911401582341	DN392B LED16/840 PSD D200 ALU GM	(0.38,0.38) SDCM<5
911401582641	DN393B LED22/830 PSD D200 ALU GM	(0.44,0.403) SDCM<5
911401582741	DN393B LED22/840 PSD D200 ALU GM	(0.38,0.38) SDCM<5
911401584841	DN392B LED16/830 PSD D200 ALU CAU	(0.44,0.403) SDCM<5
911401584941	DN392B LED16/840 PSD D200 ALU CAU	(0.38,0.38) SDCM<5
911401585241	DN393B LED22/830 PSD D200 ALU CAU	(0.44,0.403) SDCM<5
911401585341	DN393B LED22/840 PSD D200 ALU CAU	(0.38,0.38) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401586341	DN393B LED22/830 PSU D200 ALU R	(0.44,0.403) SDCM<5
911401586541	DN393B LED22/840 PSU D200 ALU R	(0.38,0.38) SDCM<5
911401573041	DN392B LED16/830 PSU D200 WH GC	(0.44,0.403) SDCM<5
911401573141	DN392B LED16/840 PSU D200 WH GC	(0.38,0.38) SDCM<5
911401573241	DN392B LED16/865 PSU D200 WH GC	(0.31,0.32) SDCM<5
911401573641	DN392B LED16/830 PSD D200 WH GC	(0.44,0.403) SDCM<5
911401573741	DN392B LED16/840 PSD D200 WH GC	(0.38,0.38) SDCM<5
911401574041	DN393B LED22/830 PSU D200 WH GC	(0.44,0.403) SDCM<5
911401574141	DN393B LED22/840 PSU D200 WH GC	(0.38,0.38) SDCM<5
911401574441	DN393B LED22/830 PSD D200 WH GC	(0.44,0.403) SDCM<5
911401574541	DN393B LED22/840 PSD D200 WH GC	(0.38,0.38) SDCM<5
911401576141	DN393B LED22/830 POE D200 WH GC	(0.44,0.403) SDCM<5
911401576241	DN393B LED22/840 POE D200 WH GC	(0.38,0.38) SDCM<5
911401579541	DN392B LED16/830 PSU D200 WH GM	(0.44,0.403) SDCM<5
911401579641	DN392B LED16/840 PSU D200 WH GM	(0.38,0.38) SDCM<5
911401579741	DN392B LED16/865 PSU D200 WH GM	(0.31,0.32) SDCM<5
911401580141	DN393B LED22/830 PSU D200 WH GM	(0.44,0.403) SDCM<5
911401580241	DN393B LED22/840 PSU D200 WH GM	(0.38,0.38) SDCM<5
911401580341	DN393B LED22/865 PSU D200 WH GM	(0.31,0.32) SDCM<5
911401582041	DN392B LED16/830 PSD D200 WH GM	(0.44,0.403) SDCM<5
911401582141	DN392B LED16/840 PSD D200 WH GM	(0.38,0.38) SDCM<5
911401582441	DN393B LED22/830 PSD D200 WH GM	(0.44,0.403) SDCM<5
911401582541	DN393B LED22/840 PSD D200 WH GM	(0.38,0.38) SDCM<5
911401583241	DN392B LED16/830 PSU D200 WH CAU	(0.44,0.403) SDCM<5
911401583341	DN392B LED16/840 PSU D200 WH CAU	(0.38,0.38) SDCM<5
911401583441	DN393B LED22/830 PSU D200 WH CAU	(0.44,0.403) SDCM<5
911401583541	DN393B LED22/840 PSU D200 WH CAU	(0.38,0.38) SDCM<5
911401584041	DN393B LED22/830 PSU D200 WH WP CAU	(0.44,0.403) SDCM<5
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	(0.38,0.38) SDCM<5
911401584641	DN392B LED16/830 PSD D200 WH CAU	(0.44,0.403) SDCM<5
911401584741	DN392B LED16/840 PSD D200 WH CAU	(0.38,0.38) SDCM<5
911401585041	DN393B LED22/830 PSD D200 WH CAU	(0.44,0.403) SDCM<5
911401585141	DN393B LED22/840 PSD D200 WH CAU	(0.38,0.38) SDCM<5
911401586241	DN393B LED22/830 PSU D200 WH R	(0.44,0.403) SDCM<5
911401586441	DN393B LED22/840 PSU D200 WH R	(0.38,0.38) SDCM<5

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
911401571841	DN390B LED6/830 PSU D100 ALU GC	0.12 %
911401571941	DN390B LED6/840 PSU D100 ALU GC	0.12 %
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	0.12 %
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	0.12 %
911401575041	DN390B LED6/865 PSU D100 ALU WP GC	0.12 %
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	0.12 %
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	0.12 %
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	0.12 %
911401576541	DN391B LED11/830 PSU D100 ALU GC	0.12 %
911401576641	DN391B LED11/840 PSU D100 ALU GC	0.12 %
911401576741	DN391B LED11/830 PSD D100 ALU GC	0.12 %
911401576841	DN391B LED11/840 PSD D100 ALU GC	0.12 %

Order Code	Full Product Name	Driver failure rate at 5000 h
911401578041	DN390B LED6/830 PSU D100 ALU GM	0.12 %
911401578141	DN390B LED6/840 PSU D100 ALU GM	0.12 %
911401578241	DN390B LED6/865 PSU D100 ALU GM	0.12 %
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	0.12 %
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	0.12 %
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	0.12 %
911401571641	DN390B LED6/830 PSU D100 WH GC	0.12 %
911401571741	DN390B LED6/840 PSU D100 WH GC	0.12 %
911401577741	DN390B LED6/830 PSU D100 WH GM	0.12 %
911401577841	DN390B LED6/840 PSU D100 WH GM	0.12 %
911401577941	DN390B LED6/865 PSU D100 WH GM	0.12 %
911401582841	DN390B LED6/830 PSU D100 WH CAU	0.12 %

Order Code	Full Product Name	Driver failure rate at 5000 h
911401582941	DN390B LED6/840 PSU D100 WH CAU	0.12 %
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	0.12 %
911401583741	DN390B LED6/840 PSU D100 WH WP CAU	0.12 %
911401572341	DN391B LED11/830 PSU D150 ALU GC	0.12 %
911401572441	DN391B LED11/840 PSU D150 ALU GC	0.12 %
911401572541	DN391B LED11/865 PSU D150 ALU GC	0.12 %
911401572841	DN391B LED11/830 PSD D150 ALU GC	0.12 %
911401572941	DN391B LED11/840 PSD D150 ALU GC	0.12 %
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	0.16 %
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	0.16 %
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	0.16 %
911401575941	DN392B LED16/830 POE D150 ALU GC	0.16 %
911401576041	DN392B LED16/840 POE D150 ALU GC	0.16 %
911401577141	DN392B LED16/830 PSU D150 ALU GC	0.16 %
911401577241	DN392B LED16/840 PSU D150 ALU GC	0.16 %
911401577541	DN392B LED16/830 PSD D150 ALU GC	0.16 %
911401577641	DN392B LED16/840 PSD D150 ALU GC	0.16 %
911401578641	DN391B LED11/830 PSU D150 ALU GM	0.12 %
911401578741	DN391B LED11/840 PSU D150 ALU GM	0.12 %
911401578841	DN391B LED11/865 PSU D150 ALU GM	0.12 %
911401579241	DN392B LED16/830 PSU D150 ALU GM	0.16 %
911401579341	DN392B LED16/840 PSU D150 ALU GM	0.16 %
911401579441	DN392B LED16/865 PSU D150 ALU GM	0.16 %
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	0.12 %
911401581141	DN391B LED11/840 PSU D150 ALU WP GM	0.12 %
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	0.12 %
911401581841	DN391B LED11/830 PSD D150 ALU GM	0.12 %
911401581941	DN391B LED11/840 PSD D150 ALU GM	0.12 %
911401584441	DN391B LED11/830 PSD D150 ALU CAU	0.12 %
911401584541	DN391B LED11/840 PSD D150 ALU CAU	0.12 %
911401585641	DN392B LED16/830 PSD D150 ALU GM	0.16 %
911401585741	DN392B LED16/840 PSD D150 ALU GM	0.16 %
911401585941	DN391B LED11/830 PSU D150 ALU R	0.12 %
911401586141	DN391B LED11/840 PSU D150 ALU R	0.12 %
911401572041	DN391B LED11/830 PSU D150 WH GC	0.12 %
911401572141	DN391B LED11/840 PSU D150 WH GC	0.12 %
911401572241	DN391B LED11/865 PSU D150 WH GC	0.12 %
911401572641	DN391B LED11/830 PSD D150 WH GC	0.12 %
911401572741	DN391B LED11/840 PSD D150 WH GC	0.12 %
911401575741	DN392B LED16/830 POE D150 WH GC	0.16 %
911401575841	DN392B LED16/840 POE D150 WH GC	0.16 %
911401576941	DN392B LED16/830 PSU D150 WH GC	0.16 %
911401577041	DN392B LED16/840 PSU D150 WH GC	0.16 %
911401577341	DN392B LED16/830 PSD D150 WH GC	0.16 %
911401577441	DN392B LED16/840 PSD D150 WH GC	0.16 %
911401578341	DN391B LED11/830 PSU D150 WH GM	0.12 %
911401578441	DN391B LED11/840 PSU D150 WH GM	0.12 %
911401578541	DN391B LED11/865 PSU D150 WH GM	0.12 %
911401578941	DN392B LED16/830 PSU D150 WH GM	0.16 %
911401579041	DN392B LED16/840 PSU D150 WH GM	0.16 %
911401579141	DN392B LED16/865 PSU D150 WH GM	0.16 %

Order Code	Full Product Name	Driver failure rate at 5000 h
911401581641	DN391B LED11/830 PSD D150 WH GM	0.12 %
911401581741	DN391B LED11/840 PSD D150 WH GM	0.12 %
911401583041	DN391B LED11/830 PSU D150 WH CAU	0.12 %
911401583141	DN391B LED11/840 PSU D150 WH CAU	0.12 %
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	0.12 %
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	0.12 %
911401584241	DN391B LED11/830 PSD D150 WH CAU	0.12 %
911401584341	DN391B LED11/840 PSD D150 WH CAU	0.12 %
911401585441	DN392B LED16/830 PSD D150 WH GM	0.16 %
911401585541	DN392B LED16/840 PSD D150 WH GM	0.16 %
911401585841	DN391B LED11/830 PSU D150 WH R	0.12 %
911401586041	DN391B LED11/840 PSU D150 WH R	0.12 %
911401573341	DN392B LED16/830 PSU D200 ALU GC	0.16 %
911401573441	DN392B LED16/840 PSU D200 ALU GC	0.16 %
911401573541	DN392B LED16/865 PSU D200 ALU GC	0.16 %
911401573841	DN392B LED16/830 PSD D200 ALU GC	0.16 %
911401573941	DN392B LED16/840 PSD D200 ALU GC	0.16 %
911401574241	DN393B LED22/830 PSU D200 ALU GC	0.12 %
911401574341	DN393B LED22/840 PSU D200 ALU GC	0.12 %
911401574641	DN393B LED22/830 PSD D200 ALU GC	0.12 %
911401574741	DN393B LED22/840 PSD D200 ALU GC	0.12 %
911401576341	DN393B LED22/830 POE D200 ALU GC	0.12 %
911401576441	DN393B LED22/840 POE D200 ALU GC	0.12 %
911401579841	DN392B LED16/830 PSU D200 ALU GM	0.16 %
911401579941	DN392B LED16/840 PSU D200 ALU GM	0.16 %
91140158004	DN392B LED16/865 PSU D200 ALU GM	0.16 %
1		
911401580441	DN393B LED22/830 PSU D200 ALU GM	0.12 %
911401580541	DN393B LED22/840 PSU D200 ALU GM	0.12 %
911401580641	DN393B LED22/865 PSU D200 ALU GM	0.12 %
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	0.12 %
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	0.12 %
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	0.12 %
911401582241	DN392B LED16/830 PSD D200 ALU GM	0.16 %
911401582341	DN392B LED16/840 PSD D200 ALU GM	0.16 %
911401582641	DN393B LED22/830 PSD D200 ALU GM	0.12 %
911401582741	DN393B LED22/840 PSD D200 ALU GM	0.12 %
911401584841	DN392B LED16/830 PSD D200 ALU CAU	0.16 %
911401584941	DN392B LED16/840 PSD D200 ALU CAU	0.16 %
911401585241	DN393B LED22/830 PSD D200 ALU CAU	0.12 %
911401585341	DN393B LED22/840 PSD D200 ALU CAU	0.12 %
911401586341	DN393B LED22/830 PSU D200 ALU R	0.12 %
911401586541	DN393B LED22/840 PSU D200 ALU R	0.12 %
911401573041	DN392B LED16/830 PSU D200 WH GC	0.16 %
911401573141	DN392B LED16/840 PSU D200 WH GC	0.16 %
911401573241	DN392B LED16/865 PSU D200 WH GC	0.16 %
911401573641	DN392B LED16/830 PSD D200 WH GC	0.16 %
911401573741	DN392B LED16/840 PSD D200 WH GC	0.16 %

Order Code	Full Product Name	Driver failure rate at 5000 h
911401574041	DN393B LED22/830 PSU D200 WH GC	0.12 %
911401574141	DN393B LED22/840 PSU D200 WH GC	0.12 %
911401574441	DN393B LED22/830 PSD D200 WH GC	0.12 %
911401574541	DN393B LED22/840 PSD D200 WH GC	0.12 %
911401576141	DN393B LED22/830 POE D200 WH GC	0.12 %
911401576241	DN393B LED22/840 POE D200 WH GC	0.12 %
911401579541	DN392B LED16/830 PSU D200 WH GM	0.16 %
911401579641	DN392B LED16/840 PSU D200 WH GM	0.16 %
911401579741	DN392B LED16/865 PSU D200 WH GM	0.16 %
911401580141	DN393B LED22/830 PSU D200 WH GM	0.12 %
911401580241	DN393B LED22/840 PSU D200 WH GM	0.12 %
911401580341	DN393B LED22/865 PSU D200 WH GM	0.12 %
911401582041	DN392B LED16/830 PSD D200 WH GM	0.16 %
911401582141	DN392B LED16/840 PSD D200 WH GM	0.16 %
911401582441	DN393B LED22/830 PSD D200 WH GM	0.12 %

Order Code	Full Product Name	Driver failure rate at 5000 h
911401582541	DN393B LED22/840 PSD D200 WH GM	0.12 %
911401583241	DN392B LED16/830 PSU D200 WH CAU	0.16 %
911401583341	DN392B LED16/840 PSU D200 WH CAU	0.16 %
911401583441	DN393B LED22/830 PSU D200 WH CAU	0.12 %
911401583541	DN393B LED22/840 PSU D200 WH CAU	0.12 %
911401584041	DN393B LED22/830 PSU D200 WH WP CAU	0.12 %
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	0.12 %
911401584641	DN392B LED16/830 PSD D200 WH CAU	0.16 %
911401584741	DN392B LED16/840 PSD D200 WH CAU	0.16 %
911401585041	DN393B LED22/830 PSD D200 WH CAU	0.12 %
911401585141	DN393B LED22/840 PSD D200 WH CAU	0.12 %
911401586241	DN393B LED22/830 PSU D200 WH R	0.12 %
911401586441	DN393B LED22/840 PSU D200 WH R	0.12 %

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401571841	DN390B LED6/830 PSU D100 ALU GC	Not applicable
911401571941	DN390B LED6/840 PSU D100 ALU GC	Not applicable
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	Not applicable
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	Not applicable
911401575041	DN390B LED6/865 PSU D100 ALU WP GC	Not applicable
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	Not applicable
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	Not applicable
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	Not applicable
911401576541	DN391B LED11/830 PSU D100 ALU GC	Not applicable
911401576641	DN391B LED11/840 PSU D100 ALU GC	Not applicable
911401576741	DN391B LED11/830 PSD D100 ALU GC	-
911401576841	DN391B LED11/840 PSD D100 ALU GC	-
911401578041	DN390B LED6/830 PSU D100 ALU GM	Not applicable
911401578141	DN390B LED6/840 PSU D100 ALU GM	Not applicable
911401578241	DN390B LED6/865 PSU D100 ALU GM	Not applicable
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	Not applicable
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	Not applicable
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	Not applicable
911401571641	DN390B LED6/830 PSU D100 WH GC	Not applicable
911401571741	DN390B LED6/840 PSU D100 WH GC	Not applicable
911401577741	DN390B LED6/830 PSU D100 WH GM	Not applicable
911401577841	DN390B LED6/840 PSU D100 WH GM	Not applicable
911401577941	DN390B LED6/865 PSU D100 WH GM	Not applicable
911401582841	DN390B LED6/830 PSU D100 WH CAU	Not applicable
911401582941	DN390B LED6/840 PSU D100 WH CAU	Not applicable
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	Not applicable
911401583741	DN390B LED6/840 PSU D100 WH WP CAU	Not applicable
911401572341	DN391B LED11/830 PSU D150 ALU GC	Not applicable
911401572441	DN391B LED11/840 PSU D150 ALU GC	Not applicable
911401572541	DN391B LED11/865 PSU D150 ALU GC	Not applicable
911401572841	DN391B LED11/830 PSD D150 ALU GC	-
911401572941	DN391B LED11/840 PSD D150 ALU GC	-

Order Code	Full Product Name	Maximum dim level
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	Not applicable
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	Not applicable
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	Not applicable
911401575941	DN392B LED16/830 POE D150 ALU GC	-
911401576041	DN392B LED16/840 POE D150 ALU GC	-
911401577141	DN392B LED16/830 PSU D150 ALU GC	Not applicable
911401577241	DN392B LED16/840 PSU D150 ALU GC	Not applicable
911401577541	DN392B LED16/830 PSD D150 ALU GC	-
911401577641	DN392B LED16/840 PSD D150 ALU GC	-
911401578641	DN391B LED11/830 PSU D150 ALU GM	Not applicable
911401578741	DN391B LED11/840 PSU D150 ALU GM	Not applicable
911401578841	DN391B LED11/865 PSU D150 ALU GM	Not applicable
911401579241	DN392B LED16/830 PSU D150 ALU GM	Not applicable
911401579341	DN392B LED16/840 PSU D150 ALU GM	Not applicable
911401579441	DN392B LED16/865 PSU D150 ALU GM	Not applicable
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	Not applicable
911401581141	DN391B LED11/840 PSU D150 ALU WP GM	Not applicable
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	Not applicable
911401581841	DN391B LED11/830 PSD D150 ALU GM	-
911401581941	DN391B LED11/840 PSD D150 ALU GM	-
911401584441	DN391B LED11/830 PSD D150 ALU CAU	-
911401584541	DN391B LED11/840 PSD D150 ALU CAU	-
911401585641	DN392B LED16/830 PSD D150 ALU GM	-
911401585741	DN392B LED16/840 PSD D150 ALU GM	-
911401585941	DN391B LED11/830 PSU D150 ALU R	Not applicable
911401586141	DN391B LED11/840 PSU D150 ALU R	Not applicable
911401572041	DN391B LED11/830 PSU D150 WH GC	Not applicable
911401572141	DN391B LED11/840 PSU D150 WH GC	Not applicable
911401572241	DN391B LED11/865 PSU D150 WH GC	Not applicable
911401572641	DN391B LED11/830 PSD D150 WH GC	-
911401572741	DN391B LED11/840 PSD D150 WH GC	-
911401575741	DN392B LED16/830 POE D150 WH GC	-

Order Code	Full Product Name	Maximum dim level
911401575841	DN392B LED16/840 POE D150 WH GC	-
911401576941	DN392B LED16/830 PSU D150 WH GC	Not applicable
911401577041	DN392B LED16/840 PSU D150 WH GC	Not applicable
911401577341	DN392B LED16/830 PSD D150 WH GC	-
911401577441	DN392B LED16/840 PSD D150 WH GC	-
911401578341	DN391B LED11/830 PSU D150 WH GM	Not applicable
911401578441	DN391B LED11/840 PSU D150 WH GM	Not applicable
911401578541	DN391B LED11/865 PSU D150 WH GM	Not applicable
911401578941	DN392B LED16/830 PSU D150 WH GM	Not applicable
911401579041	DN392B LED16/840 PSU D150 WH GM	Not applicable
911401579141	DN392B LED16/865 PSU D150 WH GM	Not applicable
911401581641	DN391B LED11/830 PSD D150 WH GM	-
911401581741	DN391B LED11/840 PSD D150 WH GM	-
911401583041	DN391B LED11/830 PSU D150 WH CAU	Not applicable
911401583141	DN391B LED11/840 PSU D150 WH CAU	Not applicable
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	Not applicable
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	Not applicable
911401584241	DN391B LED11/830 PSD D150 WH CAU	-
911401584341	DN391B LED11/840 PSD D150 WH CAU	-
911401585441	DN392B LED16/830 PSD D150 WH GM	-
911401585541	DN392B LED16/840 PSD D150 WH GM	-
911401585841	DN391B LED11/830 PSU D150 WH R	Not applicable
911401586041	DN391B LED11/840 PSU D150 WH R	Not applicable
911401573341	DN392B LED16/830 PSU D200 ALU GC	Not applicable
911401573441	DN392B LED16/840 PSU D200 ALU GC	Not applicable
911401573541	DN392B LED16/865 PSU D200 ALU GC	Not applicable
911401573841	DN392B LED16/830 PSD D200 ALU GC	-
911401573941	DN392B LED16/840 PSD D200 ALU GC	-
911401574241	DN393B LED22/830 PSU D200 ALU GC	Not applicable
911401574341	DN393B LED22/840 PSU D200 ALU GC	Not applicable
911401574641	DN393B LED22/830 PSD D200 ALU GC	-
911401574741	DN393B LED22/840 PSD D200 ALU GC	-
911401576341	DN393B LED22/830 POE D200 ALU GC	-
911401576441	DN393B LED22/840 POE D200 ALU GC	-
911401579841	DN392B LED16/830 PSU D200 ALU GM	Not applicable
911401579941	DN392B LED16/840 PSU D200 ALU GM	Not applicable
911401580041	DN392B LED16/865 PSU D200 ALU GM	Not applicable
911401580441	DN393B LED22/830 PSU D200 ALU GM	Not applicable
911401580541	DN393B LED22/840 PSU D200 ALU GM	Not applicable
911401580641	DN393B LED22/865 PSU D200 ALU GM	Not applicable
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	Not applicable
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	Not applicable
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	Not applicable

Order Code	Full Product Name	Maximum dim level
911401582241	DN392B LED16/830 PSD D200 ALU GM	-
911401582341	DN392B LED16/840 PSD D200 ALU GM	-
911401582641	DN393B LED22/830 PSD D200 ALU GM	-
911401582741	DN393B LED22/840 PSD D200 ALU GM	-
911401584841	DN392B LED16/830 PSD D200 ALU CAU	-
911401584941	DN392B LED16/840 PSD D200 ALU CAU	-
911401585241	DN393B LED22/830 PSD D200 ALU CAU	-
911401585341	DN393B LED22/840 PSD D200 ALU CAU	-
911401586341	DN393B LED22/830 PSU D200 ALU R	Not applicable
911401586541	DN393B LED22/840 PSU D200 ALU R	Not applicable
911401573041	DN392B LED16/830 PSU D200 WH GC	Not applicable
911401573141	DN392B LED16/840 PSU D200 WH GC	Not applicable
911401573241	DN392B LED16/865 PSU D200 WH GC	Not applicable
911401573641	DN392B LED16/830 PSD D200 WH GC	-
911401573741	DN392B LED16/840 PSD D200 WH GC	-
911401574041	DN393B LED22/830 PSU D200 WH GC	Not applicable
911401574141	DN393B LED22/840 PSU D200 WH GC	Not applicable
911401574441	DN393B LED22/830 PSD D200 WH GC	-
911401574541	DN393B LED22/840 PSD D200 WH GC	-
911401576141	DN393B LED22/830 POE D200 WH GC	-
911401576241	DN393B LED22/840 POE D200 WH GC	-
911401579541	DN392B LED16/830 PSU D200 WH GM	Not applicable
911401579641	DN392B LED16/840 PSU D200 WH GM	Not applicable
911401579741	DN392B LED16/865 PSU D200 WH GM	Not applicable
911401580141	DN393B LED22/830 PSU D200 WH GM	Not applicable
911401580241	DN393B LED22/840 PSU D200 WH GM	Not applicable
911401580341	DN393B LED22/865 PSU D200 WH GM	Not applicable
911401582041	DN392B LED16/830 PSD D200 WH GM	-
911401582141	DN392B LED16/840 PSD D200 WH GM	-
911401582441	DN393B LED22/830 PSD D200 WH GM	-
911401582541	DN393B LED22/840 PSD D200 WH GM	-
911401583241	DN392B LED16/830 PSU D200 WH CAU	Not applicable
911401583341	DN392B LED16/840 PSU D200 WH CAU	Not applicable
911401583441	DN393B LED22/830 PSU D200 WH CAU	Not applicable
911401583541	DN393B LED22/840 PSU D200 WH CAU	Not applicable
911401584041	DN393B LED22/830 PSU D200 WH WP CAU	Not applicable
911401584141	DN393B LED22/840 PSU D200 WH WP CAU	Not applicable
911401584641	DN392B LED16/830 PSD D200 WH CAU	-
911401584741	DN392B LED16/840 PSD D200 WH CAU	-
911401585041	DN393B LED22/830 PSD D200 WH CAU	-
911401585141	DN393B LED22/840 PSD D200 WH CAU	-
911401586241	DN393B LED22/830 PSU D200 WH R	Not applicable
911401586441	DN393B LED22/840 PSU D200 WH R	Not applicable

