



# Halogen capsules for oven lighting

## LV Halogen Oven Capsules

Halogen capsules ideal as replacement lamp for many specific oven types. Resistant to high temperatures, perfectly fitting oven application.

### Benefits

- Suitable also for ovens with pyrolysis function (tolerable ambient temperature up to 450°C, lamps must be switched off during self-cleaning)
- For use in shielded oven luminaires only

### Features

- Heat resistance up to 300°C
- Compact size, matching oven luminaire
- 2000 hours lifetime
- Instant start
- 50 000 switching cycles

### Application

- Oven lighting

# LV Halogen Oven Capsules

## Versions



G4 T 9mm (T9) Clear

## Dimensional drawing

D

Product	D (max)	L	C (max)
Caps OV 20W G4 12V 1CT/50	10 mm	22.2 mm	33 mm

