



Halogen capsules for oven lighting

MV Halogen Oven Capsules

Halogen capsules ideal as replacement lamp for many specific oven types. Resistant to high temperatures, perfectly fitting oven application.

Benefits

- Suitable also for ovens with pyrolysis function (tolerable ambient temperature up to 450°C, lamps must be switched off during self-cleaning)
- For use in shielded oven luminaires only

Features

- Heat resistance up to 300°C
- Compact size, matching oven luminaire
- 2000 hours lifetime
- Instant start
- 50 000 switching cycles

Application

- Oven lighting


MV Halogen Oven Capsules

Versions



G9 T 11mm Clear

Dimensional drawing



Product	D (max)	C (max)
Caps OV 25W G9 230V 1CT/20	12.75 mm	44.6 mm

