



# Extending the home feel onto the street

## TownTune Asymmetric Lyre DTC

As a luminaire family prepared for existing and scalable urban spaces, TownTune offers all the recent lighting innovations in terms of performance, quality of light and connectivity. The Philips TownTune family consists of three members: a central post top, an asymmetric spigot version and a version using an extending lyre post top bracket. Each of these three can be customized with a choice of different shapes for housing and an optional of decorative ring which comes in two colors. By having these options available you can create your very own lighting signature and give distinctive identity to districts and cities. The luminaire family is also equipped with the QR code-based Philips Service tag, which supports installation and maintenance work and enables you to create your digital library of lighting assets and spare parts. TownTune also makes use of the Philips Ledgine optimized lighting platform ensuring that you always have the right amount and direction of light on your street. Furthermore, thanks to being SR (System Ready), TownTune is also future-proof and is ready to be paired with both standalone and advanced control and lighting software applications such as Interact City.

# TownTune Asymmetric Lyre DTC

## Benefits

- Delivers visual comfort, and comfortable lighting experiences in urban spaces through its dedicatedly designed bowl
- Simple, pure design making it possible to integrate it into various urban environments and the option for customization through a wide range of accessories, lets cities create a unique light signature, which can also become part of the urban furniture in daytime
- Wide application coverage and offers great performance by using the latest Ledgine LED platform and providing access to a wide range of light distributions
- Ready to be paired with lighting control and software applications, by being equipped with the Philips SR (System Ready) socket
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

## Features

- Optimized Total Cost of Ownership and option of CLO (Constant Light Output)
- Excellent quality of light enabled by the Philips Ledgine optimized platform, and further optimization in L-Tune is also possible
- Choice of different shapes for housing (cone, dome), option of decorative ring and color (clear and golden)
- Ready to be paired with standalone lighting controls such as LumiStep, DynaDimmer, and LineSwitch and advanced system and software application such as Interact City
- Wide choice of lumen packages, ranging from 600 to 12,000 lumens
- Choice of color temperature: 3000 K (warm white) or 4000 K (neutral white)
- Long lifetime of 100,000 hours at minimum L80
- Suitable for new and retrofit installations
- IK08, IP66

## Application

- Urban and residential areas
- City centers and main streets
- Cycle paths, footpaths and pedestrian crossings
- Car parks

## Versions



**BDP272, TownTune Lyre with decorative top cone and clear decorative ring**

# TownTune Asymmetric Lyre DTC

## Product details



TownTune LYR BDP270



TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY DR BDP266



TownTune ASY BDP265

# TownTune Asymmetric Lyre DTC

-	
Driver failure rate at 5000 h	0.5 %
<b>Application Conditions</b>	
Maximum dim level	10%
<b>Approval and Application</b>	
Mech. impact protection code	IK09
Surge Protection (Common/Differential)	Philips standard surge protection level
<b>General Information</b>	
CE mark	CE mark
Light source color	830 warm white
Optical cover/lens type	Polycarbonate bowl/cover UV-resistant
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	Yes
Number of gear units	1 unit
Product Family Code	BDP272
Service tag	Yes
<b>Initial Performance (IEC Compliant)</b>	
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>80
<b>Light Technical</b>	
Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Upward light output ratio	0
<b>Mechanical and Housing</b>	
Color	Dark gray

## Controls and Dimming

Order Code	Full Product Name	Dimmable
912300024208	BDP272 LED59-4S/830 II DW50 DR CLO LS-6	Yes
912300024466	BDP272 LED79-4S/830 II DS50 62P	No
912300024467	BDP272 LED50-4S/830 II DM10 62P	No

## General Information

Order Code	Full Product Name	Luminaire light beam spread	Lamp family code	Optic type
912300024208	BDP272 LED59-4S/830 II DW50 DR CLO LS-6	12° - 29° x 152°	LED59	Distribution wide 50
912300024466	BDP272 LED79-4S/830 II DS50 62P	152° x 155°	LED79	Distribution symmetrical 50

Order Code	Full Product Name	Luminaire light beam spread	Lamp family code	Optic type
912300024467	BDP272 LED50-4S/830 II DM10 62P	77° - 11° x 156°	LED50	Distribution medium 10

## Initial Performance (IEC Compliant)

## TownTune Asymmetric Lyre DTC

Order Code	Full Product Name	Initial luminous flux
912300024208	BDP272 LED59-4S/830 II DW50 DR CLO LS-6	4312 lm
912300024466	BDP272 LED79-4S/830 II DS50 62P	5840 lm

Order Code	Full Product Name	Initial luminous flux
912300024467	BDP272 LED50-4S/830 II DM10 62P	3900 lm

