



Time to upgrade your conventional lighting to LumiStreet gen2

LumiStreet gen2

Increasing numbers of municipalities are having to upgrade large-scale conventional street lighting installations with energy efficient LED technology. But they are having to do this with smaller and smaller budgets. That's why the new generation of LumiStreet has been upgraded and designed to provide a solution to this challenge, it is the ideal solution for performing point-to-point replacement of conventional lighting. LumiStreet gen2 achieves this by offering high efficiency, low Total Cost of Ownership, and ease of installation and maintenance. The ease of installation and maintenance is enabled by the Philips Service tag. Moreover, the Philips SR (System Ready) socket makes it future-ready and you can pair this luminaire with lighting control and software applications such as Interact City.

Benefits

- Economical LED alternative to conventional street lights
- Offers high efficiency and energy savings
- Made of high-quality materials for longer lifetime and minimized maintenance

Features

- Good application coverage thanks to wide range of optics, tunable flux and tiltable spigot
- Easy luminaire identification due to the Philips Service tag
- Future-ready thanks to the SR (System Ready) socket
- High system efficiency with good application coverage
- Luminaire is also equipped with dedicated light recipes that help with: 1) maintaining an optimal ecosystems for bats or 2) preserving a dark night sky and reduce light pollution

LumiStreet gen2

Application

- Roads and streets
- Residential streets

Specifications

Dimming	No, yes	Ambient Temperature	-40 to +50 °C
Input voltage	220 to 240, 220-240 V	Initial LED luminaire efficacy	104, 107, 108, 109, 111, 112, 113, 116, 117, 120, 121, 122, 126, 128, 132, 133, 134, 135, 136, 137, 138, 139, 140, 141, 142, 143, 144, 145, 146, 147, 149, 150, 151, 152, 153, 155, 156, 157, 158, 159 lm/W
Inrush current (A)	11.2, 15, 21, 43, 47, 53 A	Material	Housing: aluminum die cast
Light source color	730 warm white, 740 neutral white, 830 warm white	Optic	Distribution extra wide 10, distribution medium 10, distribution medium 11, distribution medium 12, distribution medium 31, distribution medium 32, distribution medium 50, distribution narrow 10, distribution wide 10, distribution wide 50
Type	BGP291 BGP292 BGP293 BGP294 BGP391 BGP392 BGP393 BGP394		other upon request

Versions



LumiStreet gen2 Mini



LumiStreet gen2 Medium



LumiStreet gen2 Micro



LumiStreet gen2 Large

Product details

UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



LumiStreet gen2

Product details



Bottom view for spigot regulation and screw

UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2

UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2



UniStreet gen2 spigot regulation

UniStreet_LumiStreet_gen2



Product details



UniStreet_LumiStreet_gen2



UniStreet_LumiStreet_gen2

Approval and Application

Mech. impact protection code	IK08
------------------------------	------

General Information

CE mark	CE mark
Optical cover/lens type	Flat glass
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	Yes
Service tag	Yes

Light Technical

Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0

Mechanical and Housing

Color	Gray
-------	------

-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	0.5 %
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	0.5 %
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	0.5 %
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	0.5 %
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	0.5 %
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	0.5 %
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	0.5 %
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	0.5 %
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	0.5 %
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	0.5 %
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	0.5 %
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	0.5 %
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	0.5 %
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	0.5 %
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	0.5 %
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	0.5 %
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	0.5 %
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	0.5 %
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	0.5 %
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	0.5 %
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	0.5 %
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	0.5 %
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	0.5 %
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	0.5 %
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	0.5 %
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	0.5 %
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	0.5 %
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	0.5 %
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	0.5 %
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	0.5 %
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	0.5 %
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	0.5 %
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	0.5 %
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	0.5 %
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	0.5 %
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	0.5 %
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	0.5 %
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	0.5 %
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	0.5 %
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	0.5 %
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	0.5 %
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	0.5 %
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	0.5 %
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	-
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	-
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	-
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZ1-	0.5 %
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZ1-	0.5 %
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZ1-	0.5 %
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	-
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	-
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	-
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZ1-	0.5 %
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZ1-	0.5 %
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	-
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZ1-	0.5 %
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	0.5 %
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	0.5 %
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	0.5 %
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	0.5 %
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	-
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	-
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	-
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	-
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	-
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	-
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	-
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	-
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	0.5 %
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	0.5 %
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	0.5 %
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	0.5 %
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	0.5 %
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	0.5 %
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	0.5 %
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	0.5 %
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	0.5 %
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	0.5 %
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	0.5 %
910925866755	BGP293 LED149-4S/740 I DX10 76S	0.5 %
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	0.5 %
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	0.5 %
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	0.5 %
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	0.5 %
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	0.5 %
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	-
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	0.5 %
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	0.5 %
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	0.5 %
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	-
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05Z1Z1	0.5 %
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05Z1Z1	0.5 %
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05Z1Z1	0.5 %
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	-
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	-
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	0.5 %
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	-
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	-
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	-
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	-
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	-
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	-
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	0.5 %
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	0.5 %
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	0.5 %
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	0.5 %
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	0.5 %
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	0.5 %
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	0.5 %
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	0.5 %
910925866641	BGP291 LED60-4S/740 II DM11 48/60S	0.5 %
910925866644	BGP291 LED45-4S/740 II DM11 48/60S	0.5 %
910925866645	BGP291 LED60-4S/740 II DM11 48/60S	0.5 %
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	0.5 %
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	0.5 %
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	0.5 %
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	0.5 %
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	0.5 %
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	0.5 %
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	0.5 %
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	0.5 %
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	0.5 %
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	0.5 %
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	0.5 %
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	0.5 %
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	0.5 %
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	-
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	-
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05Z1Z1-	0.5 %
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	-
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	0.5 %
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	0.5 %
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05Z1Z1-	0.5 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05Z1Z1-	0.5 %
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	-
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	-
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	0.5 %
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	0.5 %
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	0.5 %
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	0.5 %
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	-
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	-
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	-
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	-
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	-
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	-
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	-
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	-
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	-
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	-
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	0.5 %
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	-
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	-
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	-
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	-
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	-
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	-
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	-
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	-
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	-
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	-
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	-
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	-
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	-
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	-
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	-
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	-
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	-
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	-
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	-

Application Conditions

Order Code	Full Product Name	Maximum dim level	Order Code	Full Product Name	Maximum dim level
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	0% (digital)	910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	0% (digital)
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	0% (digital)	910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	0% (digital)
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	0% (digital)	910925866639	BGP292 LED120-4S/740 II DM11 48/60S	0% (digital)
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	0% (digital)	910925866640	BGP292 LED85-4S/740 II DM11 48/60S	0% (digital)
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	0% (digital)	910925866642	BGP292 LED85-4S/740 II DM11 48/60S	0% (digital)
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	0% (digital)	910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	0% (digital)
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	0% (digital)	910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	0% (digital)
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	0% (digital)	910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	0% (digital)
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	0% (digital)	910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	0% (digital)
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	0% (digital)	910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	0% (digital)

Order Code	Full Product Name	Maximum dim level	Order Code	Full Product Name	Maximum dim level
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	0% (digital)	910925866444	BGP293 LED240-4S/740 I DM11 48/60S	0% (digital)
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	0% (digital)	910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	0% (digital)
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	0% (digital)	910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	0% (digital)
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	0% (digital)	910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	0% (digital)
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	0% (digital)	910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	0% (digital)
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	0% (digital)	910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	0% (digital)
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	0% (digital)	910925866643	BGP293 LED170-4S/740 II DM11 48/60S	0% (digital)
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)	910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	0% (digital)
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	0% (digital)	910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	0% (digital)
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	0% (digital)	910925866755	BGP293 LED149-4S/740 I DX10 76S	0% (digital)
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	0% (digital)	910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	0% (digital)
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	0% (digital)	910925866759	BGP293 LED139-4S/740 I DX10 48/60S	0% (digital)
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	0% (digital)	910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	0% (digital)
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	0% (digital)	910925866767	BGP293 LED149-4S/740 I DX10 48/60S	0% (digital)
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	0% (digital)	910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	0% (digital)
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	0% (digital)	910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	0% (digital)
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	0% (digital)	910925866789	BGP293 LED139-4S/740 II DM10 48/60S	0% (digital)
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	0% (digital)	910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	0% (digital)
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	0% (digital)	910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	0% (digital)
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	0% (digital)	910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	0% (digital)
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	0% (digital)	910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	0% (digital)
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	0% (digital)	910925866902	BGP293 LED80-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	0% (digital)	910925866903	BGP293 LED100-4S/740 II DM11 CLO S05Z1Z1	0% (digital)
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	0% (digital)	910925866904	BGP293 LED120-4S/740 II DM11 CLO S05Z1Z1	0% (digital)
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	0% (digital)	910925866905	BGP293 LED149-4S/740 II DM11 CLO S05Z1Z1	0% (digital)
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	0% (digital)	910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	0% (digital)
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	0% (digital)	910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	0% (digital)
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	0% (digital)	910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	0% (digital)
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)	910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	0% (digital)
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)	910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	Not applicable
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)	910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	0% (digital)	910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	0% (digital)	910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	Programmable
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	0% (digital)	910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	Programmable
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)	910925865679	BGP291 LED39-4S/740 II DM50 48/60S	0% (digital)
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)	910925866442	BGP291 LED50-4S/740 I DM11 48/60S	0% (digital)
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	0% (digital)	910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	0% (digital)
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)	910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	0% (digital)
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	0% (digital)	910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	0% (digital)
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	0% (digital)	910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	0% (digital)
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	0% (digital)	910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	0% (digital)
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	0% (digital)	910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	0% (digital)
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	Programmable	910925866641	BGP291 LED60-4S/740 II DM11 48/60S	0% (digital)
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	Programmable	910925866644	BGP291 LED45-4S/740 II DM11 48/60S	0% (digital)
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	Programmable	910925866645	BGP291 LED60-4S/740 II DM11 48/60S	0% (digital)
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	Programmable	910925866646	BGP291 LED45-4S/740 II DM11 48/60S	0% (digital)
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	Programmable	910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	0% (digital)
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	Programmable	910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	0% (digital)
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	Programmable	910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	0% (digital)
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	Programmable	910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	0% (digital)	910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	0% (digital)	910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	0% (digital)

Order Code	Full Product Name	Maximum dim level
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	0% (digital)
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	0% (digital)
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	0% (digital)
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	0% (digital)
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	0% (digital)
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	0% (digital)
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	0% (digital)
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	0% (digital)
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	0% (digital)
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	0% (digital)
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	0% (digital)
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	0% (digital)
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	0% (digital)
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	0% (digital)
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Programmable

Order Code	Full Product Name	Maximum dim level
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Programmable
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Programmable
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	Programmable
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	Programmable
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	0% (digital)
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	0% (digital)
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	0% (digital)
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	0% (digital)
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	0% (digital)
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	0% (digital)
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	0% (digital)
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	0% (digital)
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	0% (digital)
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	0% (digital)
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	0% (digital)
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	0% (digital)
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	0% (digital)
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	0% (digital)
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	Programmable
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Programmable
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	Programmable
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	Programmable
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Programmable
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	Programmable

Approval and Application

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

LumiStreet gen2

Order Code	Full Product Name	Surge Protection (Common/Differential)	Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866771	BGP292 LED75-4S/740 I DX10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866773	BGP292 LED51-4S/740 I DX10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode	910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

LumiStreet gen2

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZI-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZI-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZI-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZI-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZI-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZI-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866755	BGP293 LED149-4S/740 I DX10 76S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05ZIZI-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05ZIZI	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05ZIZI	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05ZIZI	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	Philips standard surge protection level
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
91092586809	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866641	BGP291 LED60-4S/740 II DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866644	BGP291 LED45-4S/740 II DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866645	BGP291 LED60-4S/740 II DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)	Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866652	BGP291 LED64-4S/740 II DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666913	BGP291 LED45-4S/740 II DM11 CLO S05Z1Z1-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666928	BGP291 LED20-4S/830 II DM11 CLO S05Z1Z1-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666929	BGP291 LED25-4S/740 II DM11 CLO S05Z1Z1-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666932	BGP291 LED35-4S/830 II DM11 CLO S05Z1Z1-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666933	BGP291 LED45-4S/830 II DM11 CLO S05Z1Z1-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	9109258666939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
9109258666898	BGP291 LED20-4S/740 II DM11 CLO S05Z1Z1-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05Z1Z1-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05Z1Z1-	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode	910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
			910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
			910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866690	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	Philips standard surge protection level
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Philips standard surge protection level
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	Philips standard surge protection level
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	Yes
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Yes
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	Yes
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	Yes
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	No
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	Yes
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	Yes
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	Yes
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	Yes
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	Yes
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	Yes
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	Yes
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	No
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	No
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	No

Order Code	Full Product Name	Dimmable
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	Yes
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	Yes
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	Yes
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Yes
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/60	Yes
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Yes
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Yes
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	Yes
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	Yes
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Yes
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	Yes
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	Yes
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	No
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Yes
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	Yes

Order Code	Full Product Name	Dimmable
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	Yes
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	Yes
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	No
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Yes
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	No
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	Yes
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	Yes
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	No
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Yes
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	No
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	Yes
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	Yes
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	Yes
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	Yes
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	No
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	No
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	No
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	No
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05Z1Z1-	No
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05Z1Z1-	No
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05Z1Z1-	No
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	No
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	No
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	No
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05Z1Z1-	No
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05Z1Z1-	No
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	No
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05Z1Z1-	No
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	Yes
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	Yes
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	No
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	No
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	No
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	No
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	Yes
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	Yes
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	No
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	No
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	Yes
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	Yes
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	Yes
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	Yes
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	No
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	Yes
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	Yes
910925866755	BGP293 LED149-4S/740 I DX10 76S	No

Order Code	Full Product Name	Dimmable
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	No
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	No
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	Yes
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	No
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	No
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	Yes
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	No
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	Yes
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	Yes
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	Yes
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	No
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05Z1Z1-	No
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05Z1Z1	No
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05Z1Z1	No
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05Z1Z1	No
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	No
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	No
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	No
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	No
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	Yes
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	Yes
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	No
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	No
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	No
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	Yes
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	Yes
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	Yes
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	Yes
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	Yes
910925866641	BGP291 LED60-4S/740 II DM11 48/60S	No
910925866644	BGP291 LED45-4S/740 II DM11 48/60S	No
910925866645	BGP291 LED60-4S/740 II DM11 48/60S	No
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	No
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	Yes
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	Yes
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	No
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	Yes
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	No
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	Yes
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	No
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	Yes
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	No
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	Yes
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	No
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	Yes
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	No
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05Z1Z1-	No
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	No
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05Z1Z1-	No

Order Code	Full Product Name	Dimmable
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05Z1Z1-	No
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05Z1Z1-	No
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	No
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	No
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	No
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05Z1Z1-	No
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05Z1Z1-	No
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05Z1Z1-	No
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05Z1Z1-	No
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	No
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	No
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	Yes
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	Yes
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	No
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	No
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes

Order Code	Full Product Name	Dimmable
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	No
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	No
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	No
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	Yes
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	Yes
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	No
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	Yes
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	No
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	No
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	No
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	No
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	No
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	No
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	No
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	No
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	No
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	No
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Yes
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	Yes
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	Yes
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Yes
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	Yes

General Information (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	150° - 43° x 67°	740 neutral white	LED49	1 unit
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	LED39	1 unit
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	150° - 43° x 67°	740 neutral white	LED99	1 unit
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	LED14	1 unit
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	LED120	1 unit
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	154° - 31° x 54°	740 neutral white	LED18	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	154° - 31° x 54°	740 neutral white	LED22	1 unit
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED34	1 unit
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED60	1 unit
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED80	1 unit
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED100	1 unit
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED120	1 unit
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	LED120	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	LED85	1 unit
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	LED85	1 unit
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED120	1 unit
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	150° - 43° x 67°	740 neutral white	LED75	1 unit
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	150° - 43° x 67°	740 neutral white	LED49	1 unit
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	LED27	1 unit
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	150° - 43° x 67°	740 neutral white	LED99	1 unit
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	LED34	1 unit
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	LED22	1 unit
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	150° - 43° x 67°	740 neutral white	LED75	1 unit
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	LED18	1 unit
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	LED27	1 unit
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	157° - 33° x 55°	740 neutral white	LED85	1 unit
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED49	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	160° - 42° x 54°	740 neutral white	LED74	1 unit
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	LED34	1 unit
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	160° - 42° x 54°	740 neutral white	LED94	1 unit
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	LED22	1 unit
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	157° - 33° x 55°	740 neutral white	LED109	1 unit
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED120	1 unit
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	LED22	1 unit
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	150° - 43° x 67°	740 neutral white	LED51	1 unit
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	53° x 71°	740 neutral white	LED39	1 unit
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	150° - 43° x 67°	740 neutral white	LED99	1 unit
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	150° - 43° x 67°	740 neutral white	LED75	1 unit
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	LED39	1 unit
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	150° - 43° x 67°	740 neutral white	LED51	1 unit
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	68° x 158°	740 neutral white	LED18	1 unit

LumiStreet gen2

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	61° x 150°	740 neutral white	LED39	1 unit
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	150° - 43° x 67°	740 neutral white	LED75	1 unit
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED65	1 unit
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED119	1 unit
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	157° - 33° x 55°	740 neutral white	LED39	1 unit
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	160° - 42° x 54°	740 neutral white	LED74	1 unit
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	160° - 42° x 54°	740 neutral white	LED94	1 unit
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED54	1 unit
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED64	1 unit
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	LED45	1 unit
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	-	740 neutral white	LED49	1 unit
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	157° - 33° x 55°	830 warm white	LED39	1 unit
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	157° - 33° x 55°	740 neutral white	LED49	1 unit
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED45	1 unit
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	LED35	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	157° - 33° x 55°	830 warm white	LED49	1 unit
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED35	1 unit
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	150° - 43° x 67°	740 neutral white	LED70	1 unit
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	150° - 43° x 67°	740 neutral white	LED80	1 unit
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	160° - 42° x 54°	740 neutral white	LED70	1 unit
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	160° - 42° x 54°	740 neutral white	LED120	1 unit
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED35	1 unit
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED35	1 unit
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED45	1 unit
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED45	1 unit
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED54	1 unit
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED64	1 unit
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	154° - 31° x 54°	730 warm white	LED100	1 unit
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	154° - 31° x 54°	730 warm white	LED100	1 unit
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	53° x 71°	740 neutral white	LED149	1 unit
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	150° - 43° x 67°	740 neutral white	LED120	1 unit

LumiStreet gen2

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	LED240	1 unit
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	160° - 42° x 54°	740 neutral white	LED240	1 unit
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED100	1 unit
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED139	1 unit
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED180	1 unit
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED240	1 unit
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	LED170	1 unit
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED240	1 unit
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED149	1 unit
910925866755	BGP293 LED149-4S/740 I DX10 76S	150° - 43° x 67°	740 neutral white	LED149	1 unit
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	61° x 150°	740 neutral white	LED139	1 unit
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	150° - 43° x 67°	740 neutral white	LED139	1 unit
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED149	1 unit
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	150° - 43° x 67°	740 neutral white	LED149	1 unit
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	61° x 150°	740 neutral white	LED149	1 unit
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	154° - 31° x 54°	740 neutral white	LED84	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	157° - 33° x 55°	740 neutral white	LED139	1 unit
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED84	1 unit
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED149	1 unit
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED109	1 unit
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	-	830 warm white	LED64	1 unit
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05Z1Z1-	160° - 42° x 54°	740 neutral white	LED80	1 unit
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED100	1 unit
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED120	1 unit
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED149	1 unit
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	-	740 neutral white	LED80	1 unit
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	-	830 warm white	LED80	1 unit
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	160° - 42° x 54°	740 neutral white	LED100	1 unit
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	-	740 neutral white	LED120	1 unit
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO- LS-6	-	740 neutral white	LED84	1 unit
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED60	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED80	1 unit
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED100	1 unit
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED120	1 unit
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED39	1 unit
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	LED50	1 unit
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	160° - 42° x 54°	740 neutral white	LED50	1 unit
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	154° - 31° x 54°	740 neutral white	LED8	1 unit
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED20	1 unit
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED40	1 unit
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED50	1 unit
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED64	1 unit
910925866641	BGP291 LED60-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925866644	BGP291 LED45-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	LED45	1 unit
910925866645	BGP291 LED60-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	160° - 42° x 54°	740 neutral white	LED45	1 unit
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED64	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	152° - 24° x 66°	740 neutral white	LED44	1 unit
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED34	1 unit
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED34	1 unit
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	LED34	1 unit
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED34	1 unit
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED44	1 unit
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED44	1 unit
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	LED44	1 unit
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED44	1 unit
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED51	1 unit
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED51	1 unit
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	157° - 33° x 55°	740 neutral white	LED34	1 unit
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05Z1Z1-	160° - 42° x 54°	740 neutral white	LED20	1 unit
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	-	740 neutral white	LED30	1 unit
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05Z1Z1-	160° - 42° x 54°	830 warm white	LED25	1 unit

LumiStreet gen2

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED35	1 unit
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED45	1 unit
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	157° - 33° x 55°	830 warm white	LED22	1 unit
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	160° - 42° x 54°	740 neutral white	LED45	1 unit
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	160° - 42° x 54°	740 neutral white	LED54	1 unit
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	LED20	1 unit
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED25	1 unit
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	LED35	1 unit
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	LED45	1 unit
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	-	740 neutral white	LED22	1 unit
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	157° - 33° x 55°	830 warm white	LED34	1 unit
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	150° - 43° x 67°	740 neutral white	LED45	1 unit
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	150° - 43° x 67°	740 neutral white	LED60	1 unit
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	160° - 42° x 54°	740 neutral white	LED25	1 unit
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	160° - 42° x 54°	740 neutral white	LED35	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED20	1 unit
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED20	1 unit
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED25	1 unit
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED25	1 unit
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED35	1 unit
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED35	1 unit
91092586808	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED45	1 unit
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED45	1 unit
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	154° - 31° x 54°	730 warm white	LED51	1 unit
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	154° - 31° x 54°	730 warm white	LED51	1 unit
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	160° - 42° x 54°	740 neutral white	LED340	2 units
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	154° - 31° x 54°	740 neutral white	LED180	2 units
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	154° - 31° x 54°	740 neutral white	LED240	2 units
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	160° - 42° x 54°	740 neutral white	LED240	2 units
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	LED340	2 units
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	160° - 42° x 54°	740 neutral white	LED240	2 units

LumiStreet gen2

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	-	830 warm white	LED140	2 units
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	-	830 warm white	LED240	2 units
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED400	2 units
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	-	740 neutral white	LED140	2 units
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	-	740 neutral white	LED240	2 units
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	-	740 neutral white	LED150	2 units
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	160° - 42° x 54°	740 neutral white	LED340	2 units

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED300	2 units
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED150	2 units
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED300	2 units
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	160° - 42° x 54°	740 neutral white	LED400	2 units
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED150	2 units
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED300	2 units
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED400	2 units

General Information (2/2)

Order Code	Full Product Name	Optic type	Product Family Code
910925866670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	Distribution extra wide 10	BGP292
910925866673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Distribution narrow 10	BGP292
910925866677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	Distribution extra wide 10	BGP292
910925866683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	Distribution medium 12	BGP292
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	Distribution medium 11	BGP292
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	Distribution medium 50	BGP292
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	Distribution medium 50	BGP292
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP292
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP292
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP292
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP292

Order Code	Full Product Name	Optic type	Product Family Code
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP292
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	Distribution medium 11	BGP292
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	Distribution medium 11	BGP292
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	Distribution medium 11	BGP292
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP392
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	Distribution extra wide 10	BGP292
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	Distribution extra wide 10	BGP292
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Distribution narrow 10	BGP292
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/6	Distribution extra wide 10	BGP292
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Distribution narrow 10	BGP292
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Distribution medium 12	BGP292

Order Code	Full Product Name	Optic type	Product Family Code
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	Distribution extra wide 10	BGP292
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	Distribution medium 12	BGP292
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	Distribution narrow 10	BGP292
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	Distribution medium 10	BGP292
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP292
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP292
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	Distribution narrow 10	BGP292
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	Distribution medium 11	BGP292
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	Distribution narrow 10	BGP292
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	Distribution medium 10	BGP292
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05ZIZI	Distribution medium 11	BGP292
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	Distribution medium 12	BGP292
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	Distribution extra wide 10	BGP292
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	Distribution medium 12	BGP292
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	Distribution extra wide 10	BGP292
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	Distribution extra wide 10	BGP292
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	Distribution narrow 10	BGP292
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	Distribution extra wide 10	BGP292
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	Distribution narrow 10	BGP292
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	Distribution wide 10	BGP292
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	Distribution extra wide 10	BGP292
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP292
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	Distribution medium 11	BGP292
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	Distribution medium 10	BGP292
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	Distribution medium 11	BGP292

Order Code	Full Product Name	Optic type	Product Family Code
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	Distribution medium 11	BGP292
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP292
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP292
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP292
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	Distribution medium 32	BGP292
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	Distribution medium 10	BGP292
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	Distribution medium 10	BGP292
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP292
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP292
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	Distribution medium 10	BGP292
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP292
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	Distribution extra wide 10	BGP292
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	Distribution extra wide 10	BGP292
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	Distribution medium 11	BGP292
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	Distribution medium 11	BGP292
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP292
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	Distribution medium 50	BGP292
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	Distribution medium 50	BGP292
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	Distribution medium 12	BGP293
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	Distribution extra wide 10	BGP293

Order Code	Full Product Name	Optic type	Product Family Code
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	Distribution medium 11	BGP293
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	Distribution medium 11	BGP293
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP293
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP293
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP293
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP293
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	Distribution medium 11	BGP293
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP393
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP293
910925866755	BGP293 LED149-4S/740 I DX10 76S	Distribution extra wide 10	BGP293
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	Distribution wide 10	BGP293
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	Distribution extra wide 10	BGP293
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP293
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	Distribution extra wide 10	BGP293
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	Distribution wide 10	BGP293
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	Distribution medium 50	BGP293
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	Distribution medium 10	BGP293
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP293
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP293
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP293
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	Distribution medium 31	BGP293
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05ZIZ1-	Distribution medium 11	BGP293
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05ZIZ1	Distribution medium 11	BGP293
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05ZIZ1	Distribution medium 11	BGP293
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05ZIZ1	Distribution medium 11	BGP293

Order Code	Full Product Name	Optic type	Product Family Code
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	Distribution medium 31	BGP293
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	Distribution medium 31	BGP293
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	Distribution medium 11	BGP293
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	Distribution medium 32	BGP293
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	Distribution medium 32	BGP293
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP293
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP293
91092586809	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP293
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP293
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	Distribution medium 50	BGP291
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	Distribution medium 11	BGP291
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	Distribution medium 11	BGP291
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	Distribution medium 50	BGP291
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP291
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP291
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP291
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP291
910925866641	BGP291 LED60-4S/740 II DM11 48/60S	Distribution medium 11	BGP291
910925866644	BGP291 LED45-4S/740 II DM11 48/60S	Distribution medium 11	BGP291
910925866645	BGP291 LED60-4S/740 II DM11 48/60S	Distribution medium 11	BGP291
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	Distribution medium 11	BGP291
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	Distribution medium 11	BGP391
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	Distribution wide 50	BGP291
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	Distribution medium 11	BGP291
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291

Order Code	Full Product Name	Optic type	Product Family Code
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	Distribution medium 11	BGP291
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	Distribution medium 11	BGP291
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	Distribution medium 11	BGP291
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	Distribution medium 11	BGP291
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	Distribution medium 32	BGP291
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP291
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	Distribution medium 10	BGP291
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP291
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP291
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP291
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	Distribution medium 10	BGP291
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	Distribution medium 11	BGP291
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	Distribution medium 11	BGP291
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP291
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP291
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP291
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05ZIZI-	Distribution medium 11	BGP291
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	Distribution medium 32	BGP291
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	Distribution medium 10	BGP291
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	Distribution extra wide 10	BGP291
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	Distribution extra wide 10	BGP291

Order Code	Full Product Name	Optic type	Product Family Code
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	Distribution medium 32	BGP291
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	Distribution medium 11	BGP291
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
91092586808	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11	BGP291
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	Distribution medium 50	BGP291
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	Distribution medium 50	BGP291
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	Distribution medium 11	BGP294
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	Distribution medium 50	BGP294
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	Distribution medium 50	BGP294
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	Distribution medium 11	BGP294
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	Distribution medium 11	BGP394
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	Distribution medium 11	BGP294
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	Distribution medium 31	BGP294
91092586690	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	Distribution medium 31	BGP294
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05ZIZI	Distribution medium 11	BGP294
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	Distribution medium 31	BGP294
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	Distribution medium 31	BGP294
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	Distribution medium 32	BGP294
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	Distribution medium 11	BGP294

Order Code	Full Product Name	Optic type	Product Family Code
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Distribution medium 11	BGP294
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05Z1Z1	Distribution medium 11	BGP294
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05Z1Z1	Distribution medium 11	BGP294
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05Z1Z1	Distribution medium 11	BGP294

Order Code	Full Product Name	Optic type	Product Family Code
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP294
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP294
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11	BGP294

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865670	BGP292 LED49-4S/740 I DX10 7024 D9 76S	4000 K	70	4165 lm
910925865673	BGP292 LED39-4S/740 II DN10 SW302F CLO D	4000 K	70	3420 lm
910925865677	BGP292 LED99-4S/740 I DX10 7024 D9 48/60	4000 K	70	8300 lm
910925865683	BGP292 LED14-4S/740 II DM12 SW302F CLO D	4000 K	70	1215 lm
910925866443	BGP292 LED120-4S/740 I DM11 48/60S	4000 K	70	10440 lm
910925866607	BGP292 LED18-4S/740 I DM50 D948/60S	4000 K	70	1584 lm
910925866608	BGP292 LED22-4S/740 I DM50 D948/60S	4000 K	70	1936 lm
910925866615	BGP292 LED34-4S/740 II DM50 D9 48/60S	4000 K	70	2992 lm
910925866616	BGP292 LED60-4S/740 II DM50 D9 48/60S	4000 K	70	5220 lm
910925866617	BGP292 LED80-4S/740 II DM50 D9 48/60S	4000 K	70	6880 lm
910925866618	BGP292 LED100-4S/740 II DM50 D9 48/60S	4000 K	70	8500 lm
910925866628	BGP292 LED120-4S/740 II DM50 D9 48/60S	4000 K	70	10200 lm
910925866639	BGP292 LED120-4S/740 II DM11 48/60S	4000 K	70	10440 lm
910925866640	BGP292 LED85-4S/740 II DM11 48/60S	4000 K	70	7568 lm
910925866642	BGP292 LED85-4S/740 II DM11 48/60S	4000 K	70	7568 lm
910925866657	BGP392 LED120-4S/740 II DM11 D9 48/60S	4000 K	70	10440 lm
910925866697	BGP292 LED75-4S/740 I DX10 7024 D9 48/60	4000 K	70	6460 lm
910925866698	BGP292 LED49-4S/740 I DX10 7024 D9 48/60	4000 K	70	4165 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866699	BGP292 LED27-4S/740 II DN10 SW302F CLO D	4000 K	70	2430 lm
910925866702	BGP292 LED99-4S/740 II DX10 7024 D9 48/60	4000 K	70	8300 lm
910925866703	BGP292 LED34-4S/740 II DN10 SW302F CLO D	4000 K	70	2970 lm
910925866704	BGP292 LED22-4S/740 II DM12 SW302F CLO D	4000 K	70	1890 lm
910925866705	BGP292 LED75-4S/740 I DX10 7024 D9 76S	4000 K	70	6460 lm
910925866712	BGP292 LED18-4S/740 II DM12 SW302F CLO D	4000 K	70	1575 lm
910925866716	BGP292 LED27-4S/740 II DN10 SW302F CLO D	4000 K	70	2430 lm
910925866721	BGP292 LED85-4S/740 I DM10 D9SRG10 48/60	4000 K	70	7482 lm
910925866722	BGP292 LED49-4S/740 II DM50 D9 48/60S	4000 K	70	4263 lm
910925866724	BGP292 LED74-4S/740 II DM11 CLO S05Z1Z1-	4000 K	70	6408 lm
910925866727	BGP292 LED34-4S/740 II DN10 SW302F CLO D	4000 K	70	2970 lm
910925866730	BGP292 LED94-4S/740 II DM11 CLO D9 48/60	4000 K	70	7920 lm
910925866731	BGP292 LED22-4S/740 II DN10 SW302F CLO D	4000 K	70	1890 lm
910925866734	BGP292 LED109-4S/740 II DM10 7043 D9 48/	4000 K	70	9570 lm
910925866748	BGP292 LED120-4S/740 II DM11 CLO S05Z1Z1	4000 K	70	10005 lm
910925866749	BGP292 LED22-4S/740 II DM12 SW302F CLO D	4000 K	70	1890 lm
910925866753	BGP292 LED51-4S/740 I DX10 P148/60S	4000 K	70	4420 lm
910925866761	BGP292 LED39-4S/740 II DM12 SW302F CLO D	4000 K	70	3420 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866766	BGP292 LED99-4S/740 I DX10 7024 D9 76S	4000 K	70	8300 lm
910925866771	BGP292 LED75-4S/740 I DX10 48/60S	4000 K	70	6460 lm
910925866772	BGP292 LED39-4S/740 II DN10 SW302F CLO D	4000 K	70	3420 lm
910925866773	BGP292 LED51-4S/740 I DX10 48/60S	4000 K	70	4420 lm
910925866796	BGP292 LED18-4S/740 II DN10 SW302F CLO D	4000 K	70	1575 lm
910925866804	BGP292 LED39-4S/740 II DW10 SW302F CLO D	4000 K	70	3382 lm
910925866805	BGP292 LED75-4S/740 I DX10 ALU D9 76S	4000 K	70	6460 lm
910925866809	BGP292 LED65-4S/740 II DM50 D9 48/60S	4000 K	70	5742 lm
910925866853	BGP292 LED119-4S/740 II DM11 CLO 48/60S	4000 K	70	10005 lm
910925866892	BGP292 LED39-4S/740 II DM10 MSP CLO SRTH	4000 K	70	3382 lm
910925866895	BGP292 LED74-4S/740 II DM11 CLO SRT 48/6	4000 K	70	6408 lm
910925866896	BGP292 LED94-4S/740 II DM11 CLO SRT 48/6	4000 K	70	7920 lm
910925866899	BGP292 LED54-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	4628 lm
910925866901	BGP292 LED64-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	5518 lm
910925866912	BGP292 LED45-4S/830 II DM11 CLO S05ZIZI-	3000 K	80	3827 lm
910925866915	BGP292 LED49-4S/740 II DM32 MSP CLO SRTS	4000 K	70	4320 lm
910925866918	BGP292 LED39-4S/830 II DM10 MSP CLO SRTH	3000 K	80	3344 lm
910925866919	BGP292 LED49-4S/740 II DM10 MSP CLO SRTH	4000 K	70	4224 lm
910925866930	BGP292 LED45-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	3916 lm
910925866934	BGP292 LED35-4S/830 II DM11 CLO S05ZIZI-	3000 K	80	3026 lm
910925866938	BGP292 LED49-4S/830 II DM10 MSP CLO SRTH	3000 K	80	4089 lm
910925866941	BGP292 LED35-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	3026 lm
910925867777	BGP292 LED70-4S/740 II DX10 D11 H07RN-F-	4000 K	70	5950 lm
910925867778	BGP292 LED80-4S/740 II DX10 BL1 D11 H07R	4000 K	70	6720 lm
910925867781	BGP292 LED70-4S/740 II DM11 48/76S POLE	4000 K	70	6230 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925867782	BGP292 LED120-4S/740 II DM11 48/76S POLE	4000 K	70	10440 lm
910925868082	BGP292 LED35-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3026 lm
910925868083	BGP292 LED35-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3026 lm
910925868084	BGP292 LED45-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3916 lm
910925868085	BGP292 LED45-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3827 lm
910925868086	BGP292 LED54-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	4628 lm
910925868087	BGP292 LED64-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	5518 lm
910925868107	BGP292 LED100-4S/730 II DM50 MSP 48/60S	3000 K	70	8600 lm
910925868108	BGP292 LED100-4S/730 II DM50 48/60S	3000 K	70	8600 lm
910925865671	BGP293 LED149-4S/740 I DM12 D9 SRG10 48/	4000 K	70	13200 lm
910925865680	BGP293 LED120-4S/740 I DX10 7024 D9 48/6	4000 K	70	10200 lm
910925866444	BGP293 LED240-4S/740 I DM11 48/60S	4000 K	70	20640 lm
910925866456	BGP293 LED240-4S/740 I DM11 SRT SRB SRG1	4000 K	70	20640 lm
910925866630	BGP293 LED100-4S/740 II DM50 D9 48/60S	4000 K	70	8700 lm
910925866631	BGP293 LED139-4S/740 II DM50 D9 48/60S	4000 K	70	12040 lm
910925866632	BGP293 LED180-4S/740 II DM50 D9 48/60S	4000 K	70	15300 lm
910925866633	BGP293 LED240-4S/740 II DM50 D9 48/60S	4000 K	70	20160 lm
910925866643	BGP293 LED170-4S/740 II DM11 48/60S	4000 K	70	14790 lm
910925866662	BGP393 LED240-4S/740 II DM11 D9 48/60S	4000 K	70	20640 lm
910925866723	BGP293 LED149-4S/740 II DM50 D9 48/60S	4000 K	70	12900 lm
910925866755	BGP293 LED149-4S/740 I DX10 76S	4000 K	70	12600 lm
910925866757	BGP293 LED139-4S/740 II DW10 SW302F CLO7	4000 K	70	11880 lm
910925866759	BGP293 LED139-4S/740 I DX10 48/60S	4000 K	70	11760 lm
910925866762	BGP293 LED149-4S/740 II DM50 D9 48/60S	4000 K	70	12900 lm
910925866767	BGP293 LED149-4S/740 I DX10 48/60S	4000 K	70	12600 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866777	BGP293 LED149-4S/740 II DW10 H07RN-F-2X1	4000 K	70	13200 lm
910925866786	BGP293 LED84-4S/740 I DM50 D948/60S	4000 K	70	7392 lm
910925866789	BGP293 LED139-4S/740 II DM10 48/60S	4000 K	70	12180 lm
910925866793	BGP293 LED84-4S/740 II DM50 D9 48/60S	4000 K	70	7392 lm
910925866795	BGP293 LED149-4S/740 I DM50 D9 48/60S	4000 K	70	12900 lm
910925866810	BGP293 LED109-4S/740 I DM50 D9 48/60S	4000 K	70	9570 lm
910925866894	BGP293 LED64-4S/830 II DM31 MSP CLO SRTH	3000 K	80	5456 lm
910925866902	BGP293 LED80-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	6942 lm
910925866903	BGP293 LED100-4S/740 II DM11 CLO S05ZIZI	4000 K	70	8722 lm
910925866904	BGP293 LED120-4S/740 II DM11 CLO S05ZIZI	4000 K	70	10235 lm
910925866905	BGP293 LED149-4S/740 II DM11 CLO S05ZIZI	4000 K	70	12760 lm
910925866920	BGP293 LED80-4S/740 II DM31 MSP CLO SRTH	4000 K	70	6942 lm
910925866921	BGP293 LED80-4S/830 II DM31 MSP CLO SRTH	3000 K	80	6942 lm
910925866926	BGP293 LED100-4S/740 II DM11 CLO SRT 48/	4000 K	70	8722 lm
910925866936	BGP293 LED120-4S/740 II DM32 MSP CLO SRT	4000 K	70	10350 lm
910925867860	BGP293 LED84-4S/740 II DM32 MSP CLO-LS-6	4000 K	70	7380 lm
910925868088	BGP293 LED60-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	5162 lm
910925868089	BGP293 LED80-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	6942 lm
910925868090	BGP293 LED100-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	8722 lm
910925868091	BGP293 LED120-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	10235 lm
910925865679	BGP291 LED39-4S/740 II DM50 48/60S	4000 K	70	3432 lm
910925866442	BGP291 LED50-4S/740 I DM11 48/60S	4000 K	70	4450 lm
910925866454	BGP291 LED50-4S/740 I DM11 SRT SRB SRG10	4000 K	70	4450 lm
910925866610	BGP291 LED8-4S/740 II DM50 D948/60S	4000 K	70	704 lm
910925866611	BGP291 LED20-4S/740 II DM50 D9 48/60S	4000 K	70	1740 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866612	BGP291 LED40-4S/740 II DM50 D9 48/60S	4000 K	70	3520 lm
910925866613	BGP291 LED50-4S/740 II DM50 D9 48/60S	4000 K	70	4350 lm
910925866614	BGP291 LED64-4S/740 II DM50 D9 48/60S	4000 K	70	5504 lm
910925866641	BGP291 LED60-4S/740 II DM11 48/60S	4000 K	70	5280 lm
910925866644	BGP291 LED45-4S/740 II DM11 48/60S	4000 K	70	4005 lm
910925866645	BGP291 LED60-4S/740 II DM11 48/60S	4000 K	70	5280 lm
910925866646	BGP291 LED45-4S/740 II DM11 48/60S	4000 K	70	4005 lm
910925866652	BGP391 LED64-4S/740 II DM11 D9 48/60S	4000 K	70	5632 lm
910925866780	BGP291 LED44-4S/740 I DW50 CLO D9 P1 32/	4000 K	70	3655 lm
910925866856	BGP291 LED34-4S/740 II DM11 CLO 48/60S	4000 K	70	2937 lm
910925866857	BGP291 LED34-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2937 lm
910925866858	BGP291 LED34-4S/830 II DM11 CLO 48/60S	3000 K	80	2937 lm
910925866859	BGP291 LED34-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2937 lm
910925866860	BGP291 LED44-4S/740 II DM11 CLO 48/60S	4000 K	70	3827 lm
910925866861	BGP291 LED44-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3827 lm
910925866862	BGP291 LED44-4S/830 II DM11 CLO 48/60S	3000 K	80	3738 lm
910925866863	BGP291 LED44-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3738 lm
910925866864	BGP291 LED51-4S/740 II DM11 CLO 48/60S	4000 K	70	4361 lm
910925866865	BGP291 LED51-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	4361 lm
910925866891	BGP291 LED34-4S/740 II DM10 MSP CLO SRTH	4000 K	70	2970 lm
910925866898	BGP291 LED20-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	1691 lm
910925866907	BGP291 LED30-4S/740 II DM32 MSP CLO SRTH	4000 K	70	2552 lm
910925866910	BGP291 LED25-4S/830 II DM11 CLO S05ZIZI-	3000 K	80	2136 lm
910925866911	BGP291 LED35-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	3026 lm
910925866913	BGP291 LED45-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	3916 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866917	BGP291 LED22-4S/830 II DM10 MSP CLO SRTH	3000 K	80	1848 lm
910925866924	BGP291 LED45-4S/740 II DM11 CLO SRT 48/6	4000 K	70	3916 lm
910925866925	BGP291 LED54-4S/740 II DM11 CLO SRT 48/6	4000 K	70	4628 lm
910925866928	BGP291 LED20-4S/830 II DM11 CLO S05ZIZI-	3000 K	80	1735.5 lm
910925866929	BGP291 LED25-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	2136 lm
910925866932	BGP291 LED35-4S/830 II DM11 CLO S05ZIZI-	3000 K	80	3026 lm
910925866933	BGP291 LED45-4S/830 II DM11 CLO S05ZIZI-	3000 K	80	3827 lm
910925866935	BGP291 LED22-4S/740 II DM32 MSP CLO SRTH	4000 K	70	1911 lm
910925866939	BGP291 LED34-4S/830 II DM10 MSP CLO SRTH	3000 K	80	2904 lm
910925867775	BGP291 LED45-4S/740 II DX10 D11 H07RN-F-	4000 K	70	3825 lm
910925867776	BGP291 LED60-4S/740 II DX10 BL1 D11 H07R	4000 K	70	5040 lm
910925867779	BGP291 LED25-4S/740 II DM11 48/76S POLE	4000 K	70	2275 lm
910925867780	BGP291 LED35-4S/740 II DM11 48/76S POLE	4000 K	70	3115 lm
910925868074	BGP291 LED20-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	1691 lm
910925868075	BGP291 LED20-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	1735.5 lm
910925868076	BGP291 LED25-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2136 lm
910925868077	BGP291 LED25-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2136 lm
910925868078	BGP291 LED35-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3026 lm
910925868079	BGP291 LED35-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3026 lm
910925868080	BGP291 LED45-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3916 lm
910925868081	BGP291 LED45-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3827 lm
910925868105	BGP291 LED51-4S/730 II DM50 MSP 48/60S	3000 K	70	4524 lm
910925868106	BGP291 LED51-4S/730 II DM50 48/60S	3000 K	70	4524 lm
910925866445	BGP294 LED340-4S/740 I DM11 48/60S PLS	4000 K	70	29240 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866635	BGP294 LED180-4S/740 II DM50 D9 48/60S P	4000 K	70	15660 lm
910925866636	BGP294 LED240-4S/740 II DM50 D9 48/60S P	4000 K	70	20640 lm
910925866647	BGP294 LED240-4S/740 II DM11 48/60S PLS	4000 K	70	21120 lm
910925866667	BGP394 LED340-4S/740 II DM11 D9 48/60S P	4000 K	70	29240 lm
910925866897	BGP294 LED240-4S/740 II DM11 CLO SRT 48/	4000 K	70	20240 lm
910925866908	BGP294 LED140-4S/830 II DM31 MSP CLO SRT	3000 K	80	12015 lm
910925866909	BGP294 LED240-4S/830 II DM31 MSP CLO SRT	3000 K	80	20010 lm
910925866914	BGP294 LED400-4S/740 II DM11 CLO S05ZIZI	4000 K	70	32300 lm
910925866922	BGP294 LED140-4S/740 II DM31 MSP CLO SRT	4000 K	70	12460 lm
910925866923	BGP294 LED240-4S/740 II DM31 MSP CLO SRT	4000 K	70	20240 lm
910925866937	BGP294 LED150-4S/740 II DM32 MSP CLO SRT	4000 K	70	13500 lm
910925866940	BGP294 LED340-4S/740 II DM11 CLO SRT 48/	4000 K	70	28380 lm
910925866942	BGP294 LED300-4S/740 II DM11 CLO S05ZIZI	4000 K	70	25230 lm
910925868071	BGP294 LED150-4S/740 II DM11 CLO S05ZIZI	4000 K	70	13350 lm
910925868072	BGP294 LED300-4S/740 II DM11 CLO S05ZIZI	4000 K	70	25230 lm
910925868073	BGP294 LED400-4S/740 II DM11 CLO S05ZIZI	4000 K	70	32300 lm
910925868092	BGP294 LED150-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	13350 lm
910925868093	BGP294 LED300-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	25230 lm
910925868094	BGP294 LED400-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	32300 lm

