



Get your city ready for the future with RoadCharm.

RoadCharm

Developed with the aim to become your long term partner, the system ready architecture of RoadCharm enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come. It is designed to achieve better light uniformity and a maximum spacing between poles for both pedestrian and vehicle road applications. With its die-cast aluminum housing and Philips LED platform, it is easy to maintain, has a long lifetime, and a consistency you can count on. It also offers 2 housing sizes and a range of beam optics to fully cater to different road configurations and conditions. RoadCharm offers 50% energy savings compared to conventional lamp systems, making it the perfect sustainable lighting solution for any emerging metropolis.

Benefits

- Robust & Reliable with a long service lifetime
- Elegant finless design
- System ready design
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information.

Features

- Best in class efficiency and light performance in a broad range of applications.
- Long service lifetime 100Khrs L70B10 @Ta 35°C
- System ready option with SR(Zhaga) and 7Pin NEMA socket options.
- Surge protection up to 15kV.

Application

- Pedestrian category roads (P1-P6)
- Vehicle category roads (M1-M6)
- Traffic routes and main access road
- Urban and residential area

Versions



BRP471



BRP472

Approval and Application

Mech. impact protection code	IK08
Surge Protection (Common/Differential)	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode

Controls and Dimming

Dimmable	No
-----------------	----

General Information

CE mark	CE mark
Light source color	740 neutral white
Optical cover/lens type	Polycarbonate micro lens optic
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No

Initial Performance (IEC Compliant)

Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	>70

Light Technical

Standard tilt angle posttop	-
------------------------------------	---

Mechanical and Housing

Color	Gray
--------------	------

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux
911401657805	BRP471 LED 47/NW 36W 220-240V DME	4700 lm
911401657905	BRP471 LED 58/NW 45W 220-240V DME	5800 lm
911401658005	BRP471 LED 69/NW 53W 220-240V DME	6900 lm
911401658105	BRP471 LED 79/NW 60W 220-240V DME	7900 lm
911401658205	BRP471 LED 90/NW 70W 220-240V DME	9000 lm
911401658305	BRP471 LED 102/NW 78W 220-240V DME	10200 lm
911401658405	BRP471 LED 114/NW 85W 220-240V DME	11400 lm
911401658505	BRP471 LED 124/NW 95W 220-240V DME	12400 lm
911401658605	BRP471 LED 133/NW 102W 220-240V DME	13300 lm
911401658705	BRP471 LED 145/NW 110W 220-240V DME	14500 lm
911401658805	BRP471 LED 155/NW 118W 220-240V DME	15500 lm
911401658905	BRP471 LED 165/NW 127W 220-240V DME	16500 lm
911401659005	BRP471 LED 175/NW 135W 220-240V DME	17500 lm
911401659105	BRP471 LED 165/NW 127W 220-240V DME II	16500 lm
911401659205	BRP471 LED 47/NW 36W 220-240V DME GC	4700 lm
911401659305	BRP471 LED 58/NW 45W 220-240V DME GC	5800 lm
911401659405	BRP471 LED 69/NW 53W 220-240V DME GC	6900 lm
911401659505	BRP471 LED 79/NW 60W 220-240V DME GC	7900 lm
911401659605	BRP471 LED 90/NW 70W 220-240V DME GC	9000 lm
911401659705	BRP471 LED 102/NW 78W 220-240V DME GC	10200 lm
911401659805	BRP471 LED 114/NW 85W 220-240V DME GC	11400 lm
911401659905	BRP471 LED 124/NW 95W 220-240V DME GC	12400 lm
911401660005	BRP471 LED 133/NW 102W 220-240V DME GC	13300 lm
911401660105	BRP471 LED 145/NW 110W 220-240V DME GC	14500 lm
911401660205	BRP471 LED 155/NW 118W 220-240V DME GC	15500 lm
911401660305	BRP471 LED 165/NW 127W 220-240V DME GC	16500 lm
911401660405	BRP471 LED 175/NW 135W 220-240V DME GC	17500 lm
911401676705	BRP471 LED 47/NW 36W PSD 120-277v DME	4700 lm
911401661105	BRP472 LED 189/NW 144W 220-240V DME	18900 lm
911401661205	BRP472 LED 200/NW 155W 220-240V DME	20000 lm
911401661305	BRP472 LED 210/NW 163W 220-240V DME	21000 lm
911401661405	BRP472 LED 221/NW 171W 220-240V DME	22100 lm
911401661505	BRP472 LED 231/NW 179W 220-240V DME	23100 lm
911401661605	BRP472 LED 242/NW 187W 220-240V DME	24200 lm
911401661705	BRP472 LED 252/NW 195W 220-240V DME	25200 lm
911401661805	BRP472 LED 262/NW 204W 220-240V DME	26200 lm
911401661905	BRP472 LED 273/NW 212W 220-240V DME	27300 lm
911401662005	BRP472 LED 283/NW 220W 220-240V DME	28300 lm
911401662105	BRP472 LED 293/NW 228W 220-240V DME	29300 lm
911401662205	BRP472 LED 303/NW 236W 220-240V DME	30300 lm
911401662305	BRP472 LED 313/NW 244W 220-240V DME	31300 lm
911401662405	BRP472 LED 323/NW 252W 220-240V DME	32300 lm
911401662505	BRP472 LED 333/NW 260W 220-240V DME	33300 lm
911401662605	BRP472 LED 342/NW 288W 220-240V DME	34200 lm
911401662705	BRP472 LED 189/NW 144W 220-240V DME GC	18900 lm
911401662805	BRP472 LED 200/NW 155W 220-240V DME GC	20000 lm
911401662905	BRP472 LED 210/NW 163W 220-240V DME GC	21000 lm
911401663005	BRP472 LED 221/NW 171W 220-240V DME GC	22100 lm
911401663105	BRP472 LED 231/NW 179W 220-240V DME GC	23100 lm
911401663205	BRP472 LED 242/NW 187W 220-240V DME GC	24200 lm
911401663305	BRP472 LED 252/NW 195W 220-240V DME GC	25200 lm

Order Code	Full Product Name	Initial luminous flux
911401663405	BRP472 LED 262/NW 204W 220-240V DME GC	26200 lm
911401663505	BRP472 LED 273/NW 212W 220-240V DME GC	27300 lm
911401663605	BRP472 LED 283/NW 220W 220-240V DME GC	28300 lm
911401663705	BRP472 LED 293/NW 228W 220-240V DME GC	29300 lm
911401663805	BRP472 LED 303/NW 236W 220-240V DME GC	30300 lm
911401663905	BRP472 LED 313/NW 244W 220-240V DME GC	31300 lm
911401664005	BRP472 LED 323/NW 252W 220-240V DME GC	32300 lm
911401664105	BRP472 LED 333/NW 260W 220-240V DME GC	33300 lm
911401664205	BRP472 LED 342/NW 268W 220-240V DME GC	34200 lm
911401664305	BRP472 LED 342/NW 288W 220-240V DME II	34200 lm

