



Elegant outlook design projector for the retail segment

Truefashion Projector GCGM

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

Benefits

- Slim and compact outlook design with inside track driver.
- Excellent light quality of punch effect.
- Dedicated light recipe for fashion and food.
- System connectivity with Dali-VLC.

Features

- Lumen packages (1000/2000/3000/4000lm).
- 3 beams options (NB/MB/WB).
- Dali-VLC Control.
- Track version available in 1C, 3C.
- CB, EMC, CCC, ACC.
- Lifetime 50K Hours.

Application

- Retail fashion store
- Shopping mall
- Food & large retail

Warnings and Safety

- 3 years

Truefashion Projector GCGM

Versions



GD700B 1 head WH



GD700B 1 head BK



GD700B 2 heads WH



GD700B 2 heads BK



RS700B LED10 LED20 WH



RS700B LED10 LED20 BK



RS700B LED30 LED40 WH



RS700B LED30 LED40 BK



Truefashion projector GCGM



ST700T

Approval and Application

Mech. impact protection code	-
Ingress protection code	IP20

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

CE mark	CE mark
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Truefashion Projector GCGM

Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
911401518371	GD700B LED10 830 PSU MB WH	-15 to +35 °C	-	-
911401518571	GD700B LED20 930PW PSU MB WH	-15 to +35 °C	-	-
911401530571	GD700B LED20 940PW PSU MB WH HB	-15 to +35 °C	-	-
911401518471	GD700B LED10 830 PSU MB BK	-15 to +35 °C	-	-
911401518671	GD700B LED20 930PW PSU MB BK	-15 to +35 °C	-	-
911401518771	GD700B 2XLED10 830 PSU MB WH	-15 to +35 °C	-	-
911401518971	GD700B 2XLED20 930PW PSU MB WH	-15 to +35 °C	-	-
911401518871	GD700B 2XLED10 830 PSU MB BK	-15 to +35 °C	-	-
911401519071	GD700B 2XLED20 930PW PSU MB BK	-15 to +35 °C	-	-
911401519171	RS700B LED10 830 PSU MB WH EB YM	-15 to +35 °C	-	-
911401519371	RS700B LED10 827 PSU MB WH EB YM	-15 to +35 °C	-	-
911401519471	RS700B LED10 830 PSU MB WH	-15 to +35 °C	-	-
911401519571	RS700B LED10 830 PSU WB WH	-15 to +35 °C	-	-
911401519671	RS700B LED20 830 PSU WB WH YM	-15 to +35 °C	-	-
911401519771	RS700B LED20 930PW PSU NB WH	-15 to +35 °C	-	-
911401519871	RS700B LED20 930PW PSU MB WH	-15 to +35 °C	-	-
911401519971	RS700B LED20 930PW PSU WB WH	-15 to +35 °C	-	-
911401520071	RS700B LED20 940PW PSU MB WH	-15 to +35 °C	-	-
911401520571	RS700B LED20 930PC PSU MB WH	-15 to +35 °C	-	-
911401522271	RS700B LED20 940PW PSU MB WH HB	-15 to +35 °C	-	-
911401530371	RS700B LED10 830 PSU MB WH YM	-15 to +35 °C	-	-
911401530471	RS700B LED10 830 PSU WB WH YM	-15 to +35 °C	-	-
911401519271	RS700B LED10 830 PSU MB BK EB YM	-15 to +35 °C	-	-

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
911401520171	RS700B LED20 930PW PSU NB BK	-15 to +35 °C	-	-
911401520271	RS700B LED20 930PW PSU MB BK	-15 to +35 °C	-	-
911401520371	RS700B LED20 930PW PSU WB BK	-15 to +35 °C	-	-
911401520471	RS700B LED20 940PW PSU MB BK	-15 to +35 °C	-	-
911401520671	RS700B LED30 930PW PSU NB WH	-15 to +35 °C	-	-
911401520771	RS700B LED30 930PW PSU MB WH	-15 to +35 °C	-	-
911401520871	RS700B LED30 930PW PSU WB WH	-15 to +35 °C	-	-
911401520971	RS700B LED30 940PW PSU MB WH	-15 to +35 °C	-	-
911401521471	RS700B LED30 930PC PSU MB WH	-15 to +35 °C	-	-
911401521571	RS700B LED40 930PW PSU MB WH	-15 to +35 °C	-	-
911401521671	RS700B LED40 930PW PSU WB WH	-15 to +35 °C	-	-
911401521771	RS700B LED40 940PW PSU MB WH	-15 to +35 °C	-	-
911401522171	RS700B LED40 930PC PSU MB WH	-15 to +35 °C	-	-
911401522371	RS700B LED40 940PW PSU MB WH HB	-15 to +35 °C	-	-
911401522471	RS700B LED30 930PW PSD VLC NB WH	-15 to +35 °C	-	-
911401522571	RS700B LED30 930PW PSD VLC MB WH	-15 to +35 °C	-	-
911401522671	RS700B LED30 930PW PSD VLC WB WH	-15 to +35 °C	-	-
911401521071	RS700B LED30 930PW PSU NB BK	-15 to +35 °C	-	-
911401521171	RS700B LED30 930PW PSU MB BK	-15 to +35 °C	-	-
911401521271	RS700B LED30 930PW PSU WB BK	-15 to +35 °C	-	-
911401521371	RS700B LED30 940PW PSU MB BK	-15 to +35 °C	-	-
911401521871	RS700B LED40 930PW PSU MB BK	-15 to +35 °C	-	-

Truefashion Projector GCGM

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
911401521971	RS700B LED40 930PW PSU WB BK	-15 to +35 °C	-	-
911401522071	RS700B LED40 940PW PSU MB BK	-15 to +35 °C	-	-
911401522771	RS700B LED30 930PW PSD VLC NB BK	-15 to +35 °C	-	-
911401522871	RS700B LED30 930PW PSD VLC MB BK	-15 to +35 °C	-	-
911401522971	RS700B LED30 930PW PSD VLC WB BK	-15 to +35 °C	-	-
911401546661	ST700T LED20 930PC PSU NB 1C WH	-20 to +35 °C	Not applicable	No
911401546761	ST700T LED20 930PC PSU MB 1C WH	-20 to +35 °C	Not applicable	No
911401546861	ST700T LED20 930PC PSU WB 1C WH	-20 to +35 °C	Not applicable	No
911401546961	ST700T LED20 930PC PSU NB 1C BK	-20 to +35 °C	Not applicable	No
911401547061	ST700T LED20 930PC PSU MB 1C BK	-20 to +35 °C	Not applicable	No
911401547161	ST700T LED20 930PC PSU WB 1C BK	-20 to +35 °C	Not applicable	No
911401547261	ST700T LED30 930PC PSU MB 1C WH	-20 to +35 °C	Not applicable	No
911401547361	ST700T LED30 930PC PSU WB 1C WH	-20 to +35 °C	Not applicable	No
911401547461	ST700T LED30 930PC PSU MB 1C BK	-20 to +35 °C	Not applicable	No
911401547561	ST700T LED30 930PC PSU WB 1C BK	-20 to +35 °C	Not applicable	No
911401547661	ST700T LED40 930PC PSU MB 1C WH	-20 to +35 °C	Not applicable	No
911401547761	ST700T LED40 930PC PSU WB 1C WH	-20 to +35 °C	Not applicable	No
911401547861	ST700T LED40 930PC PSU MB 1C BK	-20 to +35 °C	Not applicable	No
911401547961	ST700T LED40 930PC PSU WB 1C BK	-20 to +35 °C	Not applicable	No
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	-20 to +35 °C	Not applicable	No
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	-20 to +35 °C	Not applicable	No

Order Code	Full Product Name	Ambient temperature range	Maximum dim level	Suitable for random switching
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	-20 to +35 °C	Not applicable	No
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	-20 to +35 °C	Not applicable	No
911401561661	ST700T LED10 830 PSU MB 1C WH	-20 to +35 °C	Not applicable	No
911401561761	ST700T LED10 830 PSU WB 1C WH	-20 to +35 °C	Not applicable	No
911401561861	ST700T LED10 830 PSU MB 1C BK	-20 to +35 °C	Not applicable	No
911401561961	ST700T LED10 830 PSU WB 1C BK	-20 to +35 °C	Not applicable	No
911401562061	ST700T LED20 830 PSU NB 1C WH	-20 to +35 °C	Not applicable	No
911401562161	ST700T LED20 830 PSU WB 1C WH	-20 to +35 °C	Not applicable	No
911401562261	ST700T LED20 830 PSU NB 1C BK	-20 to +35 °C	Not applicable	No
911401562361	ST700T LED20 830 PSU WB 1C BK	-20 to +35 °C	Not applicable	No
911401575561	ST700T LED30 930PW PSU MB 3C BK	-20 to +35 °C	-	-
911401575661	ST700T LED30 930PW PSU WB 3C BK	-20 to +35 °C	-	-
911401575761	ST700T LED30 930PW PSU MB 3C WH	-20 to +35 °C	-	-
911401575861	ST700T LED30 930PW PSU WB 3C WH	-20 to +35 °C	-	-
911401575961	ST700T LED30 930PW PSD VLC MB BK	-20 to +35 °C	-	-
911401576061	ST700T LED30 930PW PSD VLC WB BK	-20 to +35 °C	-	-
911401576161	ST700T LED30 930PW PSD VLC MB WH	-20 to +35 °C	-	-
911401576261	ST700T LED30 930PW PSD VLC WB WH	-20 to +35 °C	-	-

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401518371	GD700B LED10 830 PSU MB WH	No

Order Code	Full Product Name	Dimmable
911401518571	GD700B LED20 930PW PSU MB WH	No

Truefashion Projector GCGM

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401530571	GD700B LED20 940PW PSU MB WH HB	No	911401521371	RS700B LED30 940PW PSU MB BK	No
911401518471	GD700B LED10 830 PSU MB BK	No	911401521871	RS700B LED40 930PW PSU MB BK	No
911401518671	GD700B LED20 930PW PSU MB BK	No	911401521971	RS700B LED40 930PW PSU WB BK	No
911401518771	GD700B 2XLED10 830 PSU MB WH	No	911401522071	RS700B LED40 940PW PSU MB BK	No
911401518971	GD700B 2XLED20 930PW PSU MB WH	No	911401522771	RS700B LED30 930PW PSD VLC NB BK	Yes
911401518871	GD700B 2XLED10 830 PSU MB BK	No	911401522871	RS700B LED30 930PW PSD VLC MB BK	Yes
911401519071	GD700B 2XLED20 930PW PSU MB BK	No	911401522971	RS700B LED30 930PW PSD VLC WB BK	Yes
911401519171	RS700B LED10 830 PSU MB WH EB YM	No	911401546661	ST700T LED20 930PC PSU NB 1C WH	No
911401519371	RS700B LED10 827 PSU MB WH EB YM	No	911401546761	ST700T LED20 930PC PSU MB 1C WH	No
911401519471	RS700B LED10 830 PSU MB WH	No	911401546861	ST700T LED20 930PC PSU WB 1C WH	No
911401519571	RS700B LED10 830 PSU WB WH	No	911401546961	ST700T LED20 930PC PSU NB 1C BK	No
911401519671	RS700B LED20 830 PSU WB WH YM	No	911401547061	ST700T LED20 930PC PSU MB 1C BK	No
911401519771	RS700B LED20 930PW PSU NB WH	No	911401547161	ST700T LED20 930PC PSU WB 1C BK	No
911401519871	RS700B LED20 930PW PSU MB WH	No	911401547261	ST700T LED30 930PC PSU MB 1C WH	No
911401519971	RS700B LED20 930PW PSU WB WH	No	911401547361	ST700T LED30 930PC PSU WB 1C WH	No
911401520071	RS700B LED20 940PW PSU MB WH	No	911401547461	ST700T LED30 930PC PSU MB 1C BK	No
911401520571	RS700B LED20 930PC PSU MB WH	No	911401547561	ST700T LED30 930PC PSU WB 1C BK	No
911401522271	RS700B LED20 940PW PSU MB WH HB	No	911401547661	ST700T LED40 930PC PSU MB 1C WH	No
911401530371	RS700B LED10 830 PSU MB WH YM	No	911401547761	ST700T LED40 930PC PSU WB 1C WH	No
911401530471	RS700B LED10 830 PSU WB WH YM	No	911401547861	ST700T LED40 930PC PSU MB 1C BK	No
911401519271	RS700B LED10 830 PSU MB BK EB YM	No	911401547961	ST700T LED40 930PC PSU WB 1C BK	No
911401520171	RS700B LED20 930PW PSU NB BK	No	911401548061	ST700T LED20 930PC PSU MB 1C WH HB	No
911401520271	RS700B LED20 930PW PSU MB BK	No	911401548161	ST700T LED20 930PC PSU MB 1C BK HB	No
911401520371	RS700B LED20 930PW PSU WB BK	No	911401548261	ST700T LED40 930PC PSU MB 1C WH HB	No
911401520471	RS700B LED20 940PW PSU MB BK	No	911401548361	ST700T LED40 930PC PSU MB 1C BK HB	No
911401520671	RS700B LED30 930PW PSU NB WH	No	911401561661	ST700T LED10 830 PSU MB 1C WH	No
911401520771	RS700B LED30 930PW PSU MB WH	No	911401561761	ST700T LED10 830 PSU WB 1C WH	No
911401520871	RS700B LED30 930PW PSU WB WH	No	911401561861	ST700T LED10 830 PSU MB 1C BK	No
911401520971	RS700B LED30 940PW PSU MB WH	No	911401561961	ST700T LED10 830 PSU WB 1C BK	No
911401521471	RS700B LED30 930PC PSU MB WH	No	911401562061	ST700T LED20 830 PSU NB 1C WH	No
911401521571	RS700B LED40 930PW PSU MB WH	No	911401562161	ST700T LED20 830 PSU WB 1C WH	No
911401521671	RS700B LED40 930PW PSU WB WH	No	911401562261	ST700T LED20 830 PSU NB 1C BK	No
911401521771	RS700B LED40 940PW PSU MB WH	No	911401562361	ST700T LED20 830 PSU WB 1C BK	No
911401522171	RS700B LED40 930PC PSU MB WH	No	911401575561	ST700T LED30 930PW PSU MB 3C BK	No
911401522371	RS700B LED40 940PW PSU MB WH HB	No	911401575661	ST700T LED30 930PW PSU WB 3C BK	No
911401522471	RS700B LED30 930PW PSD VLC NB WH	Yes	911401575761	ST700T LED30 930PW PSU MB 3C WH	No
911401522571	RS700B LED30 930PW PSD VLC MB WH	Yes	911401575861	ST700T LED30 930PW PSU WB 3C WH	No
911401522671	RS700B LED30 930PW PSD VLC WB WH	Yes	911401575961	ST700T LED30 930PW PSD VLC MB BK	No
911401521071	RS700B LED30 930PW PSU NB BK	No	911401576061	ST700T LED30 930PW PSD VLC WB BK	No
911401521171	RS700B LED30 930PW PSU MB BK	No	911401576161	ST700T LED30 930PW PSD VLC MB WH	No
911401521271	RS700B LED30 930PW PSU WB BK	No	911401576261	ST700T LED30 930PW PSD VLC WB WH	No

General Information

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Light source			Number of gear units	Optic type
				Driver included	ENEC mark	replaceable		
911401518371	GD700B LED10 830 PSU MB WH	-	Lens	-	-	-	-	-
911401518571	GD700B LED20 930PW PSU MB WH	-	Lens	-	-	-	-	-
911401530571	GD700B LED20 940PW PSU MB WH HB	-	Lens	-	-	-	-	-
911401518471	GD700B LED10 830 PSU MB BK	-	Lens	-	-	-	-	-
911401518671	GD700B LED20 930PW PSU MB BK	-	Lens	-	-	-	-	-
911401518771	GD700B 2XLED10 830 PSU MB WH	-	Lens	-	-	-	-	-

Truefashion Projector GCGM

Order Code	Full Product Name	Beam angle of	Optical cover/lens			Light source	Number of gear	Optic type
		light source	type	Driver included	ENEC mark	replaceable	units	
911401518971	GD700B 2XLED20 930PW PSU MB WH	-	Lens	-	-	-	-	-
911401518871	GD700B 2XLED10 830 PSU MB BK	-	Lens	-	-	-	-	-
911401519071	GD700B 2XLED20 930PW PSU MB BK	-	Lens	-	-	-	-	-
911401519171	RS700B LED10 830 PSU MB WH EB YM	-	Lens	-	-	-	-	-
911401519371	RS700B LED10 827 PSU MB WH EB YM	-	Lens	-	-	-	-	-
911401519471	RS700B LED10 830 PSU MB WH	-	Lens	-	-	-	-	-
911401519571	RS700B LED10 830 PSU WB WH	-	Lens	-	-	-	-	-
911401519671	RS700B LED20 830 PSU WB WH YM	-	Lens	-	-	-	-	-
911401519771	RS700B LED20 930PW PSU NB WH	-	Lens	-	-	-	-	-
911401519871	RS700B LED20 930PW PSU MB WH	-	Lens	-	-	-	-	-
911401519971	RS700B LED20 930PW PSU WB WH	-	Lens	-	-	-	-	-
911401520071	RS700B LED20 940PW PSU MB WH	-	Lens	-	-	-	-	-
911401520571	RS700B LED20 930PC PSU MB WH	-	Lens	-	-	-	-	-
911401522271	RS700B LED20 940PW PSU MB WH HB	-	Lens	-	-	-	-	-
911401530371	RS700B LED10 830 PSU MB WH YM	-	Lens	-	-	-	-	-
911401530471	RS700B LED10 830 PSU WB WH YM	-	Lens	-	-	-	-	-
911401519271	RS700B LED10 830 PSU MB BK EB YM	-	Lens	-	-	-	-	-
911401520171	RS700B LED20 930PW PSU NB BK	-	Lens	-	-	-	-	-
911401520271	RS700B LED20 930PW PSU MB BK	-	Lens	-	-	-	-	-
911401520371	RS700B LED20 930PW PSU WB BK	-	Lens	-	-	-	-	-
911401520471	RS700B LED20 940PW PSU MB BK	-	Lens	-	-	-	-	-
911401520671	RS700B LED30 930PW PSU NB WH	-	Lens	-	-	-	-	-
911401520771	RS700B LED30 930PW PSU MB WH	-	Lens	-	-	-	-	-
911401520871	RS700B LED30 930PW PSU WB WH	-	Lens	-	-	-	-	-
911401520971	RS700B LED30 940PW PSU MB WH	-	Lens	-	-	-	-	-
911401521471	RS700B LED30 930PC PSU MB WH	-	Lens	-	-	-	-	-
911401521571	RS700B LED40 930PW PSU MB WH	-	Lens	-	-	-	-	-
911401521671	RS700B LED40 930PW PSU WB WH	-	Lens	-	-	-	-	-
911401521771	RS700B LED40 940PW PSU MB WH	-	Lens	-	-	-	-	-
911401522171	RS700B LED40 930PC PSU MB WH	-	Lens	-	-	-	-	-
911401522371	RS700B LED40 940PW PSU MB WH HB	-	Lens	-	-	-	-	-
911401522471	RS700B LED30 930PW PSD VLC NB WH	-	Lens	-	-	-	-	-
911401522571	RS700B LED30 930PW PSD VLC MB WH	-	Lens	-	-	-	-	-
911401522671	RS700B LED30 930PW PSD VLC WB WH	-	Lens	-	-	-	-	-
911401521071	RS700B LED30 930PW PSU NB BK	-	Lens	-	-	-	-	-
911401521171	RS700B LED30 930PW PSU MB BK	-	Lens	-	-	-	-	-
911401521271	RS700B LED30 930PW PSU WB BK	-	Lens	-	-	-	-	-
911401521371	RS700B LED30 940PW PSU MB BK	-	Lens	-	-	-	-	-
911401521871	RS700B LED40 930PW PSU MB BK	-	Lens	-	-	-	-	-
911401521971	RS700B LED40 930PW PSU WB BK	-	Lens	-	-	-	-	-
911401522071	RS700B LED40 940PW PSU MB BK	-	Lens	-	-	-	-	-
911401522771	RS700B LED30 930PW PSD VLC NB BK	-	Lens	-	-	-	-	-
911401522871	RS700B LED30 930PW PSD VLC MB BK	-	Lens	-	-	-	-	-
911401522971	RS700B LED30 930PW PSD VLC WB BK	-	Lens	-	-	-	-	-
911401546661	ST700T LED20 930PC PSU NB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 15°
911401546761	ST700T LED20 930PC PSU MB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 24°
911401546861	ST700T LED20 930PC PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 30°
911401546961	ST700T LED20 930PC PSU NB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 15°
911401547061	ST700T LED20 930PC PSU MB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 24°
911401547161	ST700T LED20 930PC PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 30°
911401547261	ST700T LED30 930PC PSU MB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 23°

Truefashion Projector GCGM

Order Code	Full Product Name	Beam angle of	Optical cover/lens			Light source	Number of gear	Optic type
		light source	type	Driver included	ENEC mark	replaceable	units	
911401547361	ST700T LED30 930PC PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 33°
911401547461	ST700T LED30 930PC PSU MB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 23°
911401547561	ST700T LED30 930PC PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 33°
911401547661	ST700T LED40 930PC PSU MB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 24°
911401547761	ST700T LED40 930PC PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 34°
911401547861	ST700T LED40 930PC PSU MB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 24°
911401547961	ST700T LED40 930PC PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 34°
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	120 °	Lens	Yes	-	No	1 unit	Beam angle 21°
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	120 °	Lens	Yes	-	No	1 unit	Beam angle 21°
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	120 °	Lens	Yes	-	No	1 unit	Beam angle 24°
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	120 °	Lens	Yes	-	No	1 unit	Beam angle 24°
911401561661	ST700T LED10 830 PSU MB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 24°
911401561761	ST700T LED10 830 PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 30°
911401561861	ST700T LED10 830 PSU MB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 24°
911401561961	ST700T LED10 830 PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 30°
911401562061	ST700T LED20 830 PSU NB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 15°
911401562161	ST700T LED20 830 PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 30°
911401562261	ST700T LED20 830 PSU NB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 15°
911401562361	ST700T LED20 830 PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 30°
911401575561	ST700T LED30 930PW PSU MB 3C BK	-	Fashion proof optic beam angle 24°	-	-	-	-	-
911401575661	ST700T LED30 930PW PSU WB 3C BK	-	Fashion proof optic beam angle 36°	-	-	-	-	-
911401575761	ST700T LED30 930PW PSU MB 3C WH	-	Fashion proof optic beam angle 24°	-	-	-	-	-
911401575861	ST700T LED30 930PW PSU WB 3C WH	-	Fashion proof optic beam angle 36°	-	-	-	-	-
911401575961	ST700T LED30 930PW PSD VLC MB BK	-	Fashion proof optic beam angle 24°	-	-	-	-	-
911401576061	ST700T LED30 930PW PSD VLC WB BK	-	Fashion proof optic beam angle 36°	-	-	-	-	-
911401576161	ST700T LED30 930PW PSD VLC MB WH	-	Fashion proof optic beam angle 24°	-	-	-	-	-
911401576261	ST700T LED30 930PW PSD VLC WB WH	-	Fashion proof optic beam angle 36°	-	-	-	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Init. Color		Initial LED luminaire efficacy	Initial luminous flux	Initial input power
			Init. Corr. Color Temperature	Rendering Index			
911401518371	GD700B LED10 830 PSU MB WH	-	3000 K	>80	114 lm/W	942 lm	8 W
911401518571	GD700B LED20 930PW PSU MB WH	-	3000 K	>90	79 lm/W	1685 lm	21 W

Truefashion Projector GCGM

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color		Init. Color Rendering		Initial luminous flux	Initial input power
			Temperature	Index	Index	Initial LED luminaire efficacy		
911401530571	GD700B LED20 940PW PSU MB WH HB	-	4000 K	>90	56 lm/W	1184 lm	21 W	
911401518471	GD700B LED10 830 PSU MB BK	-	3000 K	>80	114 lm/W	942 lm	8 W	
911401518671	GD700B LED20 930PW PSU MB BK	-	3000 K	>90	79 lm/W	1685 lm	21 W	
911401518771	GD700B 2XLED10 830 PSU MB WH	-	3000 K	>80	114 lm/W	1884 lm	16 W	
911401518971	GD700B 2XLED20 930PW PSU MB WH	-	3000 K	>90	79 lm/W	3369 lm	42 W	
911401518871	GD700B 2XLED10 830 PSU MB BK	-	3000 K	>80	114 lm/W	1884 lm	16 W	
911401519071	GD700B 2XLED20 930PW PSU MB BK	-	3000 K	>90	79 lm/W	3369 lm	42 W	
911401519171	RS700B LED10 830 PSU MB WH EB YM	-	3000 K	>80	121 lm/W	979 lm	8 W	
911401519371	RS700B LED10 827 PSU MB WH EB YM	-	2700 K	>80	116 lm/W	941 lm	8 W	
911401519471	RS700B LED10 830 PSU MB WH	-	3000 K	>80	114 lm/W	942 lm	8 W	
911401519571	RS700B LED10 830 PSU WB WH	-	3000 K	>80	108 lm/W	886 lm	8 W	
911401519671	RS700B LED20 830 PSU WB WH YM	-	3000 K	>80	89 lm/W	1894 lm	21 W	
911401519771	RS700B LED20 930PW PSU NB WH	-	3000 K	>90	79 lm/W	1685 lm	21 W	
911401519871	RS700B LED20 930PW PSU MB WH	-	3000 K	>90	79 lm/W	1685 lm	21 W	
911401519971	RS700B LED20 930PW PSU WB WH	-	3000 K	>90	75 lm/W	1586 lm	21 W	
911401520071	RS700B LED20 940PW PSU MB WH	-	4000 K	>90	86 lm/W	1829 lm	21 W	
911401520571	RS700B LED20 930PC PSU MB WH	-	3000 K	>90	74 lm/W	1577 lm	21 W	
911401522271	RS700B LED20 940PW PSU MB WH HB	-	4000 K	>90	56 lm/W	1184 lm	21 W	
911401530371	RS700B LED10 830 PSU MB WH YM	-	3000 K	>80	121 lm/W	979 lm	8 W	
911401530471	RS700B LED10 830 PSU WB WH YM	-	3000 K	>80	108 lm/W	886 lm	8 W	
911401519271	RS700B LED10 830 PSU MB BK EB YM	-	3000 K	>80	121 lm/W	979 lm	8 W	
911401520171	RS700B LED20 930PW PSU NB BK	-	3000 K	>90	79 lm/W	1685 lm	21 W	
911401520271	RS700B LED20 930PW PSU MB BK	-	3000 K	>90	79 lm/W	1685 lm	21 W	
911401520371	RS700B LED20 930PW PSU WB BK	-	3000 K	>90	75 lm/W	1586 lm	21 W	
911401520471	RS700B LED20 940PW PSU MB BK	-	4000 K	>90	86 lm/W	1829 lm	21 W	
911401520671	RS700B LED30 930PW PSU NB WH	-	3000 K	>90	93 lm/W	2879 lm	31 W	
911401520771	RS700B LED30 930PW PSU MB WH	-	3000 K	>90	92 lm/W	2844 lm	31 W	
911401520871	RS700B LED30 930PW PSU WB WH	-	3000 K	>90	91 lm/W	2809 lm	31 W	
911401520971	RS700B LED30 940PW PSU MB WH	-	4000 K	>90	100 lm/W	3076 lm	31 W	
911401521471	RS700B LED30 930PC PSU MB WH	-	3000 K	>90	87 lm/W	2669 lm	31 W	
911401521571	RS700B LED40 930PW PSU MB WH	-	3000 K	>90	93 lm/W	3737 lm	40 W	
911401521671	RS700B LED40 930PW PSU WB WH	-	3000 K	>90	89 lm/W	3596 lm	40 W	
911401521771	RS700B LED40 940PW PSU MB WH	-	4000 K	>90	100 lm/W	4025 lm	40 W	
911401522171	RS700B LED40 930PC PSU MB WH	-	3000 K	>90	85 lm/W	3429 lm	40 W	
911401522371	RS700B LED40 940PW PSU MB WH HB	-	4000 K	>90	57 lm/W	2293 lm	40 W	
911401522471	RS700B LED30 930PW PSD VLC NB WH	-	3000 K	>90	89 lm/W	3159 lm	35 W	
911401522571	RS700B LED30 930PW PSD VLC MB WH	-	3000 K	>90	88 lm/W	3120 lm	35 W	
911401522671	RS700B LED30 930PW PSD VLC WB WH	-	3000 K	>90	87 lm/W	3082 lm	35 W	
911401521071	RS700B LED30 930PW PSU NB BK	-	3000 K	>90	93 lm/W	2879 lm	31 W	
911401521171	RS700B LED30 930PW PSU MB BK	-	3000 K	>90	92 lm/W	2844 lm	31 W	
911401521271	RS700B LED30 930PW PSU WB BK	-	3000 K	>90	91 lm/W	2809 lm	31 W	
911401521371	RS700B LED30 940PW PSU MB BK	-	4000 K	>90	100 lm/W	3076 lm	31 W	
911401521871	RS700B LED40 930PW PSU MB BK	-	3000 K	>90	93 lm/W	3737 lm	40 W	

Truefashion Projector GCGM

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color	Init. Color	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
			Temperature	Rendering Index			
911401521971	RS700B LED40 930PW PSU WB BK	-	3000 K	>90	89 lm/W	3596 lm	40 W
911401522071	RS700B LED40 940PW PSU MB BK	-	4000 K	>90	100 lm/W	4025 lm	40 W
911401522771	RS700B LED30 930PW PSD VLC NB BK	-	3000 K	>90	89 lm/W	3159 lm	35 W
911401522871	RS700B LED30 930PW PSD VLC MB BK	-	3000 K	>90	88 lm/W	3120 lm	35 W
911401522971	RS700B LED30 930PW PSD VLC WB BK	-	3000 K	>90	87 lm/W	3082 lm	35 W
911401546661	ST700T LED20 930PC PSU NB 1C WH	(0.422, 0.386) SDCM<3	3000 K	>90	72.1 lm/W	1604.8 lm	22.3 W
911401546761	ST700T LED20 930PC PSU MB 1C WH	(0.422, 0.386) SDCM<3	3000 K	>90	72.1 lm/W	1604.8 lm	22.3 W
911401546861	ST700T LED20 930PC PSU WB 1C WH	(0.422, 0.386) SDCM<3	3000 K	>90	67.9 lm/W	1510.4 lm	22.3 W
911401546961	ST700T LED20 930PC PSU NB 1C BK	(0.422, 0.386) SDCM<3	3000 K	>90	72.1 lm/W	1604.8 lm	22.3 W
911401547061	ST700T LED20 930PC PSU MB 1C BK	(0.422, 0.386) SDCM<3	3000 K	>90	72.1 lm/W	1604.8 lm	22.3 W
911401547161	ST700T LED20 930PC PSU WB 1C BK	(0.422, 0.386) SDCM<3	3000 K	>90	67.9 lm/W	1510.4 lm	22.3 W
911401547261	ST700T LED30 930PC PSU MB 1C WH	(0.422, 0.386) SDCM<3	3000 K	>90	70.5 lm/W	2684.72 lm	38.1 W
911401547361	ST700T LED30 930PC PSU WB 1C WH	(0.422, 0.386) SDCM<3	3000 K	>90	67.6 lm/W	2575.9 lm	38.1 W
911401547461	ST700T LED30 930PC PSU MB 1C BK	(0.422, 0.386) SDCM<3	3000 K	>90	70.5 lm/W	2684.72 lm	38.1 W
911401547561	ST700T LED30 930PC PSU WB 1C BK	(0.422, 0.386) SDCM<3	3000 K	>90	67.6 lm/W	2575.88 lm	38.1 W
911401547661	ST700T LED40 930PC PSU MB 1C WH	(0.422, 0.386) SDCM<3	3000 K	>90	75.3 lm/W	3299.16 lm	43.8 W
911401547761	ST700T LED40 930PC PSU WB 1C WH	(0.422, 0.386) SDCM<3	3000 K	>90	71.4 lm/W	3125.52 lm	43.8 W
911401547861	ST700T LED40 930PC PSU MB 1C BK	(0.422, 0.386) SDCM<3	3000 K	>90	75.3 lm/W	3299.16 lm	43.8 W
911401547961	ST700T LED40 930PC PSU WB 1C BK	(0.422, 0.386) SDCM<3	3000 K	>90	71.4 lm/W	3125.52 lm	43.8 W
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	(0.422, 0.386) SDCM<3	3000 K	>90	46.7 lm/W	1038.4 lm	22.3 W
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	(0.422, 0.386) SDCM<3	3000 K	>90	46.7 lm/W	1038.4 lm	22.3 W
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	(0.422, 0.386) SDCM<3	3000 K	>80	44.6 lm/W	1953.45 lm	43.8 W
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	(0.422, 0.386) SDCM<3	3000 K	>80	44.6 lm/W	1953.45 lm	43.8 W
911401561661	ST700T LED10 830 PSU MB 1C WH	(0.434, 0.403) SDCM<3	3000 K	>80	107.3 lm/W	1146.65 lm	10.7 W
911401561761	ST700T LED10 830 PSU WB 1C WH	(0.434, 0.403) SDCM<3	3000 K	>80	101 lm/W	1079.2 lm	10.7 W
911401561861	ST700T LED10 830 PSU MB 1C BK	(0.434, 0.403) SDCM<3	3000 K	>80	107.3 lm/W	1146.65 lm	10.7 W

Truefashion Projector GCGM

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color	Init. Color	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
			Temperature	Rendering			
911401561961	ST700T LED10 830 PSU WB 1C BK	(0.434, 0.403) SDCM<3	3000 K	>80	101 lm/W	1079.2 lm	10.7 W
911401562061	ST700T LED20 830 PSU NB 1C WH	(0.434, 0.403) SDCM<3	3000 K	>80	92.2 lm/W	2051.05 lm	22.3 W
911401562161	ST700T LED20 830 PSU WB 1C WH	(0.434, 0.403) SDCM<3	3000 K	>80	86.7 lm/W	1930.4 lm	22.3 W
911401562261	ST700T LED20 830 PSU NB 1C BK	(0.434, 0.403) SDCM<3	3000 K	>80	92.2 lm/W	2051.05 lm	22.3 W
911401562361	ST700T LED20 830 PSU WB 1C BK	(0.434, 0.403) SDCM<3	3000 K	>80	86.7 lm/W	1930.4 lm	22.3 W
911401575561	ST700T LED30 930PW PSU MB 3C BK	-	3000 K	>90	85.40831032215648 lm/W	3168.44 lm	37.1 W
911401575661	ST700T LED30 930PW PSU WB 3C BK	-	3000 K	>90	80.91313609467456 lm/W	3001.68 lm	37.1 W
911401575761	ST700T LED30 930PW PSU MB 3C WH	-	3000 K	>90	85.40831032215648 lm/W	3168.44 lm	37.1 W
911401575861	ST700T LED30 930PW PSU WB 3C WH	-	3000 K	>90	80.91313609467456 lm/W	3001.68 lm	37.1 W
911401575961	ST700T LED30 930PW PSD VLC MB BK	-	3000 K	>90	90.61613412228797 lm/W	3168.44 lm	35 W
911401576061	ST700T LED30 930PW PSD VLC WB BK	-	3000 K	>90	85.84686390532543 lm/W	3001.68 lm	35 W
911401576161	ST700T LED30 930PW PSD VLC MB WH	-	3000 K	>90	90.61613412228797 lm/W	3168.44 lm	35 W
911401576261	ST700T LED30 930PW PSD VLC WB WH	-	3000 K	>90	85.84686390532543 lm/W	3001.68 lm	35 W

Mechanical and Housing

Order Code	Full Product Name	Color	Order Code	Full Product Name	Color
911401518371	GD700B LED10 830 PSU MB WH	White RAL 9003	911401520271	RS700B LED20 930PW PSU MB BK	Black
911401518571	GD700B LED20 930PW PSU MB WH	White RAL 9003	911401520371	RS700B LED20 930PW PSU WB BK	Black
911401530571	GD700B LED20 940PW PSU MB WH HB	White RAL 9003	911401520471	RS700B LED20 940PW PSU MB BK	Black
911401518471	GD700B LED10 830 PSU MB BK	Black	911401520671	RS700B LED30 930PW PSU NB WH	White RAL 9003
911401518671	GD700B LED20 930PW PSU MB BK	Black	911401520771	RS700B LED30 930PW PSU MB WH	White RAL 9003
911401518771	GD700B 2XLED10 830 PSU MB WH	White RAL 9003	911401520871	RS700B LED30 930PW PSU WB WH	White RAL 9003
911401518971	GD700B 2XLED20 930PW PSU MB WH	White RAL 9003	911401520971	RS700B LED30 940PW PSU MB WH	White RAL 9003
911401518871	GD700B 2XLED10 830 PSU MB BK	Black	911401521471	RS700B LED30 930PC PSU MB WH	White RAL 9003
911401519071	GD700B 2XLED20 930PW PSU MB BK	Black	911401521571	RS700B LED40 930PW PSU MB WH	White RAL 9003
911401519171	RS700B LED10 830 PSU MB WH EB YM	White RAL 9003	911401521671	RS700B LED40 930PW PSU WB WH	White RAL 9003
911401519371	RS700B LED10 827 PSU MB WH EB YM	White RAL 9003	911401521771	RS700B LED40 940PW PSU MB WH	White RAL 9003
911401519471	RS700B LED10 830 PSU MB WH	White RAL 9003	911401522171	RS700B LED40 930PC PSU MB WH	White RAL 9003
911401519571	RS700B LED10 830 PSU WB WH	White RAL 9003	911401522371	RS700B LED40 940PW PSU MB WH HB	White RAL 9003
911401519671	RS700B LED20 830 PSU WB WH YM	White RAL 9003	911401522471	RS700B LED30 930PW PSD VLC NB WH	White RAL 9003
911401519771	RS700B LED20 930PW PSU NB WH	White RAL 9003	911401522571	RS700B LED30 930PW PSD VLC MB WH	White RAL 9003
911401519871	RS700B LED20 930PW PSU MB WH	White RAL 9003	911401522671	RS700B LED30 930PW PSD VLC WB WH	White RAL 9003
911401519971	RS700B LED20 930PW PSU WB WH	White RAL 9003	911401521071	RS700B LED30 930PW PSU NB BK	Black
911401520071	RS700B LED20 940PW PSU MB WH	White RAL 9003	911401521171	RS700B LED30 930PW PSU MB BK	Black
911401520571	RS700B LED20 930PC PSU MB WH	White RAL 9003	911401521271	RS700B LED30 930PW PSU WB BK	Black
911401522271	RS700B LED20 940PW PSU MB WH HB	White RAL 9003	911401521371	RS700B LED30 940PW PSU MB BK	Black
911401530371	RS700B LED10 830 PSU MB WH YM	White RAL 9003	911401521871	RS700B LED40 930PW PSU MB BK	Black
911401530471	RS700B LED10 830 PSU WB WH YM	White RAL 9003	911401521971	RS700B LED40 930PW PSU WB BK	Black
911401519271	RS700B LED10 830 PSU MB BK EB YM	Black	911401522071	RS700B LED40 940PW PSU MB BK	Black
911401520171	RS700B LED20 930PW PSU NB BK	Black	911401522771	RS700B LED30 930PW PSD VLC NB BK	Black

Truefashion Projector GCGM

Order Code	Full Product Name	Color
911401522871	RS700B LED30 930PW PSD VLC MB BK	Black
911401522971	RS700B LED30 930PW PSD VLC WB BK	Black
911401546661	ST700T LED20 930PC PSU NB 1C WH	White
911401546761	ST700T LED20 930PC PSU MB 1C WH	White
911401546861	ST700T LED20 930PC PSU WB 1C WH	White
911401546961	ST700T LED20 930PC PSU NB 1C BK	Black
911401547061	ST700T LED20 930PC PSU MB 1C BK	Black
911401547161	ST700T LED20 930PC PSU WB 1C BK	Black
911401547261	ST700T LED30 930PC PSU MB 1C WH	White
911401547361	ST700T LED30 930PC PSU WB 1C WH	White
911401547461	ST700T LED30 930PC PSU MB 1C BK	Black
911401547561	ST700T LED30 930PC PSU WB 1C BK	Black
911401547661	ST700T LED40 930PC PSU MB 1C WH	White
911401547761	ST700T LED40 930PC PSU WB 1C WH	White
911401547861	ST700T LED40 930PC PSU MB 1C BK	Black
911401547961	ST700T LED40 930PC PSU WB 1C BK	Black
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	White
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	Black

Order Code	Full Product Name	Color
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	White
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	Black
911401561661	ST700T LED10 830 PSU MB 1C WH	White
911401561761	ST700T LED10 830 PSU WB 1C WH	White
911401561861	ST700T LED10 830 PSU MB 1C BK	Black
911401561961	ST700T LED10 830 PSU WB 1C BK	Black
911401562061	ST700T LED20 830 PSU NB 1C WH	White
911401562161	ST700T LED20 830 PSU WB 1C WH	White
911401562261	ST700T LED20 830 PSU NB 1C BK	Black
911401562361	ST700T LED20 830 PSU WB 1C BK	Black
911401575561	ST700T LED30 930PW PSU MB 3C BK	White and black
911401575661	ST700T LED30 930PW PSU WB 3C BK	White and black
911401575761	ST700T LED30 930PW PSU MB 3C WH	White and black
911401575861	ST700T LED30 930PW PSU WB 3C WH	White and black
911401575961	ST700T LED30 930PW PSD VLC MB BK	White and black
911401576061	ST700T LED30 930PW PSD VLC WB BK	White and black
911401576161	ST700T LED30 930PW PSD VLC MB WH	White and black
911401576261	ST700T LED30 930PW PSD VLC WB WH	White and black

Order Code	Full Product Name	Driver failure rate at 5000 h
911401518371	GD700B LED10 830 PSU MB WH	-
911401518571	GD700B LED20 930PW PSU MB WH	-
911401530571	GD700B LED20 940PW PSU MB WH HB	-
911401518471	GD700B LED10 830 PSU MB BK	-
911401518671	GD700B LED20 930PW PSU MB BK	-
911401518771	GD700B 2XLED10 830 PSU MB WH	-
911401518971	GD700B 2XLED20 930PW PSU MB WH	-
911401518871	GD700B 2XLED10 830 PSU MB BK	-
911401519071	GD700B 2XLED20 930PW PSU MB BK	-
911401519171	RS700B LED10 830 PSU MB WH EB YM	-
911401519371	RS700B LED10 827 PSU MB WH EB YM	-
911401519471	RS700B LED10 830 PSU MB WH	-
911401519571	RS700B LED10 830 PSU WB WH	-
911401519671	RS700B LED20 830 PSU WB WH YM	-
911401519771	RS700B LED20 930PW PSU NB WH	-
911401519871	RS700B LED20 930PW PSU MB WH	-
911401519971	RS700B LED20 930PW PSU WB WH	-
911401520071	RS700B LED20 940PW PSU MB WH	-
911401520571	RS700B LED20 930PC PSU MB WH	-
911401522271	RS700B LED20 940PW PSU MB WH HB	-
911401530371	RS700B LED10 830 PSU MB WH YM	-
911401530471	RS700B LED10 830 PSU WB WH YM	-
911401519271	RS700B LED10 830 PSU MB BK EB YM	-
911401520171	RS700B LED20 930PW PSU NB BK	-
911401520271	RS700B LED20 930PW PSU MB BK	-
911401520371	RS700B LED20 930PW PSU WB BK	-
911401520471	RS700B LED20 940PW PSU MB BK	-
911401520671	RS700B LED30 930PW PSU NB WH	-
911401520771	RS700B LED30 930PW PSU MB WH	-
911401520871	RS700B LED30 930PW PSU WB WH	-

Order Code	Full Product Name	Driver failure rate at 5000 h
911401520971	RS700B LED30 940PW PSU MB WH	-
911401521471	RS700B LED30 930PC PSU MB WH	-
911401521571	RS700B LED40 930PW PSU MB WH	-
911401521671	RS700B LED40 930PW PSU WB WH	-
911401521771	RS700B LED40 940PW PSU MB WH	-
911401522171	RS700B LED40 930PC PSU MB WH	-
911401522371	RS700B LED40 940PW PSU MB WH HB	-
911401522471	RS700B LED30 930PW PSD VLC NB WH	-
911401522571	RS700B LED30 930PW PSD VLC MB WH	-
911401522671	RS700B LED30 930PW PSD VLC WB WH	-
911401521071	RS700B LED30 930PW PSU NB BK	-
911401521171	RS700B LED30 930PW PSU MB BK	-
911401521271	RS700B LED30 930PW PSU WB BK	-
911401521371	RS700B LED30 940PW PSU MB BK	-
911401521871	RS700B LED40 930PW PSU MB BK	-
911401521971	RS700B LED40 930PW PSU WB BK	-
911401522071	RS700B LED40 940PW PSU MB BK	-
911401522771	RS700B LED30 930PW PSD VLC NB BK	-
911401522871	RS700B LED30 930PW PSD VLC MB BK	-
911401522971	RS700B LED30 930PW PSD VLC WB BK	-
911401546661	ST700T LED20 930PC PSU NB 1C WH	0.14 %
911401546761	ST700T LED20 930PC PSU MB 1C WH	0.14 %
911401546861	ST700T LED20 930PC PSU WB 1C WH	0.14 %
911401546961	ST700T LED20 930PC PSU NB 1C BK	0.14 %
911401547061	ST700T LED20 930PC PSU MB 1C BK	0.14 %
911401547161	ST700T LED20 930PC PSU WB 1C BK	0.14 %
911401547261	ST700T LED30 930PC PSU MB 1C WH	0.14 %
911401547361	ST700T LED30 930PC PSU WB 1C WH	0.14 %
911401547461	ST700T LED30 930PC PSU MB 1C BK	0.14 %
911401547561	ST700T LED30 930PC PSU WB 1C BK	0.14 %

Truefashion Projector GCGM

Order Code	Full Product Name	Driver failure rate at 5000 h
911401547661	ST700T LED40 930PC PSU MB 1C WH	0.23 %
911401547761	ST700T LED40 930PC PSU WB 1C WH	0.23 %
911401547861	ST700T LED40 930PC PSU MB 1C BK	0.23 %
911401547961	ST700T LED40 930PC PSU WB 1C BK	0.23 %
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	0.14 %
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	0.14 %
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	0.23 %
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	0.23 %
911401561661	ST700T LED10 830 PSU MB 1C WH	0.14 %
911401561761	ST700T LED10 830 PSU WB 1C WH	0.14 %
911401561861	ST700T LED10 830 PSU MB 1C BK	0.14 %
911401561961	ST700T LED10 830 PSU WB 1C BK	0.14 %

Order Code	Full Product Name	Driver failure rate at 5000 h
911401562061	ST700T LED20 830 PSU NB 1C WH	0.14 %
911401562161	ST700T LED20 830 PSU WB 1C WH	0.14 %
911401562261	ST700T LED20 830 PSU NB 1C BK	0.14 %
911401562361	ST700T LED20 830 PSU WB 1C BK	0.14 %
911401575561	ST700T LED30 930PW PSU MB 3C BK	-
911401575661	ST700T LED30 930PW PSU WB 3C BK	-
911401575761	ST700T LED30 930PW PSU MB 3C WH	-
911401575861	ST700T LED30 930PW PSU WB 3C WH	-
911401575961	ST700T LED30 930PW PSD VLC MB BK	-
911401576061	ST700T LED30 930PW PSD VLC WB BK	-
911401576161	ST700T LED30 930PW PSD VLC MB WH	-
911401576261	ST700T LED30 930PW PSD VLC WB WH	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
911401518371	GD700B LED10 830 PSU MB WH	-	-
911401518571	GD700B LED20 930PW PSU MB WH	-	-
911401530571	GD700B LED20 940PW PSU MB WH HB	-	-
911401518471	GD700B LED10 830 PSU MB BK	-	-
911401518671	GD700B LED20 930PW PSU MB BK	-	-
911401518771	GD700B 2XLED10 830 PSU MB WH	-	-
911401518971	GD700B 2XLED20 930PW PSU MB WH	-	-
911401518871	GD700B 2XLED10 830 PSU MB BK	-	-
911401519071	GD700B 2XLED20 930PW PSU MB BK	-	-
911401519171	RS700B LED10 830 PSU MB WH EB YM	-	-
911401519371	RS700B LED10 827 PSU MB WH EB YM	-	-
911401519471	RS700B LED10 830 PSU MB WH	-	-
911401519571	RS700B LED10 830 PSU WB WH	-	-
911401519671	RS700B LED20 830 PSU WB WH YM	-	-
911401519771	RS700B LED20 930PW PSU NB WH	-	-
911401519871	RS700B LED20 930PW PSU MB WH	-	-
911401519971	RS700B LED20 930PW PSU WB WH	-	-
911401520071	RS700B LED20 940PW PSU MB WH	-	-
911401520571	RS700B LED20 930PC PSU MB WH	-	-
911401522271	RS700B LED20 940PW PSU MB WH HB	-	-
911401530371	RS700B LED10 830 PSU MB WH YM	-	-
911401530471	RS700B LED10 830 PSU WB WH YM	-	-
911401519271	RS700B LED10 830 PSU MB BK EB YM	-	-
911401520171	RS700B LED20 930PW PSU NB BK	-	-
911401520271	RS700B LED20 930PW PSU MB BK	-	-
911401520371	RS700B LED20 930PW PSU WB BK	-	-
911401520471	RS700B LED20 940PW PSU MB BK	-	-
911401520671	RS700B LED30 930PW PSU NB WH	-	-
911401520771	RS700B LED30 930PW PSU MB WH	-	-
911401520871	RS700B LED30 930PW PSU WB WH	-	-
911401520971	RS700B LED30 940PW PSU MB WH	-	-
911401521471	RS700B LED30 930PC PSU MB WH	-	-
911401521571	RS700B LED40 930PW PSU MB WH	-	-
911401521671	RS700B LED40 930PW PSU WB WH	-	-
911401521771	RS700B LED40 940PW PSU MB WH	-	-

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
911401522171	RS700B LED40 930PC PSU MB WH	-	-
911401522371	RS700B LED40 940PW PSU MB WH HB	-	-
911401522471	RS700B LED30 930PW PSD VLC NB WH	-	-
911401522571	RS700B LED30 930PW PSD VLC MB WH	-	-
911401522671	RS700B LED30 930PW PSD VLC WB WH	-	-
911401521071	RS700B LED30 930PW PSU NB BK	-	-
911401521171	RS700B LED30 930PW PSU MB BK	-	-
911401521271	RS700B LED30 930PW PSU WB BK	-	-
911401521371	RS700B LED30 940PW PSU MB BK	-	-
911401521871	RS700B LED40 930PW PSU MB BK	-	-
911401521971	RS700B LED40 930PW PSU WB BK	-	-
911401522071	RS700B LED40 940PW PSU MB BK	-	-
911401522771	RS700B LED30 930PW PSD VLC NB BK	-	-
911401522871	RS700B LED30 930PW PSD VLC MB BK	-	-
911401522971	RS700B LED30 930PW PSD VLC WB BK	-	-
911401546661	ST700T LED20 930PC PSU NB 1C WH	50000 h	32600 h
911401546761	ST700T LED20 930PC PSU MB 1C WH	50000 h	32600 h
911401546861	ST700T LED20 930PC PSU WB 1C WH	50000 h	32600 h
911401546961	ST700T LED20 930PC PSU NB 1C BK	50000 h	32600 h
911401547061	ST700T LED20 930PC PSU MB 1C BK	50000 h	32600 h
911401547161	ST700T LED20 930PC PSU WB 1C BK	50000 h	32600 h
911401547261	ST700T LED30 930PC PSU MB 1C WH	45000 h	21200 h
911401547361	ST700T LED30 930PC PSU WB 1C WH	45000 h	21200 h
911401547461	ST700T LED30 930PC PSU MB 1C BK	45000 h	21200 h
911401547561	ST700T LED30 930PC PSU WB 1C BK	45000 h	21200 h
911401547661	ST700T LED40 930PC PSU MB 1C WH	38700 h	18200 h
911401547761	ST700T LED40 930PC PSU WB 1C WH	38700 h	18200 h
911401547861	ST700T LED40 930PC PSU MB 1C BK	38700 h	18200 h
911401547961	ST700T LED40 930PC PSU WB 1C BK	38700 h	18200 h
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	50000 h	32600 h
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	50000 h	32600 h

Truefashion Projector GCGM

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	38700 h	18200 h
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	38700 h	18200 h
911401561661	ST700T LED10 830 PSU MB 1C WH	50000 h	32600 h
911401561761	ST700T LED10 830 PSU WB 1C WH	50000 h	32600 h
911401561861	ST700T LED10 830 PSU MB 1C BK	50000 h	32600 h
911401561961	ST700T LED10 830 PSU WB 1C BK	50000 h	32600 h
911401562061	ST700T LED20 830 PSU NB 1C WH	50000 h	32600 h
911401562161	ST700T LED20 830 PSU WB 1C WH	50000 h	32600 h

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
911401562261	ST700T LED20 830 PSU NB 1C BK	50000 h	32600 h
911401562361	ST700T LED20 830 PSU WB 1C BK	50000 h	32600 h
911401575561	ST700T LED30 930PW PSU MB 3C BK	-	-
911401575661	ST700T LED30 930PW PSU WB 3C BK	-	-
911401575761	ST700T LED30 930PW PSU MB 3C WH	-	-
911401575861	ST700T LED30 930PW PSU WB 3C WH	-	-
911401575961	ST700T LED30 930PW PSD VLC MB BK	-	-
911401576061	ST700T LED30 930PW PSD VLC WB BK	-	-
911401576161	ST700T LED30 930PW PSD VLC MB WH	-	-
911401576261	ST700T LED30 930PW PSD VLC WB WH	-	-

