



The new Coreline slim batten is slim design and come in 3 sizes and 2 CCT choices based on specific customer needs.

Coreline Slim Batten

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Benefits

- Slim and Robust design
- 50K Hours Life L70B50
- 5 Years warranty

Features

- Energy efficient with long service life. (50 000 hours - L70)
- 5 Years Warranty
- IP20, IK04
- CRI80
- 3 Different sizes L600/L1200/L1500 and 2 Different CCT (4000K/6500K) choices

Coreline Slim Batten

Application

- Offices
- Residential
- Parking Garages

Versions



Application Conditions

Ambient temperature range -20 to +40 °C

Approval and Application

Mech. impact protection code IK04

Ingress protection code IP20(front IP40)

Controls and Dimming

Dimmable No

Operating and Electrical

Input Voltage 220 to 240 V

General Information

CE mark CE mark

Protection class IEC Safety class I

Optical cover/lens type Polycarbonate
Diffuser

Initial Performance (IEC Compliant)

Init. Color Rendering Index >80

Luminous flux tolerance +/-10%

Mechanical and Housing

Color White RAL 9003

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401898780	BN126C LED22S/840 PSU L600	4000 K	104 lm/W	2200 lm	21 W
911401898880	BN126C LED22S/865 PSU L600	6500 K	104 lm/W	2200 lm	21 W
911401898980	BN126C LED41S/840 PSU L1200	4000 K	107 lm/W	4100 lm	38 W
911401899080	BN126C LED41S/865 PSU L1200	6500 K	107 lm/W	4100 lm	38 W
911401899180	BN126C LED60S/840 PSU L1500	4000 K	107 lm/W	6000 lm	56 W
911401899280	BN126C LED60S/865 PSU L1500	6500 K	107 lm/W	6000 lm	56 W

Coreline Slim Batten

