



CoreLine Trunking Gen2 – Innovative LED light lines have never been so simple

CoreLine Trunking Gen2

CoreLine Trunking Gen2 is a light-line system that is designed for simplicity. It comes in a choice of lengths, flux packages and beam shapes to suit every project and application. Easy to use and integrate with spots and sensors, CoreLine Trunking Gen2 provides consistent, high-quality lighting with added protection against accidental water ingress. The innovative system is also easy to assemble and install for faster retrofits and refurbishments.

Benefits

- Optimized, efficient design and light effect
- Consistent, high-quality light - no Color over Angle or striping artefacts
- Improved light continuity
- Easy to order, assemble and install
- InterAct ready for enhanced use in Retail and Industry applications

Features


- Intuitive, single layer architecture – only 2 12NCs needed to create a line
- Choice of 3 lengths, each with 3 flux packages
- 8 different optics with consistent light quality
- Dedicated sensor units to upgrade to InterAct system propositions
- Lumen maintenance @ 50,000 hours - L80
- Available as trunking and standalone versions

CoreLine Trunking Gen2


Application

- Food and Large Retailers
- Warehouses
- Manufacturing


Versions




LL212X




LL217X



LL217X



LL217X




Coreline Trunking Gen2 - Sensor
ready driver InterAct System ready
- Wide beam - 84° x 84°

CoreLine Trunking Gen2


Product details




CoreLine Trunking Gen2 starter kit



Coreline trunking gen2 end cap




InterAct Pro sensor unit




CoreLine Trunking Gen2 Half Blind

Accessories



Coreline Trunking Gen2 - - -
Finger-protected - 0.2 J standard -
White

Ordercode 910925867562,
910925867563




Coreline Trunking Gen2

Ordercode 910925867564



Coreline Trunking Gen2 - - - - -
White

Ordercode 910925867566




Coreline Trunking Gen2


Ordercode 910925867567

CoreLine Trunking Gen2


Accessories




Coreline Trunking Gen2
Ordercode 910925867568




Coreline Trunking Gen2
Ordercode 910925867570,
910925867571, 910925867572




Coreline Trunking Gen2 - - - - -
White
Ordercode 910925867573



Coreline Trunking Gen2
Ordercode 910925867583



Coreline Trunking Gen2
Ordercode 910925867589,
910925867595



Coreline Trunking Gen2
Accessories - 220/240 V - 50 to
60 Hz - Safety class I - Finger-
protected - 0.2 J standard - White
- CE mark
Ordercode 910925868450,
910925868451

CoreLine Trunking Gen2

Application conditions

Ambient temperature range -20 to +35 °C

Approval and application

Mech. impact protection code IK02

Ingress protection code IP20

Operating and electrical

Input Voltage 220 to 240 V

General information

Beam angle of light source 120 °

CE mark Yes

Protection class IEC Safety class I

Driver included Yes

ENEC mark ENEC plus mark

Flammability mark -

Glow-wire test Temperature 850 °C, duration 30 s

Light source replaceable No

Initial performance (IEC compliant)

Initial chromaticity (0.38, 0.38) SDCM <3

Init. Corr. Color Temperature 4000 K

Init. Color Rendering Index >80

Luminous flux tolerance +/-10%

Mechanical and housing

Color White RAL9016

Application conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	Not applicable	Yes
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	Not applicable	Yes
910925867498	LL217X 80S/840 1x PSD BV WB	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867525	LL217X 120S/840 1x PSU BV WB HE	Not applicable	Yes
910925867539	LL234X 240S/840 2x PSD BV WB HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867550	LL234X 160S/840 2x PSU BV WB	Not applicable	Yes
910925867698	LL217X 80S/840 1x PSU BV WB TW3	Not applicable	Yes
910925867699	LL234X 160S/840 1x PSU BV WB TW3	Not applicable	Yes
910925867701	LL234X 160S/840 2x PSU BV WB TW3	Not applicable	Yes
910925868236	LL217X 45S/840 1x PSU BV WB	Not applicable	Yes
910925868237	LL217X 45S/840 1x PSD BV WB	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868238	LL217X 45S/840 1x PSU BV O	Not applicable	Yes
910925868239	LL217X 45S/840 1x PSD BV O	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868240	LL217X 80S/840 1x PSU BV WB	Not applicable	Yes
910925868241	LL217X 80S/840 1x PSU BV O	Not applicable	Yes
910925868242	LL217X 80S/840 1x PSD BV O	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868391	LL217X 120S/840 1x PSU BV WB TW3	Not applicable	Yes
910925868392	LL217X 120S/840 1x PSU BV MB TW3	Not applicable	Yes
910925868393	LL217X 120S/840 1x PSU BV NB TW3	Not applicable	Yes
910925868394	LL217X 80S/840 1x PSU BV MB TW3	Not applicable	Yes
910925868395	LL217X 80S/840 1x PSU BV NB TW3	Not applicable	Yes
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	Not applicable	Yes
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)

CoreLine Trunking Gen2

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	Not applicable	Yes
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	Not applicable	Yes
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	Not applicable	Yes
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	Not applicable	Yes
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	Not applicable	Yes
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	Not applicable	Yes
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	Not applicable	Yes
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	Not applicable	Yes
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	Not applicable	Yes
910925867552	LL234X 160S/840 2x PSD O 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)

CoreLine Trunking Gen2

Order Code	Full Product Name	Maximum dim	
		level	Suitable for random switching
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	Not applicable	Yes
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	Not applicable	Yes
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	Not applicable	Yes
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	Not applicable	Yes
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	Not applicable	Yes
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	Not applicable	Yes
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	Not applicable	Yes
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	Not applicable	Yes
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	Not applicable	Yes
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	Not applicable	Yes
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	Not applicable	Yes
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	Not applicable	Yes

Order Code	Full Product Name	Maximum dim	
		level	Suitable for random switching
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	Not applicable	Yes
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	Not applicable	Yes
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	Not applicable	Yes
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	Not applicable	Yes
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	Not applicable	Yes
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	Not applicable	Yes
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	Not applicable	Yes
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	Not applicable	Yes
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	Not applicable	Yes
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	Not applicable	Yes
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	Not applicable	Yes
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	Not applicable	Yes
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	Not applicable	Yes
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	Not applicable	Yes
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	Not applicable	Yes
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	Not applicable	Yes
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867535	LL217X 80S/840 1x PSD O 7x2.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867551	LL234X 160S/840 2x PSD O 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925867556	LL234X 160S/840 2x PSU O 5x1.5	Not applicable	Yes
910925867557	LL234X 160S/840 2x PSU O 5x2.5	Not applicable	Yes

CoreLine Trunking Gen2

Order Code	Full Product Name	Maximum dim	
		level	Suitable for random switching
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	1%	Yes (relates to presence/movement detection and daylight harvesting)

Controls and dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	No	910925867536	LL217X 80S/840 1x PSD WB 7x2.5	Yes
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	Yes	910925867537	LL217X 80S/840 1x PSU WB 5x1.5	No
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	Yes	910925867538	LL217X 80S/840 1x PSU WB 5x2.5	No
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	Yes	910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	Yes
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	No	910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	Yes
910925867498	LL217X 80S/840 1x PSD BV WB	Yes	910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	Yes
910925867525	LL217X 120S/840 1x PSU BV WB HE	No	910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	No
910925867539	LL234X 240S/840 2x PSD BV WB HE	Yes	910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	No
910925867550	LL234X 160S/840 2x PSU BV WB	No	910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	Yes
910925867698	LL217X 80S/840 1x PSU BV WB TW3	No	910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	Yes
910925867699	LL234X 160S/840 1x PSU BV WB TW3	No	910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	Yes
910925867701	LL234X 160S/840 2x PSU BV WB TW3	No	910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	No
910925868236	LL217X 45S/840 1x PSU BV WB	No	910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	No
910925868237	LL217X 45S/840 1x PSD BV WB	Yes	910925867552	LL234X 160S/840 2x PSD O 7x2.5	Yes
910925868238	LL217X 45S/840 1x PSU BV O	No	910925867553	LL234X 160S/840 2x PSD WB 7x1.5	Yes
910925868239	LL217X 45S/840 1x PSD BV O	Yes	910925867554	LL234X 160S/840 2x PSD WB 7x2.5	Yes
910925868240	LL217X 80S/840 1x PSU BV WB	No	910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	Yes
910925868241	LL217X 80S/840 1x PSU BV O	No	910925867558	LL234X 160S/840 2x PSU WB 5x1.5	No
910925868242	LL217X 80S/840 1x PSD BV O	Yes	910925867559	LL234X 160S/840 2x PSU WB 5x2.5	No
910925868391	LL217X 120S/840 1x PSU BV WB TW3	No	910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	Yes
910925868392	LL217X 120S/840 1x PSU BV MB TW3	No	910925867561	LL234X 90S/840 2x PSD WB 7x1.5	Yes
910925868393	LL217X 120S/840 1x PSU BV NB TW3	No	910925868205	LL234X 160S/840 1x PSD WB 7x1.5	Yes
910925868394	LL217X 80S/840 1x PSU BV MB TW3	No	910925868217	LL234X 160S/840 2x PSU NB 5x1.5	No
910925868395	LL217X 80S/840 1x PSU BV NB TW3	No	910925868218	LL217X 80S/840 1x PSU NB 5x1.5	No
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	No	910925868232	LL234X 90S/840 2x PSU WB 5x1.5	No
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	Yes	910925868233	LL234X 90S/840 1x PSD WB 7x1.5	Yes
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	Yes	910925868234	LL217X 45S/840 1x PSU WB 5x1.5	No
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	Yes	910925868235	LL217X 45S/840 1x PSD WB 7x1.5	Yes
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	Yes	910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	No
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	Yes	910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	Yes
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	No	910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	No
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	Yes	910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	Yes
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	Yes	910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	No
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	No	910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	Yes
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	No	910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	No

CoreLine Trunking Gen2

Order Code	Full Product Name	Dimmable
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	Yes
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	Yes
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	Yes
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	Yes
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	No
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	No
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	No
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	No
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	No
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	No
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	No
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	No
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	No
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	No
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	No
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	No
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	No
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	No
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	No
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	No

Order Code	Full Product Name	Dimmable
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	No
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	No
910925868899	LL234X 90S/840 1x SIA WB 7x1.5	Yes
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	Yes
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	Yes
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	Yes
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	Yes
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	Yes
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	Yes
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	Yes
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	Yes
910925867535	LL217X 80S/840 1x PSD O 7x2.5	Yes
910925867551	LL234X 160S/840 2x PSD O 7x1.5	Yes
910925867556	LL234X 160S/840 2x PSU O 5x1.5	No
910925867557	LL234X 160S/840 2x PSU O 5x2.5	No
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	Yes
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	Yes
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	Yes
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	Yes

General information (1/2)

Order Code	Full Product Name	Lamp		Number of gear units	Optic type
		family code	Embedded control		
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	-	-	1 unit	Wide beam
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	-	-	1 unit	Wide beam
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	-	-	1 unit	Wide beam
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	-	-	1 unit	Wide beam
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	-	-	1 unit	Wide beam
910925867498	LL217X 80S/840 1x PSD BV WB	-	-	1 unit	Wide beam
910925867525	LL217X 120S/840 1x PSU BV WB HE	120S	-	1 unit	Wide beam
910925867539	LL234X 240S/840 2x PSD BV WB HE	240S	-	2 units	Wide beam
910925867550	LL234X 160S/840 2x PSU BV WB	160S	-	2 units	Wide beam

Order Code	Full Product Name	Lamp		Number of gear units	Optic type
		family code	Embedded control		
910925867698	LL217X 80S/840 1x PSU BV WB TW3	-	-	1 unit	Wide beam
910925867699	LL234X 160S/840 1x PSU BV WB TW3	-	-	1 unit	Wide beam
910925867701	LL234X 160S/840 2x PSU BV WB TW3	-	-	2 units	Wide beam
910925868236	LL217X 45S/840 1x PSU BV WB	-	-	1 unit	Wide beam
910925868237	LL217X 45S/840 1x PSD BV WB	-	-	1 unit	Wide beam
910925868238	LL217X 45S/840 1x PSU BV O	-	-	1 unit	Symmetrical
910925868239	LL217X 45S/840 1x PSD BV O	-	-	1 unit	Symmetrical
910925868240	LL217X 80S/840 1x PSU BV WB	-	-	1 unit	Wide beam
910925868241	LL217X 80S/840 1x PSU BV O	-	-	1 unit	Symmetrical
910925868242	LL217X 80S/840 1x PSD BV O	-	-	1 unit	Symmetrical

CoreLine Trunking Gen2

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Optic type
910925868391	LL217X 120S/840 1x PSU BV WB TW3	-	-	1 unit	Wide beam
910925868392	LL217X 120S/840 1x PSU BV MB TW3	-	-	1 unit	Medium beam
910925868393	LL217X 120S/840 1x PSU BV NB TW3	-	-	1 unit	Narrow beam
910925868394	LL217X 80S/840 1x PSU BV MB TW3	-	-	1 unit	Medium beam
910925868395	LL217X 80S/840 1x PSU BV NB TW3	-	-	1 unit	Narrow beam
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	-	-	1 unit	Wide beam
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	-	-	1 unit	Wide beam
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	-	-	1 unit	Wide beam
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	120S	-	1 unit	Wide beam
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	120S	-	1 unit	Wide beam
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	120S	Visible light communication	1 unit	Wide beam
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	120S	-	1 unit	Wide beam
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	80S	-	1 unit	Wide beam
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	80S	Visible light communication	1 unit	Wide beam

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Optic type
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	80S	-	1 unit	Wide beam
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	80S	-	1 unit	Wide beam
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	80S	-	1 unit	Wide beam
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	80S	-	1 unit	Wide beam
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	80S	-	1 unit	Wide beam
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	160S	-	2 units	Wide beam
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	160S	-	2 units	Wide beam
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	160S	Visible light communication	2 units	Wide beam
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	160S	-	2 units	Wide beam
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	160S	-	2 units	Wide beam
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	240S	-	2 units	Wide beam
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	240S	-	2 units	Wide beam
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	240S	Visible light communication	2 units	Wide beam
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	240S	-	2 units	Wide beam
910925867549	LL234X 240S/840 2x	240S	-	2 units	Wide beam

CoreLine Trunking Gen2

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Optic type
	PSU WB 5x2.5 HE				
910925867552	LL234X 160S/840 2x PSD O 7x2.5	160S	-	2 units	Symmetrical
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	160S	-	2 units	Wide beam
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	160S	-	2 units	Wide beam
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	160S	Visible light communication	2 units	Wide beam
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	160S	-	2 units	Wide beam
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	160S	-	2 units	Wide beam
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	80S	-	1 unit	Wide beam
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	90S	-	2 units	Wide beam
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	-	-	1 unit	Wide beam
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	-	-	2 units	Narrow beam
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	-	-	1 unit	Narrow beam
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	-	-	2 units	Wide beam
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	-	-	1 unit	Wide beam
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	-	-	1 unit	Wide beam
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	-	-	1 unit	Wide beam
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	-	-	1 unit	Wide beam

Order Code	Full Product Name	Lamp family code	Embedded control	Number of gear units	Optic type
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	-	-	1 unit	Wide beam
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	-	-	1 unit	Wide beam
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	-	-	1 unit	Wide beam
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	-	-	1 unit	Narrow beam
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	-	-	1 unit	Narrow beam
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	-	-	1 unit	Narrow beam
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	-	-	1 unit	Narrow beam
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	-	-	1 unit	Narrow beam
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	-	-	1 unit	Narrow beam
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	-	-	1 unit	Narrow beam
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	-	-	1 unit	Medium beam
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	-	-	1 unit	Narrow beam
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	-	-	1 unit	Medium beam
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	-	-	1 unit	Narrow beam
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	-	-	1 unit	Medium beam
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	-	-	1 unit	Narrow beam
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	-	-	1 unit	Medium beam
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	-	-	1 unit	Narrow beam
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	-	-	1 unit	Medium beam

CoreLine Trunking Gen2

Order Code	Full Product Name	Lamp		Number of gear	
		family code	Embedded control	units	Optic type
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	-	-	1 unit	Narrow beam
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	-	-	1 unit	Medium beam
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	-	-	1 unit	Narrow beam
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	-	-	2 units	Medium beam
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	-	-	2 units	Narrow beam
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	-	-	2 units	Medium beam
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	-	-	2 units	Narrow beam
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	-	-	2 units	Medium beam
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	-	-	2 units	Narrow beam
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	-	-	1 unit	Wide beam
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	-	-	1 unit	Wide beam
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	-	-	1 unit	Narrow beam

Order Code	Full Product Name	Lamp		Number of gear	
		family code	Embedded control	units	Optic type
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	-	-	1 unit	Narrow beam
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	-	-	1 unit	Wide beam
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	-	-	1 unit	Wide beam
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	-	-	1 unit	Narrow beam
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	-	-	1 unit	Narrow beam
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	80S	-	1 unit	Symmetrical
910925867535	LL217X 80S/840 1x PSD O 7x2.5	80S	-	1 unit	Symmetrical
910925867551	LL234X 160S/840 2x PSD O 7x1.5	160S	-	2 units	Symmetrical
910925867556	LL234X 160S/840 2x PSU O 5x1.5	160S	-	2 units	Symmetrical
910925867557	LL234X 160S/840 2x PSU O 5x2.5	160S	-	2 units	Symmetrical
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	-	-	1 unit	Wide beam
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	-	-	1 unit	Wide beam
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	-	-	1 unit	Narrow beam
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	-	-	1 unit	Narrow beam

General information (2/2)

Order Code	Full Product Name	Product	
		Family Code	Service tag
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	LL212X	Yes
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	LL212X	Yes
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	LL212X	Yes
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	LL212X	Yes
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	LL212X	Yes
910925867498	LL217X 80S/840 1x PSD BV WB	LL217X	Yes

Order Code	Full Product Name	Product	
		Family Code	Service tag
910925867525	LL217X 120S/840 1x PSU BV WB HE	LL217X	Yes
910925867539	LL234X 240S/840 2x PSD BV WB HE	LL234X	Yes
910925867550	LL234X 160S/840 2x PSU BV WB	LL234X	Yes
910925867698	LL217X 80S/840 1X PSU BV WB TW3	LL217X	Yes
910925867699	LL234X 160S/840 1X PSU BV WB TW3	LL234X	Yes
910925867701	LL234X 160S/840 2X PSU BV WB TW3	LL234X	Yes

CoreLine Trunking Gen2

Order Code	Full Product Name	Product	
		Family Code	Service tag
910925868236	LL217X 45S/840 1x PSU BV WB	LL217X	Yes
910925868237	LL217X 45S/840 1x PSD BV WB	LL217X	Yes
910925868238	LL217X 45S/840 1x PSU BV O	LL217X	Yes
910925868239	LL217X 45S/840 1x PSD BV O	LL217X	Yes
910925868240	LL217X 80S/840 1x PSU BV WB	LL217X	Yes
910925868241	LL217X 80S/840 1x PSU BV O	LL217X	Yes
910925868242	LL217X 80S/840 1x PSD BV O	LL217X	Yes
910925868391	LL217X 120S/840 1x PSU BV WB TW3	LL217X	Yes
910925868392	LL217X 120S/840 1x PSU BV MB TW3	LL217X	Yes
910925868393	LL217X 120S/840 1x PSU BV NB TW3	LL217X	Yes
910925868394	LL217X 80S/840 1x PSU BV MB TW3	LL217X	Yes
910925868395	LL217X 80S/840 1x PSU BV NB TW3	LL217X	Yes
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	LL217X	Yes
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	LL217X	Yes
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	LL217X	Yes
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	LL217X	Yes
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	LL217X	Yes
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	LL217X	Yes
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	LL217X	Yes
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	LL217X	Yes
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	LL217X	Yes
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	LL217X	Yes
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	LL217X	Yes
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	LL217X	Yes
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	LL217X	Yes
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	LL217X	Yes
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	LL234X	Yes
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	LL234X	Yes
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	LL234X	Yes
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	LL234X	Yes
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	LL234X	Yes
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	LL234X	Yes
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	LL234X	Yes
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	LL234X	Yes
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	LL234X	Yes
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	LL234X	Yes
910925867552	LL234X 160S/840 2x PSD O 7x2.5	LL234X	Yes
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	LL234X	Yes
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	LL234X	Yes
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	LL234X	Yes
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	LL234X	Yes
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	LL234X	Yes
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	LL217X	Yes
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	LL234X	Yes
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	LL234X	Yes
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	LL234X	Yes
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	LL217X	Yes
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	LL234X	Yes
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	LL234X	Yes

Order Code	Full Product Name	Product	
		Family Code	Service tag
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	LL217X	Yes
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	LL217X	Yes
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	LL234X	Yes
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	LL234X	Yes
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	LL234X	Yes
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	LL234X	Yes
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	LL234X	Yes
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	LL234X	Yes
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	LL234X	Yes
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	LL234X	Yes
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	LL234X	Yes
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	LL234X	Yes
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	LL217X	Yes
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	LL212X	Yes
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	LL212X	Yes
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	LL212X	Yes
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	LL212X	Yes
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	LL212X	Yes
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	LL212X	Yes
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	LL217X	Yes
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	LL217X	Yes
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	LL217X	Yes
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	LL217X	Yes
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	LL217X	Yes
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	LL217X	Yes
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	LL234X	Yes
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	LL234X	Yes
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	LL234X	Yes
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	LL234X	Yes
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	LL234X	Yes
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	LL234X	Yes
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	LL234X	-
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	LL234X	-
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	LL234X	-
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	LL234X	-
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	LL217X	-
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	LL217X	-
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	LL217X	-
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	LL217X	-
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	LL217X	Yes
910925867535	LL217X 80S/840 1x PSD O 7x2.5	LL217X	Yes
910925867551	LL234X 160S/840 2x PSD O 7x1.5	LL234X	Yes
910925867556	LL234X 160S/840 2x PSU O 5x1.5	LL234X	Yes
910925867557	LL234X 160S/840 2x PSU O 5x2.5	LL234X	Yes
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	LL234X	-
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	LL234X	-
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	LL234X	-
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	LL234X	-

Initial performance (IEC compliant)

CoreLine Trunking Gen2

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910925867495	LL212X 53S/840 1x PSU WB 5x1.5 HE	161 lm/W	5300 lm	33 W
910925867515	LL212X 53S/840 1x PSD WB 7x1.5	156 lm/W	5300 lm	34 W
910925867522	LL212X 53S/840 1x PSD WB 7x1.5 HE	161 lm/W	5300 lm	33 W
910925867523	LL212X 53S/840 1x PSD WB 7x2.5 HE	161 lm/W	5300 lm	33 W
910925867524	LL212X 53S/840 1x PSU WB 5x2.5 HE	161 lm/W	5300 lm	33 W
910925867498	LL217X 80S/840 1x PSD BV WB	160 lm/W	8000 lm	50 W
910925867525	LL217X 120S/840 1x PSU BV WB HE	150 lm/W	12000 lm	80 W
910925867539	LL234X 240S/840 2x PSD BV WB HE	152 lm/W	24000 lm	158 W
910925867550	LL234X 160S/840 2x PSU BV WB	157 lm/W	16000 lm	102 W
910925867698	LL217X 80S/840 1X PSU BV WB TW3	157 lm/W	8000 lm	51 W
910925867699	LL234X 160S/840 1X PSU BV WB TW3	157 lm/W	16000 lm	102 W
910925867701	LL234X 160S/840 2X PSU BV WB TW3	157 lm/W	16000 lm	102 W
910925868236	LL217X 45S/840 1x PSU BV WB	161 lm/W	4500 lm	28 W
910925868237	LL217X 45S/840 1x PSD BV WB	164 lm/W	4500 lm	27.5 W
910925868238	LL217X 45S/840 1x PSU BV O	150 lm/W	4200 lm	28 W
910925868239	LL217X 45S/840 1x PSD BV O	153 lm/W	4200 lm	27.5 W
910925868240	LL217X 80S/840 1x PSU BV WB	157 lm/W	8000 lm	51 W
910925868241	LL217X 80S/840 1x PSU BV O	145 lm/W	7400 lm	51 W
910925868242	LL217X 80S/840 1x PSD BV O	148 lm/W	7400 lm	50 W
910925868391	LL217X 120S/840 1x PSU BV WB TW3	150 lm/W	12000 lm	80 W
910925868392	LL217X 120S/840 1x PSU BV MB TW3	150 lm/W	12000 lm	80 W
910925868393	LL217X 120S/840 1x PSU BV NB TW3	150 lm/W	12000 lm	80 W
910925868394	LL217X 80S/840 1x PSU BV MB TW3	157 lm/W	8000 lm	51 W
910925868395	LL217X 80S/840 1x PSU BV NB TW3	157 lm/W	8000 lm	51 W
910925867506	LL217X 120S/840 1x PSU WB 5x2.5 HE	150 lm/W	12000 lm	80 W

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910925867509	LL217X 80S/840 1x PSD WB 7x2.5 VLC	160 lm/W	8000 lm	50 W
910925867518	LL217X 80S/840 1x PSD WB 7x1.5	160 lm/W	8000 lm	50 W
910925867526	LL217X 120S/840 1x PSD WB 7x1.5 HE	152 lm/W	12000 lm	79 W
910925867527	LL217X 120S/840 1x PSD WB 7x2.5 HE	152 lm/W	12000 lm	79 W
910925867528	LL217X 120S/840 1x PSD WB 7x2.5 VLC HE	152 lm/W	12000 lm	79 W
910925867529	LL217X 120S/840 1x PSU WB 5x1.5 HE	150 lm/W	12000 lm	80 W
910925867531	LL217X 80S/840 1x PSD WB 7x2.5 HE	165 lm/W	8000 lm	48.5 W
910925867532	LL217X 80S/840 1x PSD WB 7x2.5 VLC HE	167 lm/W	8000 lm	48 W
910925867533	LL217X 80S/840 1x PSU WB 5x2.5 HE	163 lm/W	8000 lm	49 W
910925867534	LL217X 80S/840 1x PSU WB 5x1.5 HE	163 lm/W	8000 lm	49 W
910925867536	LL217X 80S/840 1x PSD WB 7x2.5	160 lm/W	8000 lm	50 W
910925867537	LL217X 80S/840 1x PSU WB 5x1.5	157 lm/W	8000 lm	51 W
910925867538	LL217X 80S/840 1x PSU WB 5x2.5	157 lm/W	8000 lm	51 W
910925867540	LL234X 160S/840 2x PSD WB 7x1.5 HE	165 lm/W	16000 lm	97 W
910925867541	LL234X 160S/840 2x PSD WB 7x2.5 HE	165 lm/W	16000 lm	97 W
910925867542	LL234X 160S/840 2x PSD WB 7x2.5 VLC HE	167 lm/W	16000 lm	96 W
910925867543	LL234X 160S/840 2x PSU WB 5x1.5 HE	163 lm/W	16000 lm	98 W
910925867544	LL234X 160S/840 2x PSU WB 5x2.5 HE	163 lm/W	16000 lm	98 W
910925867545	LL234X 240S/840 2x PSD WB 7x1.5 HE	152 lm/W	24000 lm	158 W
910925867546	LL234X 240S/840 2x PSD WB 7x2.5 HE	152 lm/W	24000 lm	158 W
910925867547	LL234X 240S/840 2x PSD WB 7x2.5 VLC HE	152 lm/W	24000 lm	158 W
910925867548	LL234X 240S/840 2x PSU WB 5x1.5 HE	150 lm/W	24000 lm	160 W
910925867549	LL234X 240S/840 2x PSU WB 5x2.5 HE	150 lm/W	24000 lm	160 W
910925867552	LL234X 160S/840 2x PSD O 7x2.5	144 lm/W	15000 lm	100 W
910925867553	LL234X 160S/840 2x PSD WB 7x1.5	160 lm/W	16000 lm	100 W

CoreLine Trunking Gen2

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910925867554	LL234X 160S/840 2x PSD WB 7x2.5	160 lm/W	16000 lm	100 W
910925867555	LL234X 160S/840 2x PSD WB 7x2.5 VLC	160 lm/W	16000 lm	100 W
910925867558	LL234X 160S/840 2x PSU WB 5x1.5	157 lm/W	16000 lm	102 W
910925867559	LL234X 160S/840 2x PSU WB 5x2.5	157 lm/W	16000 lm	102 W
910925867560	LL217X 80S/840 1x PSD WB 7x1.5 HE	165 lm/W	8000 lm	48.5 W
910925867561	LL234X 90S/840 2x PSD WB 7x1.5	164 lm/W	9000 lm	55 W
910925868205	LL234X 160S/840 1x PSD WB 7x1.5	163 lm/W	16000 lm	98 W
910925868217	LL234X 160S/840 2x PSU NB 5x1.5	157 lm/W	16000 lm	102 W
910925868218	LL217X 80S/840 1x PSU NB 5x1.5	157 lm/W	8000 lm	51 W
910925868232	LL234X 90S/840 2x PSU WB 5x1.5	161 lm/W	9000 lm	56 W
910925868233	LL234X 90S/840 1x PSD WB 7x1.5	158 lm/W	9000 lm	57 W
910925868234	LL217X 45S/840 1x PSU WB 5x1.5	161 lm/W	4500 lm	28 W
910925868235	LL217X 45S/840 1x PSD WB 7x1.5	164 lm/W	4500 lm	27.5 W
910925868819	LL234X 45S/840 1x PSU HB WB 5x1.5	161 lm/W	4500 lm	28 W
910925868820	LL234X 45S/840 1x PSD HB WB 7x1.5	164 lm/W	4500 lm	27.5 W
910925868821	LL234X 80S/840 1x PSU HB WB 5x1.5	157 lm/W	8000 lm	51 W
910925868822	LL234X 80S/840 1x PSD HB WB 7x1.5	160 lm/W	8000 lm	50 W
910925868823	LL234X 45S/840 1x PSU HB NB 5x1.5	161 lm/W	4500 lm	28 W
910925868824	LL234X 45S/840 1x PSD HB NB 7x1.5	164 lm/W	4500 lm	27.5 W
910925868825	LL234X 80S/840 1x PSU HB NB 5x1.5	157 lm/W	8000 lm	51 W
910925868826	LL234X 80S/840 1x PSD HB NB 7x1.5	160 lm/W	8000 lm	50 W
910925868828	LL234X 90S/840 1x PSD NB 7x1.5	158 lm/W	9000 lm	57 W
910925868830	LL234X 160S/840 1x PSD NB 7x1.5	163 lm/W	16000 lm	98 W
910925868834	LL217X 80S/840 1x PSD NB 7x1.5	160 lm/W	8000 lm	50 W
910925868835	LL212X 30S/840 1x PSU MB 5x2.5	157 lm/W	3000 lm	19 W

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910925868836	LL212X 30S/840 1x PSU NB 5x2.5	157 lm/W	3000 lm	19 W
910925868837	LL212X 53S/840 1x PSU MB 5x2.5	161 lm/W	5300 lm	33 W
910925868838	LL212X 53S/840 1x PSU NB 5x2.5	161 lm/W	5300 lm	33 W
910925868839	LL212X 80S/840 1x PSU MB 5x2.5 HE	163 lm/W	8000 lm	49 W
910925868840	LL212X 80S/840 1x PSU NB 5x2.5 HE	163 lm/W	8000 lm	49 W
910925868841	LL217X 45S/840 1x PSU MB 5x2.5	161 lm/W	4500 lm	28 W
910925868842	LL217X 45S/840 1x PSU NB 5x2.5	161 lm/W	4500 lm	28 W
910925868843	LL217X 80S/840 1x PSU MB 5x2.5	157 lm/W	8000 lm	51 W
910925868844	LL217X 80S/840 1x PSU NB 5x2.5	157 lm/W	8000 lm	51 W
910925868845	LL217X 120S/840 1x PSU MB 5x2.5 HE	150 lm/W	12000 lm	80 W
910925868846	LL217X 120S/840 1x PSU NB 5x2.5 HE	150 lm/W	12000 lm	80 W
910925868847	LL234X 90S/840 2x PSU MB 5x2.5	164 lm/W	9000 lm	56 W
910925868848	LL234X 90S/840 2x PSU NB 5x2.5	164 lm/W	9000 lm	56 W
910925868849	LL234X 160S/840 2x PSU MB 5x2.5	157 lm/W	16000 lm	102 W
910925868850	LL234X 160S/840 2x PSU NB 5x2.5	157 lm/W	16000 lm	102 W
910925868851	LL234X 240S/840 2x PSU MB 5x2.5 HE	150 lm/W	24000 lm	160 W
910925868852	LL234X 240S/840 2x PSU NB 5x2.5 HE	150 lm/W	24000 lm	160 W
910925868989	LL234X 90S/840 1x SIA WB 7x1.5	158 lm/W	9000 lm	57 W
910925868990	LL234X 160S/840 1x SIA WB 7x1.5	163 lm/W	16000 lm	100 W
910925868991	LL234X 90S/840 1x SIA NB 7x1.5	158 lm/W	9000 lm	57 W
910925868992	LL234X 160S/840 1x SIA NB 7x1.5	163 lm/W	16000 lm	100 W
910925868993	LL217X 45S/840 1x SIA WB 7x1.5	164 lm/W	4500 lm	27.5 W
910925868994	LL217X 80S/840 1x SIA WB 7x1.5	160 lm/W	8000 lm	50 W
910925868995	LL217X 45S/840 1x SIA NB 7x1.5	164 lm/W	4500 lm	27.5 W
910925868996	LL217X 80S/840 1x SIA NB 7x1.5	160 lm/W	8000 lm	50 W

CoreLine Trunking Gen2

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910925867530	LL217X 80S/840 1x PSD O 7x2.5 HE	148 lm/W	7400 lm	48.5 W
910925867535	LL217X 80S/840 1x PSD O 7x2.5	144 lm/W	7400 lm	50 W
910925867551	LL234X 160S/840 2x PSD O 7x1.5	144 lm/W	15000 lm	100 W
910925867556	LL234X 160S/840 2x PSU O 5x1.5	141 lm/W	15000 lm	102 W
910925867557	LL234X 160S/840 2x PSU O 5x2.5	141 lm/W	15000 lm	102 W

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
910925868997	LL234X 45S/840 1x SIA HB WB 7x1.5	161 lm/W	4500 lm	27.5 W
910925868998	LL234X 80S/840 1x SIA HB WB 7x1.5	160 lm/W	8000 lm	50 W
910925868999	LL234X 45S/840 1x SIA HB NB 7x1.5	161 lm/W	4500 lm	27.5 W
910925869001	LL234X 80S/840 1x SIA HB NB 7x1.5	160 lm/W	8000 lm	50 W

