



# Rectangular LED highbay with elegant industrial design, optimized optical performance and long term reliability.

## GreenPerform Highbay Rectangular

As the first IP65 rectangular LED highbay under GreenPerform family, GreenPerform Highbay Rectangular with dedicated optical design, leading system efficiency and compact dimension, is the optimized solution for warehousing and logistic related applications.

### Benefits

- Optimized lighting solution delivering professional lighting environment
- Easy installation & on site alignment
- Reliable design & quality control ensures stable performance within lifetime

### Features

- Compact size with optimized thermal consideration & IP65 feature.
- Strong Energy saving story – up to 140lm/W
- Long term quality & reliability within 70Khrs long lifetime span
- Optimized optic design with individual lens, delivering good glare control (UGR 22) with NB and max. luminaire spacing with HRO.

# GreenPerform Highbay Rectangular

## Application

- Warehouses
- Manufacturing
- Distribution center
- Exhibition center

## Versions



GreenPerform Highbay Rectangular

GreenPerform Highbay Rectangular

GreenPerform Highbay Rectangular

Approval and Application	
Mech. impact protection code	IK06
Ingress protection code	IP65
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
Protection class IEC	Safety class I
Optical cover/lens type	Transparent dome
Initial Performance (IEC Compliant)	
Init. Color Rendering Index	>80
Luminous flux tolerance	+/-10%
Mechanical and Housing	
Color	Gray

## Application Conditions

Order Code	Full Product Name	Ambient temperature range
911401500071	BY570P LED100/840 PSD NB CAU	-30 to +45 °C
911401500171	BY570P LED150/850 PSD NB CAU	-30 to +45 °C
911401500271	BY570P LED150/840 PSD NB CAU	-30 to +45 °C
911401585961	BY570P LED100/CW PSU WB GC	-30 to +50 °C
911401586061	BY570P LED100/NW PSU WB GC	-30 to +50 °C
911401586161	BY570P LED100/CW PSU HRO GC	-30 to +50 °C
911401586261	BY570P LED100/NW PSU HRO GC	-30 to +50 °C
911401586361	BY570P LED150/CW PSU WB GC	-30 to +50 °C
911401586461	BY570P LED150/NW PSU WB GC	-30 to +50 °C
911401586561	BY570P LED150/CW PSU HRO GC	-30 to +50 °C
911401586661	BY570P LED150/NW PSU HRO GC	-30 to +50 °C
911401587561	BY570P LED100/NW PSD WB GC	-30 to +45 °C
911401587661	BY570P LED100/NW PSD HRO GC	-30 to +45 °C
911401587761	BY570P LED150/NW PSD WB GC	-30 to +45 °C
911401587861	BY570P LED150/NW PSD HRO GC	-30 to +45 °C
911401588361	BY570P LED100/CW PSD WB GC	-30 to +45 °C
911401588461	BY570P LED100/CW PSD HRO GC	-30 to +45 °C
911401588561	BY570P LED150/CW PSD WB GC	-30 to +45 °C
911401588661	BY570P LED150/CW PSD HRO GC	-30 to +45 °C
911401589161	BY570P LED100/CW PSU NB GC	-30 to +50 °C
911401589261	BY570P LED100/NW PSU NB GC	-30 to +50 °C
911401589361	BY570P LED150/CW PSU NB GC	-30 to +50 °C
911401589461	BY570P LED150/NW PSU NB GC	-30 to +50 °C
911401589961	BY570P LED100/CW PSD NB GC	-30 to +45 °C
911401590061	BY570P LED100/NW PSD NB GC	-30 to +45 °C
911401590161	BY570P LED150/CW PSD NB GC	-30 to +45 °C
911401590261	BY570P LED150/NW PSD NB GC	-30 to +45 °C
911401590761	BY570P LED100/CW PSU WB GM	-30 to +50 °C

## GreenPerform Highbay Rectangular

Order Code	Full Product Name	Ambient temperature range
911401590861	BY570P LED100/NW PSU WB GM	-30 to +50 °C
911401590961	BY570P LED100/CW PSU HRO GM	-30 to +50 °C
911401591061	BY570P LED100/NW PSU HRO GM	-30 to +50 °C
911401591161	BY570P LED150/CW PSU WB GM	-30 to +50 °C
911401591261	BY570P LED150/NW PSU WB GM	-30 to +50 °C
911401591361	BY570P LED150/CW PSU HRO GM	-30 to +50 °C
911401591461	BY570P LED150/NW PSU HRO GM	-30 to +50 °C
911401592361	BY570P LED100/NW PSD WB GM	-30 to +45 °C
911401592461	BY570P LED100/NW PSD HRO GM	-30 to +45 °C
911401592561	BY570P LED150/NW PSD WB GM	-30 to +45 °C
911401592661	BY570P LED150/NW PSD HRO GM	-30 to +45 °C
911401593161	BY570P LED100/CW PSD WB GM	-30 to +45 °C
911401593261	BY570P LED100/CW PSD HRO GM	-30 to +45 °C
911401593361	BY570P LED150/CW PSD WB GM	-30 to +45 °C
911401593461	BY570P LED150/CW PSD HRO GM	-30 to +45 °C
911401593961	BY570P LED100/CW PSU NB GM	-30 to +50 °C
911401594061	BY570P LED100/NW PSU NB GM	-30 to +50 °C
911401594161	BY570P LED150/CW PSU NB GM	-30 to +50 °C
911401594261	BY570P LED150/NW PSU NB GM	-30 to +50 °C
911401594761	BY570P LED100/CW PSD NB GM	-30 to +45 °C
911401594861	BY570P LED100/NW PSD NB GM	-30 to +45 °C
911401594961	BY570P LED150/CW PSD NB GM	-30 to +45 °C
911401595061	BY570P LED150/NW PSD NB GM	-30 to +45 °C
911401595561	BY570P LED100/850 PSU WB CAU	-30 to +50 °C
911401595661	BY570P LED100/840 PSU WB CAU	-30 to +50 °C
911401595761	BY570P LED100/850 PSU HRO CAU	-30 to +50 °C
911401595861	BY570P LED100/840 PSU HRO CAU	-30 to +50 °C
911401595961	BY570P LED150/850 PSU WB CAU	-30 to +50 °C
911401596061	BY570P LED150/840 PSU WB CAU	-30 to +50 °C
911401596161	BY570P LED150/850 PSU HRO CAU	-30 to +50 °C
911401596261	BY570P LED150/840 PSU HRO CAU	-30 to +50 °C
911401597561	BY570P LED100/840 PSD WB CAU	-30 to +45 °C
911401597661	BY570P LED100/840 PSD HRO CAU	-30 to +45 °C
911401597761	BY570P LED150/840 PSD WB CAU	-30 to +45 °C
911401597861	BY570P LED150/840 PSD HRO CAU	-30 to +45 °C
911401598361	BY570P LED100/850 PSD WB CAU	-30 to +45 °C
911401598461	BY570P LED100/850 PSD HRO CAU	-30 to +45 °C
911401598561	BY570P LED150/850 PSD WB CAU	-30 to +45 °C
911401598661	BY570P LED150/850 PSD HRO CAU	-30 to +45 °C
911401599161	BY570P LED100/850 PSU NB CAU	-30 to +50 °C
911401599261	BY570P LED100/840 PSU NB CAU	-30 to +50 °C
911401599361	BY570P LED150/850 PSU NB CAU	-30 to +50 °C
911401599461	BY570P LED150/840 PSU NB CAU	-30 to +50 °C
911401599961	BY570P LED100/850 PSD NB CAU	-30 to +45 °C
911401500371	BY570P LED200/850 PSD NB CAU	-30 to +45 °C
911401500471	BY570P LED200/840 PSD NB CAU	-30 to +45 °C
911401586761	BY570P LED200/CW PSU WB GC	-30 to +50 °C
911401586861	BY570P LED200/NW PSU WB GC	-30 to +50 °C
911401586961	BY570P LED200/CW PSU HRO GC	-30 to +50 °C
911401587061	BY570P LED200/NW PSU HRO GC	-30 to +50 °C
911401587961	BY570P LED200/NW PSD WB GC	-30 to +45 °C
911401588061	BY570P LED200/NW PSD HRO GC	-30 to +45 °C

## GreenPerform Highbay Rectangular

Order Code	Full Product Name	Ambient temperature range
911401588761	BY570P LED200/CW PSD WB GC	-30 to +45 °C
911401588861	BY570P LED200/CW PSD HRO GC	-30 to +45 °C
911401589561	BY570P LED200/CW PSU NB GC	-30 to +50 °C
911401589661	BY570P LED200/NW PSU NB GC	-30 to +50 °C
911401590361	BY570P LED200/CW PSD NB GC	-30 to +45 °C
911401590461	BY570P LED200/NW PSD NB GC	-30 to +45 °C
911401591561	BY570P LED200/CW PSU WB GM	-30 to +50 °C
911401591661	BY570P LED200/NW PSU WB GM	-30 to +50 °C
911401591761	BY570P LED200/CW PSU HRO GM	-30 to +50 °C
911401591861	BY570P LED200/NW PSU HRO GM	-30 to +50 °C
911401592761	BY570P LED200/NW PSD WB GM	-30 to +45 °C
911401592861	BY570P LED200/NW PSD HRO GM	-30 to +45 °C
911401593561	BY570P LED200/CW PSD WB GM	-30 to +45 °C
911401593661	BY570P LED200/CW PSD HRO GM	-30 to +45 °C
911401594361	BY570P LED200/CW PSU NB GM	-30 to +50 °C
911401594461	BY570P LED200/NW PSU NB GM	-30 to +50 °C
911401595161	BY570P LED200/CW PSD NB GM	-30 to +45 °C
911401595261	BY570P LED200/NW PSD NB GM	-30 to +45 °C
911401596361	BY570P LED200/850 PSU WB CAU	-30 to +50 °C
911401596461	BY570P LED200/840 PSU WB CAU	-30 to +50 °C
911401596561	BY570P LED200/865 PSU WB CAU CL	-30 to +50 °C
911401596661	BY570P LED200/840 PSU WB CAU CL	-30 to +50 °C
911401596761	BY570P LED200/850 PSU HRO CAU	-30 to +50 °C
911401596861	BY570P LED200/840 PSU HRO CAU	-30 to +50 °C
911401597961	BY570P LED200/840 PSD WB CAU	-30 to +45 °C
911401598061	BY570P LED200/840 PSD HRO CAU	-30 to +45 °C
911401598761	BY570P LED200/850 PSD WB CAU	-30 to +45 °C
911401598861	BY570P LED200/850 PSD HRO CAU	-30 to +45 °C
911401599561	BY570P LED200/850 PSU NB CAU	-30 to +50 °C
911401599661	BY570P LED200/840 PSU NB CAU	-30 to +50 °C
911401500571	BY570P LED250/850 PSD NB CAU	-30 to +45 °C
911401500671	BY570P LED250/840 PSD NB CAU	-30 to +45 °C
911401587161	BY570P LED250/CW PSU WB GC	-30 to +50 °C
911401587261	BY570P LED250/NW PSU WB GC	-30 to +50 °C
911401587361	BY570P LED250/CW PSU HRO GC	-30 to +50 °C
911401587461	BY570P LED250/NW PSU HRO GC	-30 to +50 °C
911401588161	BY570P LED250/NW PSD WB GC	-30 to +45 °C
911401588261	BY570P LED250/NW PSD HRO GC	-30 to +45 °C
911401588961	BY570P LED250/CW PSD WB GC	-30 to +45 °C
911401589061	BY570P LED250/CW PSD HRO GC	-30 to +45 °C
911401589761	BY570P LED250/CW PSU NB GC	-30 to +50 °C
911401589861	BY570P LED250/NW PSU NB GC	-30 to +50 °C
911401590561	BY570P LED250/CW PSD NB GC	-30 to +45 °C
911401590661	BY570P LED250/NW PSD NB GC	-30 to +45 °C
911401591961	BY570P LED250/CW PSU WB GM	-30 to +50 °C
911401592061	BY570P LED250/NW PSU WB GM	-30 to +50 °C
911401592161	BY570P LED250/CW PSU HRO GM	-30 to +50 °C
911401592261	BY570P LED250/NW PSU HRO GM	-30 to +50 °C
911401592961	BY570P LED250/NW PSD WB GM	-30 to +45 °C
911401593061	BY570P LED250/NW PSD HRO GM	-30 to +45 °C
911401593761	BY570P LED250/CW PSD WB GM	-30 to +45 °C
911401593861	BY570P LED250/CW PSD HRO GM	-30 to +45 °C

## GreenPerform Highbay Rectangular

Order Code	Full Product Name	Ambient temperature range
911401594561	BY570P LED250/CW PSU NB GM	-30 to +50 °C
911401594661	BY570P LED250/NW PSU NB GM	-30 to +50 °C
911401595361	BY570P LED250/CW PSD NB GM	-30 to +45 °C
911401595461	BY570P LED250/NW PSD NB GM	-30 to +45 °C
911401596961	BY570P LED250/850 PSU WB CAU	-30 to +50 °C
911401597061	BY570P LED250/840 PSU WB CAU	-30 to +50 °C
911401597161	BY570P LED250/865 PSU WB CAU CL	-30 to +50 °C
911401597261	BY570P LED250/840 PSU WB CAU CL	-30 to +50 °C
911401597361	BY570P LED250/850 PSU HRO CAU	-30 to +50 °C
911401597461	BY570P LED250/840 PSU HRO CAU	-30 to +50 °C
911401598161	BY570P LED250/840 PSD WB CAU	-30 to +45 °C
911401598261	BY570P LED250/840 PSD HRO CAU	-30 to +45 °C
911401598961	BY570P LED250/850 PSD WB CAU	-30 to +45 °C
911401599061	BY570P LED250/850 PSD HRO CAU	-30 to +45 °C
911401599761	BY570P LED250/850 PSU NB CAU	-30 to +50 °C
911401599861	BY570P LED250/840 PSU NB CAU	-30 to +50 °C

### Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401500071	BY570P LED100/840 PSD NB CAU	Yes	911401591261	BY570P LED150/NW PSU WB GM	No
911401500171	BY570P LED150/850 PSD NB CAU	Yes	911401591361	BY570P LED150/CW PSU HRO GM	No
911401500271	BY570P LED150/840 PSD NB CAU	Yes	911401591461	BY570P LED150/NW PSU HRO GM	No
911401585961	BY570P LED100/CW PSU WB GC	No	911401592361	BY570P LED100/NW PSD WB GM	Yes
911401586061	BY570P LED100/NW PSU WB GC	No	911401592461	BY570P LED100/NW PSD HRO GM	Yes
911401586161	BY570P LED100/CW PSU HRO GC	No	911401592561	BY570P LED150/NW PSD WB GM	Yes
911401586261	BY570P LED100/NW PSU HRO GC	No	911401592661	BY570P LED150/NW PSD HRO GM	Yes
911401586361	BY570P LED150/CW PSU WB GC	No	911401593161	BY570P LED100/CW PSD WB GM	Yes
911401586461	BY570P LED150/NW PSU WB GC	No	911401593261	BY570P LED100/CW PSD HRO GM	Yes
911401586561	BY570P LED150/CW PSU HRO GC	No	911401593361	BY570P LED150/CW PSD WB GM	Yes
911401586661	BY570P LED150/NW PSU HRO GC	No	911401593461	BY570P LED150/CW PSD HRO GM	Yes
911401587561	BY570P LED100/NW PSD WB GC	Yes	911401593961	BY570P LED100/CW PSU NB GM	No
911401587661	BY570P LED100/NW PSD HRO GC	Yes	911401594061	BY570P LED100/NW PSU NB GM	No
911401587761	BY570P LED150/NW PSD WB GC	Yes	911401594161	BY570P LED150/CW PSU NB GM	No
911401587861	BY570P LED150/NW PSD HRO GC	Yes	911401594261	BY570P LED150/NW PSU NB GM	No
911401588361	BY570P LED100/CW PSD WB GC	Yes	911401594761	BY570P LED100/CW PSD NB GM	Yes
911401588461	BY570P LED100/CW PSD HRO GC	Yes	911401594861	BY570P LED100/NW PSD NB GM	Yes
911401588561	BY570P LED150/CW PSD WB GC	Yes	911401594961	BY570P LED150/CW PSD NB GM	Yes
911401588661	BY570P LED150/CW PSD HRO GC	Yes	911401595061	BY570P LED150/NW PSD NB GM	Yes
911401589161	BY570P LED100/CW PSU NB GC	No	911401595561	BY570P LED100/850 PSU WB CAU	No
911401589261	BY570P LED100/NW PSU NB GC	No	911401595661	BY570P LED100/840 PSU WB CAU	No
911401589361	BY570P LED150/CW PSU NB GC	No	911401595761	BY570P LED100/850 PSU HRO CAU	No
911401589461	BY570P LED150/NW PSU NB GC	No	911401595861	BY570P LED100/840 PSU HRO CAU	No
911401589961	BY570P LED100/CW PSD NB GC	Yes	911401595961	BY570P LED150/850 PSU WB CAU	No
911401590061	BY570P LED100/NW PSD NB GC	Yes	911401596061	BY570P LED150/840 PSU WB CAU	No
911401590161	BY570P LED150/CW PSD NB GC	Yes	911401596161	BY570P LED150/850 PSU HRO CAU	No
911401590261	BY570P LED150/NW PSD NB GC	Yes	911401596261	BY570P LED150/840 PSU HRO CAU	No
911401590761	BY570P LED100/CW PSU WB GM	No	911401597561	BY570P LED100/840 PSD WB CAU	Yes
911401590861	BY570P LED100/NW PSU WB GM	No	911401597661	BY570P LED100/840 PSD HRO CAU	Yes
911401590961	BY570P LED100/CW PSU HRO GM	No	911401597761	BY570P LED150/840 PSD WB CAU	Yes
911401591061	BY570P LED100/NW PSU HRO GM	No	911401597861	BY570P LED150/840 PSD HRO CAU	Yes
911401591161	BY570P LED150/CW PSU WB GM	No	911401598361	BY570P LED100/850 PSD WB CAU	Yes

## GreenPerform Highbay Rectangular

Order Code	Full Product Name	Dimmable
911401598461	BY570P LED100/850 PSD HRO CAU	Yes
911401598561	BY570P LED150/850 PSD WB CAU	Yes
911401598661	BY570P LED150/850 PSD HRO CAU	Yes
911401599161	BY570P LED100/850 PSU NB CAU	No
911401599261	BY570P LED100/840 PSU NB CAU	No
911401599361	BY570P LED150/850 PSU NB CAU	No
911401599461	BY570P LED150/840 PSU NB CAU	No
911401599961	BY570P LED100/850 PSD NB CAU	Yes
911401500371	BY570P LED200/850 PSD NB CAU	Yes
911401500471	BY570P LED200/840 PSD NB CAU	Yes
911401586761	BY570P LED200/CW PSU WB GC	No
911401586861	BY570P LED200/NW PSU WB GC	No
911401586961	BY570P LED200/CW PSU HRO GC	No
911401587061	BY570P LED200/NW PSU HRO GC	No
911401587961	BY570P LED200/NW PSD WB GC	Yes
911401588061	BY570P LED200/NW PSD HRO GC	Yes
911401588761	BY570P LED200/CW PSD WB GC	Yes
911401588861	BY570P LED200/CW PSD HRO GC	Yes
911401589561	BY570P LED200/CW PSU NB GC	No
911401589661	BY570P LED200/NW PSU NB GC	No
911401590361	BY570P LED200/CW PSD NB GC	Yes
911401590461	BY570P LED200/NW PSD NB GC	Yes
911401591561	BY570P LED200/CW PSU WB GM	No
911401591661	BY570P LED200/NW PSU WB GM	No
911401591761	BY570P LED200/CW PSU HRO GM	No
911401591861	BY570P LED200/NW PSU HRO GM	No
911401592761	BY570P LED200/NW PSD WB GM	Yes
911401592861	BY570P LED200/NW PSD HRO GM	Yes
911401593561	BY570P LED200/CW PSD WB GM	Yes
911401593661	BY570P LED200/CW PSD HRO GM	Yes
911401594361	BY570P LED200/CW PSU NB GM	No
911401594461	BY570P LED200/NW PSU NB GM	No
911401595161	BY570P LED200/CW PSD NB GM	Yes
911401595261	BY570P LED200/NW PSD NB GM	Yes
911401596361	BY570P LED200/850 PSU WB CAU	No
911401596461	BY570P LED200/840 PSU WB CAU	No
911401596561	BY570P LED200/865 PSU WB CAU CL	No
911401596661	BY570P LED200/840 PSU WB CAU CL	No
911401596761	BY570P LED200/850 PSU HRO CAU	No
911401596861	BY570P LED200/840 PSU HRO CAU	No
911401597961	BY570P LED200/840 PSD WB CAU	Yes
911401598061	BY570P LED200/840 PSD HRO CAU	Yes

Order Code	Full Product Name	Dimmable
911401598761	BY570P LED200/850 PSD WB CAU	Yes
911401598861	BY570P LED200/850 PSD HRO CAU	Yes
911401599561	BY570P LED200/850 PSU NB CAU	No
911401599661	BY570P LED200/840 PSU NB CAU	No
911401500571	BY570P LED250/850 PSD NB CAU	Yes
911401500671	BY570P LED250/840 PSD NB CAU	Yes
911401587161	BY570P LED250/CW PSU WB GC	No
911401587261	BY570P LED250/NW PSU WB GC	No
911401587361	BY570P LED250/CW PSU HRO GC	No
911401587461	BY570P LED250/NW PSU HRO GC	No
911401588161	BY570P LED250/NW PSD WB GC	Yes
911401588261	BY570P LED250/NW PSD HRO GC	Yes
911401588961	BY570P LED250/CW PSD WB GC	Yes
911401589061	BY570P LED250/CW PSD HRO GC	Yes
911401589761	BY570P LED250/CW PSU NB GC	No
911401589861	BY570P LED250/NW PSU NB GC	No
911401590561	BY570P LED250/CW PSD NB GC	Yes
911401590661	BY570P LED250/NW PSD NB GC	Yes
911401591961	BY570P LED250/CW PSU WB GM	No
911401592061	BY570P LED250/NW PSU WB GM	No
911401592161	BY570P LED250/CW PSU HRO GM	No
911401592261	BY570P LED250/NW PSU HRO GM	No
911401592961	BY570P LED250/NW PSD WB GM	Yes
911401593061	BY570P LED250/NW PSD HRO GM	Yes
911401593761	BY570P LED250/CW PSD WB GM	Yes
911401593861	BY570P LED250/CW PSD HRO GM	Yes
911401594561	BY570P LED250/CW PSU NB GM	No
911401594661	BY570P LED250/NW PSU NB GM	No
911401595361	BY570P LED250/CW PSD NB GM	Yes
911401595461	BY570P LED250/NW PSD NB GM	Yes
911401596961	BY570P LED250/850 PSU WB CAU	No
911401597061	BY570P LED250/840 PSU WB CAU	No
911401597161	BY570P LED250/865 PSU WB CAU CL	No
911401597261	BY570P LED250/840 PSU WB CAU CL	No
911401597361	BY570P LED250/850 PSU HRO CAU	No
911401597461	BY570P LED250/840 PSU HRO CAU	No
911401598161	BY570P LED250/840 PSD WB CAU	Yes
911401598261	BY570P LED250/840 PSD HRO CAU	Yes
911401598961	BY570P LED250/850 PSD WB CAU	Yes
911401599061	BY570P LED250/850 PSD HRO CAU	Yes
911401599761	BY570P LED250/850 PSU NB CAU	No
911401599861	BY570P LED250/840 PSU NB CAU	No

### General Information

Order Code	Full Product Name	CE mark
911401500071	BY570P LED100/840 PSD NB CAU	-
911401500171	BY570P LED150/850 PSD NB CAU	-
911401500271	BY570P LED150/840 PSD NB CAU	-
911401585961	BY570P LED100/CW PSU WB GC	-
911401586061	BY570P LED100/NW PSU WB GC	-
911401586161	BY570P LED100/CW PSU HRO GC	-

Order Code	Full Product Name	CE mark
911401586261	BY570P LED100/NW PSU HRO GC	-
911401586361	BY570P LED150/CW PSU WB GC	-
911401586461	BY570P LED150/NW PSU WB GC	-
911401586561	BY570P LED150/CW PSU HRO GC	-
911401586661	BY570P LED150/NW PSU HRO GC	-
911401587561	BY570P LED100/NW PSD WB GC	-

## GreenPerform Highbay Rectangular

Order Code	Full Product Name	CE mark	Order Code	Full Product Name	CE mark
911401587661	BY570P LED100/NW PSD HRO GC	-	911401598461	BY570P LED100/850 PSD HRO CAU	-
911401587761	BY570P LED150/NW PSD WB GC	-	911401598561	BY570P LED150/850 PSD WB CAU	-
911401587861	BY570P LED150/NW PSD HRO GC	-	911401598661	BY570P LED150/850 PSD HRO CAU	-
911401588361	BY570P LED100/CW PSD WB GC	-	911401599161	BY570P LED100/850 PSU NB CAU	-
911401588461	BY570P LED100/CW PSD HRO GC	-	911401599261	BY570P LED100/840 PSU NB CAU	-
911401588561	BY570P LED150/CW PSD WB GC	-	911401599361	BY570P LED150/850 PSU NB CAU	-
911401588661	BY570P LED150/CW PSD HRO GC	-	911401599461	BY570P LED150/840 PSU NB CAU	-
911401589161	BY570P LED100/CW PSU NB GC	-	911401599961	BY570P LED100/850 PSD NB CAU	-
911401589261	BY570P LED100/NW PSU NB GC	-	911401500371	BY570P LED200/850 PSD NB CAU	-
911401589361	BY570P LED150/CW PSU NB GC	-	911401500471	BY570P LED200/840 PSD NB CAU	-
911401589461	BY570P LED150/NW PSU NB GC	-	911401586761	BY570P LED200/CW PSU WB GC	-
911401589961	BY570P LED100/CW PSD NB GC	-	911401586861	BY570P LED200/NW PSU WB GC	-
911401590061	BY570P LED100/NW PSD NB GC	-	911401586961	BY570P LED200/CW PSU HRO GC	-
911401590161	BY570P LED150/CW PSD NB GC	-	911401587061	BY570P LED200/NW PSU HRO GC	-
911401590261	BY570P LED150/NW PSD NB GC	-	911401587961	BY570P LED200/NW PSD WB GC	-
911401590761	BY570P LED100/CW PSU WB GM	CE mark	911401588061	BY570P LED200/NW PSD HRO GC	-
911401590861	BY570P LED100/NW PSU WB GM	CE mark	911401588761	BY570P LED200/CW PSD WB GC	-
911401590961	BY570P LED100/CW PSU HRO GM	CE mark	911401588861	BY570P LED200/CW PSD HRO GC	-
911401591061	BY570P LED100/NW PSU HRO GM	CE mark	911401589561	BY570P LED200/CW PSU NB GC	-
911401591161	BY570P LED150/CW PSU WB GM	CE mark	911401589661	BY570P LED200/NW PSU NB GC	-
911401591261	BY570P LED150/NW PSU WB GM	CE mark	911401590361	BY570P LED200/CW PSD NB GC	-
911401591361	BY570P LED150/CW PSU HRO GM	CE mark	911401590461	BY570P LED200/NW PSD NB GC	-
911401591461	BY570P LED150/NW PSU HRO GM	CE mark	911401591561	BY570P LED200/CW PSU WB GM	CE mark
911401592361	BY570P LED100/NW PSD WB GM	CE mark	911401591661	BY570P LED200/NW PSU WB GM	CE mark
911401592461	BY570P LED100/NW PSD HRO GM	CE mark	911401591761	BY570P LED200/CW PSU HRO GM	CE mark
911401592561	BY570P LED150/NW PSD WB GM	CE mark	911401591861	BY570P LED200/NW PSU HRO GM	CE mark
911401592661	BY570P LED150/NW PSD HRO GM	CE mark	911401592761	BY570P LED200/NW PSD WB GM	CE mark
911401593161	BY570P LED100/CW PSD WB GM	CE mark	911401592861	BY570P LED200/NW PSD HRO GM	CE mark
911401593261	BY570P LED100/CW PSD HRO GM	CE mark	911401593561	BY570P LED200/CW PSD WB GM	CE mark
911401593361	BY570P LED150/CW PSD WB GM	CE mark	911401593661	BY570P LED200/CW PSD HRO GM	CE mark
911401593461	BY570P LED150/CW PSD HRO GM	CE mark	911401594361	BY570P LED200/CW PSU NB GM	CE mark
911401593961	BY570P LED100/CW PSU NB GM	CE mark	911401594461	BY570P LED200/NW PSU NB GM	CE mark
911401594061	BY570P LED100/NW PSU NB GM	CE mark	911401595161	BY570P LED200/CW PSD NB GM	CE mark
911401594161	BY570P LED150/CW PSU NB GM	CE mark	911401595261	BY570P LED200/NW PSD NB GM	CE mark
911401594261	BY570P LED150/NW PSU NB GM	CE mark	911401596361	BY570P LED200/850 PSU WB CAU	-
911401594761	BY570P LED100/CW PSD NB GM	CE mark	911401596461	BY570P LED200/840 PSU WB CAU	-
911401594861	BY570P LED100/NW PSD NB GM	CE mark	911401596561	BY570P LED200/865 PSU WB CAU CL	-
911401594961	BY570P LED150/CW PSD NB GM	CE mark	911401596661	BY570P LED200/840 PSU WB CAU CL	-
911401595061	BY570P LED150/NW PSD NB GM	CE mark	911401596761	BY570P LED200/850 PSU HRO CAU	-
911401595561	BY570P LED100/850 PSU WB CAU	-	911401596861	BY570P LED200/840 PSU HRO CAU	-
911401595661	BY570P LED100/840 PSU WB CAU	-	911401597961	BY570P LED200/840 PSD WB CAU	-
911401595761	BY570P LED100/850 PSU HRO CAU	-	911401598061	BY570P LED200/840 PSD HRO CAU	-
911401595861	BY570P LED100/840 PSU HRO CAU	-	911401598761	BY570P LED200/850 PSD WB CAU	-
911401595961	BY570P LED150/850 PSU WB CAU	-	911401598861	BY570P LED200/850 PSD HRO CAU	-
911401596061	BY570P LED150/840 PSU WB CAU	-	911401599561	BY570P LED200/850 PSU NB CAU	-
911401596161	BY570P LED150/850 PSU HRO CAU	-	911401599661	BY570P LED200/840 PSU NB CAU	-
911401596261	BY570P LED150/840 PSU HRO CAU	-	911401500571	BY570P LED250/850 PSD NB CAU	-
911401597561	BY570P LED100/840 PSD WB CAU	-	911401500671	BY570P LED250/840 PSD NB CAU	-
911401597661	BY570P LED100/840 PSD HRO CAU	-	911401587161	BY570P LED250/CW PSU WB GC	-
911401597761	BY570P LED150/840 PSD WB CAU	-	911401587261	BY570P LED250/NW PSU WB GC	-
911401597861	BY570P LED150/840 PSD HRO CAU	-	911401587361	BY570P LED250/CW PSU HRO GC	-
911401598361	BY570P LED100/850 PSD WB CAU	-	911401587461	BY570P LED250/NW PSU HRO GC	-



## GreenPerform Highbay Rectangular

Order Code	Full Product Name	CE mark
911401588161	BY570P LED250/NW PSD WB GC	-
911401588261	BY570P LED250/NW PSD HRO GC	-
911401588961	BY570P LED250/CW PSD WB GC	-
911401589061	BY570P LED250/CW PSD HRO GC	-
911401589761	BY570P LED250/CW PSU NB GC	-
911401589861	BY570P LED250/NW PSU NB GC	-
911401590561	BY570P LED250/CW PSD NB GC	-
911401590661	BY570P LED250/NW PSD NB GC	-
911401591961	BY570P LED250/CW PSU WB GM	CE mark
911401592061	BY570P LED250/NW PSU WB GM	CE mark
911401592161	BY570P LED250/CW PSU HRO GM	CE mark
911401592261	BY570P LED250/NW PSU HRO GM	CE mark
911401592961	BY570P LED250/NW PSD WB GM	CE mark
911401593061	BY570P LED250/NW PSD HRO GM	CE mark
911401593761	BY570P LED250/CW PSD WB GM	CE mark
911401593861	BY570P LED250/CW PSD HRO GM	CE mark

Order Code	Full Product Name	CE mark
911401594561	BY570P LED250/CW PSU NB GM	CE mark
911401594661	BY570P LED250/NW PSU NB GM	CE mark
911401595361	BY570P LED250/CW PSD NB GM	CE mark
911401595461	BY570P LED250/NW PSD NB GM	CE mark
911401596961	BY570P LED250/850 PSU WB CAU	-
911401597061	BY570P LED250/840 PSU WB CAU	-
911401597161	BY570P LED250/865 PSU WB CAU CL	-
911401597261	BY570P LED250/840 PSU WB CAU CL	-
911401597361	BY570P LED250/850 PSU HRO CAU	-
911401597461	BY570P LED250/840 PSU HRO CAU	-
911401598161	BY570P LED250/840 PSD WB CAU	-
911401598261	BY570P LED250/840 PSD HRO CAU	-
911401598961	BY570P LED250/850 PSD WB CAU	-
911401599061	BY570P LED250/850 PSD HRO CAU	-
911401599761	BY570P LED250/850 PSU NB CAU	-
911401599861	BY570P LED250/840 PSU NB CAU	-

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401500071	BY570P LED100/840 PSD NB CAU	4000 K	133 lm/W	10000 lm	75 W
911401500171	BY570P LED150/850 PSD NB CAU	5000 K	126 lm/W	15000 lm	119 W
911401500271	BY570P LED150/840 PSD NB CAU	4000 K	126 lm/W	15000 lm	119 W
911401585961	BY570P LED100/CW PSU WB GC	6500 K	145 lm/W	10000 lm	69 W
911401586061	BY570P LED100/NW PSU WB GC	4000 K	145 lm/W	10000 lm	69 W
911401586161	BY570P LED100/CW PSU HRO GC	6500 K	145 lm/W	10000 lm	69 W
911401586261	BY570P LED100/NW PSU HRO GC	4000 K	145 lm/W	10000 lm	69 W
911401586361	BY570P LED150/CW PSU WB GC	6500 K	135 lm/W	15000 lm	111 W
911401586461	BY570P LED150/NW PSU WB GC	4000 K	135 lm/W	15000 lm	111 W
911401586561	BY570P LED150/CW PSU HRO GC	6500 K	135 lm/W	15000 lm	111 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401586661	BY570P LED150/NW PSU HRO GC	4000 K	135 lm/W	15000 lm	111 W
911401587561	BY570P LED100/NW PSD WB GC	4000 K	133 lm/W	10000 lm	75 W
911401587661	BY570P LED100/NW PSD HRO GC	4000 K	133 lm/W	10000 lm	75 W
911401587761	BY570P LED150/NW PSD WB GC	4000 K	126 lm/W	15000 lm	119 W
911401587861	BY570P LED150/NW PSD HRO GC	4000 K	126 lm/W	15000 lm	119 W
911401588361	BY570P LED100/CW PSD WB GC	6500 K	133 lm/W	10000 lm	75 W
911401588461	BY570P LED100/CW PSD HRO GC	6500 K	133 lm/W	10000 lm	75 W
911401588561	BY570P LED150/CW PSD WB GC	6500 K	126 lm/W	15000 lm	119 W
911401588661	BY570P LED150/CW PSD HRO GC	6500 K	126 lm/W	15000 lm	119 W
911401589161	BY570P LED100/CW PSU NB GC	6500 K	145 lm/W	10000 lm	69 W



## GreenPerform Highbay Rectangular

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401589261	BY570P LED100/NW PSU NB GC	4000 K	145 lm/W	10000 lm	69 W
911401589361	BY570P LED150/CW PSU NB GC	6500 K	135 lm/W	15000 lm	111 W
911401589461	BY570P LED150/NW PSU NB GC	4000 K	135 lm/W	15000 lm	111 W
911401589961	BY570P LED100/CW PSD NB GC	6500 K	133 lm/W	10000 lm	75 W
911401590061	BY570P LED100/NW PSD NB GC	4000 K	133 lm/W	10000 lm	75 W
911401590161	BY570P LED150/CW PSD NB GC	6500 K	126 lm/W	15000 lm	119 W
911401590261	BY570P LED150/NW PSD NB GC	4000 K	126 lm/W	15000 lm	119 W
911401590761	BY570P LED100/CW PSU WB GM	6500 K	145 lm/W	10000 lm	69 W
911401590861	BY570P LED100/NW PSU WB GM	4000 K	145 lm/W	10000 lm	69 W
911401590961	BY570P LED100/CW PSU HRO GM	6500 K	145 lm/W	10000 lm	69 W
911401591061	BY570P LED100/NW PSU HRO GM	4000 K	145 lm/W	10000 lm	69 W
911401591161	BY570P LED150/CW PSU WB GM	6500 K	135 lm/W	15000 lm	111 W
911401591261	BY570P LED150/NW PSU WB GM	4000 K	135 lm/W	15000 lm	111 W
911401591361	BY570P LED150/CW PSU HRO GM	6500 K	135 lm/W	15000 lm	111 W
911401591461	BY570P LED150/NW PSU HRO GM	4000 K	135 lm/W	15000 lm	111 W
911401592361	BY570P LED100/NW PSD WB GM	4000 K	133 lm/W	10000 lm	75 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401592461	BY570P LED100/NW PSD HRO GM	4000 K	133 lm/W	10000 lm	75 W
911401592561	BY570P LED150/NW PSD WB GM	4000 K	126 lm/W	15000 lm	119 W
911401592661	BY570P LED150/NW PSD HRO GM	4000 K	126 lm/W	15000 lm	119 W
911401593161	BY570P LED100/CW PSD WB GM	6500 K	133 lm/W	10000 lm	75 W
911401593261	BY570P LED100/CW PSD HRO GM	6500 K	133 lm/W	10000 lm	75 W
911401593361	BY570P LED150/CW PSD WB GM	6500 K	126 lm/W	15000 lm	119 W
911401593461	BY570P LED150/CW PSD HRO GM	6500 K	126 lm/W	15000 lm	119 W
911401593961	BY570P LED100/CW PSU NB GM	6500 K	145 lm/W	10000 lm	69 W
911401594061	BY570P LED100/NW PSU NB GM	4000 K	145 lm/W	10000 lm	69 W
911401594161	BY570P LED150/CW PSU NB GM	6500 K	135 lm/W	15000 lm	111 W
911401594261	BY570P LED150/NW PSU NB GM	4000 K	135 lm/W	15000 lm	111 W
911401594761	BY570P LED100/CW PSD NB GM	6500 K	133 lm/W	10000 lm	75 W
911401594861	BY570P LED100/NW PSD NB GM	4000 K	133 lm/W	10000 lm	75 W
911401594961	BY570P LED150/CW PSD NB GM	6500 K	126 lm/W	15000 lm	119 W
911401595061	BY570P LED150/NW PSD NB GM	4000 K	126 lm/W	15000 lm	119 W
911401595561	BY570P LED100/850 PSU WB CAU	5000 K	145 lm/W	10000 lm	69 W

## GreenPerform Highbay Rectangular

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401595661	BY570P LED100/840 PSU WB CAU	4000 K	145 lm/W	10000 lm	69 W
911401595761	BY570P LED100/850 PSU HRO CAU	5000 K	145 lm/W	10000 lm	69 W
911401595861	BY570P LED100/840 PSU HRO CAU	4000 K	145 lm/W	10000 lm	69 W
911401595961	BY570P LED150/850 PSU WB CAU	5000 K	135 lm/W	15000 lm	111 W
911401596061	BY570P LED150/840 PSU WB CAU	4000 K	135 lm/W	15000 lm	111 W
911401596161	BY570P LED150/850 PSU HRO CAU	5000 K	135 lm/W	15000 lm	111 W
911401596261	BY570P LED150/840 PSU HRO CAU	4000 K	135 lm/W	15000 lm	111 W
911401597561	BY570P LED100/840 PSD WB CAU	4000 K	133 lm/W	10000 lm	75 W
911401597661	BY570P LED100/840 PSD HRO CAU	4000 K	133 lm/W	10000 lm	75 W
911401597761	BY570P LED150/840 PSD WB CAU	4000 K	126 lm/W	15000 lm	119 W
911401597861	BY570P LED150/840 PSD HRO CAU	4000 K	126 lm/W	15000 lm	119 W
911401598361	BY570P LED100/850 PSD WB CAU	5000 K	133 lm/W	10000 lm	75 W
911401598461	BY570P LED100/850 PSD HRO CAU	5000 K	133 lm/W	10000 lm	75 W
911401598561	BY570P LED150/850 PSD WB CAU	5000 K	126 lm/W	15000 lm	119 W
911401598661	BY570P LED150/850 PSD HRO CAU	5000 K	126 lm/W	15000 lm	119 W
911401599161	BY570P LED100/850 PSU NB CAU	5000 K	145 lm/W	10000 lm	69 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401599261	BY570P LED100/840 PSU NB CAU	4000 K	145 lm/W	10000 lm	69 W
911401599361	BY570P LED150/850 PSU NB CAU	5000 K	135 lm/W	15000 lm	111 W
911401599461	BY570P LED150/840 PSU NB CAU	4000 K	135 lm/W	15000 lm	111 W
911401599961	BY570P LED100/850 PSD NB CAU	5000 K	133 lm/W	10000 lm	75 W
911401500371	BY570P LED200/850 PSD NB CAU	5000 K	132 lm/W	20000 lm	152 W
911401500471	BY570P LED200/840 PSD NB CAU	4000 K	132 lm/W	20000 lm	152 W
911401586761	BY570P LED200/CW PSU WB GC	6500 K	139 lm/W	20000 lm	144 W
911401586861	BY570P LED200/NW PSU WB GC	4000 K	139 lm/W	20000 lm	144 W
911401586961	BY570P LED200/CW PSU HRO GC	6500 K	139 lm/W	20000 lm	144 W
911401587061	BY570P LED200/NW PSU HRO GC	4000 K	139 lm/W	20000 lm	144 W
911401587961	BY570P LED200/NW PSD WB GC	4000 K	132 lm/W	20000 lm	152 W
911401588061	BY570P LED200/NW PSD HRO GC	4000 K	132 lm/W	20000 lm	152 W
911401588761	BY570P LED200/CW PSD WB GC	6500 K	132 lm/W	20000 lm	152 W
911401588861	BY570P LED200/CW PSD HRO GC	6500 K	132 lm/W	20000 lm	152 W
911401589561	BY570P LED200/CW PSU NB GC	6500 K	139 lm/W	20000 lm	144 W
911401589661	BY570P LED200/NW PSU NB GC	4000 K	139 lm/W	20000 lm	144 W

## GreenPerform Highbay Rectangular

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401590361	BY570P LED200/CW PSD NB GC	6500 K	132 lm/W	20000 lm	152 W
911401590461	BY570P LED200/NW PSD NB GC	4000 K	132 lm/W	20000 lm	152 W
911401591561	BY570P LED200/CW PSU WB GM	6500 K	139 lm/W	20000 lm	144 W
911401591661	BY570P LED200/NW PSU WB GM	4000 K	139 lm/W	20000 lm	144 W
911401591761	BY570P LED200/CW PSU HRO GM	6500 K	139 lm/W	20000 lm	144 W
911401591861	BY570P LED200/NW PSU HRO GM	4000 K	139 lm/W	20000 lm	144 W
911401592761	BY570P LED200/NW PSD WB GM	4000 K	132 lm/W	20000 lm	152 W
911401592861	BY570P LED200/NW PSD HRO GM	4000 K	132 lm/W	20000 lm	152 W
911401593561	BY570P LED200/CW PSD WB GM	6500 K	132 lm/W	20000 lm	152 W
911401593661	BY570P LED200/CW PSD HRO GM	6500 K	132 lm/W	20000 lm	152 W
911401594361	BY570P LED200/CW PSU NB GM	6500 K	139 lm/W	20000 lm	144 W
911401594461	BY570P LED200/NW PSU NB GM	4000 K	139 lm/W	20000 lm	144 W
911401595161	BY570P LED200/CW PSD NB GM	6500 K	132 lm/W	20000 lm	152 W
911401595261	BY570P LED200/NW PSD NB GM	4000 K	132 lm/W	20000 lm	152 W
911401596361	BY570P LED200/850 PSU WB CAU	5000 K	139 lm/W	20000 lm	144 W
911401596461	BY570P LED200/840 PSU WB CAU	4000 K	139 lm/W	20000 lm	144 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401596561	BY570P LED200/865 PSU WB CAU CL	6500 K	139 lm/W	20000 lm	144 W
911401596661	BY570P LED200/840 PSU WB CAU CL	4000 K	139 lm/W	20000 lm	144 W
911401596761	BY570P LED200/850 PSU HRO CAU	5000 K	139 lm/W	20000 lm	144 W
911401596861	BY570P LED200/840 PSU HRO CAU	4000 K	139 lm/W	20000 lm	144 W
911401597961	BY570P LED200/840 PSD WB CAU	4000 K	132 lm/W	20000 lm	152 W
911401598061	BY570P LED200/840 PSD HRO CAU	4000 K	132 lm/W	20000 lm	152 W
911401598761	BY570P LED200/850 PSD WB CAU	5000 K	132 lm/W	20000 lm	152 W
911401598861	BY570P LED200/850 PSD HRO CAU	5000 K	132 lm/W	20000 lm	152 W
911401599561	BY570P LED200/850 PSU NB CAU	5000 K	139 lm/W	20000 lm	144 W
911401599661	BY570P LED200/840 PSU NB CAU	4000 K	139 lm/W	20000 lm	144 W
911401500571	BY570P LED250/850 PSD NB CAU	5000 K	128 lm/W	25000 lm	199 W
911401500671	BY570P LED250/840 PSD NB CAU	4000 K	128 lm/W	25000 lm	199 W
911401587161	BY570P LED250/CW PSU WB GC	6500 K	140 lm/W	25000 lm	182 W
911401587261	BY570P LED250/NW PSU WB GC	4000 K	140 lm/W	25000 lm	182 W
911401587361	BY570P LED250/CW PSU HRO GC	6500 K	140 lm/W	25000 lm	182 W
911401587461	BY570P LED250/NW PSU HRO GC	4000 K	140 lm/W	25000 lm	182 W

## GreenPerform Highbay Rectangular

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401588161	BY570P LED250/NW PSD WB GC	4000 K	128 lm/W	25000 lm	199 W
911401588261	BY570P LED250/NW PSD HRO GC	4000 K	128 lm/W	25000 lm	199 W
911401588961	BY570P LED250/CW PSD WB GC	6500 K	128 lm/W	25000 lm	199 W
911401589061	BY570P LED250/CW PSD HRO GC	6500 K	128 lm/W	25000 lm	199 W
911401589761	BY570P LED250/CW PSU NB GC	6500 K	140 lm/W	25000 lm	182 W
911401589861	BY570P LED250/NW PSU NB GC	4000 K	140 lm/W	25000 lm	182 W
911401590561	BY570P LED250/CW PSD NB GC	6500 K	128 lm/W	25000 lm	199 W
911401590661	BY570P LED250/NW PSD NB GC	4000 K	128 lm/W	25000 lm	199 W
911401591961	BY570P LED250/CW PSU WB GM	6500 K	140 lm/W	25000 lm	182 W
911401592061	BY570P LED250/NW PSU WB GM	4000 K	140 lm/W	25000 lm	182 W
911401592161	BY570P LED250/CW PSU HRO GM	6500 K	140 lm/W	25000 lm	182 W
911401592261	BY570P LED250/NW PSU HRO GM	4000 K	140 lm/W	25000 lm	182 W
911401592961	BY570P LED250/NW PSD WB GM	4000 K	128 lm/W	25000 lm	199 W
911401593061	BY570P LED250/NW PSD HRO GM	4000 K	128 lm/W	25000 lm	199 W
911401593761	BY570P LED250/CW PSD WB GM	6500 K	128 lm/W	25000 lm	199 W
911401593861	BY570P LED250/CW PSD HRO GM	6500 K	128 lm/W	25000 lm	199 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401594561	BY570P LED250/CW PSU NB GM	6500 K	140 lm/W	25000 lm	182 W
911401594661	BY570P LED250/NW PSU NB GM	4000 K	140 lm/W	25000 lm	182 W
911401595361	BY570P LED250/CW PSD NB GM	6500 K	128 lm/W	25000 lm	199 W
911401595461	BY570P LED250/NW PSD NB GM	4000 K	128 lm/W	25000 lm	199 W
911401596961	BY570P LED250/850 PSU WB CAU	5000 K	140 lm/W	25000 lm	182 W
911401597061	BY570P LED250/840 PSU WB CAU	4000 K	140 lm/W	25000 lm	182 W
911401597161	BY570P LED250/865 PSU WB CAU CL	6500 K	140 lm/W	25000 lm	182 W
911401597261	BY570P LED250/840 PSU WB CAU CL	4000 K	140 lm/W	25000 lm	182 W
911401597361	BY570P LED250/850 PSU HRO CAU	5000 K	140 lm/W	25000 lm	182 W
911401597461	BY570P LED250/840 PSU HRO CAU	4000 K	140 lm/W	25000 lm	182 W
911401598161	BY570P LED250/840 PSD WB CAU	4000 K	128 lm/W	25000 lm	199 W
911401598261	BY570P LED250/840 PSD HRO CAU	4000 K	128 lm/W	25000 lm	199 W
911401598961	BY570P LED250/850 PSD WB CAU	5000 K	128 lm/W	25000 lm	199 W
911401599061	BY570P LED250/850 PSD HRO CAU	5000 K	128 lm/W	25000 lm	199 W
911401599761	BY570P LED250/850 PSU NB CAU	5000 K	140 lm/W	25000 lm	182 W
911401599861	BY570P LED250/840 PSU NB CAU	4000 K	140 lm/W	25000 lm	182 W

## GreenPerform Highbay Rectangular

