



# The flood Tango light that brightens your world

## Tango G4 LED Flood

Philips Tango G4 LED Floodlight is the 4th generation of the Tango LED family. A new range lighting that delivers higher efficacy and has an optimized windage area, and less weight thanks to its technical design. This product introduction is the ideal solution for a wide range of area lighting and recreational sports lighting applications. It incorporates the latest LED light source, one-piece optical system, heat sink and driver into a compact and robust housing that meets globally-recognized safety standards. Its specially-designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, Tango G4 LED floodlights deliver superior performance and a longer lifetime, bringing area lighting to a whole new level.

### Benefits

- Saves 10% more energy than Tango G3
- Covers a wide range of applications
- Optimized design: 23% less weight and 35% less windage area (size) than Tango Gen3
- Create a brighter, energetic, and safer environment
- Robust and reliable design.

# Tango G4 LED Flood

## Features

- Higher system efficacy with typical 140lm/W
- Full range of lumen packages to cover multiple flood, area, and sport lighting applications.
- Multiple optic options for flexible lighting design
- High quality ADC1 diecast aluminum housing and steel bracket.
- High reliability: housing tested to ISO 9227 Salt Spray Fog Standard (small and medium housing 500 hours, large housing 1000 hours)
- Overall luminaire is rated for IP66 and IK08 protection.
- 10kV or 15kV Surge protection Device

## Application

- General flood lighting
- Large industrial areas / Car Park Areas
- Billboard
- Airport Apron
- Port & Container Yard
- Building facades
- Transportation Terminals & Tollways
- Recreational Sports Stadium

## Warnings and Safety

- please pay attention to the mounting instructions

## Versions



Tango G4,Flood



BVP49X



BVP49X



BVP49X



Tango G4,Flood



# Tango G4 LED Flood

## Approval and application

Mech. impact protection code IK08

## General information

CE mark CE mark

Driver included Yes

## Initial performance (IEC compliant)

Init. Color Rendering Index >70

## Controls and dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401600007	BVP433 LED418/NW 220~240V 305W NB GC	No	911401604307	BVP433 LED460/CW 220~240V 345W AMB GM	No
911401600107	BVP433 LED418/NW 220~240V 305W S6 GC	No	911401604407	BVP433 LED430/CW 220~240V 345W SAWB GM	No
911401600207	BVP433 LED413/CW 220~240V 305W SMB GC	No	911401604507	BVP433 LED470/CW 220~240V 345W NB GM	No
911401600307	BVP433 LED413/CW 220~240V 305W SWB GC	No	911401604607	BVP433 LED470/CW 220~240V 345W S6 GM	No
911401600407	BVP433 LED409/CW 220~240V 305W AMB GC	No	911401605007	BVP433 LED517/NW 220~240V 380W SMB GC	No
911401600507	BVP433 LED382/CW 220~240V 305W SAWB GC	No	911401605107	BVP433 LED517/NW 220~240V 380W SWB GC	No
911401600607	BVP433 LED418/CW 220~240V 305W NB GC	No	911401605207	BVP433 LED511/NW 220~240V 380W AMB GC	No
911401600707	BVP433 LED418/CW 220~240V 305W S6 GC	No	911401605307	BVP433 LED477/NW 220~240V 380W SAWB GC	No
911401600907	BVP433 LED413/NW 220~240V 305W SMB GM	No	911401605407	BVP433 LED522/NW 220~240V 380W NB GC	No
911401601007	BVP433 LED413/NW 220~240V 305W SWB GM	No	911401605507	BVP433 LED522/NW 220~240V 380W S6 GC	No
911401601107	BVP433 LED409/NW 220~240V 305W AMB GM	No	911401605607	BVP433 LED517/CW 220~240V 380W SMB GC	No
911401601207	BVP433 LED382/NW 220~240V 305W SAWB GM	No	911401605707	BVP433 LED517/CW 220~240V 380W SWB GC	No
911401601307	BVP433 LED418/NW 220~240V 305W NB GM	No	911401605807	BVP433 LED511/CW 220~240V 380W AMB GC	No
911401601407	BVP433 LED418/NW 220~240V 305W S6 GM	No	911401605907	BVP433 LED477/CW 220~240V 380W SAWB GC	No
911401601507	BVP433 LED413/CW 220~240V 305W SMB GM	No	911401606007	BVP433 LED522/CW 220~240V 380W NB GC	No
911401601607	BVP433 LED413/CW 220~240V 305W SWB GM	No	911401606107	BVP433 LED522/CW 220~240V 380W S6 GC	No
911401601707	BVP433 LED409/CW 220~240V 305W AMB GM	No	911401606507	BVP433 LED517/NW 220~240V 380W SMB GM	No
911401601807	BVP433 LED382/CW 220~240V 305W SAWB GM	No	911401606607	BVP433 LED517/NW 220~240V 380W SWB GM	No
911401601907	BVP433 LED418/CW 220~240V 305W NB GM	No	911401606707	BVP433 LED511/NW 220~240V 380W AMB GM	No
911401602007	BVP433 LED418/CW 220~240V 305W S6 GM	No	911401606807	BVP433 LED477/NW 220~240V 380W SAWB GM	No
911401602207	BVP433 LED465/NW 220~240V 345W SMB GC	No	911401606907	BVP433 LED522/NW 220~240V 380W NB GM	No
911401602307	BVP433 LED465/NW 220~240V 345W SWB GC	No	911401607007	BVP433 LED522/NW 220~240V 380W S6 GM	No
911401602407	BVP433 LED460/NW 220~240V 345W AMB GC	No	911401607107	BVP433 LED517/CW 220~240V 380W SMB GM	No
911401602507	BVP433 LED430/NW 220~240V 345W SAWB GC	No	911401607207	BVP433 LED517/CW 220~240V 380W SWB GM	No
911401602607	BVP433 LED470/NW 220~240V 345W NB GC	No	911401607307	BVP433 LED511/CW 220~240V 380W AMB GM	No
911401602707	BVP433 LED470/NW 220~240V 345W S6 GC	No	911401607407	BVP433 LED477/CW 220~240V 380W SAWB GM	No
911401602807	BVP433 LED465/CW 220~240V 345W SMB GC	No	911401607507	BVP433 LED522/CW 220~240V 380W NB GM	No
911401602907	BVP433 LED465/CW 220~240V 345W SWB GC	No	911401607607	BVP433 LED522/CW 220~240V 380W S6 GM	No
911401603007	BVP433 LED460/CW 220~240V 345W AMB GC	No	911401607807	BVP433 LED359/NW 300W SAWB CM GC	No
911401603107	BVP433 LED430/CW 220~240V 345W SAWB GC	No	911401607907	BVP433 LED384/CW 300W AMB CM GM	No
911401603207	BVP433 LED470/CW 220~240V 345W NB GC	No	911401694306	BVP433 LED310/NW 220~240V 230W SWB GC	No
911401603307	BVP433 LED470/CW 220~240V 345W S6 GC	No	911401694406	BVP433 LED307/NW 220~240V 230W AMB GC	No
911401603507	BVP433 LED465/NW 220~240V 345W SMB GM	No	911401694506	BVP433 LED286/NW 220~240V 230W SAWB GC	No
911401603607	BVP433 LED465/NW 220~240V 345W SWB GM	No	911401694606	BVP433 LED313/NW 220~240V 230W NB GC	No
911401603707	BVP433 LED460/NW 220~240V 345W AMB GM	No	911401694706	BVP433 LED313/NW 220~240V 230W S6 GC	No
911401603807	BVP433 LED430/NW 220~240V 345W SAWB GM	No	911401694806	BVP433 LED310/CW 220~240V 230W SMB GC	No
911401603907	BVP433 LED470/NW 220~240V 345W NB GM	No	911401694906	BVP433 LED310/CW 220~240V 230W SWB GC	No
911401604007	BVP433 LED470/NW 220~240V 345W S6 GM	No	911401695006	BVP433 LED307/CW 220~240V 230W AMB GC	No
911401604107	BVP433 LED465/CW 220~240V 345W SMB GM	No	911401695106	BVP433 LED286/CW 220~240V 230W SAWB GC	No
911401604207	BVP433 LED465/CW 220~240V 345W SWB GM	No	911401695206	BVP433 LED313/CW 220~240V 230W NB GC	No

## Tango G4 LED Flood

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401695306	BVP433 LED313/CW 220~240V 230W S6 GC	No	911401659307	BVP491 LED93/NW 70W SWB LP	No
911401695506	BVP433 LED310/NW 220~240V 230W SMB GM	No	911401659407	BVP491 LED112/NW 85W SWB LP	No
911401695606	BVP433 LED310/NW 220~240V 230W SWB GM	No	911401659507	BVP491 LED136/NW 100W SWB LP	No
911401695706	BVP433 LED307/NW 220~240V 230W AMB GM	No	911401659607	BVP491 LED68/NW 50W SWB LP P7	Yes
911401695806	BVP433 LED286/NW 220~240V 230W SAWB GM	No	911401659707	BVP491 LED93/NW 70W SWB LP P7	Yes
911401695906	BVP433 LED313/NW 220~240V 230W NB GM	No	911401659807	BVP491 LED112/NW 85W SWB LP P7	Yes
911401696006	BVP433 LED313/NW 220~240V 230W S6 GM	No	911401659907	BVP491 LED136/NW 100W SWB LP P7	Yes
911401696106	BVP433 LED310/CW 220~240V 230W SMB GM	No	911401660007	BVP491 LED68/NW 50W SWB FP DALI/CM	Yes
911401696206	BVP433 LED310/CW 220~240V 230W SWB GM	No	911401660107	BVP491 LED93/NW 70W SWB FP DALI/CM	Yes
911401696306	BVP433 LED307/CW 220~240V 230W AMB GM	No	911401660207	BVP491 LED112/NW 85W SWB FP DALI/CM	Yes
911401696406	BVP433 LED286/CW 220~240V 230W SAWB GM	No	911401660307	BVP491 LED136/NW 100W SWB FP DALI/CM	Yes
911401696506	BVP433 LED313/CW 220~240V 230W NB GM	No	911401660407	BVP491 LED66/CW 50W AMB FP DALI/CM P7	Yes
911401696606	BVP433 LED313/CW 220~240V 230W S6 GM	No	911401660507	BVP491 LED90/CW 70W AMB FP DALI/CM P7	Yes
911401696906	BVP433 LED344/NW 220~240V 255W SMB GC	No	911401660607	BVP491 LED108/CW 85W AMB FP DALI/CM P7	Yes
911401697006	BVP433 LED344/NW 220~240V 255W SWB GC	No	911401660707	BVP491 LED132/CW 100W AMB FP DALI/CM P7	Yes
911401697106	BVP433 LED341/NW 220~240V 255W AMB GC	No	911401660807	BVP491 LED66/CW 50W AMB SR	Yes
911401697206	BVP433 LED318/NW 220~240V 255W SAWB GC	No	911401660907	BVP491 LED90/CW 70W AMB SR	Yes
911401697306	BVP433 LED348/NW 220~240V 255W NB GC	No	911401661007	BVP491 LED108/CW 85W AMB SR	Yes
911401697406	BVP433 LED348/NW 220~240V 255W S6 GC	No	911401661107	BVP491 LED132/CW 100W AMB SR	Yes
911401697506	BVP433 LED344/CW 220~240V 255W SMB GC	No	911401661207	BVP492 LED144/WW 120W AMB	No
911401697606	BVP433 LED344/CW 220~240V 255W SWB GC	No	911401661307	BVP492 LED166/WW 135W AMB	No
911401697706	BVP433 LED341/CW 220~240V 255W AMB GC	No	911401661407	BVP492 LED183/WW 150W AMB	No
911401697806	BVP433 LED318/CW 220~240V 255W SAWB GC	No	911401661507	BVP492 LED200/WW 165W AMB	No
911401697906	BVP433 LED348/CW 220~240V 255W NB GC	No	911401661607	BVP492 LED222/WW 180W AMB	No
911401698006	BVP433 LED348/CW 220~240V 255W S6 GC	No	911401661707	BVP492 LED244/WW 200W AMB	No
911401698306	BVP433 LED344/NW 220~240V 255W SMB GM	No	911401661807	BVP492 LED157/CW 120W SMB 1-10V	Yes
911401698406	BVP433 LED344/NW 220~240V 255W SWB GM	No	911401661907	BVP492 LED181/CW 135W SMB 1-10V	Yes
911401698506	BVP433 LED341/NW 220~240V 255W AMB GM	No	911401662007	BVP492 LED200/CW 150W SMB 1-10V	Yes
911401698606	BVP433 LED318/NW 220~240V 255W SAWB GM	No	911401662107	BVP492 LED218/CW 165W SMB 1-10V	Yes
911401698706	BVP433 LED348/NW 220~240V 255W NB GM	No	911401662207	BVP492 LED242/CW 180W SMB 1-10V	Yes
911401698806	BVP433 LED348/NW 220~240V 255W S6 GM	No	911401662307	BVP492 LED266/CW 200W SMB 1-10V	Yes
911401698906	BVP433 LED344/CW 220~240V 255W SMB GM	No	911401662407	BVP492 LED159/NW 120W SWB 1-10V P7	Yes
911401699006	BVP433 LED344/CW 220~240V 255W SWB GM	No	911401662507	BVP492 LED183/NW 135W SWB 1-10V P7	Yes
911401699106	BVP433 LED341/CW 220~240V 255W AMB GM	No	911401662607	BVP492 LED201/NW 150W SWB 1-10V P7	Yes
911401699206	BVP433 LED318/CW 220~240V 255W SAWB GM	No	911401662707	BVP492 LED219/NW 165W SWB 1-10V P7	Yes
911401699306	BVP433 LED348/CW 220~240V 255W NB GM	No	911401662807	BVP492 LED244/NW 180W SWB 1-10V P7	Yes
911401699406	BVP433 LED348/CW 220~240V 255W S6 GM	No	911401662907	BVP492 LED268/NW 200W SWB 1-10V P7	Yes
911401699606	BVP433 LED413/NW 220~240V 305W SMB GC	No	911401663007	BVP492 LED144/WW 120W AMB LP	Yes
911401699706	BVP433 LED413/NW 220~240V 305W SWB GC	No	911401663107	BVP492 LED166/WW 135W AMB LP	Yes
911401699806	BVP433 LED409/NW 220~240V 305W AMB GC	No	911401663207	BVP492 LED183/WW 150W AMB LP	Yes
911401699906	BVP433 LED382/NW 220~240V 305W SAWB GC	No	911401663307	BVP492 LED200/WW 165W AMB LP	Yes
911401658207	BVP491 LED68/NW 50W SWB	No	911401663407	BVP492 LED222/WW 180W AMB LP	Yes
911401658307	BVP491 LED93/NW 70W SWB	No	911401663507	BVP492 LED244/WW 200W AMB LP	Yes
911401658407	BVP491 LED112/NW 85W SWB	No	911401663607	BVP492 LED157/CW 120W SMB LP P7	Yes
911401658507	BVP491 LED136/NW 100W SWB	No	911401663707	BVP492 LED181/CW 135W SMB LP P7	Yes
911401658607	BVP491 LED90/CW 70W AMB 1-10V	Yes	911401663807	BVP492 LED200/CW 150W SMB LP P7	Yes
911401658707	BVP491 LED108/CW 85W AMB 1-10V	Yes	911401663907	BVP492 LED218/CW 165W SMB LP P7	Yes
911401658807	BVP491 LED132/CW 100W AMB 1-10V	Yes	911401664007	BVP492 LED242/CW 180W SMB LP P7	Yes
911401658907	BVP491 LED87/WW 70W SMB 1-10V P7	Yes	911401664107	BVP492 LED266/CW 200W SMB LP P7	Yes
911401659007	BVP491 LED104/WW 85W SMB 1-10V P7	Yes	911401664207	BVP492 LED157/CW 120W SMB FP DALI/CM	Yes
911401659107	BVP491 LED127/WW 100W SMB 1-10V P7	Yes	911401664307	BVP492 LED181/CW 135W SMB FP DALI/CM	Yes
911401659207	BVP491 LED68/NW 50W SWB LP	No	911401664407	BVP492 LED200/CW 150W SMB FP DALI/CM	Yes

## Tango G4 LED Flood

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401664507	BVP492 LED157/CW 120W SMB FP DALI/CM P7	Yes	911401680606	BVP431 LED92/CW 220~240V 70W SMB GC	No
911401664607	BVP492 LED181/CW 135W SMB FP DALI/CM P7	Yes	911401680706	BVP431 LED92/CW 220~240V 70W SWB GC	No
911401664707	BVP492 LED200/CW 150W SMB FP DALI/CM P7	Yes	911401680806	BVP431 LED91/CW 220~240V 70W AMB GC	No
911401664807	BVP492 LED157/CW 120W SMB SR	Yes	911401681206	BVP431 LED92/NW 220~240V 70W SMB GM	No
911401664907	BVP492 LED181/CW 140W SMB SR	Yes	911401681306	BVP431 LED92/NW 220~240V 70W SWB GM	No
911401665007	BVP492 LED200/CW 150W SMB SR	Yes	911401681406	BVP431 LED91/NW 220~240V 70W AMB GM	No
911401665107	BVP493 LED261/WW 230W SAWB	No	911401681506	BVP431 LED92/CW 220~240V 70W SMB GM	No
911401665207	BVP493 LED341/NW 255W SWB	No	911401681606	BVP431 LED92/CW 220~240V 70W SWB GM	No
911401665307	BVP493 LED388/WW 305W NB	No	911401681706	BVP431 LED91/CW 220~240V 70W AMB GM	No
911401665407	BVP493 LED460/CW 345W SWB	No	911401681806	BVP431 LED92/NW 70W SWB ANZ CL	No
911401665507	BVP493 LED485/WW 380W NB	No	911401682206	BVP431 LED136/NW 220~240V 100W SMB GC	No
911401665607	BVP493 LED261/WW 230W SAWB 1-10V	Yes	911401682306	BVP431 LED136/NW 220~240V 100W SWB GC	No
911401665707	BVP493 LED341/NW 255W SWB 1-10V	Yes	911401682406	BVP431 LED134/NW 220~240V 100W AMB GC	No
911401665807	BVP493 LED388/WW 305W NB 1-10V	Yes	911401682506	BVP431 LED135/CW 220~240V 100W SMB GC	No
911401665907	BVP493 LED460/CW 345W SWB 1-10V	Yes	911401682606	BVP431 LED135/CW 220~240V 100W SWB GC	No
911401666007	BVP493 LED485/WW 380W NB 1-10V	Yes	911401682706	BVP431 LED133/CW 220~240V 100W AMB GC	No
911401666107	BVP493 LED261/WW 230W SAWB 1-10V P7	Yes	911401683206	BVP431 LED136/NW 220~240V 100W SWB GM	No
911401666207	BVP493 LED341/NW 255W SWB 1-10V P7	Yes	911401683306	BVP431 LED134/NW 220~240V 100W AMB GM	No
911401666307	BVP493 LED388/WW 305W NB 1-10V P7	Yes	911401683406	BVP431 LED135/CW 220~240V 100W SMB GM	No
911401666407	BVP493 LED460/CW 345W SWB 1-10V P7	Yes	911401683506	BVP431 LED135/CW 220~240V 100W SWB GM	No
911401666507	BVP493 LED485/WW 380W NB 1-10V P7	Yes	911401683606	BVP431 LED133/CW 220~240V 100W AMB GM	No
911401666607	BVP493 LED261/WW 230W SAWB LP	Yes	911401683706	BVP431 LED136/NW 100W SWB ANZ CL	No
911401666707	BVP493 LED341/NW 255W SWB LP	Yes	911401683906	BVP431 LED134/NW 100W AMB CM GC	No
911401666807	BVP493 LED388/WW 310W NB LP	Yes	911401684006	BVP431 LED133/CW 100W AMB CM GM	No
911401666907	BVP493 LED460/CW 350W SWB LP	Yes	911401686906	BVP432 LED161/CW 220~240V 120W SWB GC	No
911401667007	BVP493 LED485/WW 380W NB LP	Yes	911401687606	BVP432 LED161/CW 220~240V 120W SWB GM	No
911401667207	BVP493 LED261/WW 230W SAWB LP P7	Yes	911401688506	BVP432 LED204/CW 220~240V 150W SWB GC	No
911401667307	BVP493 LED341/NW 255W SWB LP P7	Yes	911401688606	BVP432 LED202/CW 220~240V 150W AMB GC	No
911401667407	BVP493 LED388/WW 310W NB LP P7	Yes	911401689006	BVP432 LED206/NW 220~240V 150W SMB GM	No
911401667507	BVP493 LED460/CW 350W SWB LP P7	Yes	911401689106	BVP432 LED206/NW 220~240V 150W SWB GM	No
911401667607	BVP493 LED485/WW 380W NB LP P7	Yes	911401689206	BVP432 LED203/NW 220~240V 150W AMB GM	No
911401667807	BVP493 LED261/WW 230W SAWB FP DALI/CM	Yes	911401689306	BVP432 LED204/CW 220~240V 150W SMB GM	No
911401667907	BVP493 LED341/NW 260W SWB FP DALI/CM	Yes	911401689406	BVP432 LED204/CW 220~240V 150W SWB GM	No
911401668007	BVP493 LED370/WW 300W NB FP DALI/CM	Yes	911401689506	BVP432 LED202/CW 220~240V 150W AMB GM	No
911401668107	BVP493 LED261/WW 230W SAWB FP DALI/CM P7	Yes	911401689906	BVP432 LED274/NW 220~240V 200W SMB GC	No
911401668207	BVP493 LED341/NW 260W SWB FP DALI/CM P7	Yes	911401690006	BVP432 LED274/NW 220~240V 200W SWB GC	No
911401668307	BVP493 LED370/WW 300W NB FP DALI/CM P7	Yes	911401690106	BVP432 LED271/NW 220~240V 200W AMB GC	No
911401668407	BVP493 LED261/WW 230W SAWB SR	Yes	911401690206	BVP432 LED272/CW 220~240V 200W SMB GC	No
911401668507	BVP493 LED341/NW 260W SWB SR	Yes	911401690306	BVP432 LED272/CW 220~240V 200W SWB GC	No
911401668607	BVP493 LED370/WW 295W NB SR	Yes	911401690406	BVP432 LED269/CW 220~240V 200W AMB GC	No
911401678706	BVP431 LED68/NW 220~240V 50W SMB GC	No	911401690806	BVP432 LED274/NW 220~240V 200W SMB GM	No
911401678806	BVP431 LED68/NW 220~240V 50W SWB GC	No	911401690906	BVP432 LED274/NW 220~240V 200W SWB GM	No
911401678906	BVP431 LED67/NW 220~240V 50W AMB GC	No	911401691006	BVP432 LED271/NW 220~240V 200W AMB GM	No
911401679406	BVP431 LED68/NW 220~240V 50W SMB GM	No	911401691106	BVP432 LED272/CW 220~240V 200W SMB GM	No
911401679506	BVP431 LED68/NW 220~240V 50W SWB GM	No	911401691206	BVP432 LED272/CW 220~240V 200W SWB GM	No
911401679606	BVP431 LED67/NW 220~240V 50W AMB GM	No	911401691306	BVP432 LED269/CW 220~240V 200W AMB GM	No
911401680306	BVP431 LED92/NW 220~240V 70W SMB GC	No	911401691406	BVP432 LED274/NW 200W SWB ANZ CL	No
911401680406	BVP431 LED92/NW 220~240V 70W SWB GC	No	911401691606	BVP432 LED203/NW 150W AMB CM GC	No
911401680506	BVP431 LED91/NW 220~240V 70W AMB GC	No	911401691706	BVP432 LED202/CW 150W AMB CM GM	No

### General information

## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401600007	BVP433 LED418/NW 220~240V 305W NB GC	740 neutral white	Polycarbonate bowl/cover	-
911401600107	BVP433 LED418/NW 220~240V 305W S6 GC	740 neutral white	Polycarbonate bowl/cover	-
911401600207	BVP433 LED413/CW 220~240V 305W SMB GC	757 cool white	Polycarbonate bowl/cover	-
911401600307	BVP433 LED413/CW 220~240V 305W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401600407	BVP433 LED409/CW 220~240V 305W AMB GC	757 cool white	Polycarbonate bowl/cover	-
911401600507	BVP433 LED382/CW 220~240V 305W SAWB GC	757 cool white	Polycarbonate bowl/cover	-
911401600607	BVP433 LED418/CW 220~240V 305W NB GC	757 cool white	Polycarbonate bowl/cover	-
911401600707	BVP433 LED418/CW 220~240V 305W S6 GC	757 cool white	Polycarbonate bowl/cover	-
911401600907	BVP433 LED413/NW 220~240V 305W SMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401601007	BVP433 LED413/NW 220~240V 305W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401601107	BVP433 LED409/NW 220~240V 305W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401601207	BVP433 LED382/NW 220~240V 305W SAWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401601307	BVP433 LED418/NW 220~240V 305W NB GM	740 neutral white	Polycarbonate bowl/cover	-
911401601407	BVP433 LED418/NW 220~240V 305W S6 GM	740 neutral white	Polycarbonate bowl/cover	-
911401601507	BVP433 LED413/CW 220~240V 305W SMB GM	757 cool white	Polycarbonate bowl/cover	-
911401601607	BVP433 LED413/CW 220~240V 305W SWB GM	757 cool white	Polycarbonate bowl/cover	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401601707	BVP433 LED409/CW 220~240V 305W AMB GM	757 cool white	Polycarbonate bowl/cover	-
911401601807	BVP433 LED382/CW 220~240V 305W SAWB GM	757 cool white	Polycarbonate bowl/cover	-
911401601907	BVP433 LED418/CW 220~240V 305W NB GM	757 cool white	Polycarbonate bowl/cover	-
911401602007	BVP433 LED418/CW 220~240V 305W S6 GM	757 cool white	Polycarbonate bowl/cover	-
911401602207	BVP433 LED465/NW 220~240V 345W SMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401602307	BVP433 LED465/NW 220~240V 345W SWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401602407	BVP433 LED460/NW 220~240V 345W AMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401602507	BVP433 LED430/NW 220~240V 345W SAWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401602607	BVP433 LED470/NW 220~240V 345W NB GC	740 neutral white	Polycarbonate bowl/cover	-
911401602707	BVP433 LED470/NW 220~240V 345W S6 GC	740 neutral white	Polycarbonate bowl/cover	-
911401602807	BVP433 LED465/CW 220~240V 345W SMB GC	757 cool white	Polycarbonate bowl/cover	-
911401602907	BVP433 LED465/CW 220~240V 345W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401603007	BVP433 LED460/CW 220~240V 345W AMB GC	757 cool white	Polycarbonate bowl/cover	-
911401603107	BVP433 LED430/CW 220~240V 345W SAWB GC	757 cool white	Polycarbonate bowl/cover	-
911401603207	BVP433 LED470/CW 220~240V 345W NB GC	757 cool white	Polycarbonate bowl/cover	-
911401603307	BVP433 LED470/CW 220~240V 345W S6 GC	757 cool white	Polycarbonate bowl/cover	-

## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401603507	BVP433 LED465/NW 220~240V 345W SMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401603607	BVP433 LED465/NW 220~240V 345W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401603707	BVP433 LED460/NW 220~240V 345W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401603807	BVP433 LED430/NW 220~240V 345W SAWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401603907	BVP433 LED470/NW 220~240V 345W NB GM	740 neutral white	Polycarbonate bowl/cover	-
911401604007	BVP433 LED470/NW 220~240V 345W S6 GM	740 neutral white	Polycarbonate bowl/cover	-
911401604107	BVP433 LED465/CW 220~240V 345W SMB GM	757 cool white	Polycarbonate bowl/cover	-
911401604207	BVP433 LED465/CW 220~240V 345W SWB GM	757 cool white	Polycarbonate bowl/cover	-
911401604307	BVP433 LED460/CW 220~240V 345W AMB GM	757 cool white	Polycarbonate bowl/cover	-
911401604407	BVP433 LED430/CW 220~240V 345W SAWB GM	757 cool white	Polycarbonate bowl/cover	-
911401604507	BVP433 LED470/CW 220~240V 345W NB GM	757 cool white	Polycarbonate bowl/cover	-
911401604607	BVP433 LED470/CW 220~240V 345W S6 GM	757 cool white	Polycarbonate bowl/cover	-
911401605007	BVP433 LED517/NW 220~240V 380W SMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401605107	BVP433 LED517/NW 220~240V 380W SWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401605207	BVP433 LED511/NW 220~240V 380W AMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401605307	BVP433 LED477/NW 220~240V 380W SAWB GC	740 neutral white	Polycarbonate bowl/cover	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401605407	BVP433 LED522/NW 220~240V 380W NB GC	740 neutral white	Polycarbonate bowl/cover	-
911401605507	BVP433 LED522/NW 220~240V 380W S6 GC	740 neutral white	Polycarbonate bowl/cover	-
911401605607	BVP433 LED517/CW 220~240V 380W SMB GC	757 cool white	Polycarbonate bowl/cover	-
911401605707	BVP433 LED517/CW 220~240V 380W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401605807	BVP433 LED511/CW 220~240V 380W AMB GC	757 cool white	Polycarbonate bowl/cover	-
911401605907	BVP433 LED477/CW 220~240V 380W SAWB GC	757 cool white	Polycarbonate bowl/cover	-
911401606007	BVP433 LED522/CW 220~240V 380W NB GC	757 cool white	Polycarbonate bowl/cover	-
911401606107	BVP433 LED522/CW 220~240V 380W S6 GC	757 cool white	Polycarbonate bowl/cover	-
911401606507	BVP433 LED517/NW 220~240V 380W SMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401606607	BVP433 LED517/NW 220~240V 380W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401606707	BVP433 LED511/NW 220~240V 380W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401606807	BVP433 LED477/NW 220~240V 380W SAWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401606907	BVP433 LED522/NW 220~240V 380W NB GM	740 neutral white	Polycarbonate bowl/cover	-
911401607007	BVP433 LED522/NW 220~240V 380W S6 GM	740 neutral white	Polycarbonate bowl/cover	-
911401607107	BVP433 LED517/CW 220~240V 380W SMB GM	757 cool white	Polycarbonate bowl/cover	-
911401607207	BVP433 LED517/CW 220~240V 380W SWB GM	757 cool white	Polycarbonate bowl/cover	-

## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401607307	BVP433 LED511/CW 220~240V 380W AMB GM	757 cool white	Polycarbonate bowl/cover	-
911401607407	BVP433 LED477/CW 220~240V 380W SAWB GM	757 cool white	Polycarbonate bowl/cover	-
911401607507	BVP433 LED522/CW 220~240V 380W NB GM	757 cool white	Polycarbonate bowl/cover	-
911401607607	BVP433 LED522/CW 220~240V 380W S6 GM	757 cool white	Polycarbonate bowl/cover	-
911401607807	BVP433 LED359/NW 300W SAWB CM GC	740 neutral white	Polycarbonate bowl/cover	-
911401607907	BVP433 LED384/CW 300W AMB CM GM	757 cool white	Polycarbonate bowl/cover	-
911401694306	BVP433 LED310/NW 220~240V 230W SWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401694406	BVP433 LED307/NW 220~240V 230W AMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401694506	BVP433 LED286/NW 220~240V 230W SAWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401694606	BVP433 LED313/NW 220~240V 230W NB GC	740 neutral white	Polycarbonate bowl/cover	-
911401694706	BVP433 LED313/NW 220~240V 230W S6 GC	740 neutral white	Polycarbonate bowl/cover	-
911401694806	BVP433 LED310/CW 220~240V 230W SMB GC	757 cool white	Polycarbonate bowl/cover	-
911401694906	BVP433 LED310/CW 220~240V 230W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401695006	BVP433 LED307/CW 220~240V 230W AMB GC	757 cool white	Polycarbonate bowl/cover	-
911401695106	BVP433 LED286/CW 220~240V 230W SAWB GC	757 cool white	Polycarbonate bowl/cover	-
911401695206	BVP433 LED313/CW 220~240V 230W NB GC	757 cool white	Polycarbonate bowl/cover	-
911401695306	BVP433 LED313/CW 220~240V 230W S6 GC	757 cool white	Polycarbonate bowl/cover	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401695506	BVP433 LED310/NW 220~240V 230W SMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401695606	BVP433 LED310/NW 220~240V 230W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401695706	BVP433 LED307/NW 220~240V 230W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401695806	BVP433 LED286/NW 220~240V 230W SAWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401695906	BVP433 LED313/NW 220~240V 230W NB GM	740 neutral white	Polycarbonate bowl/cover	-
911401696006	BVP433 LED313/NW 220~240V 230W S6 GM	740 neutral white	Polycarbonate bowl/cover	-
911401696106	BVP433 LED310/CW 220~240V 230W SMB GM	757 cool white	Polycarbonate bowl/cover	-
911401696206	BVP433 LED310/CW 220~240V 230W SWB GM	757 cool white	Polycarbonate bowl/cover	-
911401696306	BVP433 LED307/CW 220~240V 230W AMB GM	757 cool white	Polycarbonate bowl/cover	-
911401696406	BVP433 LED286/CW 220~240V 230W SAWB GM	757 cool white	Polycarbonate bowl/cover	-
911401696506	BVP433 LED313/CW 220~240V 230W NB GM	757 cool white	Polycarbonate bowl/cover	-
911401696606	BVP433 LED313/CW 220~240V 230W S6 GM	757 cool white	Polycarbonate bowl/cover	-
911401696906	BVP433 LED344/NW 220~240V 255W SMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401697006	BVP433 LED344/NW 220~240V 255W SWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401697106	BVP433 LED341/NW 220~240V 255W AMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401697206	BVP433 LED318/NW 220~240V 255W SAWB GC	740 neutral white	Polycarbonate bowl/cover	-



## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401697306	BVP433 LED348/NW 220~240V 255W NB GC	740 neutral white	Polycarbonate bowl/cover	-
911401697406	BVP433 LED348/NW 220~240V 255W S6 GC	740 neutral white	Polycarbonate bowl/cover	-
911401697506	BVP433 LED344/CW 220~240V 255W SMB GC	757 cool white	Polycarbonate bowl/cover	-
911401697606	BVP433 LED344/CW 220~240V 255W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401697706	BVP433 LED341/CW 220~240V 255W AMB GC	757 cool white	Polycarbonate bowl/cover	-
911401697806	BVP433 LED318/CW 220~240V 255W SAWB GC	757 cool white	Polycarbonate bowl/cover	-
911401697906	BVP433 LED348/CW 220~240V 255W NB GC	757 cool white	Polycarbonate bowl/cover	-
911401698006	BVP433 LED348/CW 220~240V 255W S6 GC	757 cool white	Polycarbonate bowl/cover	-
911401698306	BVP433 LED344/NW 220~240V 255W SMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401698406	BVP433 LED344/NW 220~240V 255W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401698506	BVP433 LED341/NW 220~240V 255W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401698606	BVP433 LED318/NW 220~240V 255W SAWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401698706	BVP433 LED348/NW 220~240V 255W NB GM	740 neutral white	Polycarbonate bowl/cover	-
911401698806	BVP433 LED348/NW 220~240V 255W S6 GM	740 neutral white	Polycarbonate bowl/cover	-
911401698906	BVP433 LED344/CW 220~240V 255W SMB GM	757 cool white	Polycarbonate bowl/cover	-
911401699006	BVP433 LED344/CW 220~240V 255W SWB GM	757 cool white	Polycarbonate bowl/cover	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401699106	BVP433 LED341/CW 220~240V 255W AMB GM	757 cool white	Polycarbonate bowl/cover	-
911401699206	BVP433 LED318/CW 220~240V 255W SAWB GM	757 cool white	Polycarbonate bowl/cover	-
911401699306	BVP433 LED348/CW 220~240V 255W NB GM	757 cool white	Polycarbonate bowl/cover	-
911401699406	BVP433 LED348/CW 220~240V 255W S6 GM	757 cool white	Polycarbonate bowl/cover	-
911401699606	BVP433 LED413/NW 220~240V 305W SMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401699706	BVP433 LED413/NW 220~240V 305W SWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401699806	BVP433 LED409/NW 220~240V 305W AMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401699906	BVP433 LED382/NW 220~240V 305W SAWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401658207	BVP491 LED68/NW 50W SWB	White	Glass	For mounting on normally flammable surfaces
911401658307	BVP491 LED93/NW 70W SWB	White	Glass	For mounting on normally flammable surfaces
911401658407	BVP491 LED112/NW 85W SWB	White	Glass	For mounting on normally flammable surfaces
911401658507	BVP491 LED136/NW 100W SWB	White	Glass	For mounting on normally flammable surfaces
911401658607	BVP491 LED90/CW 70W AMB 1-10V	Cool white	Glass	For mounting on normally flammable surfaces
911401658707	BVP491 LED108/CW 85W AMB 1-10V	Cool white	Glass	For mounting on normally flammable surfaces
911401658807	BVP491 LED132/CW 100W AMB 1-10V	Cool white	Glass	For mounting on normally

## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
				flammable surfaces
911401658907	BVP491 LED87/WW 70W SMB 1-10V P7	Warm white	Glass	For mounting on normally flammable surfaces
911401659007	BVP491 LED104/WW 85W SMB 1-10V P7	Warm white	Glass	For mounting on normally flammable surfaces
911401659107	BVP491 LED127/WW 100W SMB 1-10V P7	Warm white	Glass	For mounting on normally flammable surfaces
911401659207	BVP491 LED68/NW 50W SWB LP	White	Glass	For mounting on normally flammable surfaces
911401659307	BVP491 LED93/NW 70W SWB LP	White	Glass	For mounting on normally flammable surfaces
911401659407	BVP491 LED112/NW 85W SWB LP	White	Glass	For mounting on normally flammable surfaces
911401659507	BVP491 LED136/NW 100W SWB LP	White	Glass	For mounting on normally flammable surfaces
911401659607	BVP491 LED68/NW 50W SWB LP P7	White	Glass	For mounting on normally flammable surfaces
911401659707	BVP491 LED93/NW 70W SWB LP P7	White	Glass	For mounting on normally flammable surfaces
911401659807	BVP491 LED112/NW 85W SWB LP P7	White	Glass	For mounting on normally flammable surfaces
911401659907	BVP491 LED136/NW 100W SWB LP P7	White	Glass	For mounting on normally flammable surfaces
911401660007	BVP491 LED68/NW 50W SWB FP DALI/CM	White	Glass	For mounting on normally flammable surfaces

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401660107	BVP491 LED93/NW 70W SWB FP DALI/CM	White	Glass	For mounting on normally flammable surfaces
911401660207	BVP491 LED112/NW 85W SWB FP DALI/CM	White	Glass	For mounting on normally flammable surfaces
911401660307	BVP491 LED136/NW 100W SWB FP DALI/CM	White	Glass	For mounting on normally flammable surfaces
911401660407	BVP491 LED66/CW 50W AMB FP DALI/CM P7	Cool white	Glass	For mounting on normally flammable surfaces
911401660507	BVP491 LED90/CW 70W AMB FP DALI/CM P7	Cool white	Glass	For mounting on normally flammable surfaces
911401660607	BVP491 LED108/CW 85W AMB FP DALI/CM P7	Cool white	Glass	For mounting on normally flammable surfaces
911401660707	BVP491 LED132/CW 100W AMB FP DALI/CM P7	Cool white	Glass	For mounting on normally flammable surfaces
911401660807	BVP491 LED66/CW 50W AMB SR	Cool white	Glass	For mounting on normally flammable surfaces
911401660907	BVP491 LED90/CW 70W AMB SR	Cool white	Glass	For mounting on normally flammable surfaces
911401661007	BVP491 LED108/CW 85W AMB SR	Cool white	Glass	For mounting on normally flammable surfaces
911401661107	BVP491 LED132/CW 100W AMB SR	Cool white	Glass	For mounting on normally flammable surfaces
911401661207	BVP492 LED144/WW 120W AMB	Warm white	Glass	For mounting on normally flammable surfaces
911401661307	BVP492 LED166/WW 135W AMB	Warm white	Glass	For mounting on normally

## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
				flammable surfaces
911401661407	BVP492 LED183/WW 150W AMB	Warm white	Glass	For mounting on normally flammable surfaces
911401661507	BVP492 LED200/WW 165W AMB	Warm white	Glass	For mounting on normally flammable surfaces
911401661607	BVP492 LED222/WW 180W AMB	Warm white	Glass	For mounting on normally flammable surfaces
911401661707	BVP492 LED244/WW 200W AMB	Warm white	Glass	For mounting on normally flammable surfaces
911401661807	BVP492 LED157/CW 120W SMB 1-10V	Cool white	Glass	For mounting on normally flammable surfaces
911401661907	BVP492 LED181/CW 135W SMB 1-10V	Cool white	Glass	For mounting on normally flammable surfaces
911401662007	BVP492 LED200/CW 150W SMB 1-10V	Cool white	Glass	For mounting on normally flammable surfaces
911401662107	BVP492 LED218/CW 165W SMB 1-10V	Cool white	Glass	For mounting on normally flammable surfaces
911401662207	BVP492 LED242/CW 180W SMB 1-10V	Cool white	Glass	For mounting on normally flammable surfaces
911401662307	BVP492 LED266/CW 200W SMB 1-10V	Cool white	Glass	For mounting on normally flammable surfaces
911401662407	BVP492 LED159/NW 120W SWB 1-10V P7	White	Glass	For mounting on normally flammable surfaces
911401662507	BVP492 LED183/NW 135W SWB 1-10V P7	White	Glass	For mounting on normally flammable surfaces

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401662607	BVP492 LED201/NW 150W SWB 1-10V P7	White	Glass	For mounting on normally flammable surfaces
911401662707	BVP492 LED219/NW 165W SWB 1-10V P7	White	Glass	For mounting on normally flammable surfaces
911401662807	BVP492 LED244/NW 180W SWB 1-10V P7	White	Glass	For mounting on normally flammable surfaces
911401662907	BVP492 LED268/NW 200W SWB 1-10V P7	White	Glass	For mounting on normally flammable surfaces
911401663007	BVP492 LED144/WW 120W AMB LP	Warm white	Glass	For mounting on normally flammable surfaces
911401663107	BVP492 LED166/WW 135W AMB LP	Warm white	Glass	For mounting on normally flammable surfaces
911401663207	BVP492 LED183/WW 150W AMB LP	Warm white	Glass	For mounting on normally flammable surfaces
911401663307	BVP492 LED200/WW 165W AMB LP	Warm white	Glass	For mounting on normally flammable surfaces
911401663407	BVP492 LED222/WW 180W AMB LP	Warm white	Glass	For mounting on normally flammable surfaces
911401663507	BVP492 LED244/WW 200W AMB LP	Warm white	Glass	For mounting on normally flammable surfaces
911401663607	BVP492 LED157/CW 120W SMB LP P7	Cool white	Glass	For mounting on normally flammable surfaces
911401663707	BVP492 LED181/CW 135W SMB LP P7	Cool white	Glass	For mounting on normally flammable surfaces
911401663807	BVP492 LED200/CW 150W SMB LP P7	Cool white	Glass	For mounting on normally flammable surfaces

## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
				flammable surfaces
911401663907	BVP492 LED218/CW 165W SMB LP P7	Cool white	Glass	For mounting on normally flammable surfaces
911401664007	BVP492 LED242/CW 180W SMB LP P7	Cool white	Glass	For mounting on normally flammable surfaces
911401664107	BVP492 LED266/CW 200W SMB LP P7	Cool white	Glass	For mounting on normally flammable surfaces
911401664207	BVP492 LED157/CW 120W SMB FP DALI/CM	Cool white	Glass	For mounting on normally flammable surfaces
911401664307	BVP492 LED181/CW 135W SMB FP DALI/CM	Cool white	Glass	For mounting on normally flammable surfaces
911401664407	BVP492 LED200/CW 150W SMB FP DALI/CM	Cool white	Glass	For mounting on normally flammable surfaces
911401664507	BVP492 LED157/CW 120W SMB FP DALI/CM P7	Cool white	Glass	For mounting on normally flammable surfaces
911401664607	BVP492 LED181/CW 135W SMB FP DALI/CM P7	Cool white	Glass	For mounting on normally flammable surfaces
911401664707	BVP492 LED200/CW 150W SMB FP DALI/CM P7	Cool white	Glass	For mounting on normally flammable surfaces
911401664807	BVP492 LED157/CW 120W SMB SR	Cool white	Glass	For mounting on normally flammable surfaces
911401664907	BVP492 LED181/CW 140W SMB SR	Cool white	Glass	For mounting on normally flammable surfaces
911401665007	BVP492 LED200/CW 150W SMB SR	Cool white	Glass	For mounting on normally flammable surfaces

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401665107	BVP493 LED261/WW 230W SAWB	Warm white	Glass	For mounting on normally flammable surfaces
911401665207	BVP493 LED341/NW 255W SWB	White	Glass	For mounting on normally flammable surfaces
911401665307	BVP493 LED388/WW 305W NB	Warm white	Glass	For mounting on normally flammable surfaces
911401665407	BVP493 LED460/CW 345W SWB	Cool white	Glass	For mounting on normally flammable surfaces
911401665507	BVP493 LED485/WW 380W NB	Warm white	Glass	For mounting on normally flammable surfaces
911401665607	BVP493 LED261/WW 230W SAWB 1-10V	Warm white	Glass	For mounting on normally flammable surfaces
911401665707	BVP493 LED341/NW 255W SWB 1-10V	White	Glass	For mounting on normally flammable surfaces
911401665807	BVP493 LED388/WW 305W NB 1-10V	Warm white	Glass	For mounting on normally flammable surfaces
911401665907	BVP493 LED460/CW 345W SWB 1-10V	Cool white	Glass	For mounting on normally flammable surfaces
911401666007	BVP493 LED485/WW 380W NB 1-10V	Warm white	Glass	For mounting on normally flammable surfaces
911401666107	BVP493 LED261/WW 230W SAWB 1-10V P7	Warm white	Glass	For mounting on normally flammable surfaces
911401666207	BVP493 LED341/NW 255W SWB 1-10V P7	White	Glass	For mounting on normally flammable surfaces

## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401666307	BVP493 LED388/WW 305W NB 1-10V P7	Warm white	Glass	For mounting on normally flammable surfaces
911401666407	BVP493 LED460/CW 345W SWB 1-10V P7	Cool white	Glass	For mounting on normally flammable surfaces
911401666507	BVP493 LED485/WW 380W NB 1-10V P7	Warm white	Glass	For mounting on normally flammable surfaces
911401666607	BVP493 LED261/WW 230W SAWB LP	Warm white	Glass	For mounting on normally flammable surfaces
911401666707	BVP493 LED341/NW 255W SWB LP	White	Glass	For mounting on normally flammable surfaces
911401666807	BVP493 LED388/WW 310W NB LP	Warm white	Glass	For mounting on normally flammable surfaces
911401666907	BVP493 LED460/CW 350W SWB LP	Cool white	Glass	For mounting on normally flammable surfaces
911401667007	BVP493 LED485/WW 380W NB LP	Warm white	Glass	For mounting on normally flammable surfaces
911401667207	BVP493 LED261/WW 230W SAWB LP P7	Warm white	Glass	For mounting on normally flammable surfaces
911401667307	BVP493 LED341/NW 255W SWB LP P7	White	Glass	For mounting on normally flammable surfaces
911401667407	BVP493 LED388/WW 310W NB LP P7	Warm white	Glass	For mounting on normally flammable surfaces
911401667507	BVP493 LED460/CW 350W SWB LP P7	Warm white	Glass	For mounting on normally flammable surfaces

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401667607	BVP493 LED485/WW 380W NB LP P7	Warm white	Glass	For mounting on normally flammable surfaces
911401667807	BVP493 LED261/WW 230W SAWB FP DALI/CM	Warm white	Glass	For mounting on normally flammable surfaces
911401667907	BVP493 LED341/NW 260W SWB FP DALI/CM	White	Glass	For mounting on normally flammable surfaces
911401668007	BVP493 LED370/WW 300W NB FP DALI/CM	Warm white	Glass	For mounting on normally flammable surfaces
911401668107	BVP493 LED261/WW 230W SAWB FP DALI/CM P7	Warm white	Glass	For mounting on normally flammable surfaces
911401668207	BVP493 LED341/NW 260W SWB FP DALI/CM P7	White	Glass	For mounting on normally flammable surfaces
911401668307	BVP493 LED370/WW 300W NB FP DALI/CM P7	Warm white	Glass	For mounting on normally flammable surfaces
911401668407	BVP493 LED261/WW 230W SAWB SR	Warm white	Glass	For mounting on normally flammable surfaces
911401668507	BVP493 LED341/NW 260W SWB SR	White	Glass	For mounting on normally flammable surfaces
911401668607	BVP493 LED370/WW 295W NB SR	Warm white	Glass	For mounting on normally flammable surfaces
911401678706	BVP431 LED68/NW 220~240V 50W SMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401678806	BVP431 LED68/NW 220~240V 50W SWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401678906	BVP431 LED67/NW 220~240V 50W AMB GC	740 neutral white	Polycarbonate bowl/cover	-

## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401679406	BVP431 LED68/NW 220~240V 50W SMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401679506	BVP431 LED68/NW 220~240V 50W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401679606	BVP431 LED67/NW 220~240V 50W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401680306	BVP431 LED92/NW 220~240V 70W SMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401680406	BVP431 LED92/NW 220~240V 70W SWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401680506	BVP431 LED91/NW 220~240V 70W AMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401680606	BVP431 LED92/CW 220~240V 70W SMB GC	757 cool white	Polycarbonate bowl/cover	-
911401680706	BVP431 LED92/CW 220~240V 70W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401680806	BVP431 LED91/CW 220~240V 70W AMB GC	757 cool white	Polycarbonate bowl/cover	-
911401681206	BVP431 LED92/NW 220~240V 70W SMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401681306	BVP431 LED92/NW 220~240V 70W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401681406	BVP431 LED91/NW 220~240V 70W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401681506	BVP431 LED92/CW 220~240V 70W SMB GM	757 cool white	Polycarbonate bowl/cover	-
911401681606	BVP431 LED92/CW 220~240V 70W SWB GM	757 cool white	Polycarbonate bowl/cover	-
911401681706	BVP431 LED91/CW 220~240V 70W AMB GM	757 cool white	Polycarbonate bowl/cover	-
911401681806	BVP431 LED92/NW 70W SWB ANZ CL	740 neutral white	Polycarbonate bowl/cover	-
911401682206	BVP431 LED136/NW 220~240V 100W SMB GC	740 neutral white	Polycarbonate bowl/cover	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401682306	BVP431 LED136/NW 220~240V 100W SWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401682406	BVP431 LED134/NW 220~240V 100W AMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401682506	BVP431 LED135/CW 220~240V 100W SMB GC	757 cool white	Polycarbonate bowl/cover	-
911401682606	BVP431 LED135/CW 220~240V 100W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401682706	BVP431 LED133/CW 220~240V 100W AMB GC	757 cool white	Polycarbonate bowl/cover	-
911401683206	BVP431 LED136/NW 220~240V 100W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401683306	BVP431 LED134/NW 220~240V 100W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401683406	BVP431 LED135/CW 220~240V 100W SMB GM	757 cool white	Polycarbonate bowl/cover	-
911401683506	BVP431 LED135/CW 220~240V 100W SWB GM	757 cool white	Polycarbonate bowl/cover	-
911401683606	BVP431 LED133/CW 220~240V 100W AMB GM	757 cool white	Polycarbonate bowl/cover	-
911401683706	BVP431 LED136/NW 100W SWB ANZ CL	740 neutral white	Polycarbonate bowl/cover	-
911401683906	BVP431 LED134/NW 100W AMB CM GC	740 neutral white	Polycarbonate bowl/cover	-
911401684006	BVP431 LED133/CW 100W AMB CM GM	757 cool white	Polycarbonate bowl/cover	-
911401686906	BVP432 LED161/CW 220~240V 120W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401687606	BVP432 LED161/CW 220~240V 120W SWB GM	757 cool white	Polycarbonate bowl/cover	-
911401688506	BVP432 LED204/CW 220~240V 150W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401688606	BVP432 LED202/CW 220~240V 150W AMB GC	757 cool white	Polycarbonate bowl/cover	-

## Tango G4 LED Flood

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401689006	BVP432 LED206/NW 220~240V 150W SMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401689106	BVP432 LED206/NW 220~240V 150W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401689206	BVP432 LED203/NW 220~240V 150W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401689306	BVP432 LED204/CW 220~240V 150W SMB GM	757 cool white	Polycarbonate bowl/cover	-
911401689406	BVP432 LED204/CW 220~240V 150W SWB GM	757 cool white	Polycarbonate bowl/cover	-
911401689506	BVP432 LED202/CW 220~240V 150W AMB GM	757 cool white	Polycarbonate bowl/cover	-
911401689906	BVP432 LED274/NW 220~240V 200W SMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401690006	BVP432 LED274/NW 220~240V 200W SWB GC	740 neutral white	Polycarbonate bowl/cover	-
911401690106	BVP432 LED271/NW 220~240V 200W AMB GC	740 neutral white	Polycarbonate bowl/cover	-
911401690206	BVP432 LED272/CW 220~240V 200W SMB GC	757 cool white	Polycarbonate bowl/cover	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark
911401690306	BVP432 LED272/CW 220~240V 200W SWB GC	757 cool white	Polycarbonate bowl/cover	-
911401690406	BVP432 LED269/CW 220~240V 200W AMB GC	757 cool white	Polycarbonate bowl/cover	-
911401690806	BVP432 LED274/NW 220~240V 200W SMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401690906	BVP432 LED274/NW 220~240V 200W SWB GM	740 neutral white	Polycarbonate bowl/cover	-
911401691006	BVP432 LED271/NW 220~240V 200W AMB GM	740 neutral white	Polycarbonate bowl/cover	-
911401691106	BVP432 LED272/CW 220~240V 200W SMB GM	757 cool white	Polycarbonate bowl/cover	-
911401691206	BVP432 LED272/CW 220~240V 200W SWB GM	757 cool white	Polycarbonate bowl/cover	-
911401691306	BVP432 LED269/CW 220~240V 200W AMB GM	757 cool white	Polycarbonate bowl/cover	-
911401691406	BVP432 LED274/NW 200W SWB ANZ CL	740 neutral white	Polycarbonate bowl/cover	-
911401691606	BVP432 LED203/NW 150W AMB CM GC	740 neutral white	Polycarbonate bowl/cover	-
911401691706	BVP432 LED202/CW 150W AMB CM GM	757 cool white	Polycarbonate bowl/cover	-

### Initial performance (IEC compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401600007	BVP433 LED418/NW 220~240V 305W NB GC	4000 K	38200 lm
911401600107	BVP433 LED418/NW 220~240V 305W S6 GC	4000 K	41800 lm
911401600207	BVP433 LED413/CW 220~240V 305W SMB GC	5700 K	41300 lm
911401600307	BVP433 LED413/CW 220~240V 305W SWB GC	5700 K	41300 lm
911401600407	BVP433 LED409/CW 220~240V 305W AMB GC	5700 K	40900 lm
911401600507	BVP433 LED382/CW 220~240V 305W SAWB GC	5700 K	38200 lm
911401600607	BVP433 LED418/CW 220~240V 305W NB GC	5700 K	41800 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401600707	BVP433 LED418/CW 220~240V 305W S6 GC	5700 K	41800 lm
911401600907	BVP433 LED413/NW 220~240V 305W SMB GM	4000 K	41300 lm
911401601007	BVP433 LED413/NW 220~240V 305W SWB GM	4000 K	41300 lm
911401601107	BVP433 LED409/NW 220~240V 305W AMB GM	4000 K	40900 lm
911401601207	BVP433 LED382/NW 220~240V 305W SAWB GM	4000 K	38200 lm
911401601307	BVP433 LED418/NW 220~240V 305W NB GM	4000 K	41800 lm
911401601407	BVP433 LED418/NW 220~240V 305W S6 GM	4000 K	41800 lm

## Tango G4 LED Flood

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401601507	BVP433 LED413/CW 220~240V 305W SMB GM	5700 K	41300 lm
911401601607	BVP433 LED413/CW 220~240V 305W SWB GM	5700 K	41300 lm
911401601707	BVP433 LED409/CW 220~240V 305W AMB GM	5700 K	40900 lm
911401601807	BVP433 LED382/CW 220~240V 305W SAWB GM	5700 K	38200 lm
911401601907	BVP433 LED418/CW 220~240V 305W NB GM	5700 K	41800 lm
911401602007	BVP433 LED418/CW 220~240V 305W S6 GM	5700 K	41800 lm
911401602207	BVP433 LED465/NW 220~240V 345W SMB GC	4000 K	46500 lm
911401602307	BVP433 LED465/NW 220~240V 345W SWB GC	4000 K	46500 lm
911401602407	BVP433 LED460/NW 220~240V 345W AMB GC	4000 K	46000 lm
911401602507	BVP433 LED430/NW 220~240V 345W SAWB GC	4000 K	43000 lm
911401602607	BVP433 LED470/NW 220~240V 345W NB GC	4000 K	47000 lm
911401602707	BVP433 LED470/NW 220~240V 345W S6 GC	4000 K	47000 lm
911401602807	BVP433 LED465/CW 220~240V 345W SMB GC	5700 K	46500 lm
911401602907	BVP433 LED465/CW 220~240V 345W SWB GC	5700 K	46500 lm
911401603007	BVP433 LED460/CW 220~240V 345W AMB GC	5700 K	46000 lm
911401603107	BVP433 LED430/CW 220~240V 345W SAWB GC	5700 K	43000 lm
911401603207	BVP433 LED470/CW 220~240V 345W NB GC	5700 K	47000 lm
911401603307	BVP433 LED470/CW 220~240V 345W S6 GC	5700 K	47000 lm
911401603507	BVP433 LED465/NW 220~240V 345W SMB GM	4000 K	46500 lm
911401603607	BVP433 LED465/NW 220~240V 345W SWB GM	4000 K	46500 lm
911401603707	BVP433 LED460/NW 220~240V 345W AMB GM	4000 K	46000 lm
911401603807	BVP433 LED430/NW 220~240V 345W SAWB GM	4000 K	43000 lm
911401603907	BVP433 LED470/NW 220~240V 345W NB GM	4000 K	47000 lm
911401604007	BVP433 LED470/NW 220~240V 345W S6 GM	4000 K	47000 lm
911401604107	BVP433 LED465/CW 220~240V 345W SMB GM	5700 K	46500 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401604207	BVP433 LED465/CW 220~240V 345W SWB GM	5700 K	46500 lm
911401604307	BVP433 LED460/CW 220~240V 345W AMB GM	5700 K	46000 lm
911401604407	BVP433 LED430/CW 220~240V 345W SAWB GM	5700 K	43000 lm
911401604507	BVP433 LED470/CW 220~240V 345W NB GM	5700 K	47000 lm
911401604607	BVP433 LED470/CW 220~240V 345W S6 GM	5700 K	47000 lm
911401605007	BVP433 LED517/NW 220~240V 380W SMB GC	4000 K	51700 lm
911401605107	BVP433 LED517/NW 220~240V 380W SWB GC	4000 K	51700 lm
911401605207	BVP433 LED511/NW 220~240V 380W AMB GC	4000 K	51100 lm
911401605307	BVP433 LED477/NW 220~240V 380W SAWB GC	4000 K	47700 lm
911401605407	BVP433 LED522/NW 220~240V 380W NB GC	4000 K	52200 lm
911401605507	BVP433 LED522/NW 220~240V 380W S6 GC	4000 K	52200 lm
911401605607	BVP433 LED517/CW 220~240V 380W SMB GC	5700 K	51700 lm
911401605707	BVP433 LED517/CW 220~240V 380W SWB GC	5700 K	51700 lm
911401605807	BVP433 LED511/CW 220~240V 380W AMB GC	5700 K	51100 lm
911401605907	BVP433 LED477/CW 220~240V 380W SAWB GC	5700 K	47700 lm
911401606007	BVP433 LED522/CW 220~240V 380W NB GC	5700 K	52200 lm
911401606107	BVP433 LED522/CW 220~240V 380W S6 GC	5700 K	52200 lm
911401606507	BVP433 LED517/NW 220~240V 380W SMB GM	4000 K	51700 lm
911401606607	BVP433 LED517/NW 220~240V 380W SWB GM	4000 K	51700 lm
911401606707	BVP433 LED511/NW 220~240V 380W AMB GM	4000 K	47700 lm
911401606807	BVP433 LED477/NW 220~240V 380W SAWB GM	4000 K	52200 lm
911401606907	BVP433 LED522/NW 220~240V 380W NB GM	4000 K	52200 lm
911401607007	BVP433 LED522/NW 220~240V 380W S6 GM	4000 K	52200 lm
911401607107	BVP433 LED517/CW 220~240V 380W SMB GM	5700 K	51700 lm
911401607207	BVP433 LED517/CW 220~240V 380W SWB GM	5700 K	51700 lm



## Tango G4 LED Flood

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401607307	BVP433 LED511/CW 220~240V 380W AMB GM	5700 K	51100 lm
911401607407	BVP433 LED477/CW 220~240V 380W SAWB GM	5700 K	47700 lm
911401607507	BVP433 LED522/CW 220~240V 380W NB GM	5700 K	52200 lm
911401607607	BVP433 LED522/CW 220~240V 380W S6 GM	5700 K	52200 lm
911401607807	BVP433 LED359/NW 300W SAWB CM GC	4000 K	35900 lm
911401607907	BVP433 LED384/CW 300W AMB CM GM	5700 K	38400 lm
911401694306	BVP433 LED310/NW 220~240V 230W SWB GC	4000 K	31000 lm
911401694406	BVP433 LED307/NW 220~240V 230W AMB GC	4000 K	30700 lm
911401694506	BVP433 LED286/NW 220~240V 230W SAWB GC	4000 K	28600 lm
911401694606	BVP433 LED313/NW 220~240V 230W NB GC	4000 K	31300 lm
911401694706	BVP433 LED313/NW 220~240V 230W S6 GC	4000 K	31300 lm
911401694806	BVP433 LED310/CW 220~240V 230W SMB GC	5700 K	31000 lm
911401694906	BVP433 LED310/CW 220~240V 230W SWB GC	5700 K	31000 lm
911401695006	BVP433 LED307/CW 220~240V 230W AMB GC	5700 K	30700 lm
911401695106	BVP433 LED286/CW 220~240V 230W SAWB GC	5700 K	28600 lm
911401695206	BVP433 LED313/CW 220~240V 230W NB GC	5700 K	31300 lm
911401695306	BVP433 LED313/CW 220~240V 230W S6 GC	5700 K	31300 lm
911401695506	BVP433 LED310/NW 220~240V 230W SMB GM	4000 K	31000 lm
911401695606	BVP433 LED310/NW 220~240V 230W SWB GM	4000 K	31000 lm
911401695706	BVP433 LED307/NW 220~240V 230W AMB GM	4000 K	30700 lm
911401695806	BVP433 LED286/NW 220~240V 230W SAWB GM	4000 K	28600 lm
911401695906	BVP433 LED313/NW 220~240V 230W NB GM	4000 K	31300 lm
911401696006	BVP433 LED313/NW 220~240V 230W S6 GM	4000 K	31300 lm
911401696106	BVP433 LED310/CW 220~240V 230W SMB GM	5700 K	31000 lm
911401696206	BVP433 LED310/CW 220~240V 230W SWB GM	5700 K	31000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux	
911401696306	BVP433 LED307/CW 220~240V 230W AMB GM	5700 K	30700 lm	
911401696406	BVP433 LED286/CW 220~240V 230W SAWB GM	5700 K	28600 lm	
911401696506	BVP433 LED313/CW 220~240V 230W NB GM	5700 K	31300 lm	
911401696606	BVP433 LED313/CW 220~240V 230W S6 GM	5700 K	31300 lm	
911401696906	BVP433 LED344/NW 220~240V 255W SMB GC	4000 K	34400 lm	
911401697006	BVP433 LED344/NW 220~240V 255W SWB GC	4000 K	34400 lm	
911401697106	BVP433 LED341/NW 220~240V 255W AMB GC	4000 K	34100 lm	
911401697206	BVP433 LED318/NW 220~240V 255W SAWB GC	4000 K	31800 lm	
911401697306	BVP433 LED348/NW 220~240V 255W NB GC	4000 K	34800 lm	
911401697406	BVP433 LED348/NW 220~240V 255W S6 GC	4000 K	34800 lm	
911401697506	BVP433 LED344/CW 220~240V 255W SMB GC	5700 K	34400 lm	
911401697606	BVP433 LED344/CW 220~240V 255W SWB GC	5700 K	34400 lm	
911401697706	BVP433 LED341/CW 220~240V 255W AMB GC	5700 K	34100 lm	
911401697806	BVP433 LED318/CW 220~240V 255W SAWB GC	5700 K	31800 lm	
911401697906	BVP433 LED348/CW 220~240V 255W NB GC	5700 K	34800 lm	
911401698006	BVP433 LED348/CW 220~240V 255W S6 GC	5700 K	34800 lm	
911401698306	BVP433 LED344/NW 220~240V 255W SMB GM	4000 K	34400 lm	
911401698406	BVP433 LED344/NW 220~240V 255W SWB GM	4000 K	34400 lm	
911401698506	BVP433 LED341/NW 220~240V 255W AMB GM	4000 K	34100 lm	
911401698606	BVP433 LED318/NW 220~240V 255W SAWB GM	4000 K	31800 lm	
911401698706	BVP433 LED348/NW 220~240V 255W NB GM	4000 K	34800 lm	
911401698806	BVP433 LED348/NW 220~240V 255W S6 GM	4000 K	34800 lm	
911401698906	BVP433 LED344/CW 220~240V 255W SMB GM	5700 K	34400 lm	
911401699006	BVP433 LED344/CW 220~240V 255W SWB GM	5700 K	34400 lm	
6	911401699106	BVP433 LED341/CW 220~240V	5700 K	34100 lm
		255W AMB GM		

## Tango G4 LED Flood

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401699206	BVP433 LED318/CW 220~240V 255W SAWB GM	5700 K	31800 lm
911401699306	BVP433 LED348/CW 220~240V 255W NB GM	5700 K	34800 lm
911401699406	BVP433 LED348/CW 220~240V 255W S6 GM	5700 K	34800 lm
911401699606	BVP433 LED413/NW 220~240V 305W SMB GC	4000 K	41300 lm
911401699706	BVP433 LED413/NW 220~240V 305W SWB GC	4000 K	41300 lm
911401699806	BVP433 LED409/NW 220~240V 305W AMB GC	4000 K	41300 lm
911401699906	BVP433 LED382/NW 220~240V 305W SAWB GC	4000 K	40900 lm
911401658207	BVP491 LED68/NW 50W SWB	4000 K	6800 lm
911401658307	BVP491 LED93/NW 70W SWB	4000 K	9300 lm
911401658407	BVP491 LED112/NW 85W SWB	4000 K	11200 lm
911401658507	BVP491 LED136/NW 100W SWB	4000 K	13600 lm
911401658607	BVP491 LED90/CW 70W AMB 1-10V	5700 K	9000 lm
911401658707	BVP491 LED108/CW 85W AMB 1-10V	5700 K	10800 lm
911401658807	BVP491 LED132/CW 100W AMB 1-10V	5700 K	13200 lm
911401658907	BVP491 LED87/WW 70W SMB 1-10V P7	3000 K	8700 lm
911401659007	BVP491 LED104/WW 85W SMB 1-10V P7	3000 K	10400 lm
911401659107	BVP491 LED127/WW 100W SMB 1-10V P7	3000 K	12700 lm
911401659207	BVP491 LED68/NW 50W SWB LP	4000 K	6800 lm
911401659307	BVP491 LED93/NW 70W SWB LP	4000 K	9300 lm
911401659407	BVP491 LED112/NW 85W SWB LP	4000 K	11200 lm
911401659507	BVP491 LED136/NW 100W SWB LP	4000 K	13600 lm
911401659607	BVP491 LED68/NW 50W SWB LP P7	4000 K	6800 lm
911401659707	BVP491 LED93/NW 70W SWB LP P7	4000 K	9300 lm
911401659807	BVP491 LED112/NW 85W SWB LP P7	4000 K	11200 lm
911401659907	BVP491 LED136/NW 100W SWB LP P7	4000 K	13600 lm
911401660007	BVP491 LED68/NW 50W SWB FP DALI/CM	4000 K	6800 lm
911401660107	BVP491 LED93/NW 70W SWB FP DALI/CM	4000 K	9300 lm
911401660207	BVP491 LED112/NW 85W SWB FP DALI/CM	4000 K	11200 lm
911401660307	BVP491 LED136/NW 100W SWB FP DALI/CM	4000 K	13600 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401660407	BVP491 LED66/CW 50W AMB FP DALI/CM P7	5700 K	6600 lm
911401660507	BVP491 LED90/CW 70W AMB FP DALI/CM P7	5700 K	9000 lm
911401660607	BVP491 LED108/CW 85W AMB FP DALI/CM P7	5700 K	10800 lm
911401660707	BVP491 LED132/CW 100W AMB FP DALI/CM P7	5700 K	13200 lm
911401660807	BVP491 LED66/CW 50W AMB SR	5700 K	6600 lm
911401660907	BVP491 LED90/CW 70W AMB SR	5700 K	9000 lm
911401661007	BVP491 LED108/CW 85W AMB SR	5700 K	10800 lm
911401661107	BVP491 LED132/CW 100W AMB SR	5700 K	13200 lm
911401661207	BVP492 LED144/WW 120W AMB	3000 K	14400 lm
911401661307	BVP492 LED166/WW 135W AMB	3000 K	16600 lm
911401661407	BVP492 LED183/WW 150W AMB	3000 K	18300 lm
911401661507	BVP492 LED200/WW 165W AMB	3000 K	20000 lm
911401661607	BVP492 LED222/WW 180W AMB	3000 K	22200 lm
911401661707	BVP492 LED244/WW 200W AMB	3000 K	24400 lm
911401661807	BVP492 LED157/CW 120W SMB 1-10V	5700 K	15700 lm
911401661907	BVP492 LED181/CW 135W SMB 1-10V	5700 K	18100 lm
911401662007	BVP492 LED200/CW 150W SMB 1-10V	5700 K	20000 lm
911401662107	BVP492 LED218/CW 165W SMB 1-10V	5700 K	21800 lm
911401662207	BVP492 LED242/CW 180W SMB 1-10V	5700 K	24200 lm
911401662307	BVP492 LED266/CW 200W SMB 1-10V	5700 K	26600 lm
911401662407	BVP492 LED159/NW 120W SWB 1-10V P7	4000 K	15900 lm
911401662507	BVP492 LED183/NW 135W SWB 1-10V P7	4000 K	18300 lm
911401662607	BVP492 LED201/NW 150W SWB 1-10V P7	4000 K	20100 lm
911401662707	BVP492 LED219/NW 165W SWB 1-10V P7	4000 K	21900 lm
911401662807	BVP492 LED244/NW 180W SWB 1-10V P7	4000 K	24400 lm
911401662907	BVP492 LED268/NW 200W SWB 1-10V P7	4000 K	26800 lm
911401663007	BVP492 LED144/WW 120W AMB LP	3000 K	14400 lm
911401663107	BVP492 LED166/WW 135W AMB LP	3000 K	16600 lm
911401663207	BVP492 LED183/WW 150W AMB LP	3000 K	18300 lm

## Tango G4 LED Flood

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401663307	BVP492 LED200/WW 165W AMB LP	3000 K	20000 lm
911401663407	BVP492 LED222/WW 180W AMB LP	3000 K	22200 lm
911401663507	BVP492 LED244/WW 200W AMB LP	3000 K	24400 lm
911401663607	BVP492 LED157/CW 120W SMB LP P7	5700 K	15700 lm
911401663707	BVP492 LED181/CW 135W SMB LP P7	5700 K	18100 lm
911401663807	BVP492 LED200/CW 150W SMB LP P7	5700 K	20000 lm
911401663907	BVP492 LED218/CW 165W SMB LP P7	5700 K	21800 lm
911401664007	BVP492 LED242/CW 180W SMB LP P7	5700 K	24200 lm
911401664107	BVP492 LED266/CW 200W SMB LP P7	5700 K	26600 lm
911401664207	BVP492 LED157/CW 120W SMB FP DALI/CM	5700 K	15700 lm
911401664307	BVP492 LED181/CW 135W SMB FP DALI/CM	5700 K	18100 lm
911401664407	BVP492 LED200/CW 150W SMB FP DALI/CM	5700 K	20000 lm
911401664507	BVP492 LED157/CW 120W SMB FP DALI/CM P7	5700 K	15700 lm
911401664607	BVP492 LED181/CW 135W SMB FP DALI/CM P7	5700 K	18100 lm
911401664707	BVP492 LED200/CW 150W SMB FP DALI/CM P7	5700 K	20000 lm
911401664807	BVP492 LED157/CW 120W SMB SR	5700 K	15700 lm
911401664907	BVP492 LED181/CW 140W SMB SR	5700 K	18100 lm
911401665007	BVP492 LED200/CW 150W SMB SR	5700 K	20000 lm
911401665107	BVP493 LED261/WW 230W SAWB	3000 K	26100 lm
911401665207	BVP493 LED341/NW 255W SWB	4000 K	34100 lm
911401665307	BVP493 LED388/WW 305W NB	3000 K	38800 lm
911401665407	BVP493 LED460/CW 345W SWB	5700 K	46000 lm
911401665507	BVP493 LED485/WW 380W NB	3000 K	48500 lm
911401665607	BVP493 LED261/WW 230W SAWB 1-10V	3000 K	26100 lm
911401665707	BVP493 LED341/NW 255W SWB 1-10V	4000 K	34100 lm
911401665807	BVP493 LED388/WW 305W NB 1-10V	3000 K	38800 lm
911401665907	BVP493 LED460/CW 345W SWB 1-10V	5700 K	46000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401666007	BVP493 LED485/WW 380W NB 1-10V	3000 K	48500 lm
911401666107	BVP493 LED261/WW 230W SAWB 1-10V P7	3000 K	26100 lm
911401666207	BVP493 LED341/NW 255W SWB 1-10V P7	4000 K	34100 lm
911401666307	BVP493 LED388/WW 305W NB 1-10V P7	3000 K	38800 lm
911401666407	BVP493 LED460/CW 345W SWB 1-10V P7	5700 K	46000 lm
911401666507	BVP493 LED485/WW 380W NB 1-10V P7	3000 K	48500 lm
911401666607	BVP493 LED261/WW 230W SAWB LP	3000 K	26100 lm
911401666707	BVP493 LED341/NW 255W SWB LP	4000 K	34100 lm
911401666807	BVP493 LED388/WW 310W NB LP	3000 K	38800 lm
911401666907	BVP493 LED460/CW 350W SWB LP	5700 K	46000 lm
911401667007	BVP493 LED485/WW 380W NB LP	3000 K	48500 lm
911401667207	BVP493 LED261/WW 230W SAWB LP P7	3000 K	26100 lm
911401667307	BVP493 LED341/NW 255W SWB LP P7	4000 K	34100 lm
911401667407	BVP493 LED388/WW 310W NB LP P7	3000 K	38800 lm
911401667507	BVP493 LED460/CW 350W SWB LP P7	5700 K	46000 lm
911401667607	BVP493 LED485/WW 380W NB LP P7	3000 K	48500 lm
911401667807	BVP493 LED261/WW 230W SAWB FP DALI/CM	3000 K	26100 lm
911401667907	BVP493 LED341/NW 260W SWB FP DALI/CM	4000 K	34100 lm
911401668007	BVP493 LED370/WW 300W NB FP DALI/CM	3000 K	37000 lm
911401668107	BVP493 LED261/WW 230W SAWB FP DALI/CM P7	3000 K	26100 lm
911401668207	BVP493 LED341/NW 260W SWB FP DALI/CM P7	4000 K	34100 lm
911401668307	BVP493 LED370/WW 300W NB FP DALI/CM P7	3000 K	37000 lm
911401668407	BVP493 LED261/WW 230W SAWB SR	3000 K	26100 lm
911401668507	BVP493 LED341/NW 260W SWB SR	4000 K	34100 lm
911401668607	BVP493 LED370/WW 295W NB SR	3000 K	37000 lm

## Tango G4 LED Flood

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401678706	BVP431 LED68/NW 220~240V 50W SMB GC	4000 K	6800 lm
911401678806	BVP431 LED68/NW 220~240V 50W SWB GC	4000 K	6800 lm
911401678906	BVP431 LED67/NW 220~240V 50W AMB GC	4000 K	6700 lm
911401679406	BVP431 LED68/NW 220~240V 50W SMB GM	4000 K	6800 lm
911401679506	BVP431 LED68/NW 220~240V 50W SWB GM	4000 K	6800 lm
911401679606	BVP431 LED67/NW 220~240V 50W AMB GM	4000 K	6700 lm
911401680306	BVP431 LED92/NW 220~240V 70W SMB GC	4000 K	9200 lm
911401680406	BVP431 LED92/NW 220~240V 70W SWB GC	4000 K	9200 lm
911401680506	BVP431 LED91/NW 220~240V 70W AMB GC	4000 K	9100 lm
911401680606	BVP431 LED92/CW 220~240V 70W SMB GC	5700 K	9200 lm
911401680706	BVP431 LED92/CW 220~240V 70W SWB GC	5700 K	9200 lm
911401680806	BVP431 LED91/CW 220~240V 70W AMB GC	5700 K	9100 lm
911401681206	BVP431 LED92/NW 220~240V 70W SMB GM	4000 K	9200 lm
911401681306	BVP431 LED92/NW 220~240V 70W SWB GM	4000 K	9200 lm
911401681406	BVP431 LED91/NW 220~240V 70W AMB GM	4000 K	9100 lm
911401681506	BVP431 LED92/CW 220~240V 70W SMB GM	5700 K	9200 lm
911401681606	BVP431 LED92/CW 220~240V 70W SWB GM	5700 K	9200 lm
911401681706	BVP431 LED91/CW 220~240V 70W AMB GM	5700 K	9100 lm
911401681806	BVP431 LED92/NW 70W SWB ANZ CL	4000 K	9200 lm
911401682206	BVP431 LED136/NW 220~240V 100W SMB GC	4000 K	13600 lm
911401682306	BVP431 LED136/NW 220~240V 100W SWB GC	4000 K	13600 lm
911401682406	BVP431 LED134/NW 220~240V 100W AMB GC	4000 K	13400 lm
911401682506	BVP431 LED135/CW 220~240V 100W SMB GC	5700 K	13500 lm
911401682606	BVP431 LED135/CW 220~240V 100W SWB GC	5700 K	13500 lm
911401682706	BVP431 LED133/CW 220~240V 100W AMB GC	5700 K	13300 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401683206	BVP431 LED136/NW 220~240V 100W SWB GM	4000 K	13600 lm
911401683306	BVP431 LED134/NW 220~240V 100W AMB GM	4000 K	13400 lm
911401683406	BVP431 LED135/CW 220~240V 100W SMB GM	5700 K	13500 lm
911401683506	BVP431 LED135/CW 220~240V 100W SWB GM	5700 K	13500 lm
911401683606	BVP431 LED133/CW 220~240V 100W AMB GM	5700 K	13300 lm
911401683706	BVP431 LED136/NW 100W SWB ANZ CL	4000 K	13600 lm
911401683906	BVP431 LED134/NW 100W AMB CM GC	4000 K	13400 lm
911401684006	BVP431 LED133/CW 100W AMB CM GM	5700 K	13300 lm
911401686906	BVP432 LED161/CW 220~240V 120W SWB GC	5700 K	16100 lm
911401687606	BVP432 LED161/CW 220~240V 120W SWB GM	5700 K	16100 lm
911401688506	BVP432 LED204/CW 220~240V 150W SWB GC	5700 K	20400 lm
911401688606	BVP432 LED202/CW 220~240V 150W AMB GC	5700 K	20200 lm
911401689006	BVP432 LED206/NW 220~240V 150W SMB GM	4000 K	20600 lm
911401689106	BVP432 LED206/NW 220~240V 150W SWB GM	4000 K	20600 lm
911401689206	BVP432 LED203/NW 220~240V 150W AMB GM	4000 K	20300 lm
911401689306	BVP432 LED204/CW 220~240V 150W SMB GM	5700 K	20400 lm
911401689406	BVP432 LED204/CW 220~240V 150W SWB GM	5700 K	20400 lm
911401689506	BVP432 LED202/CW 220~240V 150W AMB GM	5700 K	20200 lm
911401689906	BVP432 LED274/NW 220~240V 200W SMB GC	4000 K	27400 lm
911401690006	BVP432 LED274/NW 220~240V 200W SWB GC	4000 K	27400 lm
911401690106	BVP432 LED271/NW 220~240V 200W AMB GC	4000 K	27100 lm
911401690206	BVP432 LED272/CW 220~240V 200W SMB GC	5700 K	27200 lm
911401690306	BVP432 LED272/CW 220~240V 200W SWB GC	5700 K	27200 lm
911401690406	BVP432 LED269/CW 220~240V 200W AMB GC	5700 K	26900 lm
911401690806	BVP432 LED274/NW 220~240V 200W SMB GM	4000 K	27400 lm

# Tango G4 LED Flood

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401690906	BVP432 LED274/NW 220~240V 200W SWB GM	4000 K	27400 lm
911401691006	BVP432 LED271/NW 220~240V 200W AMB GM	4000 K	27100 lm
911401691106	BVP432 LED272/CW 220~240V 200W SMB GM	5700 K	27200 lm
911401691206	BVP432 LED272/CW 220~240V 200W SWB GM	5700 K	27200 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401691306	BVP432 LED269/CW 220~240V 200W AMB GM	5700 K	26900 lm
911401691406	BVP432 LED274/NW 200W SWB ANZ CL	4000 K	27400 lm
911401691606	BVP432 LED203/NW 150W AMB CM GC	4000 K	20300 lm
911401691706	BVP432 LED202/CW 150W AMB CM GM	5700 K	20200 lm

## Mechanical and housing

Order Code	Full Product Name	Color
911401600007	BVP433 LED418/NW 220~240V 305W NB GC	Gray
911401600107	BVP433 LED418/NW 220~240V 305W S6 GC	Gray
911401600207	BVP433 LED413/CW 220~240V 305W SMB GC	Gray
911401600307	BVP433 LED413/CW 220~240V 305W SWB GC	Gray
911401600407	BVP433 LED409/CW 220~240V 305W AMB GC	Gray
911401600507	BVP433 LED382/CW 220~240V 305W SAWB GC	Gray
911401600607	BVP433 LED418/CW 220~240V 305W NB GC	Gray
911401600707	BVP433 LED418/CW 220~240V 305W S6 GC	Gray
911401600907	BVP433 LED413/NW 220~240V 305W SMB GM	Gray
911401601007	BVP433 LED413/NW 220~240V 305W SWB GM	Gray
911401601107	BVP433 LED409/NW 220~240V 305W AMB GM	Gray
911401601207	BVP433 LED382/NW 220~240V 305W SAWB GM	Gray
911401601307	BVP433 LED418/NW 220~240V 305W NB GM	Gray
911401601407	BVP433 LED418/NW 220~240V 305W S6 GM	Gray
911401601507	BVP433 LED413/CW 220~240V 305W SMB GM	Gray
911401601607	BVP433 LED413/CW 220~240V 305W SWB GM	Gray
911401601707	BVP433 LED409/CW 220~240V 305W AMB GM	Gray
911401601807	BVP433 LED382/CW 220~240V 305W SAWB GM	Gray
911401601907	BVP433 LED418/CW 220~240V 305W NB GM	Gray
911401602007	BVP433 LED418/CW 220~240V 305W S6 GM	Gray
911401602207	BVP433 LED465/NW 220~240V 345W SMB GC	Gray
911401602307	BVP433 LED465/NW 220~240V 345W SWB GC	Gray
911401602407	BVP433 LED460/NW 220~240V 345W AMB GC	Gray
911401602507	BVP433 LED430/NW 220~240V 345W SAWB GC	Gray
911401602607	BVP433 LED470/NW 220~240V 345W NB GC	Gray
911401602707	BVP433 LED470/NW 220~240V 345W S6 GC	Gray
911401602807	BVP433 LED465/CW 220~240V 345W SMB GC	Gray
911401602907	BVP433 LED465/CW 220~240V 345W SWB GC	Gray
911401603007	BVP433 LED460/CW 220~240V 345W AMB GC	Gray
911401603107	BVP433 LED430/CW 220~240V 345W SAWB GC	Gray
911401603207	BVP433 LED470/CW 220~240V 345W NB GC	Gray
911401603307	BVP433 LED470/CW 220~240V 345W S6 GC	Gray
911401603507	BVP433 LED465/NW 220~240V 345W SMB GM	Gray
911401603607	BVP433 LED465/NW 220~240V 345W SWB GM	Gray
911401603707	BVP433 LED460/NW 220~240V 345W AMB GM	Gray
911401603807	BVP433 LED430/NW 220~240V 345W SAWB GM	Gray
911401603907	BVP433 LED470/NW 220~240V 345W NB GM	Gray
911401604007	BVP433 LED470/NW 220~240V 345W S6 GM	Gray
911401604107	BVP433 LED465/CW 220~240V 345W SMB GM	Gray

Order Code	Full Product Name	Color
911401604207	BVP433 LED465/CW 220~240V 345W SWB GM	Gray
911401604307	BVP433 LED460/CW 220~240V 345W AMB GM	Gray
911401604407	BVP433 LED430/CW 220~240V 345W SAWB GM	Gray
911401604507	BVP433 LED470/CW 220~240V 345W NB GM	Gray
911401604607	BVP433 LED470/CW 220~240V 345W S6 GM	Gray
911401605007	BVP433 LED517/NW 220~240V 380W SMB GC	Gray
911401605107	BVP433 LED517/NW 220~240V 380W SWB GC	Gray
911401605207	BVP433 LED511/NW 220~240V 380W AMB GC	Gray
911401605307	BVP433 LED477/NW 220~240V 380W SAWB GC	Gray
911401605407	BVP433 LED522/NW 220~240V 380W NB GC	Gray
911401605507	BVP433 LED522/NW 220~240V 380W S6 GC	Gray
911401605607	BVP433 LED517/CW 220~240V 380W SMB GC	Gray
911401605707	BVP433 LED517/CW 220~240V 380W SWB GC	Gray
911401605807	BVP433 LED511/CW 220~240V 380W AMB GC	Gray
911401605907	BVP433 LED477/CW 220~240V 380W SAWB GC	Gray
911401606007	BVP433 LED522/CW 220~240V 380W NB GC	Gray
911401606107	BVP433 LED522/CW 220~240V 380W S6 GC	Gray
911401606507	BVP433 LED517/NW 220~240V 380W SMB GM	Gray
911401606607	BVP433 LED517/NW 220~240V 380W SWB GM	Gray
911401606707	BVP433 LED511/NW 220~240V 380W AMB GM	Gray
911401606807	BVP433 LED477/NW 220~240V 380W SAWB GM	Gray
911401606907	BVP433 LED522/NW 220~240V 380W NB GM	Gray
911401607007	BVP433 LED522/NW 220~240V 380W S6 GM	Gray
911401607107	BVP433 LED517/CW 220~240V 380W SMB GM	Gray
911401607207	BVP433 LED517/CW 220~240V 380W SWB GM	Gray
911401607307	BVP433 LED511/CW 220~240V 380W AMB GM	Gray
911401607407	BVP433 LED477/CW 220~240V 380W SAWB GM	Gray
911401607507	BVP433 LED522/CW 220~240V 380W NB GM	Gray
911401607607	BVP433 LED522/CW 220~240V 380W S6 GM	Gray
911401607807	BVP433 LED359/NW 300W SAWB CM GC	Gray
911401607907	BVP433 LED384/CW 300W AMB CM GM	Gray
911401694306	BVP433 LED310/NW 220~240V 230W SWB GC	Gray
911401694406	BVP433 LED307/NW 220~240V 230W AMB GC	Gray
911401694506	BVP433 LED286/NW 220~240V 230W SAWB GC	Gray
911401694606	BVP433 LED313/NW 220~240V 230W NB GC	Gray
911401694706	BVP433 LED313/NW 220~240V 230W S6 GC	Gray
911401694806	BVP433 LED310/CW 220~240V 230W SMB GC	Gray
911401694906	BVP433 LED310/CW 220~240V 230W SWB GC	Gray
911401695006	BVP433 LED307/CW 220~240V 230W AMB GC	Gray

## Tango G4 LED Flood

Order Code	Full Product Name	Color	Order Code	Full Product Name	Color
911401695106	BVP433 LED286/CW 220~240V 230W SAWB GC	Gray	911401659107	BVP491 LED127/WW 100W SMB 1-10V P7	grey
911401695206	BVP433 LED313/CW 220~240V 230W NB GC	Gray	911401659207	BVP491 LED68/NW 50W SWB LP	grey
911401695306	BVP433 LED313/CW 220~240V 230W S6 GC	Gray	911401659307	BVP491 LED93/NW 70W SWB LP	grey
911401695506	BVP433 LED310/NW 220~240V 230W SMB GM	Gray	911401659407	BVP491 LED112/NW 85W SWB LP	grey
911401695606	BVP433 LED310/NW 220~240V 230W SWB GM	Gray	911401659507	BVP491 LED136/NW 100W SWB LP	grey
911401695706	BVP433 LED307/NW 220~240V 230W AMB GM	Gray	911401659607	BVP491 LED68/NW 50W SWB LP P7	grey
911401695806	BVP433 LED286/NW 220~240V 230W SAWB GM	Gray	911401659707	BVP491 LED93/NW 70W SWB LP P7	grey
911401695906	BVP433 LED313/NW 220~240V 230W NB GM	Gray	911401659807	BVP491 LED112/NW 85W SWB LP P7	grey
911401696006	BVP433 LED313/NW 220~240V 230W S6 GM	Gray	911401659907	BVP491 LED136/NW 100W SWB LP P7	grey
911401696106	BVP433 LED310/CW 220~240V 230W SMB GM	Gray	911401660007	BVP491 LED68/NW 50W SWB FP DALI/CM	grey
911401696206	BVP433 LED310/CW 220~240V 230W SWB GM	Gray	911401660107	BVP491 LED93/NW 70W SWB FP DALI/CM	grey
911401696306	BVP433 LED307/CW 220~240V 230W AMB GM	Gray	911401660207	BVP491 LED112/NW 85W SWB FP DALI/CM	grey
911401696406	BVP433 LED286/CW 220~240V 230W SAWB GM	Gray	911401660307	BVP491 LED136/NW 100W SWB FP DALI/CM	grey
911401696506	BVP433 LED313/CW 220~240V 230W NB GM	Gray	911401660407	BVP491 LED66/CW 50W AMB FP DALI/CM P7	grey
911401696606	BVP433 LED313/CW 220~240V 230W S6 GM	Gray	911401660507	BVP491 LED90/CW 70W AMB FP DALI/CM P7	grey
911401696906	BVP433 LED344/NW 220~240V 255W SMB GC	Gray	911401660607	BVP491 LED108/CW 85W AMB FP DALI/CM P7	grey
911401697006	BVP433 LED344/NW 220~240V 255W SWB GC	Gray	911401660707	BVP491 LED132/CW 100W AMB FP DALI/CM P7	grey
911401697106	BVP433 LED341/NW 220~240V 255W AMB GC	Gray	911401660807	BVP491 LED66/CW 50W AMB SR	grey
911401697206	BVP433 LED318/NW 220~240V 255W SAWB GC	Gray	911401660907	BVP491 LED90/CW 70W AMB SR	grey
911401697306	BVP433 LED348/NW 220~240V 255W NB GC	Gray	911401661007	BVP491 LED108/CW 85W AMB SR	grey
911401697406	BVP433 LED348/NW 220~240V 255W S6 GC	Gray	911401661107	BVP491 LED132/CW 100W AMB SR	grey
911401697506	BVP433 LED344/CW 220~240V 255W SMB GC	Gray	911401661207	BVP492 LED144/WW 120W AMB	grey
911401697606	BVP433 LED344/CW 220~240V 255W SWB GC	Gray	911401661307	BVP492 LED166/WW 135W AMB	grey
911401697706	BVP433 LED341/CW 220~240V 255W AMB GC	Gray	911401661407	BVP492 LED183/WW 150W AMB	grey
911401697806	BVP433 LED318/CW 220~240V 255W SAWB GC	Gray	911401661507	BVP492 LED200/WW 165W AMB	grey
911401697906	BVP433 LED348/CW 220~240V 255W NB GC	Gray	911401661607	BVP492 LED222/WW 180W AMB	grey
911401698006	BVP433 LED348/CW 220~240V 255W S6 GC	Gray	911401661707	BVP492 LED244/WW 200W AMB	grey
911401698306	BVP433 LED344/NW 220~240V 255W SMB GM	Gray	911401661807	BVP492 LED157/CW 120W SMB 1-10V	grey
911401698406	BVP433 LED344/NW 220~240V 255W SWB GM	Gray	911401661907	BVP492 LED181/CW 135W SMB 1-10V	grey
911401698506	BVP433 LED341/NW 220~240V 255W AMB GM	Gray	911401662007	BVP492 LED200/CW 150W SMB 1-10V	grey
911401698606	BVP433 LED318/NW 220~240V 255W SAWB GM	Gray	911401662107	BVP492 LED218/CW 165W SMB 1-10V	grey
911401698706	BVP433 LED348/NW 220~240V 255W NB GM	Gray	911401662207	BVP492 LED242/CW 180W SMB 1-10V	grey
911401698806	BVP433 LED348/NW 220~240V 255W S6 GM	Gray	911401662307	BVP492 LED266/CW 200W SMB 1-10V	grey
911401698906	BVP433 LED344/CW 220~240V 255W SMB GM	Gray	911401662407	BVP492 LED159/NW 120W SWB 1-10V P7	grey
911401699006	BVP433 LED344/CW 220~240V 255W SWB GM	Gray	911401662507	BVP492 LED183/NW 135W SWB 1-10V P7	grey
911401699106	BVP433 LED341/CW 220~240V 255W AMB GM	Gray	911401662607	BVP492 LED201/NW 150W SWB 1-10V P7	grey
911401699206	BVP433 LED318/CW 220~240V 255W SAWB GM	Gray	911401662707	BVP492 LED219/NW 165W SWB 1-10V P7	grey
911401699306	BVP433 LED348/CW 220~240V 255W NB GM	Gray	911401662807	BVP492 LED244/NW 180W SWB 1-10V P7	grey
911401699406	BVP433 LED348/CW 220~240V 255W S6 GM	Gray	911401662907	BVP492 LED268/NW 200W SWB 1-10V P7	grey
911401699606	BVP433 LED413/NW 220~240V 305W SMB GC	Gray	911401663007	BVP492 LED144/WW 120W AMB LP	grey
911401699706	BVP433 LED413/NW 220~240V 305W SWB GC	Gray	911401663107	BVP492 LED166/WW 135W AMB LP	grey
911401699806	BVP433 LED409/NW 220~240V 305W AMB GC	Gray	911401663207	BVP492 LED183/WW 150W AMB LP	grey
911401699906	BVP433 LED382/NW 220~240V 305W SAWB GC	Gray	911401663307	BVP492 LED200/WW 165W AMB LP	grey
911401658207	BVP491 LED68/NW 50W SWB	grey	911401663407	BVP492 LED222/WW 180W AMB LP	grey
911401658307	BVP491 LED93/NW 70W SWB	grey	911401663507	BVP492 LED244/WW 200W AMB LP	grey
911401658407	BVP491 LED112/NW 85W SWB	grey	911401663607	BVP492 LED157/CW 120W SMB LP P7	grey
911401658507	BVP491 LED136/NW 100W SWB	grey	911401663707	BVP492 LED181/CW 135W SMB LP P7	grey
911401658607	BVP491 LED90/CW 70W AMB 1-10V	grey	911401663807	BVP492 LED200/CW 150W SMB LP P7	grey
911401658707	BVP491 LED108/CW 85W AMB 1-10V	grey	911401663907	BVP492 LED218/CW 165W SMB LP P7	grey
911401658807	BVP491 LED132/CW 100W AMB 1-10V	grey	911401664007	BVP492 LED242/CW 180W SMB LP P7	grey
911401658907	BVP491 LED87/WW 70W SMB 1-10V P7	grey	911401664107	BVP492 LED266/CW 200W SMB LP P7	grey
911401659007	BVP491 LED104/WW 85W SMB 1-10V P7	grey	911401664207	BVP492 LED157/CW 120W SMB FP DALI/CM	grey

## Tango G4 LED Flood

Order Code	Full Product Name	Color	Order Code	Full Product Name	Color
911401664307	BVP492 LED181/CW 135W SMB FP DALI/CM	grey	911401680506	BVP431 LED91/NW 220~240V 70W AMB GC	Gray
911401664407	BVP492 LED200/CW 150W SMB FP DALI/CM	grey	911401680606	BVP431 LED92/CW 220~240V 70W SMB GC	Gray
911401664507	BVP492 LED157/CW 120W SMB FP DALI/CM P7	grey	911401680706	BVP431 LED92/CW 220~240V 70W SWB GC	Gray
911401664607	BVP492 LED181/CW 135W SMB FP DALI/CM P7	grey	911401680806	BVP431 LED91/CW 220~240V 70W AMB GC	Gray
911401664707	BVP492 LED200/CW 150W SMB FP DALI/CM P7	grey	911401681206	BVP431 LED92/NW 220~240V 70W SMB GM	Gray
911401664807	BVP492 LED157/CW 120W SMB SR	grey	911401681306	BVP431 LED92/NW 220~240V 70W SWB GM	Gray
911401664907	BVP492 LED181/CW 140W SMB SR	grey	911401681406	BVP431 LED91/NW 220~240V 70W AMB GM	Gray
911401665007	BVP492 LED200/CW 150W SMB SR	grey	911401681506	BVP431 LED92/CW 220~240V 70W SMB GM	Gray
911401665107	BVP493 LED261/WW 230W SAWB	grey	911401681606	BVP431 LED92/CW 220~240V 70W SWB GM	Gray
911401665207	BVP493 LED341/NW 255W SWB	grey	911401681706	BVP431 LED91/CW 220~240V 70W AMB GM	Gray
911401665307	BVP493 LED388/WW 305W NB	grey	911401681806	BVP431 LED92/NW 70W SWB ANZ CL	Gray
911401665407	BVP493 LED460/CW 345W SWB	grey	911401682206	BVP431 LED136/NW 220~240V 100W SMB GC	Gray
911401665507	BVP493 LED485/WW 380W NB	grey	911401682306	BVP431 LED136/NW 220~240V 100W SWB GC	Gray
911401665607	BVP493 LED261/WW 230W SAWB 1-10V	grey	911401682406	BVP431 LED134/NW 220~240V 100W AMB GC	Gray
911401665707	BVP493 LED341/NW 255W SWB 1-10V	grey	911401682506	BVP431 LED135/CW 220~240V 100W SMB GC	Gray
911401665807	BVP493 LED388/WW 305W NB 1-10V	grey	911401682606	BVP431 LED135/CW 220~240V 100W SWB GC	Gray
911401665907	BVP493 LED460/CW 345W SWB 1-10V	grey	911401682706	BVP431 LED133/CW 220~240V 100W AMB GC	Gray
911401666007	BVP493 LED485/WW 380W NB 1-10V	grey	911401683206	BVP431 LED136/NW 220~240V 100W SWB GM	Gray
911401666107	BVP493 LED261/WW 230W SAWB 1-10V P7	grey	911401683306	BVP431 LED134/NW 220~240V 100W AMB GM	Gray
911401666207	BVP493 LED341/NW 255W SWB 1-10V P7	grey	911401683406	BVP431 LED135/CW 220~240V 100W SMB GM	Gray
911401666307	BVP493 LED388/WW 305W NB 1-10V P7	grey	911401683506	BVP431 LED135/CW 220~240V 100W SWB GM	Gray
911401666407	BVP493 LED460/CW 345W SWB 1-10V P7	grey	911401683606	BVP431 LED133/CW 220~240V 100W AMB GM	Gray
911401666507	BVP493 LED485/WW 380W NB 1-10V P7	grey	911401683706	BVP431 LED136/NW 100W SWB ANZ CL	Gray
911401666607	BVP493 LED261/WW 230W SAWB LP	grey	911401683906	BVP431 LED134/NW 100W AMB CM GC	Gray
911401666707	BVP493 LED341/NW 255W SWB LP	grey	911401684006	BVP431 LED133/CW 100W AMB CM GM	Gray
911401666807	BVP493 LED388/WW 310W NB LP	grey	911401686906	BVP432 LED161/CW 220~240V 120W SWB GC	Gray
911401666907	BVP493 LED460/CW 350W SWB LP	grey	911401687606	BVP432 LED161/CW 220~240V 120W SWB GM	Gray
911401667007	BVP493 LED485/WW 380W NB LP	grey	911401688506	BVP432 LED204/CW 220~240V 150W SWB GC	Gray
911401667207	BVP493 LED261/WW 230W SAWB LP P7	grey	911401688606	BVP432 LED202/CW 220~240V 150W AMB GC	Gray
911401667307	BVP493 LED341/NW 255W SWB LP P7	grey	911401689006	BVP432 LED206/NW 220~240V 150W SMB GM	Gray
911401667407	BVP493 LED388/WW 310W NB LP P7	grey	911401689106	BVP432 LED206/NW 220~240V 150W SWB GM	Gray
911401667507	BVP493 LED460/CW 350W SWB LP P7	grey	911401689206	BVP432 LED203/NW 220~240V 150W AMB GM	Gray
911401667607	BVP493 LED485/WW 380W NB LP P7	grey	911401689306	BVP432 LED204/CW 220~240V 150W SMB GM	Gray
911401667807	BVP493 LED261/WW 230W SAWB FP DALI/CM	grey	911401689406	BVP432 LED204/CW 220~240V 150W SWB GM	Gray
911401667907	BVP493 LED341/NW 260W SWB FP DALI/CM	grey	911401689506	BVP432 LED202/CW 220~240V 150W AMB GM	Gray
911401668007	BVP493 LED370/WW 300W NB FP DALI/CM	grey	911401689906	BVP432 LED274/NW 220~240V 200W SMB GC	Gray
911401668107	BVP493 LED261/WW 230W SAWB FP DALI/CM P7	grey	911401690006	BVP432 LED274/NW 220~240V 200W SWB GC	Gray
911401668207	BVP493 LED341/NW 260W SWB FP DALI/CM P7	grey	911401690106	BVP432 LED271/NW 220~240V 200W AMB GC	Gray
911401668307	BVP493 LED370/WW 300W NB FP DALI/CM P7	grey	911401690206	BVP432 LED272/CW 220~240V 200W SMB GC	Gray
911401668407	BVP493 LED261/WW 230W SAWB SR	grey	911401690306	BVP432 LED272/CW 220~240V 200W SWB GC	Gray
911401668507	BVP493 LED341/NW 260W SWB SR	grey	911401690406	BVP432 LED269/CW 220~240V 200W AMB GC	Gray
911401668607	BVP493 LED370/WW 295W NB SR	grey	911401690806	BVP432 LED274/NW 220~240V 200W SMB GM	Gray
911401678706	BVP431 LED68/NW 220~240V 50W SMB GC	Gray	911401690906	BVP432 LED274/NW 220~240V 200W SWB GM	Gray
911401678806	BVP431 LED68/NW 220~240V 50W SWB GC	Gray	911401691006	BVP432 LED271/NW 220~240V 200W AMB GM	Gray
911401678906	BVP431 LED67/NW 220~240V 50W AMB GC	Gray	911401691106	BVP432 LED272/CW 220~240V 200W SMB GM	Gray
911401679406	BVP431 LED68/NW 220~240V 50W SMB GM	Gray	911401691206	BVP432 LED272/CW 220~240V 200W SWB GM	Gray
911401679506	BVP431 LED68/NW 220~240V 50W SWB GM	Gray	911401691306	BVP432 LED269/CW 220~240V 200W AMB GM	Gray
911401679606	BVP431 LED67/NW 220~240V 50W AMB GM	Gray	911401691406	BVP432 LED274/NW 200W SWB ANZ CL	Gray
911401680306	BVP431 LED92/NW 220~240V 70W SMB GC	Gray	911401691606	BVP432 LED203/NW 150W AMB CM GC	Gray
911401680406	BVP431 LED92/NW 220~240V 70W SWB GC	Gray	911401691706	BVP432 LED202/CW 150W AMB CM GM	Gray

## Tango G4 LED Flood

