



EFix TCS260

TCS260 2x35-80W HFPI C6 WH

EFix surface mounted - 2 pcs - 35 W, 49 W, 80 W - HF Performer Intelligent - High-gloss optic double parabolic closed

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

Product data

General Information		Internal wiring	
Number of light sources	2 pcs	Internal wiring	Standard
Lamp family code	TL5 [TL5]	Protection class IEC	Safety class I
Lamp power	35 49 80 W	Flammability mark	For mounting on normally flammable surfaces
Kombipack	-	CE mark	CE mark
Gear	HFPI [HF Performer Intelligent]	Product family code	TCS260 [EFix surface mounted]
Optic type	High-gloss optic double parabolic closed	Light Technical	
Optical cover/lens type	-	Light Distribution	Direct lighting
Emergency lighting	-		
Embedded control	-		

EFix TCS260

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

Mechanical and Housing

Housing configuration	Basic version
Fixation point length distance (Nom)	1300 mm
Overall length	1541 mm
Color	White
Dimensions (Height x Width x Depth)	NaN x NaN x 1541 mm (NaN x NaN x 60.7 in)

Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	--------------------------

Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

Product Data

Full product code	872790061322300
Order product name	TCS260 2x35-80W HFPI C6 WH
EAN/UPC - Product	8727900613223
Order code	910402461912
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910402461912
Net Weight (Piece)	4.200 kg



Dimensional drawing



EFix TCS260

