



# ArenaVision MVF403

## MVF403 MHN-LA1000W/956 A1 SI

ARENAVISION - MASTER MHN-LA - 1000 W

ArenaVision MVF403 takes sports floodlighting to the highest level, offering very high light output, optical efficiency, ease of installation, reliability and flexibility. It is ideal for indoor sports halls (1000 W version) as well as many outdoor sports and other lighting applications. The integrated system of oval optics and compact double-ended MHN-LA 1000W or MHN-SA HO 2000W lamps ensures outstanding system efficiency and low glare. A built-in reflector skirt reduces spill light and glare even further. The MHN-SA HO 2000W/956 and MHN-LA 1000W/956 lamps meet the highest international CTV requirements. With the MHN-LA 1000W/842 lamp, the natural color rendering and comfortable atmosphere are well suited to TV and filming as well as other floodlighting applications. Hot re-strike versions are available for all lamp types, enabling immediate restoration of lighting after power supply failure. The (optional) flicker-free version of ArenaVision MVF403 MHN-LA 1000W is designed to ensure that the flicker effect is fully eliminated in order to guarantee perfect images filmed with super-slow-motion cameras at sports events. The flicker-free version of ArenaVision MVF403 comes equipped with a special electronic ignitor, which works in combination with Philips' electronic flicker-free ballast GearUnits (ECM330), to be ordered separately.

### Product data

General Information		Protection class IEC	
Number of light sources	1 pc	Protection class IEC	Safety class I
Lamp family code	MHN-LA [ MASTER MHN-LA]	CE mark	CE mark
Lamp power	1000 W	ENEC mark	ENEC mark
Light source color	956 daylight	Optic type outdoor	Beam category A1
Kombipack	Lamp(s) included	Aiming memory	-
Gear	-	Product family code	MVF403 [ ARENAVISION]
Optical cover/lens type	Front-glass downlighting version		

# ArenaVision MVF403

## Operating and Electrical

Lamp supply voltage	230 V [ 230]
Input Voltage	230 V
Ignitor	Series

## Mechanical and Housing

Dimensions (Height x Width x Depth)	NaN x NaN x NaN mm (NaN x NaN x NaN in)
-------------------------------------	---

## Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]

## Initial Performance (IEC Compliant)


Init. Corr. Color Temperature	5600 K
-------------------------------	--------

## Product Data

Full product code	872790050265700
Order product name	MVF403 MHN-LA1000W/956 A1 SI
EAN/UPC - Product	8727900502657
Order code	910502223118
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910502223118
Net Weight (Piece)	14.500 kg



## Dimensional drawing



ArenaVision MVF403/MVF404

