



# Zadora, fixed

## QBS570 1xHAL-MR50-45W 12V BR ALU

1 pc - 45 W - 12 V - Aluminum

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

### Product data

General information	
Number of light sources	1 pc
Lamp power	45 W
Cap-Base	GU5.3 [ GU5.3]
Gear	-
Driver/power unit/transformer	-
Luminaire light beam spread	108°
Protection class IEC	Safety class II

Operating and electrical	
Input Voltage	12 V
Input Frequency	50 to 60 Hz

Mechanical and housing	
Overall length	33 mm
Overall width	170 mm
Overall height	170 mm
Color	Aluminum
Dimensions (Height x Width x Depth)	170 x 170 x 33 mm (6.7 x 6.7 x 1.3 in)

Approval and application	
Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK03 [ 0.3 J]

Application conditions	
Ambient temperature range	-10 to +35 °C


  

Product data	
Full product code	871155957323699
Order product name	QBS570 1xHAL-MR50-45W 12V BR ALU
EAN/UPC - Product	8711559573236
Order code	910502538318
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	80
Material Nr. (12NC)	910502538318
Net Weight (Piece)	0.150 kg



## Zadora, fixed

### Dimensional drawing



QBS570 1xHAL-MR50-45W 12V BR ALU

