



# Cleanroom LED CR250B

## CR150B LED35S/840 PSU W30L120 IP54

LED GreenLine 3500 lm, 840 neutral white, Power supply unit (On/Off), Dust accumulation-protected, splash-proof

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65 and IP54-rated luminaires that are safe to use and come at an attractive price. This family of Philips Cleanroom CR250B fixtures represent true value for money: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this cleanroom LED lighting family can be used in a wide range of applications. These cleanroom luminaires are also compliant with all relevant standards (CE, EMC, RoHS).

### Product data

General Information	
Lamp family code	GRN35 [LED GreenLine 3500 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Lighting Technology	LED
Value ladder	Performance

CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on easily flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	3,500 lumen
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color rendering index (CRI)	>80
Number of light sources	2
Light source color	840 neutral white

# Cleanroom LED CR250B

Optic type	-
Optical cover/lens type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	110°
Unified glare rating CEN	Not applicable

## Operating and Electrical

Line Frequency	50 to 60 Hz
Input Voltage	220-240 V
Inrush current	13 A
Inrush time	270 ms
Power Consumption	40 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 0.75 m without plug
Number of products on MCB of 16 A type B	24

## Temperature

Ambient temperature range	0 to +40 °C
---------------------------	-------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

## Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	-
Optical cover/lens material	Polymethyl methacrylate
Fixation material	-
Housing Color	White
Optical cover/lens finish	Opal
Overall length	1,195 mm
Overall width	295 mm
Overall height	86 mm
Dimensions (Height x Width x Depth)	86 x 295 x 1195 mm

## Approval and Application

Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Sustainability rating	-
Protection class IEC	Safety class II

## Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <4
Luminous flux tolerance	+/-5%
Power consumption tolerance	+/-5%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70


## Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

## Product Data

Full product code	871869607293600
Order product name	CR150B LED35S/840 PSU W30L120 IP54
EAN/UPC - Product	8718696072936
Order code	910503910177
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910503910177
Full product name	CR150B LED35S/840 PSU W30L120 IP54
EAN/UPC - Case	8718696072936
EAN/UPC - Product/Case	8718696072936

## Dimensional drawing



## Cleanroom LED CR250B

