



# Coreline Highbay Gen4

## BY120P G4 LED100S/840 PSD NB

Coreline Highbay Gen4, 73 W, 10500 lm, 4000 K, DALI, 55°, IP65, IK07

CoreLine Highbay Gen4 delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, highly-efficient luminaire with a very long-lifetime, it delivers great energy savings and requires less maintenance. At the same time, CoreLine Highbay is very easy to handle. The luminaire can be installed on your existing grid and the electrical connection is a straightforward task, with no need to open the luminaire and an external IP65 connector. With a choice of two beam angles: narrow and wide beam, you can adjust your lighting plan to suit your exact needs. This range also includes Interact Ready luminaires with integrated wireless communications and integrated movement and daylight sensors. So CoreLine Highbay Gen4 is ready to be used with any Interact connected lighting system.

### Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	10,500 lm
Number of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	144 lm/W
Light source engine type	LED	Color rendering index (CRI)	>80
Value ladder	Performance	Beam angle of light source	55 degree(s)
CE mark	CE mark		
Warranty period	5 years		
Flammability mark	For mounting on easily flammable surfaces		
ENEC mark	ENEC mark		
Glow-wire test	Temperature 650 °C, duration 30 s		
EU RoHS compliant	Yes		

# Coreline Highbay Gen4

Light source color	840 neutral white
Optic type	Narrow beam
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	55°
Unified glare rating CEN	22

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	73 W
Power Factor (Fraction)	0.95
Connection	Connection unit 3-pole
Cable	Cable 0.3 m with connector 3-pole
Number of products on MCB of 16 A type B	13

## Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Gray
Optical cover finish	Clear
Overall height	445 mm
Overall diameter	385 mm

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.3 %
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80

## Application Conditions

Performance ambient temperature Tq	35 °C
Maximum dim level	1%
Suitable for random switching	Yes

## Product Data

Order product name	BY120P G4 LED100S/840 PSD NB
Full product name	BY120P G4 LED100S/840 PSD NB
Full product code	871016333702900
Order code	911401574451
Material Nr. (12NC)	911401574451
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163337029
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163337029

## Coreline Highbay Gen4

### Dimensional drawing

