



GreenSpace G5

DN390B LED6/830 PSU D100 WH CAU

- Power supply unit (ON/OFF) - High-gloss high reflectance -
Transparent bowl with white cover - 80°

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Light Technical	
Luminous Flux	570 lumen
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	104 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	72 degree(s)
Light source color	830 warm white
Optic type	High-gloss high reflectance
Optical cover/lens type	Transparent bowl with white cover
Luminaire light beam spread	80°
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz

Power Consumption	5.5 W
Inrush current	2.2 A
Inrush time	0.045 ms
Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Cable	Cable with plug
Number of products on MCB of 16 A type B	48
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (ON/OFF)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate

GreenSpace G5

Optical cover/lens material	Polycarbonate
Housing Color	Black and white
Optical cover/lens finish	Matte
Overall length	0 mm
Overall width	0 mm
Overall height	98 mm
Overall diameter	120 mm
Dimensions (Height x Width x Depth)	98 x 0 x 0 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	CE mark
Warranty period	3 years

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44,0.403) SDCM<5

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.12 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Full product code	911401582841
Order product name	DN390B LED6/830 PSU D100 WH CAU
Order code	911401582841
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material number (12NC)	911401582841
Full product name	DN390B LED6/830 PSU D100 WH CAU



Dimensional drawing

