



# UNIIn-ground

## BBP403 LED RGB 9W 24V L300 GC

UNIIn-ground - 160 lm - 9 W - -

UNIIn-ground family provide a completed range of up-lights in terms of wattage, beam angle, color temperature, etc. It is to make your space distinctive with more safety and convenience as well. Compact and robust design with aluminum housing, waterproof connectors are all for ensuring long-lasting operation without your more caring after installation. Waterproof connector is to give more ease to installation and save your installation cost. Apart from high-quality white light, RGB (and mono RGB) are available with DMX512 decoder built-in side.

### Product data

General information	
Light source color	Red, green and blue
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	Glass
Control interface	-
Connection	Screw connection block 5-pole
Cable	Cable 0.3 m with connector 5-pole
Protection class IEC	Safety class III
Flammability mark	-
CE mark	-
Light source engine type	LED
Serviceability class	Class C, luminaire without serviceable parts, not serviceable

Light technical	
Standard tilt angle posttop	-

Operating and electrical	
Input Voltage	24 DC V
Input Frequency	- Hz
Power Factor (Min)	-
Power Factor (Nom)	-

Controls and dimming	
Dimmable	No

Mechanical and housing	
Housing Material	Aluminum
Optic material	Glass
Optical cover/lens material	Polycarbonate
Mounting device	Recessed mounting box square
Optical cover/lens finish	Frosted
Overall length	300 mm
Overall width	48 mm
Overall height	108 mm


## UNIIn-ground

Color	Aluminum and gray
Dimensions (Height x Width x Depth)	108 x 48 x 300 mm
<b>Approval and application</b>	
Ingress protection code	IP67 [ Dust penetration-protected, watertight]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
<b>Initial performance (IEC compliant)</b>	
Initial luminous flux (system flux)	160 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	17 lm/W
Init. Corr. Color Temperature	-
Init. Color Rendering Index	-
Initial input power	9 W
Power consumption tolerance	+/-10%

<b>Application conditions</b>	
Ambient temperature range	-40 to +50 °C
<b>Product data</b>	
Full product code	911401755442
Order product name	BBP403 LED RGB 9W 24V L300 GC
Order code	911401755442
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	911401755442
Net Weight (Piece)	1.000 kg



## Dimensional drawing



BBP403 LED RGB 9W 24V L300 GC

