



Solar Battery Sub System

XGS321 12V/250AH IP68 Gel Bat sys 3yrs

A range of 65 Ah to 250 Ah 12/24V, valve regulated lead acid (VRLA) battery with gel electrolyte technology to get long service lifetime and high performance in deep discharging. It can be used in wide range of ambient temperature and keep good performance of constant power input

Product data

General Information	
CE mark	CE mark
Warranty period	3 years
EU RoHS compliant	Yes

Operating and Electrical	
Input Voltage	12 DC V
Battery type	Gel
Battery ampere hour	250 Ah
Battery voltage	12 V
Battery charging & discharging cycles	750
Cable connection kit	Included
Cable	Cable 2.8 m 4.0 sqmm with KBI connectors

Temperature	
Ambient temperature range	-20 to +55 °C

Mechanical and Housing	
Overall length	520 mm
Overall width	269 mm

Overall height	220 mm
Dimensions (Height x Width x Depth)	220 x 269 x 520 mm

Approval and Application	
Ingress protection code	IP68 [Dust penetration-protected, pressure watertight]

Application Conditions	
Ambient temperature range for charging	-20 °C to +55 °C
Ambient temperature range for discharging (when light is on)	-20 °C to +55 °C

Product Data	
Order product name	XGS321 12V/250AH IP68 Gel Bat sys 3yrs
Full product name	XGS321 12V/250AH IP68 Gel Bat sys 3yrs
Full product code	872016952144500
Order code	911401819502
Material Nr. (12NC)	911401819502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169521445
Numerator - Packs per outer box	1


Solar Battery Sub System

EAN/UPC - Case

8720169521445


Dimensional drawing

12V Gel Battery Subsystem



Description	Battery Size (cm) LxWxH
MS332 12V/105Ah-IP68 gel battery subsys	35x16,5x21,5
MS331 12V/105Ah-IP68 gel battery subsys	35,5x17,2x21,5
MS333 12V/120Ah-IP68 gel battery subsys	35,5x17,2x21,5
MS334 12V/120Ah-IP68 gel battery subsys	40,5x17,4x21,5
MS335 12V/150Ah-IP68 gel battery subsys	40,5x17,2x21
MS336 12V/150Ah-IP68 gel battery subsys	52,2x13,8x21,8
MS337 12V/220Ah-IP68 gel battery subsys	52,2x13,8x21,8
MS338 12V/220Ah-IP68 gel battery subsys	52,2x13,8x21,8

24V Gel Battery Subsystem



Description	Battery Size (cm) LxWxH
MS332 12V/105Ah-IP68 Gel Bat. Sys. For 24	35x16,5x21,5
MS333 12V/105Ah-IP68 Gel Bat. Sys. For 24	35,5x17,2x21,5
MS334 12V/120Ah-IP68 Gel Bat. Sys. For 24	35,5x17,2x21,5
MS335 12V/150Ah-IP68 Gel Bat. Sys. For 24	40,5x17,4x21,5
MS336 12V/150Ah-IP68 Gel Bat. Sys. For 24	40,5x17,2x21
MS337 12V/180Ah-IP68 Gel Bat. Sys. For 24	52,2x13,8x21,8
MS338 12V/220Ah-IP68 Gel Bat. Sys. For 24	52,2x13,8x21,8
MS339 12V/220Ah-IP68 Gel Bat. Sys. For 24	52,2x13,8x21,8

